


## Lithium Manganese Dioxide Battery

CR2032

**SPECIFICATIONS**

<b>Minimum No Load Voltage:</b>	3.1 V
<b>Minimum On Load Voltage:</b>	2.1V on 150Ohms at 1000
<b>Minimum Life</b>	430 H 6.81k Ohms Hr/Day 2 V
<b>Rated Capacity</b>	180 mAh on 6.81kOhms to 2V
<b>Volume</b>	.98 cm <sup>3</sup>
<b>Weight</b>	2.8g
<b>Physical Size in mm</b>	<b>Max</b> <b>Min</b>
Height/Length	3.2   2.9
Width/Diameter	20   19.7
Depth	

## Typical Discharge Characteristics

