


Product Data Sheet

Part No. PB-1408 Non-Washable Type



DIMENSIONS



Type	Unit	PB-1408-1
Rated Voltage	(VDC)	12
Operating Voltage	(VDC)	3~16
Current Consumption	(mA)	≤ 7
Sound Output (Min)	(dB)	≥ 80
Resonant Frequency	(Hz)	4000±500
Operating Temp	(C)	-20~+70
Storage Temp	(C)	-30~+80
Weight	(g)	1
Dimension	mm	13.8 x H7.5
*Value applying at rated voltage		
*distance for measurement 10cm		

Type	Unit	PB-1408-2
Rated Voltage	(VDC)	12
Operating Voltage	(VDC)	3~16
Current Consumption	(mA)	≤10
Sound Output (Min)	(dB)	≥ 85
Resonant Frequency	(Hz)	4800±400
Operating Temp	(C)	-20~+70
Storage Temp	(C)	-30~+80
Weight	(g)	1
Dimension	mm	13.8 x H7.5
*Value applying at rated voltage		
*distance for measurement 10cm		