

BMP®71 Label Printer Materials

www.BradyID.com/bmp71

Self Laminating Wire Markers

Protected printing area offers superior chemical and abrasion resistance. Features a non-printed clear area that wraps around and overlaminates the printed text.




Figure 4




Figure 7





Figure 19



Self-Laminating Labels

Diagram	Part Number	Labels/Roll	Material	Color	Approx. Wire Gauge	A Inch	(mm)	Label Dimensions B Inch	(mm)	C Inch	(mm)	Recommended Ribbon
Fig. 7	BM71-21-427*	1000	B-427	White	Cables	1.000	(25.400)	2.500	(63.500)	0.750	(19.050)	M71-R4300
Fig. 7	M71-21-427	100	B-427	White	Cables	1.000	(25.400)	2.500	(63.500)	0.750	(19.050)	M71-R4300
Fig. 7	M71-21-427-YL	100	B-427	Yellow	Cables	1.000	(25.400)	2.500	(63.500)	0.750	(19.050)	M71-R4300
Fig. 19	BM71-64-427*	1000	B-427	White	Cables	1.000	(25.400)	3.375	(85.730)	1.125	(28.580)	M71-R4300
Fig. 19	M71-64-427	100	B-427	White	Cables	1.000	(25.400)	3.375	(85.730)	1.125	(28.580)	M71-R4300
Fig. 7	BM71-23-427*	1000	B-427	White	Cables	1.000	(25.400)	4.000	(101.600)	1.000	(25.400)	M71-R4300
Fig. 7	M71-23-427	100	B-427	White	Cables	1.000	(25.400)	4.000	(101.600)	1.000	(25.400)	M71-R4300
Fig. 7	BM71-109-427*	500	B-427	White	Cables	1.500	(38.100)	4.000	(101.600)	1.500	(38.100)	M71-R4300
Fig. 7	BM71-33-427*	500	B-427	White	Cables	1.500	(38.100)	4.000	(101.600)	1.000	(25.400)	M71-R4300
Fig. 7	M71-109-427	100	B-427	White	Cables	1.500	(38.100)	4.000	(101.600)	1.500	(38.100)	M71-R4300
Fig. 7	M71-33-427	100	B-427	White	Cables	1.500	(38.100)	4.000	(101.600)	1.000	(25.400)	M71-R4300
Fig. 7	M71-33-427-YL	100	B-427	Yellow	Cables	1.500	(38.100)	4.000	(101.600)	1.000	(25.400)	M71-R4300
Fig. 7	BM71-34-427*	500	B-427	White	Cables	1.500	(38.100)	6.000	(152.400)	1.500	(38.100)	M71-R4300
Fig. 7	M71-34-427	50	B-427	White	Cables	1.500	(38.100)	6.000	(152.400)	1.500	(38.100)	M71-R4300
Fig. 7	M71-66-427	100	B-427	White	Cables	1.938	(49.230)	3.150	(80.000)	1.000	(25.400)	M71-R4300
Fig. 7	M71-10-427	750	B-427	White	16-10	0.250	(6.350)	0.750	(19.050)	0.375	(9.530)	M71-R4300
Fig. 7	BM71-11-427*	5000	B-427	White	16-10	0.500	(12.700)	0.750	(19.050)	0.375	(9.530)	M71-R4300
Fig. 7	M71-11-427	500	B-427	White	16-10	0.500	(12.700)	0.750	(19.050)	0.375	(9.530)	M71-R4300
Fig. 7	M71-96-427	250	B-427	White	16-10	1.000	(25.400)	0.750	(19.050)	0.375	(9.530)	M71-R4300
Fig. 7	BM71-17-427*	5000	B-427	White	12-10	0.500	(12.700)	1.000	(25.400)	0.375	(9.530)	M71-R4300
Fig. 7	M71-17-427	500	B-427	White	12-10	0.500	(12.700)	1.000	(25.400)	0.375	(9.530)	M71-R4300
Fig. 7	BM71-19-427*	2500	B-427	White	12-10	1.000	(25.400)	1.000	(25.400)	0.375	(9.530)	M71-R4300
Fig. 7	M71-19-427	250	B-427	White	12-10	1.000	(25.400)	1.000	(25.400)	0.375	(9.530)	M71-R4300
Fig. 7	M71-19-427-YL	250	B-427	Yellow	12-10	1.000	(25.400)	1.000	(25.400)	0.375	(9.530)	M71-R4300
Fig. 7	M71-104-427	250	B-427	White	12-10	1.500	(38.100)	1.000	(25.400)	0.375	(9.530)	M71-R4300
Fig. 7	M71-28-427	750	B-427	White	10-4	0.250	(6.350)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	BM71-29-427*	5000	B-427	White	10-4	0.500	(12.700)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-29-427	500	B-427	White	10-4	0.500	(12.700)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	BM71-18-427*	2500	B-427	White	10-4	0.750	(19.050)	1.000	(25.400)	0.375	(9.530)	M71-R4300
Fig. 7	M71-18-427	250	B-427	White	10-4	0.750	(19.050)	1.000	(25.400)	0.375	(9.530)	M71-R4300
Fig. 7	BM71-30-427*	2500	B-427	White	10-4	0.750	(19.050)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-30-427	250	B-427	White	10-4	0.750	(19.050)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-30-427-BL	250	B-427	Blue	10-4	0.750	(19.050)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-30-427-PL	250	B-427	Purple	10-4	0.750	(19.050)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-30-427-RD	250	B-427	Red	10-4	0.750	(19.050)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-103-427	250	B-427	White	10-4	1.000	(25.400)	1.250	(31.750)	0.500	(12.700)	M71-R4300
Fig. 7	BM71-31-427*	2500	B-427	White	10-4	1.000	(25.400)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-31-427	250	B-427	White	10-4	1.000	(25.400)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-31-427-GN	250	B-427	Green	10-4	1.000	(25.400)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-31-427-RD	250	B-427	Red	10-4	1.000	(25.400)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-31-427-YL	250	B-427	Yellow	10-4	1.000	(25.400)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 4	M71-30-427-AW	250	B-427	White	10-4	1.500	(38.100)	0.750	(19.050)	—	—	M71-R4300
Fig. 7	BM71-32-427*	1000	B-427	White	10-4	1.500	(38.100)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-32-427	250	B-427	White	10-4	1.500	(38.100)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-32-427-YL	250	B-427	Yellow	10-4	1.500	(38.100)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-88-427	250	B-427	White	10-4	1.750	(44.450)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	BM71-107-427*	1000	B-427	White	10-4	2.000	(50.800)	1.500	(38.100)	0.500	(12.700)	M71-R4300
Fig. 7	M71-107-427	100	B-427	White	10-4	2.000	(50.800)	1.500	(38.100)	0.500	(12.700)	M71-R4300

* "B" indicates bulk roll.

See all ribbon colors on page 115.