

**STOCK AND CUSTOM SOLUTIONS FOR ENHANCING YOUR PRODUCT'S VALUE**

**ECO-FRIENDLY  
PRODUCTS**



**COMPARTMENTED  
BOXES**

**CASES**



**MEDICAL  
PRODUCTS**

**TOOL BOXES**



**SPECIALTY  
STORAGE**

# OVERVIEW

## Single Source Solutions... In Plastic

**Flambeau, Inc.** is a worldwide industry leader in thermoplastic manufacturing, specializing in both injection and blow molding. Flambeau possesses the largest array of proprietary stock products and storage containers for both Consumer and Original Equipment markets. Our unique competitive advantage is the ability to offer customized stock solutions through value-add manufacturing. Our range of service includes offering custom colors; labels; special decorating; engraved logo plates; finishing; special processing; small production run quantities; and comprehensive assistance with design and customization requirements.

Flambeau is your “**art to part**” source for your plastic packaging requirements. Should your application require a solution that does not exist within our stock offering, our program management team is available to offer our **full range of services**. These services include part design; prototyping; mold design and fabrication; manufacturing and assembly; sampling; custom quoting; and product fulfillment programs.

**NEW** Flambeau is continuously adding timely new products and programs to our Packaging offering. We are pleased to announce “**NEW**” in this catalog:

- Medical Device storage box (pg. 62) for heart pace makers and miniature implantable devices.
- Large 9" Black Ribbon case (pg. 45) great for protecting sensitive electronics and hand held devices.
- Infinity FV 6.5 Blow Mold Express Service case (pg. 39) extends the Infinity product line for “off the shelf” cases.
- Merchant 15 Series cases (pg. 36) the largest cases in Merchant category with open core or partitioned storage features.
- Rolling Tote Storage Cabinet (pg. 55) great for light commercial MRO product storage and transportation.
- Gun Cases (pg. 53) provides wide range of choices for rifle and small fire arm storage and transportation.

Choose Flambeau ZERUST to enhance case performance against rust and tarnish when storing and protecting your valuables in these great new products from Flambeau!

 Flambeau is also pleased to make nearly all our manufactured polyolefin based products **biodegradable!** (Minimum quantities may apply). Several popular Flambeau boxes and cases are now manufactured and stocked this way (see our Frog friendly  icon) where applicable!

**We encourage you to examine all we can offer at:**



[www.flambeaucases.com](http://www.flambeaucases.com)

**-or-**



[www.flambeau.com](http://www.flambeau.com)

## Profile & History

Flambeau Packaging & Storage Solutions is a division of Flambeau, Inc., a member of the Nordic Group of Companies. Founded in 1947, today the Nordic Group has sales in excess of \$350 million and operates with more than 2,000 associates worldwide. Headquartered in Baraboo, Wisconsin, Flambeau has manufacturing facilities throughout the United States with additional locations in England and Mexico. Flambeau continues to foster core values such as **Family, Integrity, Leadership, Teamwork, and Knowledge** to pursue **Excellence** with people who care and are committed to anticipate the professional service that you need, when you need it!

## Quality: TS/ISO Accreditation

There is a difference! By adhering to the strictest quality standards in all aspects of our business, Flambeau exceeds your quality expectations through a commitment of ongoing and continuous quality improvements and proactive cost reductions.

## Customer Service

Our professional Customer Service associates are eager to help answer questions and solve problems! We are committed to help provide solutions whether it's an ordinary question or a technical challenge. Please contact us toll-free at **800-344-5716**.



## Flambeau Manufacturing Locations

### UNITED STATES

- Baraboo, WI
- Columbus, IN
- Middlefield, OH
- Madison, GA
- Redlands, CA
- Weldon, NC

### INTERNATIONAL

- Ramsgate, Kent, England
- Saltillo, Coahuila, Mexico



# ENVIRONMENTALLY FRIENDLY FROM FLAMBEAU®

## **Biodegradable Products**

**Flambeau's Packaging Division NOW OFFERS:**



## **Completely 100 % Biodegradable & 100 % Recyclable Storage Cases and Boxes**



Biodegradation occurs with our uniquely manufactured products in either an aerobic and or anaerobic environment:

-  In Landfills
-  In Compost (backyards as well as commercial facilities) or
-  Buried in the ground

Flambeau's biodegradable manufacturing process does not produce any toxic residues. Once our products return to the environment in compost or landfill hosts then, nothing but a safe biomass and humus results.

-  Aerobic—Biomass, CO<sub>2</sub>, Water
-  Anaerobic—Biomass, Methane, CO<sub>2</sub>, some Water

Moreover, the physical characteristics of Flambeau's "eco-friendly" packaging are equal to those of our traditional packaging---which emphasizes Flambeau's commitment to manufacture high quality, durable, plastic packaging. Products manufactured by Flambeau utilizing our "eco-friendly" process and materials do not affect our merchandise guarantee!

**We offer: Completely 100 % Biodegradable & 100 % Recyclable.** Ensures customers disposal of product lessens their carbon footprint on the environment & provides additional value to items sold.

No degradation by exposure to external stresses during storage, shipping, handling, or normal use. Provides an indefinite shelf life and similar service life as our standard resins.

Technical & Physical properties of cases and boxes made with Flambeau eco-friendly materials are equivalent to our traditional packaging---maintaining Flambeau's commitment to manufacturing high quality products.

Flambeau's capability with biodegradable packaging extends across the entire polyolefin product line, and can be manufactured and made available in most products with production quantities as small as 1,000 units.

Flambeau currently stocks a number of popular Flambeau boxes incorporating our "eco" friendly materials. Look for the "bio frog" icon!

***Contact customer service to see if your packaging can be biodegradable!***



Can be made 



Can be made 

**Be sure to contact Flambeau Customer Service at 1-800-344-5716 for assistance with ordering your boxes and cases with this timely new offering from Flambeau!**

# SOFT-SIDES: FLAMBEAU®

Flambeau... a world leader in manufacturing Plastic Cases and Boxes **INTRODUCES...**  
**SOFT-SIDE BAGS AND CASES!**



## **NEW OFFERING!**

Flambeau is pleased to offer an extensive range of canvas bags and cases for your customization! Countless options with canvas bags and cases are at your fingertips!

Your products can now be stored, protected, or merchandised with unlimited canvas choices!

## **MANY CHOICES!**

Choose sewn products with hard cases! Choose any combination of Flambeau rigid boxes and cases from our vast stock product line to use in combination with your canvas choice!

## **TURN-KEY SERVICE...**

Your company brand / logo is critical to your marketing success. Flambeau can help you design the right solution for your products.

- Your company identity
- Your color scheme
- Your products uniquely packaged
- Your custom solution

## **CONTACT US TODAY!**

Contact Flambeau today

Phone: **1-800-344-5716** or **1-440-632-1631**

or see your factory salesman for more details!

*Great for protecting  
and transporting  
instruments,  
equipment, tools,  
small electronic devices,  
medical equipment,  
sports products, and  
much, much more!*



# SPECIAL PROGRAMS & OFFERINGS

## **EXPRESS SERVICE** *What You Need, When You Need It.*

Flambeau's **Express Service<sup>SM</sup>** program is our way of providing the industry's largest selection of in-stock, ready-to-ship cases and boxes which ship within 24 business hours of your order. With minimum order quantities from one unit to single case quantities, this program truly gives you the flexibility and convenience to order exactly "What You Need, When You Need It."

**Qualifying products are marked throughout the catalog with this symbol "E".**



Low volume custom boxes are now available through Flambeau's **Blue Diamond Program<sup>SM</sup>**! Select in-stock injection molded boxes are available for custom decorating with a hot stamp. Company names and logos have never been easier!

**Qualifying products are available in case quantities and marked throughout the catalog with a "F" symbol.**



\*See "Customized Stock and Custom Options" Section: "Hot Stamp Labeling" **page 9**, and for an example of available hot stamp colors see **page 8**.

## **"Special Order" / Non-Stock Products**

Our goal is to offer you the most comprehensive selection of products possible. Although most products are in-stock and ready to ship, we offer a wide variety of products that are not stocked.

**Non-stock products are marked in the catalog as "S" and are available with reasonable lead-times.** Please inquire with a Customer Service associate at 800-344-5716 for additional product and production details.

For your convenience & order processing speed we accept:



# CAPABILITIES

## **Stock Products – “Off Our Shelf to Yours”**

With over 300 **in-stock** product choices, Flambeau has the most extensive selection of injection boxes and heavy-duty blow molded cases for applications in every industry. Most products are in-stock and ready-to-ship. **Express Service™** and **Blue Diamond** programs (see overview section) make it easy to order with no minimums and/or low quantities with custom printing. Any non-stock items are marked “**Ⓢ**” and are available through scheduled production. Although all of our cases are available without foam, many blow molded cases are available with foam. We use two-pound polyurethane convoluted foam in the lid and flat foam in the base (as shown). When the case is closed, lid and base foam touch to hold parts securely.

## **Stock Blow Molded Case Options**



## **Customized Stock Products – “Personalized”**

Because we understand the importance of **customization**, our stock proprietary products are designed to easily adapt to your needs. For your convenience, we take our stock products **“off-the-shelf”** and add customization of your choice. \*See **“Customized Stock and Custom Options”** section starting on **page 9**.

## **Contract Manufacturing – “Art-To-Part” Customization**

Beyond our proprietary products, Flambeau offers total program management from “art-to-part”. With a reputation of providing **single-source solutions** we are prepared for your most challenging project. We utilize our in-house engineering and design services, prototyping, tool fabrication, unique product production techniques, and post mold operations, such as custom assembly, so your specific needs can be met. You can be sure that Flambeau will provide personal service as our dedicated cross-functional associate team works the details. We make your vision a reality. \*See **“Customized Stock and Custom Options”** section.



***\*Most products can be produced with custom resins and colors upon request. Please contact a Customer Service associate at 800-344-5716 for details.***

# ZERUST® & TARNISH INHIBITOR CAPABILITIES

## FLAMBEAU® ZERUST® PRODUCTS STOP RUST



by releasing an invisible, odorless, non-toxic, non-flammable, and non-reactive proprietary corrosion inhibiting vapor that protects metal components from corrosion for up to five years. Flambeau Zerust corrosion inhibitor is molded directly into plastic. Inside a relatively well-sealed package made from Flambeau Zerust materials, or within an enclosure containing them, this vapor will settle on all exposed metal surfaces, forming a very thin protective layer (only a few molecules thick). This molecular layer inhibits the electrochemical reactions at the surface of the metal that cause corrosion.

Flambeau Zerust products do not affect the electrical or mechanical properties or functionality of the metal components that they protect. In fact, they actually help improve reliability by preventing corrosion damage too small to be seen by the naked eye. **See page 34 for ordering information.**

### THE 24 HOUR TEST



Test performed with distilled water & Flambeau® Zerust® Capsule submerged 48 hours prior to adding metal.

### THE 1 MONTH TEST



**Tarnish Inhibitor** by Flambeau provides safe, long-term protective storage for sterling silver items. The patented Tarnish Inhibitor additive forms a harmless protective layer around silver surfaces preventing tarnishing for up to five years.

Flambeau stocks select Super Satchels™ and Tuff Tainers® with Tarnish Inhibitor or Zerust molded within the product. Most products incorporating the Tarnish Inhibitor or Zerust features are available through our **Special Order Program** and may require certain minimum quantities.

**See page 34 for ordering information for Tarnish Inhibitor and Zerust Divider Packs.** These divider packs provide the same great protection molded in the “divider” for use in Flambeau Super Satchels and Tuff Tainers.

# CUSTOM COLORS, OPTIONS & CUSTOMIZABLE STOCK

## **Stock\*/Custom Blended\*\* Colors**

Flambeau keeps a comprehensive selection of color resins “in-house” and ready for production.  
*\*Colors must meet minimum order requirements \*\*Custom blended colors available upon request*

### **Available Injection Molded Colors:**

|                                                                                                                         |                                                                                                                 |                                                                                                           |                                                                                                                        |                                                                                                                          |
|-------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|
|  <b>Taupe</b><br>PMS 409C               |  <b>Black</b><br>PMS 6C        |  <b>Gray</b><br>PMS 432C |  <b>Yellow</b><br>PMS 109C           |  <b>Blue</b><br>PMS 289C              |
|  <b>Orange</b><br>PMS 1665C             |  <b>Evergreen</b><br>PMS 553C  |  <b>Red</b><br>PMS 1805C |  <b>Translucent Blue</b><br>PMS 307C |  <b>Translucent Red</b><br>PMS 198C   |
|  <b>Translucent Yellow</b><br>PMS 3955C |  <b>Translucent</b><br>PMS N/A |  <b>White</b><br>PMS 77C |  <b>Olive Green</b><br>PMS 418C      |  <b>Translucent Green</b><br>PMS 354C |

### **Available Blow Molded Colors:**

|                                                                                                            |                                                                                                             |                                                                                                                |
|------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------|
|  <b>Orange</b><br>PMS 158C |  <b>White</b><br>PMS 77C   |  <b>Black</b><br>PMS 6C       |
|  <b>Gray</b><br>PMS 433C   |  <b>Silver</b><br>PMS 877C |  <b>Blue</b><br>PMS 307C      |
|  <b>Red</b><br>PMS 187C    |  <b>Yellow</b><br>PMS 116C |  <b>Evergreen</b><br>PMS 553C |

### **Available Hot Stamp Foil Colors:**

|                                                                                                                           |                                                                                                               |                                                                                                                 |
|---------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|
|  <b>Black</b><br>PMS 6C                  |  <b>White</b><br>PMS 77C   |  <b>Blue</b><br>PMS 286C     |
|  <b>Yellow</b><br>Crown Roll<br>PMS 114C |  <b>Green</b><br>PMS 3308C |  <b>Platinum</b><br>PMS 877C |
|  <b>Red</b><br>PMS 186C                  |  <b>Gold</b><br>PMS 871C   |                                                                                                                 |

## **Color Options**

Many stocked and custom colors are available. Please contact a Customer Service associate at 800-344-5716 for details.

See stocked colors on above.



## **In-mold Decorating**

*\* Injection or blow molded products*

A revolutionary new and popular process that is quickly replacing the application of labels and other decorating processes, in-mold decorating provides an incredible opportunity to decorate large or multiple areas with confidence of quality. This process allows us to apply a graphic label(s) robotically while in production. The result – better product presentation with guaranteed straight, crisp, clear graphics that are impervious to most chemicals, peeling, bubbling, cracking or falling off all together.



# CUSTOMIZED STOCK & CUSTOM OPTIONS

## **Engraving**

*\* Injection or blow molded products*

We use lid and base inserts on our stock and proprietary products. This allows you the flexibility to insert a custom engraved company logo and/or design plate on one or both sides of your case.



## **Hot Stamp Labeling**

*\* Injection molded products only*

Hot stamping is a very common and economical way of getting your product customized. Stamping typically is done in a single color but can be as many as three colors. Best results are on a smooth surface.

See *Blue Diamond Program<sup>SM</sup>* on **page 5** for details.



## **Labels**

*\* Injection or blow molded products*

Although quickly being replaced by in-mold labeling, adhesive-backed labels can be added to most products in a post-mold secondary application. Should you choose this method over another method of decorating, we can offer a number of suggestions to help you in this process. Please contact a Customer Service associate for additional information at 800-344-5716.



## **Handles, Latches & Accessories**

A variety of handles and latches are available for our blow molded cases. For pricing and availability please contact a Customer Service associate at 800-344-5716. For pictures and descriptions see "Options" on **pages 46-47**.

# CUSTOMIZED STOCK & CUSTOM OPTIONS

## **Custom Interiors - “Cores”**

*\* Injection or blow molded products*

Custom “cores” or interiors can be tooled at the Flambeau Technology Center™ for the majority of product Flambeau manufactures. This is an excellent cost-effective alternative to foam or thermoformed inserts for high-volume requirements. Flambeau’s design engineering staff will help you determine the best options to meet your objectives.



## **Custom Foam Interiors**

*\* Injection or blow molded products*

The professional look, moderate cost and flexibility of die-cut foam have made it a popular choice in numerous industries. Contact a Customer Service associate for pricing and lead-time at 800-344-5716.



# FREQUENTLY ASKED QUESTIONS

## 1. What are your order minimums, lead-times & fulfillment times?

*Standard lead-times are based on order acceptance/confirmation and customer approval of any applicable artwork and/or the part type and/or classification.*

| Program                            | Ship Time                | Minimums                                                                           |
|------------------------------------|--------------------------|------------------------------------------------------------------------------------|
| Stock Products                     | Within 3 Business Days   | Full Carton Quantities                                                             |
| Express Service                    | Within 24 Business Hours | Single Unit- Blow Mold Products;<br>Full Case Quantity - Injection Molded Products |
| Blue Diamond Program <sup>SM</sup> | Up to 4 Weeks            | Case Quantity                                                                      |
| Special Order/Non-Stock            | Up to 6 Weeks            | Call                                                                               |
| Custom                             | Call                     | Call                                                                               |

## 2. What size area and location on your boxes can be used for printing?

*Each area is slightly different based on the product you have selected. Please contact one of our Customer Service associates for details at 800-344-5716.*

## 3. What file formats do you accept for artwork for hot stamps, in-mold decorating or printing?

**Programs:** Illustrator (preferred), Freehand, Photoshop      **File Formats:** AI (preferred), EPS, TIFF, or JPEG      **Quality:** 300 dpi at 100% size

## 4. Can you hot stamp a blow molded case?

*No, you can only hot stamp an injection molded box. There are three (3) choices for customizing a blow molded case. Engraving a plate, in-mold decorating (labeling) or standard adhesive labels are the best choices for decorating. These choices typically require a minimum order of 500 pieces and have additional charges associated with set up and/or tooling. Please contact a Customer Service associate for more details & a quote specific to your project at 800-344-5716.*

## 5. How do I know whether to use a blow molded or injection molded product?

*If a custom interior for presentation and protection is most important, then a blow molded, double-wall case such as the Infinity™ would be the best choice. If compartmentalization and visualization for Point of Purchase is required, one of our injection molded cases or boxes would be a good choice.*

## 6. What modifications can I make to a stock case?

*Modifications include interior custom cores, handles, latches, case color and even material. A detailed request for quote (RFQ) should be filled out by our sales staff. Flambeau associates are trained to help you make economical and functional decisions about the right case for your application and product.*

## 7. How do I decide what type of custom interior to use?

*We offer either custom molded interiors or custom foam interiors. Although size, weight, application and type of part are considerations, we typically will recommend you consider custom foam for annual volumes of 750 units or less. Our Flambeau Technology Center™ can fabricate a tool for custom molded interiors and our staff of engineers would be happy to assist you in the design.*

## 8. What material should I use for my compartmented box application?

*If clarity is most important, styrene is an excellent choice. If durability is most important, polypropylene is the best choice. If clarity and durability are important, Styrene-Butadiene Methyl Methacrylate is the best choice.*

## 9. How many times can you open and close the integral hinge before it cracks or breaks?


*Our integral hinge boxes are manufactured to withstand thousands of openings and, therefore, it is reasonable to expect that under normal use, the hinge will last for the life of the product.*

# COMPARTMENTED BOXES

## A-Series Boxes

### Styrene

The original Flambeau styrene box. The A-Series has a distinct stout look with very square corners and true 90° walls. Still a very popular pick with customers from many industries.



■ Clarity\*  
■ Impact Resistance  
■ Chemical Resistance


**Can Be Made**



## Diamondback™ Boxes

### Styrene

With a slight architectural edge radius & rounded corners, this box is crystal clear like glass and is excellent for merchandising and general display of products. This box also has small stacking feet to keep displays neater and features an easy open hinge. US Patent D412,786



■ Clarity\*  
■ Impact Resistance  
■ Chemical Resistance


**Can Be Made**



## Precision Boxes

### Styrene Butadiene Methyl Methacrylate

Molded from styrene butadiene methyl methacrylate, this box features transparent clarity and impact resistance even in the harshest conditions. The Precision excels in wet applications with its rust-proof hinge.



■ Clarity\*  
■ Impact Resistance  
■ Chemical Resistance


**Can Be Made**



## Mighty-Tuff™ Boxes

### Cellulose Propionate

Just as the name implies, the Mighty-Tuff is tough! This transparent cellulose propionate material excels in industrial and institutional environments. With a double metal hinge you can be sure that this box will take almost any punishment you can give it.



■ Clarity\*  
■ Impact Resistance  
■ Chemical Resistance

**Can Be Made**




## M-Series Boxes

### Polypropylene

Extra heavy-duty construction makes the polypropylene M-Series boxes tough and durable. These workhorse boxes feature a heavy-duty, heat-sealed hinge and overlapping lid to inhibit dust. Impervious to most household chemicals, solvents, oil and gasoline, these boxes keep items safe and organized.



**Can Be Made**




■ Clarity\*  
■ Impact Resistance  
■ Chemical Resistance

# COMPARTMENTED BOXES

## V-Series Boxes

### Polypropylene

With a living hinge (flex hinge) and dual positive snap lock latches these single compartment boxes are excellent for storage of larger items or for the autoclave process.



■ Clarity\*  
■ Impact Resistance  
■ Chemical Resistance


Can Be Made



## K-Series Boxes

### Styrene Butadiene Copolymer

Noted for heavy-duty applications, this styrene butadiene copolymer box has excellent impact properties and also maintains scratch-resistant and transparent qualities.



■ Clarity\*  
■ Impact Resistance  
■ Chemical Resistance


Can Be Made



## Tuff Tainer® Boxes

### Polypropylene

The Tuff Tainer is made with polypropylene and features a detachable lid and movable dividers that allow you to configure your compartment space to your liking. The majority of these boxes include two positive locking latches and will resist most common chemicals, gasoline & oil.



■ Clarity\*  
■ Impact Resistance  
■ Chemical Resistance

Can Be Made



Mechanical latch found on T4007 & T5007 Tuff Tainers




Integral latch found on all Tuff Tainers except T4007 & T5007



## IDS™ (Infinite Divider System) Boxes

### Polypropylene

Made of polypropylene, this ultimate organizational system gives you the flexibility you have always dreamed of by allowing you to move each divider 1/16 (0.16 cm) of an inch along the ribbed compartment. IDS boxes fit in the IDS Cabinet shown on page 49.



■ Clarity\*  
■ Impact Resistance  
■ Chemical Resistance




## T-Series Boxes

### Polypropylene

T-Series boxes provide the same durable construction as the popular M-Series, but are made with translucent polypropylene. These boxes are perfect for "visualizing" components within the box. The T-Series are impervious to most household chemicals, solvents, and gasoline. Great for storage and protection.

Can Be Made



■ Clarity\*  
■ Impact Resistance  
■ Chemical Resistance

# COMPARTMENTED BOXES

With a reputation for selection, Flambeau is now asking the industry to “*think outside of the box*” with the addition of the Blue Diamond Program<sup>SM</sup>! Now you can add custom printing to select products at low volume order quantities. With the industry’s largest selection of sizes and material types you can expect to find what you need right on our shelf. Finding a compartmented box has never been easier.

Even with over 300 stock choices, sometimes we have a request for a unique size or compartment configuration. If so, please let us know. Most of our products can be altered to accommodate a special material or core (compartment) requirement for your project. Finally, we will accommodate you by building a tool specifically for your project right in our Technology Center.

## Compartmented Box Size Reference Chart

To help you find what you need we have added a size reference chart that lists all of Flambeau's compartmented boxes from their smallest to largest dimension.

| BOX MATERIAL KEY               |                           |                                              |                                                                                                                                                                                                           | SYMBOL KEY |
|--------------------------------|---------------------------|----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  = Blue Diamond<br> = Special Order |            |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |                                                                                                                                                                                                           |            |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |                                                                                                                                                                                                           |            |

| Inside L x W x D                                       | Model                                                                                                                                                                                                | Fixed Comps | Material                   | Page |
|--------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|----------------------------|------|
| 3-11/16" x 2-9/16" x 13/16"<br>(9.37 x 6.51 x 2.06 cm) | 2020-2                                                                                                              | 1           | SBMM                       | 20   |
| 4" x 3-3/8" x 13/16"<br>(10.16 x 8.57 x 2.06 cm)       | 2040-2                                                                                                              | 1           | WP                         | 20   |
| 4-1/4" diameter x 3/4"<br>(10.80 diameter x 1.91 cm)   | A01                                                                                                                 | 1           | Styrene                    | 20   |
| 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm) | 5200CL                                                                                                                                                                                               | 1           | TCP                        | 20   |
| 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm) | 5202CL                                                                                                                                                                                               | 2           | TCP                        | 20   |
| 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm) | 5204CL                                                                                                                                                                                               | 4           | TCP                        | 20   |
| 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm) | 5206CL                                                                                                            | 6           | TCP                        | 20   |
| 4-5/16" x 2-5/8" x 1-1/8"<br>(10.95 x 6.67 x 2.86 cm)  | T1002                                                                                                             | 4           | TP                         | 20   |
| 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)       | A226<br>K226                                                                                                      | 1           | Styrene<br>SBC             | 20   |
| 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)       | A228                                                                                                              | 8           | Styrene                    | 20   |
| 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)       | A221<br>T221<br>M221                                                                                              | 4           | Styrene<br>TP<br>YP        | 20   |
| 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)       | A220<br>T220<br>K220 <br>M220  | 6           | Styrene<br>TP<br>SBC<br>YP | 21   |
| 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)     | DB221                                                                                                                                                                                                | 4           | Styrene                    | 21   |
| 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)     | DB228                                                                                                             | 8           | Styrene                    | 21   |
| 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)     | DB220                                                                                                                                                                                                | 6           | Styrene                    | 21   |
| 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)     | DB226                                                                                                                                                                                                | 1           | Styrene                    | 21   |
| 5-1/8" x 3-9/16" x 1-1/2"<br>(13.02 x 9.05 x 3.81 cm)  | A101                                                                                                                                                                                                 | 1           | Styrene                    | 21   |

| Inside L x W x D                                         | Model                                                                                                                                                                                                    | Fixed Comps | Material                   | Page |
|----------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|----------------------------|------|
| 5-5/8" x 2-15/16" x 1-1/8"<br>(14.29 x 7.46 x 2.86 cm)   | A154                                                                                                                                                                                                     | 4           | Styrene                    | 21   |
| 5-5/8" x 2-15/16" x 1-1/8"<br>(14.29 x 7.46 x 2.86 cm)   | A155<br>T155                                                                                                                                                                                             | 5           | Styrene<br>TP              | 21   |
| 5-5/8" x 3-5/8" x 1-1/8"<br>(14.29 x 9.21 x 1.91 cm)     | 3030-2                                                                                                                | 1           | SBMM                       | 21   |
| 5-7/8" x 3-3/4" x 1-5/8"<br>(14.92 x 9.53 x 4.13 cm)     | A250                                                                                                                                                                                                     | 1           | Styrene                    | 21   |
| 6-5/8" x 3-3/8" x 1-5/16"<br>(16.83 x 8.57 x 3.33 cm)    | T300                                                                                                                | 3           | TP                         | 22   |
| 6-11/16" x 3-5/16" x 1-5/16"<br>(16.99 x 8.41 x 3.33 cm) | T2003                                                                                                               | 3           | TP                         | 22   |
| 6-3/4" x 3-3/16" x 1/2"<br>(17.15 x 8.10 x 1.27 cm)      | A213-SL                                                                                                                                                                                                  | 10          | Styrene                    | 22   |
| 6-3/4" x 3-3/16" x 1/2"<br>(17.15 x 8.10 x 1.27 cm)      | A216-SL                                                                                                             | 1           | Styrene                    | 22   |
| 6-3/4" x 3-3/16" x 1/2"<br>(17.15 x 8.10 x 1.27 cm)      | A210-SL                                                                                                             | 9           | Styrene                    | 22   |
| 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | A213                                                                                                                                                                                                     | 10          | Styrene                    | 22   |
| 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | A214                                                                                                                                                                                                     | 2           | Styrene                    | 22   |
| 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | A215<br>T215<br>K215 <br>M215  | 5           | Styrene<br>TP<br>SBC<br>YP | 22   |
| 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | A210<br>T210 <br>K210 <br>M210 | 9           | Styrene<br>TP<br>SBC<br>YP | 22   |
| 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | A219<br>T219<br>K219                                                                                                | 12          | Styrene<br>TP<br>SBC       | 22   |
| 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | A217                                                                                                                                                                                                     | 7           | Styrene                    | 22   |
| 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | A211                                                                                                                | 6           | Styrene                    | 22   |

# COMPARTMENTED BOXES

## Compartmented Box Size Reference Chart - continued

| BOX MATERIAL KEY               |                           |                                              |  |  | SYMBOL KEY |                   |
|--------------------------------|---------------------------|----------------------------------------------|--|--|------------|-------------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  |  |            | ◆ = Blue Diamond  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |  |  |            | Ⓢ = Special Order |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |  |  |            |                   |

| Inside L x W x D                                       | Model                              | Fixed Comps | Material                   | Page |
|--------------------------------------------------------|------------------------------------|-------------|----------------------------|------|
| 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm) | A216 ◆<br>K216                     | 1           | Styrene<br>SBC             | 23   |
| 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm) | A212                               | 5           | Styrene                    | 23   |
| 6-7/8" x 2-1/16" x 1"<br>(17.46 x 5.24 x 2.54 cm)      | A701<br>K701 Ⓢ                     | 1           | Styrene<br>SBC             | 23   |
| 7" x 3-1/4" x 1"<br>(17.78 x 8.26 x 2.54 cm)           | V301 ◆<br>V301PT                   | 1           | OP<br>SP                   | 23   |
| 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)       | DB216                              | 1           | Styrene                    | 23   |
| 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)       | DB211                              | 6           | Styrene                    | 23   |
| 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)       | DB219                              | 12          | Styrene                    | 23   |
| 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)       | DB210                              | 9           | Styrene                    | 23   |
| 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)       | DB213 ◆                            | 10          | Styrene                    | 24   |
| 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)       | DB217                              | 7           | Styrene                    | 24   |
| 7" x 4" x 1-1/16"<br>(17.78 x 10.16 x 2.70 cm)         | 5126CL                             | 17          | TCP                        | 24   |
| 7" x 4" x 1-1/16"<br>(17.78 x 10.16 x 2.70 cm)         | 5127CL                             | 11          | TCP                        | 24   |
| 7" x 4" x 1-1/16"<br>(17.78 x 10.16 x 2.70 cm)         | 5128CL                             | 6           | TCP                        | 24   |
| 7-1/8" x 5-1/8" x 1-9/16"<br>(18.10 x 13.02 x 3.97 cm) | A401                               | 1           | Styrene                    | 24   |
| 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)         | A204                               | 12          | Styrene                    | 24   |
| 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)         | A206<br>K206 ◆                     | 1           | Styrene<br>SBC             | 24   |
| 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)         | A209                               | 9           | Styrene                    | 24   |
| 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)         | A200 ◆<br>T200<br>K200 ◆<br>M200 Ⓢ | 18          | Styrene<br>TP<br>SBC<br>YP | 25   |
| 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)         | A208 ◆<br>K208 ◆<br>M208           | 12          | Styrene<br>SBC<br>YP       | 25   |
| 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)         | A201<br>T201<br>K201 ◆<br>M201     | 12          | Styrene<br>TP<br>SBC<br>YP | 25   |
| 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)         | A203<br>T203 ◆<br>K203 ◆<br>M203   | 6           | Styrene<br>TP<br>SBC<br>YP | 25   |
| 8-1/8" x 4-1/8" x 1-3/16"<br>(20.64 x 10.48 x 3.02 cm) | V401 ◆                             | 1           | SP                         | 25   |

| Inside L x W x D                                         | Model                            | Fixed Comps | Material                   | Page |
|----------------------------------------------------------|----------------------------------|-------------|----------------------------|------|
| 8-1/8" x 4-1/8" x 1-3/16"<br>(20.64 x 10.48 x 3.02 cm)   | V402-2 Ⓢ                         | 2           | SP                         | 25   |
| 8-1/8" x 4-1/8" x 2-5/8"<br>(20.64 x 10.48 x 6.67 cm)    | V401D-2 ◆                        | 1           | SP                         | 25   |
| 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm)  | DB201                            | 12          | Styrene                    | 25   |
| 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm)  | DB203                            | 6           | Styrene                    | 25   |
| 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm)  | DB208 ◆                          | 12          | Styrene                    | 26   |
| 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm)  | DB200 ◆                          | 18          | Styrene                    | 26   |
| 8-1/2" x 4-1/4" x 1-3/16"<br>(21.59 x 10.80 x 3.02 cm)   | DB206 Ⓢ                          | 1           | Styrene                    | 26   |
| 8-1/2" x 4-1/4" x 1-3/16"<br>(21.59 x 10.80 x 3.02 cm)   | DB204                            | 12          | Styrene                    | 26   |
| 8-3/4" x 4-5/16" x 1-1/4"<br>(22.23 x 10.95 x 3.18 cm)   | 4040-2 ◆                         | 1           | SBMM                       | 26   |
| 8-7/8" x 4-1/8" x 1-3/16"<br>(22.54 x 10.48 x 3.02 cm)   | T3003 ◆                          | 3           | TP                         | 26   |
| 9-5/8" x 6-9/16" x 1-1/2"<br>(24.45 x 16.69 x 3.81 cm)   | A166-36<br>K166-36 ◆             | 36          | Styrene<br>SBC             | 26   |
| 10" x 4-1/4" x 1-1/2"<br>(25.40 x 10.80 x 3.81 cm)       | V501 ◆                           | 1           | SP                         | 26   |
| 10" x 4-1/4" x 1-1/2"<br>(25.40 x 10.80 x 3.81 cm)       | V506-2 Ⓢ                         | 6           | SP                         | 26   |
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | T616R<br>K616R Ⓢ<br>M616R Ⓢ      | 4           | TP<br>SBC<br>YP            | 27   |
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | A623 Ⓢ<br>T623<br>K623 Ⓢ<br>M623 | 13          | Styrene<br>TP<br>SBC<br>YP | 27   |
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | A612 Ⓢ<br>T612<br>M612           | 12          | Styrene<br>TP<br>YP        | 27   |
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | A602<br>T602<br>K602<br>M602     | 12          | Styrene<br>TP<br>SBC<br>YP | 27   |
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | A606<br>T606 ◆<br>K606 ◆<br>M606 | 6           | Styrene<br>TP<br>SBC<br>YP | 27   |
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | A613                             | 13          | Styrene                    | 27   |
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | A607 Ⓢ<br>K607 Ⓢ                 | 7           | Styrene<br>SBC             | 27   |
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | T600 ◆                           | 6           | TP                         | 27   |

# COMPARTMENTED BOXES

## Compartmented Box Size Reference Chart - continued

| BOX MATERIAL KEY               |                           |                                              |  |  | SYMBOL KEY        |  |
|--------------------------------|---------------------------|----------------------------------------------|--|--|-------------------|--|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  |  | ◆ = Blue Diamond  |  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |  |  | Ⓢ = Special Order |  |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |  |  |                   |  |

| Inside L x W x D                                            | Model                                    | Fixed Comps | Material                                 | Page |
|-------------------------------------------------------------|------------------------------------------|-------------|------------------------------------------|------|
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm)    | A601<br>K601<br>C601                     | 1           | Styrene<br>SBC<br>Conductive             | 27   |
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm)    | A618<br>T618 ◆<br>K618 ◆<br>M618<br>C618 | 18          | Styrene<br>TP<br>SBC<br>YP<br>Conductive | 28   |
| 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm)    | A603 Ⓢ                                   | 3           | Styrene                                  | 28   |
| 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)     | A612D Ⓢ<br>T612D Ⓢ<br>K612D Ⓢ<br>M612D Ⓢ | 12          | Styrene<br>TP<br>SBC<br>YP               | 28   |
| 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)     | A618D Ⓢ<br>T618D Ⓢ<br>K618D Ⓢ<br>M618D Ⓢ | 18          | Styrene<br>TP<br>SBC<br>YP               | 28   |
| 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)     | A601D Ⓢ<br>K601D Ⓢ                       | 1           | Styrene<br>SBC                           | 28   |
| 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)     | A606D Ⓢ<br>T606D ◆<br>K606D Ⓢ<br>M606D Ⓢ | 6           | Styrene<br>TP<br>SBC<br>YP               | 28   |
| 10-9/16" x 8-1/4" x 1-9/16"<br>(26.83 x 20.96 x 3.97 cm)    | A924-2                                   | 24          | Styrene                                  | 28   |
| 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)     | T4007 ◆                                  | 6           | TP                                       | 28   |
| 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)     | T4007AT                                  | 6           | TP                                       | 28   |
| 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)     | T4007E ◆                                 | 6           | TP                                       | 29   |
| 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)     | T4000                                    | 1           | TP                                       | 29   |
| 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | DB606                                    | 6           | Styrene                                  | 29   |
| 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | DB613 ◆                                  | 13          | Styrene                                  | 29   |
| 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | DB601 Ⓢ                                  | 1           | Styrene                                  | 29   |
| 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | DB618                                    | 18          | Styrene                                  | 29   |
| 11-15/16" x 5-15/16" x 1-7/16"<br>(30.32 x 15.08 x 3.65 cm) | 5129-1                                   | 1           | TCP                                      | 29   |
| 11-15/16" x 5-15/16" x 1-7/16"<br>(30.32 x 15.08 x 3.65 cm) | 5129CL                                   | 24          | TCP                                      | 29   |
| 11-15/16" x 5-15/16" x 1-7/16"<br>(30.32 x 15.08 x 3.65 cm) | 5130CL                                   | 6           | TCP                                      | 29   |
| 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)      | A801<br>K801 ◆<br>C801                   | 1           | Styrene<br>SBC<br>Conductive             | 30   |

| Inside L x W x D                                          | Model                                    | Fixed Comps | Material                                 | Page |
|-----------------------------------------------------------|------------------------------------------|-------------|------------------------------------------|------|
| 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)    | A812<br>K812<br>M812                     | 12          | Styrene<br>SBC<br>YP                     | 30   |
| 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)    | A824<br>T824 ◆<br>K824 ◆<br>M824<br>C824 | 24          | Styrene<br>TP<br>SBC<br>YP<br>Conductive | 30   |
| 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)    | A818 Ⓢ<br>K818<br>M818                   | 18          | Styrene<br>SBC<br>YP                     | 30   |
| 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)    | M808 Ⓢ                                   | 8           | YP                                       | 30   |
| 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)    | A806 Ⓢ<br>T806<br>K806<br>M806           | 6           | Styrene<br>TP<br>SBC<br>YP               | 30   |
| 13-1/8" x 8-7/8" x 1-15/16"<br>(33.34 x 22.54 x 4.92 cm)  | T901 Ⓢ                                   | 1           | TP                                       | 30   |
| 13-1/8" x 8-7/8" x 1-15/16"<br>(33.34 x 22.54 x 4.92 cm)  | 999-2                                    | 4           | TP                                       | 30   |
| 13-1/8" x 8-7/8" x 1-15/16"<br>(33.34 x 22.54 x 4.92 cm)  | T900 ◆                                   | 4           | TP                                       | 30   |
| 13-1/2" x 5-3/4" x 2"<br>(34.29 x 14.61 x 5.08 cm)        | V601 ◆                                   | 1           | SP                                       | 31   |
| 13-11/16" x 8-3/16" x 1-3/4"<br>(34.77 x 20.80 x 4.45 cm) | T5007 ◆                                  | 4           | TP                                       | 31   |
| 13-11/16" x 8-3/16" x 1-3/4"<br>(34.77 x 20.80 x 4.45 cm) | T5007AT                                  | 4           | TP                                       | 31   |
| 13-11/16" x 8-3/16" x 1-3/4"<br>(34.77 x 20.80 x 4.45 cm) | T5007E ◆                                 | 4           | TP                                       | 31   |
| 15-1/4" x 8-7/8" x 1-3/8"<br>(38.74 x 22.54 x 3.49 cm)    | T6004 ◆                                  | 6           | TP                                       | 31   |
| 15-1/4" x 8-7/8" x 3"<br>(38.74 x 22.54 x 7.62 cm)        | T7003                                    | 6           | TP                                       | 31   |
| 15-1/4" x 8-7/8" x 3"<br>(38.74 x 22.54 x 7.62 cm)        | T7004 ◆                                  | 7           | TP                                       | 31   |
| 15-1/4" x 8-7/8" x 3"<br>(38.74 x 22.54 x 7.62 cm)        | T7000 ◆                                  | 1           | TP                                       | 31   |
| 17" x 7-1/8" x 2"<br>(43.18 x 18.10 x 5.08 cm)            | V701 ◆                                   | 1           | SP                                       | 31   |

# COMPARTMENTED BOXES

## Compartmented Box Number of Compartments Reference Chart

To help you find what you need we have added a reference chart that lists all of Flambeau's compartmented boxes by how many compartments they have.

| BOX MATERIAL KEY               |  |                           |  |                                              | SYMBOL KEY |                                       |  |  |  |
|--------------------------------|--|---------------------------|--|----------------------------------------------|------------|---------------------------------------|--|--|--|
| TP = Translucent Polypropylene |  | YP = Yellow Polypropylene |  | TCP = Transparent Cellulose Propionate       |            | ⬠ = Blue Diamond<br>Ⓢ = Special Order |  |  |  |
| SP = Taupe Polypropylene       |  | WP = White Polypropylene  |  | SBC = Styrene-Butadiene Copolymer            |            |                                       |  |  |  |
| OP = Orange Polypropylene      |  |                           |  | SBMM = Styrene Butadiene Methyl Methacrylate |            |                                       |  |  |  |

| Fixed Comps | Model                | Inside L x W x D                                         | Material                     | Page |
|-------------|----------------------|----------------------------------------------------------|------------------------------|------|
| 1           | 2020-2 ⬠             | 3-11/16" x 2-9/16" x 13/16"<br>(9.37 x 6.51 x 2.06 cm)   | SBMM                         | 20   |
| 1           | 2040-2 Ⓢ             | 4" x 3-3/8" x 13/16"<br>(10.16 x 8.57 x 2.06 cm)         | WP                           | 20   |
| 1           | A01 Ⓢ                | 4-1/4" diameter x 3/4"<br>(10.80 diameter x 1.91 cm)     | Styrene                      | 20   |
| 1           | 5200CL               | 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm)   | TCP                          | 20   |
| 1           | A226<br>K226 ⬠       | 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)         | Styrene<br>SBC               | 20   |
| 1           | DB226                | 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)       | Styrene                      | 21   |
| 1           | A101                 | 5-1/8" x 3-9/16" x 1-1/2"<br>(13.02 x 9.05 x 3.81 cm)    | Styrene                      | 21   |
| 1           | 3030-2 ⬠             | 5-5/8" x 3-5/8" x 1-1/8"<br>(14.29 x 9.21 x 2.86 cm)     | SBMM                         | 21   |
| 1           | A250                 | 5-7/8" x 3-3/4" x 1-5/8"<br>(14.92 x 9.53 x 4.13 cm)     | Styrene                      | 21   |
| 1           | A216-SL Ⓢ            | 6-3/4" x 3-3/16" x 1/2"<br>(17.15 x 8.10 x 1.27 cm)      | Styrene                      | 22   |
| 1           | A216 ⬠<br>K216       | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | Styrene<br>SBC               | 23   |
| 1           | A701<br>K701 Ⓢ       | 6-7/8" x 2-1/16" x 1"<br>(17.46 x 5.24 x 2.54 cm)        | Styrene<br>SBC               | 23   |
| 1           | V301 ⬠<br>V301PT     | 7" x 3-1/4" x 1"<br>(17.78 x 8.26 x 2.54 cm)             | OP<br>SP                     | 23   |
| 1           | DB216                | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)         | Styrene                      | 23   |
| 1           | A401                 | 7-1/8" x 5-1/8" x 1-9/16"<br>(18.10 x 13.02 x 3.97 cm)   | Styrene                      | 24   |
| 1           | A206<br>K206 ⬠       | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)           | Styrene<br>SBC               | 24   |
| 1           | V401 ⬠               | 8-1/8" x 4-1/8" x 1-3/16"<br>(20.64 x 10.48 x 3.02 cm)   | SP                           | 25   |
| 1           | V401D-2 ⬠            | 8-1/8" x 4-1/8" x 2-5/8"<br>(20.64 x 10.48 x 6.67 cm)    | SP                           | 25   |
| 1           | DB206 Ⓢ              | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm)  | Styrene                      | 26   |
| 1           | 4040-2 ⬠             | 8-3/4" x 4-5/16" x 7/8"<br>(22.23 x 10.95 x 2.22 cm)     | SBMM                         | 26   |
| 1           | V501 ⬠               | 10" x 4-1/4" x 1-1/2"<br>(25.40 x 10.80 x 3.81 cm)       | SP                           | 26   |
| 1           | A601<br>K601<br>C601 | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | Styrene<br>SBC<br>Conductive | 27   |
| 1           | A601D Ⓢ<br>K601D Ⓢ   | 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)  | Styrene<br>SBC               | 28   |
| 1           | T4000                | 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)  | TP                           | 29   |

| Fixed Comps | Model                       | Inside L x W x D                                            | Material                     | Page |
|-------------|-----------------------------|-------------------------------------------------------------|------------------------------|------|
| 1           | DB601 Ⓢ                     | 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | Styrene                      | 29   |
| 1           | 5129-1                      | 11-15/16" x 5-15/16" x 1-7/16"<br>(30.32 x 15.08 x 3.65 cm) | TCP                          | 29   |
| 1           | A801<br>K801 ⬠<br>C801      | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)      | Styrene<br>SBC<br>Conductive | 30   |
| 1           | T901 Ⓢ                      | 13-1/8" x 8-7/8" x 1-15/16"<br>(33.34 x 22.54 x 4.92 cm)    | TP                           | 30   |
| 1           | V601 ⬠                      | 13-1/2" x 5-3/4" x 2"<br>(34.29 x 14.61 x 5.08 cm)          | SP                           | 31   |
| 1           | T7000 ⬠                     | 15-1/4" x 8-7/8" x 3"<br>(38.74 x 22.54 x 7.62 cm)          | TP                           | 31   |
| 1           | V701 ⬠                      | 17" x 7-1/8" x 2"<br>(43.18 x 18.10 x 5.08 cm)              | SP                           | 31   |
| 2           | 5202CL                      | 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm)      | TCP                          | 20   |
| 2           | A214                        | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)      | Styrene                      | 22   |
| 2           | V402-2 Ⓢ                    | 8-1/8" x 4-1/8" x 1-3/16"<br>(20.64 x 10.48 x 3.02 cm)      | SP                           | 25   |
| 3           | T300 ⬠                      | 6-5/8" x 3-3/8" x 1-5/16"<br>(16.83 x 8.57 x 3.33 cm)       | TP                           | 22   |
| 3           | T2003 ⬠                     | 6-11/16" x 3-5/16" x 1-5/16"<br>(16.99 x 8.41 x 3.33 cm)    | TP                           | 22   |
| 3           | T3003 ⬠                     | 8-7/8" x 4-1/8" x 1-3/16"<br>(22.54 x 10.48 x 3.02 cm)      | TP                           | 26   |
| 3           | A603 Ⓢ                      | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm)    | Styrene                      | 28   |
| 4           | 5204CL                      | 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm)      | TCP                          | 20   |
| 4           | T1002 ⬠                     | 4-5/16" x 2-5/8" x 1-1/8"<br>(10.95 x 6.67 x 2.86 cm)       | TP                           | 20   |
| 4           | A221<br>T221<br>M221 Ⓢ      | 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)            | Styrene<br>TP<br>YP          | 20   |
| 4           | DB221                       | 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)          | Styrene                      | 21   |
| 4           | A154                        | 5-5/8" x 2-15/16" x 1-1/8"<br>(14.29 x 7.46 x 2.86 cm)      | Styrene                      | 21   |
| 4           | T616R<br>K616R Ⓢ<br>M616R Ⓢ | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm)    | TP<br>SBC<br>YP              | 27   |
| 4           | 999-2                       | 13-1/8" x 8-7/8" x 1-15/16"<br>(33.34 x 22.54 x 4.92 cm)    | TP                           | 30   |

# COMPARTMENTED BOXES

## Compartmented Box Number of Compartments Reference Chart - continued

| BOX MATERIAL KEY               |                           |                                              |  |  | SYMBOL KEY        |  |
|--------------------------------|---------------------------|----------------------------------------------|--|--|-------------------|--|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  |  | ◆ = Blue Diamond  |  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |  |  | Ⓢ = Special Order |  |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |  |  |                   |  |

| Fixed Comps | Model                                    | Inside L x W x D                                          | Material                   | Page |
|-------------|------------------------------------------|-----------------------------------------------------------|----------------------------|------|
| 4           | T900 ◆                                   | 13-1/8" x 8-7/8" x 1-15/16"<br>(33.34 x 22.54 x 4.92 cm)  | TP                         | 30   |
| 4           | T5007 ◆                                  | 13-11/16" x 8-3/16" x 1-3/4"<br>(34.77 x 20.80 x 4.45 cm) | TP                         | 31   |
| 4           | T5007AT                                  | 13-11/16" x 8-3/16" x 1-3/4"<br>(34.77 x 20.80 x 4.45 cm) | TP                         | 31   |
| 4           | T5007E ◆                                 | 13-11/16" x 8-3/16" x 1-3/4"<br>(34.77 x 20.80 x 4.45 cm) | TP                         | 31   |
| 5           | A155<br>T155                             | 5-5/8" x 2-15/16" x 1-1/8"<br>(14.29 x 7.46 x 2.86 cm)    | Styrene<br>TP              | 21   |
| 5           | A215<br>T215<br>K215 ◆<br>M215 Ⓢ         | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)    | Styrene<br>TP<br>SBC<br>YP | 22   |
| 5           | A212                                     | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)    | Styrene                    | 23   |
| 6           | 5206CL Ⓢ                                 | 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm)    | TCP                        | 20   |
| 6           | A220<br>T220<br>K220 ◆<br>M220 Ⓢ         | 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)          | Styrene<br>TP<br>SBC<br>YP | 21   |
| 6           | DB220                                    | 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)        | Styrene                    | 21   |
| 6           | A211 ◆                                   | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)    | Styrene                    | 23   |
| 6           | DB211                                    | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)          | Styrene                    | 23   |
| 6           | 5128CL                                   | 7" x 4" x 1-1/16"<br>(17.78 x 10.16 x 2.70 cm)            | TCP                        | 24   |
| 6           | A203<br>T203 ◆<br>K203 ◆<br>M203         | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)            | Styrene<br>TP<br>SBC<br>YP | 25   |
| 6           | DB203                                    | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm)   | Styrene                    | 25   |
| 6           | V506-2 Ⓢ                                 | 10" x 4-1/4" x 1-1/2"<br>(25.40 x 10.80 x 3.81 cm)        | SP                         | 25   |
| 6           | A606<br>T606 ◆<br>K606 ◆<br>M606         | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm)  | Styrene<br>TP<br>SBC<br>YP | 27   |
| 6           | T600 ◆                                   | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm)  | TP                         | 27   |
| 6           | A606D Ⓢ<br>T606D ◆<br>K606D Ⓢ<br>M606D Ⓢ | 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)   | Styrene<br>TP<br>SBC<br>YP | 28   |
| 6           | T4007 ◆                                  | 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)   | TP                         | 28   |
| 6           | T4007AT                                  | 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)   | TP                         | 28   |

| Fixed Comps | Model                            | Inside L x W x D                                            | Material                   | Page |
|-------------|----------------------------------|-------------------------------------------------------------|----------------------------|------|
| 6           | T4007E ◆                         | 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)     | TP                         | 29   |
| 6           | DB606                            | 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | Styrene                    | 29   |
| 6           | 5130CL                           | 11-15/16" x 5-15/16" x 1-7/16"<br>(30.32 x 15.08 x 3.65 cm) | TCP                        | 29   |
| 6           | A806 Ⓢ<br>T806<br>K806<br>M806   | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)      | Styrene<br>TP<br>SBC<br>YP | 30   |
| 6           | T6004 ◆                          | 15-1/4" x 8-7/8" x 1-3/8"<br>(38.74 x 22.54 x 3.49 cm)      | TP                         | 31   |
| 6           | T7003                            | 15-1/4" x 8-7/8" x 3"<br>(38.74 x 22.54 x 7.62 cm)          | TP                         | 31   |
| 7           | A217                             | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)      | Styrene                    | 23   |
| 7           | DB217                            | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)            | Styrene                    | 24   |
| 7           | A607 Ⓢ<br>K607 Ⓢ                 | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm)    | Styrene<br>SBC             | 27   |
| 7           | T7004 ◆                          | 15-1/4" x 8-7/8" x 3"<br>(38.74 x 22.54 x 7.62 cm)          | TP                         | 31   |
| 8           | A228 ◆                           | 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)            | Styrene                    | 20   |
| 8           | DB228 ◆                          | 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)          | Styrene                    | 21   |
| 8           | M808 Ⓢ                           | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)      | YP                         | 30   |
| 9           | A210-SL Ⓢ                        | 6-3/4" x 3-3/16" x 1/2"<br>(17.15 x 8.10 x 1.27 cm)         | Styrene                    | 22   |
| 9           | A210<br>T210 ◆<br>K210 ◆<br>M210 | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)      | Styrene<br>TP<br>SBC<br>YP | 22   |
| 9           | DB210                            | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)            | Styrene                    | 23   |
| 9           | A209                             | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)              | Styrene                    | 24   |
| 10          | A213-SL                          | 6-3/4" x 3-3/16" x 1/2"<br>(17.15 x 8.10 x 1.27 cm)         | Styrene                    | 22   |
| 10          | A213                             | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)      | Styrene                    | 22   |
| 10          | DB213 ◆                          | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)            | Styrene                    | 24   |
| 11          | 5127CL                           | 7" x 4" x 1-1/16"<br>(17.78 x 10.16 x 2.70 cm)              | TCP                        | 24   |
| 12          | A219<br>T219<br>K219 ◆           | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)      | Styrene<br>TP<br>SBC       | 23   |
| 12          | DB219                            | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)            | Styrene                    | 23   |

# COMPARTMENTED BOXES

## Compartmented Box Number of Compartments Reference Chart - continued

| BOX MATERIAL KEY               |                           |                                              |  |  | SYMBOL KEY                                                                                          |  |
|--------------------------------|---------------------------|----------------------------------------------|--|--|-----------------------------------------------------------------------------------------------------|--|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  |  |  = Blue Diamond  |  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |  |  |  = Special Order |  |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |  |  |                                                                                                     |  |










| Fixed Comps | Model                                                                                                                                                                                                                                                                                                                                                                            | Inside L x W x D                                         | Material                                 | Page |
|-------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------|------------------------------------------|------|
| 12          | A204                                                                                                                                                                                                                                                                                                                                                                             | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)           | Styrene                                  | 24   |
| 12          | A208 <br>K208 <br>M208                                                                                                                                                                                         | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)           | Styrene<br>SBC<br>YP                     | 25   |
| 12          | A201<br>T201<br>K201 <br>M201                                                                                                                                                                                                                                                                   | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)           | Styrene<br>TP<br>SBC<br>YP               | 25   |
| 12          | DB201                                                                                                                                                                                                                                                                                                                                                                            | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm)  | Styrene                                  | 25   |
| 12          | DB208                                                                                                                                                                                                                                                                                           | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm)  | Styrene                                  | 26   |
| 12          | DB204                                                                                                                                                                                                                                                                                                                                                                            | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm)  | Styrene                                  | 26   |
| 12          | A612 <br>T612<br>M612                                                                                                                                                                                                                                                                           | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | Styrene<br>TP<br>YP                      | 27   |
| 12          | A602<br>T602<br>K602<br>M602                                                                                                                                                                                                                                                                                                                                                     | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | Styrene<br>TP<br>SBC<br>YP               | 27   |
| 12          | A612D <br>T612D <br>K612D <br>M612D  | 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)  | Styrene<br>TP<br>SBC<br>YP               | 28   |
| 12          | A812<br>K812<br>M812                                                                                                                                                                                                                                                                                                                                                             | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)   | Styrene<br>SBC<br>YP                     | 30   |
| 13          | A623 <br>T623<br>K623 <br>M623                                                                                                                                                                             | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | Styrene<br>TP<br>SBC<br>YP               | 27   |
| 13          | A613                                                                                                                                                                                                                                                                                                                                                                             | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | Styrene                                  | 27   |
| 13          | DB613                                                                                                                                                                                                                                                                                         | 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)      | Styrene                                  | 29   |
| 17          | 5126CL                                                                                                                                                                                                                                                                                                                                                                           | 7" x 4" x 1-1/16"<br>(17.78 x 10.16 x 2.70 cm)           | TCP                                      | 24   |
| 18          | A200 <br>T200<br>K200 <br>M200                                                                                          | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)           | Styrene<br>TP<br>SBC<br>YP               | 25   |
| 18          | DB200                                                                                                                                                                                                                                                                                         | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm)  | Styrene                                  | 26   |
| 18          | A618<br>T618 <br>K618 <br>M618<br>C618                                                                                                                                                                     | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | Styrene<br>TP<br>SBC<br>YP<br>Conductive | 28   |

| Fixed Comps | Model                                                                                                                                                                                                                                                                                                                                                                            | Inside L x W x D                                            | Material                                 | Page |
|-------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------|------------------------------------------|------|
| 18          | DB618                                                                                                                                                                                                                                                                                                                                                                            | 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | Styrene                                  | 29   |
| 18          | A618D <br>T618D <br>K618D <br>M618D  | 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)     | Styrene<br>TP<br>SBC<br>YP               | 28   |
| 18          | A818 <br>K818<br>M818                                                                                                                                                                                                                                                                         | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)      | Styrene<br>SBC<br>YP                     | 30   |
| 24          | A924-2                                                                                                                                                                                                                                                                                                                                                                           | 10-9/16" x 8-1/4" x 1-9/16"<br>(26.83 x 20.96 x 3.97 cm)    | Styrene                                  | 28   |
| 24          | 5129CL                                                                                                                                                                                                                                                                                                                                                                           | 11-15/16" x 5-15/16" x 1-7/16"<br>(30.32 x 15.08 x 3.65 cm) | TCP                                      | 29   |
| 24          | A824<br>T824 <br>K824 <br>M824<br>C824                                                                                                                                                                     | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)      | Styrene<br>TP<br>SBC<br>YP<br>Conductive | 30   |
| 36          | A166-36<br>K166-36                                                                                                                                                                                                                                                                           | 9-5/8" x 6-9/16" x 1-1/2"<br>(24.45 x 16.69 x 3.81 cm)      | Styrene<br>SBC                           | 26   |

# COMPARTMENTED BOXES

Boxes 3-11/16" x 2-9/16" x 13/16" through 4-3/8" x 2-5/8" x 1"  
(9.37 x 6.51 x 2.06 cm) through (11.11 x 6.67 x 2.54 cm)

| BOX MATERIAL KEY               |                           |                                              |  |  | SYMBOL KEY        |
|--------------------------------|---------------------------|----------------------------------------------|--|--|-------------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  |  | ◆ = Blue Diamond  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |  |  | Ⓢ = Special Order |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |  |  |                   |








| Box Diagram                                                                                                                                                                                               | Model Number           | Stock Number               | Family                                 | Material            | Dimensions (Inside, L x W x D)                         | Packed |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|----------------------------|----------------------------------------|---------------------|--------------------------------------------------------|--------|
| <br>1 Compartment                                                                                                        | 2020-2 ◆               | 6240AA                     | ■ Precision                            | SBMM                | 3-11/16" x 2-9/16" x 13/16"<br>(9.37 x 6.51 x 2.06 cm) | 24/ctn |
| <br>1 Compartment                                                                                                        | 2040-2 Ⓢ               | 6242FA                     | - -                                    | WP                  | 4" x 3-3/8" x 13/16"<br>(10.16 x 8.57 x 2.06 cm)       | 36/ctn |
| <br>1 Compartment                                                                                                        | A01 Ⓢ                  | 6685CC                     | ■ A-Series                             | Styrene             | 4-1/4" diameter x 3/4"<br>(10.80 diameter x 1.91 cm)   | 80/ctn |
| <br>1 Compartment                                                                                                         | 5200CL                 | 6230MT                     | ■ Mighty-Tuff                          | TCP                 | 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm) | 12/ctn |
| <br>2 Compartments (L x W): A= 2-1/8" x 2-5/8" (5.40 x 6.67 cm)                                                          | 5202CL                 | 6232MT                     | ■ Mighty-Tuff                          | TCP                 | 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm) | 12/ctn |
| <br>4 Compartments (L x W): A= 2-1/8" x 1-1/4" (5.40 x 3.18 cm)                                                         | 5204CL                 | 6234MT                     | ■ Mighty-Tuff                          | TCP                 | 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm) | 12/ctn |
| <br>6 Compartments (L x W): A= 1-3/8" x 1-5/16" (3.49 x 3.33 cm)                                                        | 5206CL Ⓢ               | 6236MT                     | ■ Mighty-Tuff                          | TCP                 | 4-5/16" x 2-5/8" x 1-1/16"<br>(10.95 x 6.67 x 2.70 cm) | 12/ctn |
| <br>4 Compartments & 2 Removable Dividers (L x W): A= 3" x 1-1/4" (7.62 x 3.18 cm), B= 1-1/4" x 1-1/4" (3.18 x 3.18 cm) | T1002 ◆                | 6709TE                     | ■ Tuff Tainer                          | TP                  | 4-5/16" x 2-5/8" x 1-1/8"<br>(10.95 x 6.67 x 2.86 cm)  | 12/ctn |
| <br>1 Compartment                                                                                                       | A226<br>K226 ◆         | 6644CB<br>6644KB           | ■ A-Series<br>■ K-Series               | Styrene<br>SBC      | 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)       | 36/ctn |
| <br>8 Compartments (L x W): A= 1" x 1-1/4" (2.54 x 3.18 cm)                                                             | A228 ◆                 | 6646CB                     | ■ A-Series                             | Styrene             | 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)       | 36/ctn |
| <br>4 Compartments<br>(L x W): A= 2-3/16" x 1-5/16" (5.56 x 3.33 cm)                                                    | A221<br>T221<br>M221 Ⓢ | 6642CB<br>6706TE<br>6706TF | ■ A-Series<br>■ T-Series<br>■ M-Series | Styrene<br>TP<br>YP | 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)       | 36/ctn |

\* Adding color to the resins effects the clarity of the finished product

Boxes 4-3/8" x 2-5/8" x 1" through 5-7/8" x 3-3/4" x 1-5/8"  
(11.11 x 6.67 x 2.54 cm) through (14.92 x 9.53 x 4.13 cm)

# COMPARTMENTED BOXES

| BOX MATERIAL KEY               |                           |                                              | SYMBOL KEY        |
|--------------------------------|---------------------------|----------------------------------------------|-------------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       | ◆ = Blue Diamond  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            | Ⓢ = Special Order |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |                   |

| Box Diagram                                                                                                                                                          | Model Number                                                 | Stock Number                         | Family                                                                   | Material                   | Dimensions (Inside, L x W x D)                         | Packed |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------|--------------------------------------|--------------------------------------------------------------------------|----------------------------|--------------------------------------------------------|--------|
| <br><b>6 Compartments</b><br>(L x W): <b>A=</b> 1-3/8" x 1-1/4" (3.49 x 3.18 cm)    | <b>A220</b><br><b>T220</b><br><b>K220</b> ◆<br><b>M220</b> Ⓢ | 6640CB<br>6704TE<br>6640KB<br>6704TF | <b>A-Series</b><br><b>T-Series</b><br><b>K-Series</b><br><b>M-Series</b> | Styrene<br>TP<br>SBC<br>YP | 4-3/8" x 2-5/8" x 1"<br>(11.11 x 6.67 x 2.54 cm)       | 36/ctn |
| <br><b>4 Compartments</b><br>(L x W): <b>A=</b> 2-3/16" x 1-5/16" (5.56 x 3.33 cm)  | <b>DB221</b>                                                 | 6742CD                               | <b>Diamondback</b>                                                       | Styrene                    | 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)     | 24/ctn |
| <br><b>8 Compartments</b><br>(L x W): <b>A=</b> 1-1/16" x 1-5/16" (2.70 x 3.33 cm)  | <b>DB228</b> ◆                                               | 6746CD                               | <b>Diamondback</b>                                                       | Styrene                    | 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)     | 24/ctn |
| <br><b>6 Compartments</b><br>(L x W): <b>A=</b> 1-5/16" x 1-7/16" (3.33 x 3.65 cm) | <b>DB220</b>                                                 | 6740CD                               | <b>Diamondback</b>                                                       | Styrene                    | 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)     | 24/ctn |
| <br><b>1 Compartment</b>                                                          | <b>DB226</b>                                                 | 6744CD                               | <b>Diamondback</b>                                                       | Styrene                    | 4-1/2" x 2-11/16" x 1"<br>(11.43 x 6.83 x 2.54 cm)     | 24/ctn |
| <br><b>1 Compartment</b>                                                          | <b>A101</b>                                                  | 6600CB                               | <b>A-Series</b>                                                          | Styrene                    | 5-1/8" x 3-9/16" x 1-1/2"<br>(13.02 x 9.05 x 3.81 cm)  | 36/ctn |
| <br><b>4 Compartments</b> (L x W): <b>A=</b> 2-3/4" x 1-7/16" (6.99 x 3.65 cm)    | <b>A154</b>                                                  | 6602CB                               | <b>A-Series</b>                                                          | Styrene                    | 5-5/8" x 2-15/16" x 1-1/8"<br>(14.29 x 7.46 x 2.86 cm) | 36/ctn |
| <br><b>5 Compartments</b><br>(L x W): <b>A=</b> 1" x 2-7/8" (2.54 x 7.30 cm)      | <b>A155</b><br><b>T155</b>                                   | 6604CB<br>6688TE                     | <b>A-Series</b><br><b>T-Series</b>                                       | Styrene<br>TP              | 5-5/8" x 2-15/16" x 1-1/8"<br>(14.29 x 7.46 x 2.86 cm) | 36/ctn |
| <br><b>1 Compartment</b>                                                          | <b>3030-2</b> ◆                                              | 6730AA                               | <b>Precision</b>                                                         | SBMM                       | 5-5/8" x 3-5/8" x 1-1/8"<br>(14.29 x 9.21 x 2.86 cm)   | 36/ctn |
| <br><b>1 Compartment, Box has Lift-Off Lid (Non-Hinged)</b>                       | <b>A250</b>                                                  | 6648CB                               | <b>A-Series</b>                                                          | Styrene                    | 5-7/8" x 3-3/4" x 1-5/8"<br>(14.92 x 9.53 x 4.13 cm)   | 36/ctn |











\* Adding color to the resins effects the clarity of the finished product

For Customer Service Inquiries Call 1-800-344-5716

# COMPARTMENTED BOXES

Boxes 6-5/8" x 3-3/8" x 1-5/16" through 6-3/4" x 3-3/16" x 1-3/16"  
(16.83 x 8.57 x 3.33 cm) through (17.15 x 8.10 x 3.02 cm)

| BOX MATERIAL KEY               |                           |                                              |                                                                                                                                                                                                           |  | SYMBOL KEY |
|--------------------------------|---------------------------|----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  = Blue Diamond<br> = Special Order |  |            |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |                                                                                                                                                                                                           |  |            |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |                                                                                                                                                                                                           |  |            |










| Box Diagram                                                                                                                                                                                                        | Model Number                                                                                                                                                                                         | Stock Number                         | Family                                                                                                                                                                                                                                                                                                                                                                                       | Material                   | Dimensions (Inside, L x W x D)                           | Packed |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|----------------------------------------------------------|--------|
|                                                                                                                                    | T300                                                                                                                | 6715ID                               |  IDS                                                                                                                                                                                                                                                                                                        | TP                         | 6-5/8" x 3-3/8" x 1-5/16"<br>(16.83 x 8.57 x 3.33 cm)    | 12/ctn |
| 3 Compartments & 6 IDS Dividers (Ref. page 34) (L x W): A= 6-5/8" x 1-1/16" (16.83 x 2.70 cm)                                                                                                                      |                                                                                                                                                                                                      |                                      |                                                                                                                                                                                                                                                                                                                                                                                              |                            |                                                          |        |
|                                                                                                                                    | T2003                              | 6703TE                               |  Tuff Tainer                                                                                                                                                                                                                                                                                                | TP                         | 6-11/16" x 3-5/16" x 1-5/16"<br>(16.99 x 8.41 x 3.33 cm) | 12/ctn |
| 3 Compartments & 15 Removable Dividers (L x W): A= 6-11/16" x 1-1/16" (16.99 x 2.70 cm)                                                                                                                            |                                                                                                                                                                                                      |                                      |                                                                                                                                                                                                                                                                                                                                                                                              |                            |                                                          |        |
|                                                                                                                                    | A213-SL                                                                                                                                                                                              | 6627CS                               |  A-Series                                                                                                                                                                                                                                                                                                   | Styrene                    | 6-3/4" x 3-3/16" x 1/2"<br>(17.15 x 8.10 x 1.27 cm)      | 36/ctn |
| 10 Compartments (L x W): A= 1-1/2" x 1-5/8" (3.81 x 4.13 cm), B= 1-7/16" x 1-5/8" (3.65 x 4.13 cm), C= 1-5/16" x 1-5/8" (3.33 x 4.13 cm), D= 1-1/4" x 1-5/8" (3.18 x 4.13 cm), E= 1-1/8" x 1-5/8" (2.86 x 4.13 cm) |                                                                                                                                                                                                      |                                      |                                                                                                                                                                                                                                                                                                                                                                                              |                            |                                                          |        |
|                                                                                                                                    | A216-SL                                                                                                             | 6632CS                               |  A-Series                                                                                                                                                                                                                                                                                                   | Styrene                    | 6-3/4" x 3-3/16" x 1/2"<br>(17.15 x 8.10 x 1.27 cm)      | 36/ctn |
| 1 Compartment                                                                                                                                                                                                      |                                                                                                                                                                                                      |                                      |                                                                                                                                                                                                                                                                                                                                                                                              |                            |                                                          |        |
|                                                                                                                                   | A210-SL                                                                                                           | 6622CS                               |  A-Series                                                                                                                                                                                                                                                                                                 | Styrene                    | 6-3/4" x 3-3/16" x 1/2"<br>(17.15 x 8.10 x 1.27 cm)      | 36/ctn |
| 9 Compartments (L x W): A= 1-1/8" x 1-5/8" (2.86 x 4.13 cm), B= 1-1/8" x 3-3/8" (2.86 x 8.57 cm)                                                                                                                   |                                                                                                                                                                                                      |                                      |                                                                                                                                                                                                                                                                                                                                                                                              |                            |                                                          |        |
|                                                                                                                                  | A213                                                                                                                                                                                                 | 6621CM                               |  A-Series                                                                                                                                                                                                                                                                                                 | Styrene                    | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | 36/ctn |
| 10 Compartments (L x W): A= 1-1/2" x 1-5/8" (3.81 x 4.13 cm), B= 1-7/16" x 1-5/8" (3.65 x 4.13 cm), C= 1-5/16" x 1-5/8" (3.33 x 4.13 cm), D= 1-1/4" x 1-5/8" (3.18 x 4.13 cm), E= 1-1/8" x 1-5/8" (2.86 x 4.13 cm) |                                                                                                                                                                                                      |                                      |                                                                                                                                                                                                                                                                                                                                                                                              |                            |                                                          |        |
|                                                                                                                                  | A214                                                                                                                                                                                                 | 6628CB                               |  A-Series                                                                                                                                                                                                                                                                                                 | Styrene                    | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | 36/ctn |
| 2 Compartments (L x W): A= 3-5/16" x 3-1/4" (8.41 x 8.26 cm)                                                                                                                                                       |                                                                                                                                                                                                      |                                      |                                                                                                                                                                                                                                                                                                                                                                                              |                            |                                                          |        |
|                                                                                                                                  | A215<br>T215<br>K215 <br>M215  | 6630CB<br>6702TE<br>6630KB<br>6702TF |  A-Series<br> T-Series<br> K-Series<br> M-Series | Styrene<br>TP<br>SBC<br>YP | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | 36/ctn |
| 5 Compartments (L x W): A= 1-5/16" x 3-3/16" (3.33 x 8.10 cm)                                                                                                                                                      |                                                                                                                                                                                                      |                                      |                                                                                                                                                                                                                                                                                                                                                                                              |                            |                                                          |        |
|                                                                                                                                  | A210<br>T210 <br>K210 <br>M210 | 6622CB<br>6698TE<br>6622KB<br>6698TF |  A-Series<br> T-Series<br> K-Series<br> M-Series | Styrene<br>TP<br>SBC<br>YP | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | 36/ctn |
| 9 Compartments (L x W): A= 1-5/16" x 1-9/16" (3.33 x 3.97 cm), B= 1-1/8" x 3-3/16" (2.86 x 8.10 cm)                                                                                                                |                                                                                                                                                                                                      |                                      |                                                                                                                                                                                                                                                                                                                                                                                              |                            |                                                          |        |
|                                                                                                                                  | A219<br>T219<br>K219                                                                                              | 6636CB<br>6701TE<br>6636KB           |  A-Series<br> T-Series<br> K-Series                                                                                                 | Styrene<br>TP<br>SBC       | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)   | 36/ctn |
| 12 Compartments (L x W): A= 1-7/16" x 1-1/16" (3.65 x 2.70 cm)                                                                                                                                                     |                                                                                                                                                                                                      |                                      |                                                                                                                                                                                                                                                                                                                                                                                              |                            |                                                          |        |

\* Adding color to the resins effects the clarity of the finished product

Boxes 6-3/4" x 3-3/16" x 1-3/16" through 7" x 3-3/8" x 1-1/8"  
(17.15 x 8.10 x 3.02 cm) through (17.78 x 8.57 x 2.86 cm)

# COMPARTMENTED BOXES

| BOX MATERIAL KEY               |                           |                                              | SYMBOL KEY        |
|--------------------------------|---------------------------|----------------------------------------------|-------------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       | ◆ = Blue Diamond  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            | Ⓢ = Special Order |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |                   |

| Box Diagram                                                                                                                              | Model Number     | Stock Number     | Family               | Material       | Dimensions (Inside, L x W x D)                          | Packed  |
|------------------------------------------------------------------------------------------------------------------------------------------|------------------|------------------|----------------------|----------------|---------------------------------------------------------|---------|
|                                                         | A217             | 6634CB           | A-Series             | Styrene        | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)  | 36/ctn  |
| 7 Compartments (L x W): A= 1-5/16" x 1-5/8" (3.33 x 4.13 cm), B= 4" x 1-1/16" (10.16 x 2.70 cm)                                          |                  |                  |                      |                |                                                         |         |
|                                                         | A211 ◆           | 6624CB           | A-Series             | Styrene        | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)  | 36/ctn  |
| 6 Compartments (L x W): A= 1-1/16" x 3-3/16" (2.70 x 8.10 cm)                                                                            |                  |                  |                      |                |                                                         |         |
|                                                         | A216 ◆<br>K216   | 6632CB<br>6632KB | A-Series<br>K-Series | Styrene<br>SBC | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)  | 36/ctn  |
| 1 Compartment                                                                                                                            |                  |                  |                      |                |                                                         |         |
|                                                         | A212             | 6626CB           | A-Series             | Styrene        | 6-3/4" x 3-3/16" x 1-3/16"<br>(17.15 x 8.10 x 3.02 cm)) | 36/ctn  |
| 5 Compartments (L x W): A= 2-1/2" x 1-5/8" (6.35 x 4.13 cm), B= 1-5/8" x 3-1/4" (4.13 x 8.26 cm)                                         |                  |                  |                      |                |                                                         |         |
|                                                       | A701<br>K701 Ⓢ   | 6670CB<br>6670KB | A-Series<br>K-Series | Styrene<br>SBC | 6-7/8" x 2-1/16" x 1"<br>(17.46 x 5.24 x 2.54 cm)       | 36/ctn  |
| 1 Compartment                                                                                                                            |                  |                  |                      |                |                                                         |         |
|                                                       | V301 ◆<br>V301PT | 6142VB<br>6650VC | V-Series<br>V-Series | OP<br>SP       | 6-7/8" x 2-1/16" x 1"<br>(17.46 x 5.24 x 2.54 cm)       | 36/ctn  |
| 1 Compartment                                                                                                                            |                  |                  |                      |                |                                                         |         |
|                                                       | DB216            | 6732CD           | Diamondback          | Styrene        | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)        | 25/ctn  |
| 1 Compartment                                                                                                                            |                  |                  |                      |                |                                                         |         |
|                                                       | DB211            | 6724CD           | Diamondback          | Styrene        | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)        | 25/ctn  |
| 6 Compartments (L x W): A= 1-1/16" x 3-5/16" (2.70 x 8.41 cm)                                                                            |                  |                  |                      |                |                                                         |         |
|                                                       | DB219            | 6736CD           | Diamondback          | Styrene        | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)        | 225/ctn |
| 12 Compartments (L x W): A= 1-3/4" x 1-1/16" (4.45 x 2.70 cm)                                                                            |                  |                  |                      |                |                                                         |         |
|                                                       | DB210            | 6722CD           | Diamondback          | Styrene        | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)        | 25/ctn  |
| 9 Compartments (L x W): A= 1-3/8" x 1-5/8" (3.49 x 4.13 cm), B= 1-5/16" x 1-5/8" (3.33 x 4.13 cm), C= 1-5/16" x 3-5/16" (3.33 x 8.41 cm) |                  |                  |                      |                |                                                         |         |










\* Adding color to the resins effects the clarity of the finished product

For Customer Service Inquiries Call 1-800-344-5716

# COMPARTMENTED BOXES

Boxes 7" x 3-3/8" x 1-1/8" (17.78 x 8.57 x 2.86 cm) through 8" x 4" x 1-3/16" (20.32 x 10.16 x 3.02 cm)

| BOX MATERIAL KEY               |                           |                                              |                                                                                                                                                                                                           |  | SYMBOL KEY |
|--------------------------------|---------------------------|----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  = Blue Diamond<br> = Special Order |  |            |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |                                                                                                                                                                                                           |  |            |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |                                                                                                                                                                                                           |  |            |










| Box Diagram                                                                                                                                                                                                                                                          | Model Number                                                                                     | Stock Number     | Family                                                                                                                                                                                       | Material       | Dimensions (Inside, L x W x D)                         | Packed |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|--------------------------------------------------------|--------|
|  <p><b>10 Compartments</b><br/>(L x W): <b>A</b>= 1-5/16" x 1-5/8" (3.33 x 4.13 cm)</p>                                                                                              | DB213           | 6721CD           |  Diamondback                                                                                                | Styrene        | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)       | 25/ctn |
|  <p><b>7 Compartments</b><br/>(L x W): <b>A</b>= 1-5/16" x 1-5/8" (3.33 x 4.13 cm), <b>B</b>= 4-1/8" x 1-1/8" (10.48 x 2.86 cm)</p>                                                  | DB217                                                                                            | 6734CD           |  Diamondback                                                                                                | Styrene        | 7" x 3-3/8" x 1-1/8"<br>(17.78 x 8.57 x 2.86 cm)       | 25/ctn |
|  <p><b>17 Compartments</b><br/>(L x W): <b>A</b>= 1-1/4" x 7/8" (3.18 x 2.22 cm), <b>B</b>= 1-3/16" x 4" (3.02 x 10.16 cm)</p>                                                       | 5126CL                                                                                           | 6220MT           |  Mighty-Tuff                                                                                                | TCP            | 7" x 4" x 1-1/16"<br>(17.78 x 10.16 x 2.70 cm)         | 12/ctn |
|  <p><b>11 Compartments</b><br/>(L x W): <b>A</b>= 1-3/16" x 4" (3.02 x 10.16 cm), <b>B</b>= 1-1/4" x 2" (3.18 x 5.08 cm), <b>C</b>= 1-1/4" x 7/8" (3.18 x 2.22 cm)</p>              | 5127CL                                                                                           | 6222MT           |  Mighty-Tuff                                                                                               | TCP            | 7" x 4" x 1-1/16"<br>(17.78 x 10.16 x 2.70 cm)         | 12/ctn |
|  <p><b>6 Compartments</b><br/>(L x W): <b>A</b>= 1-3/16" x 4" (3.02 x 10.16 cm)</p>                                                                                                | 5128CL                                                                                           | 6224MT           |  Mighty-Tuff                                                                                              | TCP            | 7" x 4" x 1-1/16"<br>(17.78 x 10.16 x 2.70 cm)         | 12/ctn |
|  <p><b>1 Compartment</b></p>                                                                                                                                                       | A401                                                                                             | 6650CB           |  A-Series                                                                                                 | Styrene        | 7-1/8" x 5-1/8" x 1-9/16"<br>(18.10 x 13.02 x 3.97 cm) | 36/ctn |
|  <p><b>12 Compartments</b><br/>(L x W): <b>A</b>= 2-5/8" x 1-5/16" (6.67 x 3.33 cm), <b>B</b>= 1-5/16" x 1-1/4" (3.33 x 3.18 cm), <b>C</b>= 2-5/8" x 2-11/16" (6.67 x 6.83 cm)</p> | A204                                                                                             | 6614CB           |  A-Series                                                                                                 | Styrene        | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)         | 24/ctn |
|  <p><b>1 Compartment</b></p>                                                                                                                                                       | A206<br>K206  | 6616CB<br>6616KB |  A-Series<br> K-Series | Styrene<br>SBC | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)         | 24/ctn |
|  <p><b>9 Compartments</b><br/>(L x W): <b>A</b>= 2-5/8" x 1-5/16" (6.67 x 3.33 cm), <b>B</b>= 1-1/4" x 1-5/16" (3.18 x 3.33 cm), <b>C</b>= 4" x 4" (10.16 x 10.16 cm)</p>          | A209                                                                                             | 6620CB           |  A-Series                                                                                                 | Styrene        | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)         | 24/ctn |

\* Adding color to the resins effects the clarity of the finished product

Boxes 8" x 4" x 1-3/16" through 8-7/16" x 4-1/4" x 1-3/16"  
(20.32 x 10.16 x 3.02 cm) through (21.43 x 10.80 x 3.02 cm)

# COMPARTMENTED BOXES

| BOX MATERIAL KEY               |                           |                                              | SYMBOL KEY        |
|--------------------------------|---------------------------|----------------------------------------------|-------------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       | ◆ = Blue Diamond  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            | Ⓢ = Special Order |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |                   |

| Box Diagram                                                                                                                                                                                                                                                         | Model Number     | Stock Number | Family             | Material | Dimensions (Inside, L x W x D)                          | Packed |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|--------------|--------------------|----------|---------------------------------------------------------|--------|
|  <p><b>18 Compartments</b><br/>(L x W): <b>A</b>= 1-1/4" x 1-1/4" (3.18 x 3.18 cm)</p>                                                                                             | <b>A200</b> ◆    | 6608CB       | <b>A-Series</b>    | Styrene  | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)          | 24/ctn |
|                                                                                                                                                                                                                                                                     | <b>T200</b>      | 6690TE       | <b>T-Series</b>    | TP       |                                                         |        |
|                                                                                                                                                                                                                                                                     | <b>K200</b> ◆    | 6608KB       | <b>K-Series</b>    | SBC      |                                                         |        |
|                                                                                                                                                                                                                                                                     | <b>M200</b> Ⓢ    | 6690TF       | <b>M-Series</b>    | YP       |                                                         |        |
|  <p><b>12 Compartments</b><br/>(L x W): <b>A</b>= 1-1/4" x 1-15/16" (3.18 x 4.92 cm)</p>                                                                                           | <b>A208</b> ◆    | 6618CB       | <b>A-Series</b>    | Styrene  | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)          | 24/ctn |
|                                                                                                                                                                                                                                                                     | <b>K208</b> ◆    | 6618KB       | <b>K-Series</b>    | SBC      |                                                         |        |
|                                                                                                                                                                                                                                                                     | <b>M208</b>      | 6696TF       | <b>M-Series</b>    | YP       |                                                         |        |
|  <p><b>12 Compartments</b> (L x W): <b>A</b>= 1-5/16" x 1-5/16" (3.33 x 3.33 cm), <b>B</b>= 1-5/16" x 4" (3.33 x 10.16 cm), <b>C</b>= 1-5/16" x 2" (3.33 x 5.08 cm)</p>            | <b>A201</b>      | 6610CB       | <b>A-Series</b>    | Styrene  | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)          | 24/ctn |
|                                                                                                                                                                                                                                                                     | <b>T201</b>      | 6692TE       | <b>T-Series</b>    | TP       |                                                         |        |
|                                                                                                                                                                                                                                                                     | <b>K201</b> ◆    | 6610KB       | <b>K-Series</b>    | SBC      |                                                         |        |
|                                                                                                                                                                                                                                                                     | <b>M201</b>      | 6692TF       | <b>M-Series</b>    | YP       |                                                         |        |
|  <p><b>6 Compartments</b><br/>(L x W): <b>A</b>= 1-1/4" x 4" (3.18 x 10.16 cm)</p>                                                                                               | <b>A203</b>      | 6612CB       | <b>A-Series</b>    | Styrene  | 8" x 4" x 1-3/16"<br>(20.32 x 10.16 x 3.02 cm)          | 24/ctn |
|                                                                                                                                                                                                                                                                     | <b>T203</b> ◆    | 6694TE       | <b>T-Series</b>    | TP       |                                                         |        |
|                                                                                                                                                                                                                                                                     | <b>K203</b> ◆    | 6612KB       | <b>K-Series</b>    | SBC      |                                                         |        |
|                                                                                                                                                                                                                                                                     | <b>M203</b>      | 6694TF       | <b>M-Series</b>    | YP       |                                                         |        |
|  <p><b>1 Compartment</b></p>                                                                                                                                                     | <b>V401</b> ◆    | 6152VB       | <b>V-Series</b>    | SP       | 8-1/8" x 4-1/8" x 1-3/16"<br>(20.64 x 10.48 x 3.02 cm)  | 24/ctn |
|  <p><b>2 Compartments</b> (L x W): <b>A</b>= 8-1/4" x 1-1/4" (20.96 x 10.16 cm)</p>                                                                                              | <b>V402-2</b> Ⓢ  | 6655VA       | <b>V-Series</b>    | SP       | 8-1/8" x 4-1/8" x 1-3/16"<br>(20.64 x 10.48 x 3.02 cm)  | 24/ctn |
|  <p><b>1 Compartment</b></p>                                                                                                                                                     | <b>V401D-2</b> ◆ | 6654DV       | <b>V-Series</b>    | SP       | 8-1/8" x 4-1/8" x 2-5/8"<br>(20.64 x 10.48 x 6.67 cm)   | 24/ctn |
|  <p><b>12 Compartments</b> (L x W): <b>A</b>= 1-5/16" x 1-5/16" (3.33 x 3.33 cm), <b>B</b>= 1-5/16" x 4-1/4" (3.33 x 10.80 cm), <b>C</b>= 1-5/16" x 2-1/16" (3.33 x 5.24 cm)</p> | <b>DB201</b>     | 6710CD       | <b>Diamondback</b> | Styrene  | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm) | 24/ctn |
|                                                                                                                                                                                                                                                                     | <b>DB203</b>     | 6712CD       | <b>Diamondback</b> | Styrene  |                                                         |        |
|  <p><b>6 Compartments</b> (L x W): <b>A</b>= 1-3/8" x 4-1/4" (3.49 x 10.80 cm), <b>B</b>= 1-5/16" x 4-1/4" (3.33 x 10.80 cm)</p>                                                 |                  |              |                    |          |                                                         |        |









\* Adding color to the resins effects the clarity of the finished product

For Customer Service Inquiries Call 1-800-344-5716

# COMPARTMENTED BOXES

Boxes 8-7/16" x 4-1/4" x 1-3/16" through 10" x 4-1/4" x 1-1/2"  
(21.43 x 10.80 x 3.02 cm) through (25.40 x 10.80 x 3.81 cm)










| BOX MATERIAL KEY               |                           |                                              |                                                                                                                                                                                                           |  | SYMBOL KEY |
|--------------------------------|---------------------------|----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  = Blue Diamond<br> = Special Order |  |            |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |                                                                                                                                                                                                           |  |            |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |                                                                                                                                                                                                           |  |            |

| Box Diagram                                                                                                                                                                                                                                                   | Model Number                                                                                                         | Stock Number     | Family                                                                                                                                                                                       | Material       | Dimensions (Inside, L x W x D)                          | Packed           |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------|------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|---------------------------------------------------------|------------------|
| <br><b>12 Compartments</b><br>(L x W): <b>A</b> = 1-3/8" x 2-1/16" (3.49 x 5.24 cm)                                                                                           | DB208                               | 6718CD           |  Diamondback                                                                                                | Styrene        | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm) | 48/ctn           |
| <br><b>18 Compartments</b><br>(L x W): <b>A</b> = 1-3/8" x 1-3/8" (3.49 x 3.49 cm)                                                                                            | DB200                               | 6708CD           |  Diamondback                                                                                                | Styrene        | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm) | 24/ctn           |
| <br><b>1 Compartment</b>                                                                                                                                                      | DB206                               | 6716CD           |  Diamondback                                                                                                | Styrene        | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm) | 24/ctn           |
| <br><b>12 Compartments</b> (L x W): <b>A</b> = 2-3/4" x 1-3/8" (6.99 x 3.49 cm),<br><b>B</b> = 1-3/8" x 1-3/8" (3.49 x 3.49 cm), <b>C</b> = 2-3/4" x 2-3/4" (6.99 x 6.99 cm) | DB204                                                                                                                | 6714CD           |  Diamondback                                                                                                | Styrene        | 8-7/16" x 4-1/4" x 1-3/16"<br>(21.43 x 10.80 x 3.02 cm) | 24/ctn           |
| <br><b>1 Compartment</b>                                                                                                                                                    | 4040-2                            | 6740AA           |  Precision                                                                                                | SBMM           | 8-3/4" x 4-5/16" x 1-1/4"<br>(22.23 x 10.95 x 3.18 cm)  | 24/ctn           |
| <br><b>3 Compartments &amp; 15 Removable Dividers</b><br>(L x W): <b>A</b> = 8-7/8" x 1-3/8" (22.54 x 3.49 cm)                                                              | T3003                             | 6707TE           |  Tuff Tainer                                                                                              | TP             | 8-7/8" x 4-1/8" x 1-3/16"<br>(22.54 x 10.48 x 3.02 cm)  | 12/ctn           |
| <br><b>36 Compartments</b><br>(L x W): <b>A</b> = 1-9/16" x 1-1/16" (3.97 x 2.70 cm)                                                                                        | <b>A166-36</b><br><b>K166-36</b>  | 6606CB<br>6606KB |  A-Series<br> K-Series | Styrene<br>SBC | 9-5/8" x 6-9/16" x 1-1/2"<br>(24.45 x 16.69 x 3.81 cm)  | 12/ctn<br>24/ctn |
| <br><b>1 Compartment</b>                                                                                                                                                    | V501                              | 6160VB           |  V-Series                                                                                                 | SP             | 10" x 4-1/4" x 1-1/2"<br>(25.40 x 10.80 x 3.81 cm)      | 24/ctn           |
| <br><b>6 Compartments</b><br>(L x W): <b>A</b> = 1-5/8" x 4-1/4" (4.13 x 10.80 cm)                                                                                          | V506-2                            | 6660VA           |  V-Series                                                                                                 | SP             | 10" x 4-1/4" x 1-1/2"<br>(25.40 x 10.80 x 3.81 cm)      | 24/ctn           |

\* Adding color to the resins effects the clarity of the finished product

Boxes 10-1/2" x 6-3/16" x 1-9/16" through 10-1/2" x 6-3/16" x 1-9/16"  
(26.67 x 15.72 x 33.97 cm) through (26.67 x 15.72 x 3.97 cm)

# COMPARTMENTED BOXES

| BOX MATERIAL KEY                                                                                                                             |                                                                                                                                            |                           |                                                                                              |                                              |                                                          | SYMBOL KEY                                                                                                                                                                                                |
|----------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|----------------------------------------------------------------------------------------------|----------------------------------------------|----------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| TP = Translucent Polypropylene                                                                                                               |                                                                                                                                            | YP = Yellow Polypropylene |                                                                                              | TCP = Transparent Cellulose Propionate       |                                                          |  = Blue Diamond<br> = Special Order |
| SP = Taupe Polypropylene                                                                                                                     |                                                                                                                                            | WP = White Polypropylene  |                                                                                              | SBC = Styrene-Butadiene Copolymer            |                                                          |                                                                                                                                                                                                           |
| OP = Orange Polypropylene                                                                                                                    |                                                                                                                                            |                           |                                                                                              | SBMM = Styrene Butadiene Methyl Methacrylate |                                                          |                                                                                                                                                                                                           |
| Box Diagram                                                                                                                                  | Model Number                                                                                                                               | Stock Number              | Family                                                                                       | Material                                     | Dimensions (Inside, L x W x D)                           | Packed                                                                                                                                                                                                    |
|                                                             | T616R                                                                                                                                      | 6713TE                    |  T-Series   | TP                                           | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 24/ctn                                                                                                                                                                                                    |
|                                                                                                                                              | K616R                                                     | 6665KB                    |  K-Series   | SBC                                          |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | M616R                                                     | 6713TF                    |  M-Series   | YP                                           |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | 4 Compartments & 12 Removable Dividers<br>(L x W): A= 10-3/8" x 1-1/2" (26.35 x 3.81 cm)                                                   |                           |                                                                                              |                                              |                                                          |                                                                                                                                                                                                           |
|                                                             | A623                                                      | 6668CB                    |  A-Series   | Styrene                                      | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 24/ctn                                                                                                                                                                                                    |
|                                                                                                                                              | T623                                                                                                                                       | 6715TE                    |  T-Series   | TP                                           |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | K623                                                      | 6668KB                    |  K-Series   | SBC                                          |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | M623                                                                                                                                       | 6716TF                    |  M-Series   | YP                                           |                                                          |                                                                                                                                                                                                           |
| 13 Compartments<br>(L x W): A= 10-3/8" x 2-5/8" (26.35 x 6.67 cm), B= 1-11/16" x 1-5/16" (4.29 x 3.33 cm), C= 1-11/16" x 2" (4.29 x 5.08 cm) |                                                                                                                                            |                           |                                                                                              |                                              |                                                          |                                                                                                                                                                                                           |
|                                                             | A612                                                      | 6662CB                    |  A-Series   | Styrene                                      | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 24/ctn                                                                                                                                                                                                    |
|                                                                                                                                              | T612                                                                                                                                       | 6712TE                    |  T-Series   | TP                                           |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | M612                                                                                                                                       | 6712TF                    |  M-Series   | YP                                           |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | 12 Compartments<br>(L x W): A= 1-11/16" x 2" (4.29 x 5.08 cm), B= 1-11/16" x 4-1/8" (4.29 x 10.48 cm)                                      |                           |                                                                                              |                                              |                                                          |                                                                                                                                                                                                           |
|                                                            | A602                                                                                                                                       | 6654CB                    |  A-Series   | Styrene                                      | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 24/ctn                                                                                                                                                                                                    |
|                                                                                                                                              | T602                                                                                                                                       | 6708TE                    |  T-Series  | TP                                           |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | K602                                                                                                                                       | 6654KB                    |  K-Series | SBC                                          |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | M602                                                                                                                                       | 6708TF                    |  M-Series | YP                                           |                                                          |                                                                                                                                                                                                           |
| 12 Compartments<br>(L x W): A= 1-11/16" x 3-1/16" (4.29 x 7.78 cm)                                                                           |                                                                                                                                            |                           |                                                                                              |                                              |                                                          |                                                                                                                                                                                                           |
|                                                           | A606                                                                                                                                       | 6658CB                    |  A-Series | Styrene                                      | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 24/ctn                                                                                                                                                                                                    |
|                                                                                                                                              | T606                                                    | 6710TE                    |  T-Series | TP                                           |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | K606                                                    | 6658KB                    |  K-Series | SBC                                          |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | M606                                                                                                                                       | 6710TF                    |  M-Series | YP                                           |                                                          |                                                                                                                                                                                                           |
| 6 Compartments<br>(L x W): A= 1-11/16" x 6-1/4" (4.29 x 15.88 cm)                                                                            |                                                                                                                                            |                           |                                                                                              |                                              |                                                          |                                                                                                                                                                                                           |
|                                                           | A613                                                                                                                                       | 6664CB                    |  A-Series | Styrene                                      | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 24/ctn                                                                                                                                                                                                    |
|                                                                                                                                              | 13 Compartments (L x W): A= 1-11/16" x 2" (4.29 x 5.08 cm), B= 1-11/16" x 4-1/16" (4.29 x 10.32 cm), C= 3-1/2" x 4-1/16" (8.89 x 10.32 cm) |                           |                                                                                              |                                              |                                                          |                                                                                                                                                                                                           |
|                                                           | A607                                                    | 6660CB                    |  A-Series | Styrene                                      | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 24/ctn                                                                                                                                                                                                    |
|                                                                                                                                              | K607                                                    | 6660KB                    |  K-Series | SBC                                          |                                                          |                                                                                                                                                                                                           |
| 7 Compartments<br>(L x W): A= 1-11/16" x 2" (4.29 x 5.08 cm), B= 10-1/2" x 4-1/16" (26.67 x 10.32 cm)                                        |                                                                                                                                            |                           |                                                                                              |                                              |                                                          |                                                                                                                                                                                                           |
|                                                           | T600                                                    | 6719ID                    |  IDS      | TP                                           | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 6/ctn                                                                                                                                                                                                     |
| 6 Compartments & 10 IDS Dividers (Ref. page 34) (L x W): A= 1-11/16" x 6-3/16" (4.29 x 15.72 cm)                                             |                                                                                                                                            |                           |                                                                                              |                                              |                                                          |                                                                                                                                                                                                           |
|                                                           | A601                                                                                                                                       | 6652CB                    |  A-Series | Styrene                                      | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 24/ctn                                                                                                                                                                                                    |
|                                                                                                                                              | K601                                                                                                                                       | 6652KB                    |  K-Series | SBC                                          |                                                          |                                                                                                                                                                                                           |
|                                                                                                                                              | C601                                                                                                                                       | 6707TC                    | --                                                                                           | Conductive                                   |                                                          |                                                                                                                                                                                                           |
| 1 Compartment                                                                                                                                |                                                                                                                                            |                           |                                                                                              |                                              |                                                          |                                                                                                                                                                                                           |








\* Adding color to the resins effects the clarity of the finished product

For Customer Service Inquiries Call 1-800-344-5716

# COMPARTMENTED BOXES

Boxes 10-1/2" x 6-3/16" x 1-9/16" through 10-5/8" x 6-5/8" x 1-9/16"  
(26.67 x 15.72 x 3.97 cm) through (26.99 x 16.83 x 3.97 cm)





| BOX MATERIAL KEY               |                           |                                              |  |  | SYMBOL KEY        |
|--------------------------------|---------------------------|----------------------------------------------|--|--|-------------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  |  | ⬢ = Blue Diamond  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |  |  | Ⓢ = Special Order |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |  |  |                   |

| Box Diagram                                                                                                                                                                                                                                                        | Model Number | Stock Number | Family        | Material   | Dimensions (Inside, L x W x D)                           | Packed |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|--------------|---------------|------------|----------------------------------------------------------|--------|
|  <p><b>18 Compartments</b><br/>(L x W): A= 1-3/4" x 2-1/16" (4.45 x 5.24 cm)</p>                                                                                                   | A618         | 6666CB       | ■ A-Series    | Styrene    | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 24/ctn |
|                                                                                                                                                                                                                                                                    | T618 ⬢       | 6714TE       | ■ T-Series    | TP         |                                                          |        |
|                                                                                                                                                                                                                                                                    | K618 ⬢       | 6666KB       | ■ K-Series    | SBC        |                                                          |        |
|                                                                                                                                                                                                                                                                    | M618         | 6714TF       | ■ M-Series    | YP         |                                                          |        |
|                                                                                                                                                                                                                                                                    | C618         | 6714TC       | --            | Conductive |                                                          |        |
|  <p><b>3 Compartments</b> (L x W): A= 10-1/2" x 2-1/16" (26.67 x 5.24 cm)</p>                                                                                                      | A603 Ⓢ       | 6656CB       | ■ A-Series    | Styrene    | 10-1/2" x 6-3/16" x 1-9/16"<br>(26.67 x 15.72 x 3.97 cm) | 24/ctn |
|  <p><b>12 Compartments</b><br/>(L x W): A= 1-11/16" x 2" (4.29 x 5.08 cm), B= 1-11/16" x 4-1/8" (4.29 x 10.48 cm)</p>                                                              | A612D Ⓢ      | 6662DB       | ■ A-Series    | Styrene    | 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)  | 24/ctn |
|                                                                                                                                                                                                                                                                    | T612D Ⓢ      | 6713DB       | ■ T-Series    | TP         |                                                          |        |
|                                                                                                                                                                                                                                                                    | K612D Ⓢ      | 6663DK       | ■ K-Series    | SBC        |                                                          |        |
|                                                                                                                                                                                                                                                                    | M612D Ⓢ      | 6712DB       | ■ M-Series    | YP         |                                                          |        |
|  <p><b>18 Compartments</b><br/>(L x W): A= 1-3/4" x 2-1/16" (4.45 x 5.24 cm)</p>                                                                                                  | A618D Ⓢ      | 6666DB       | ■ A-Series    | Styrene    | 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)  | 24/ctn |
|                                                                                                                                                                                                                                                                    | T618D Ⓢ      | 6715DB       | ■ T-Series    | TP         |                                                          |        |
|                                                                                                                                                                                                                                                                    | K618D Ⓢ      | 6666DK       | ■ K-Series    | SBC        |                                                          |        |
|                                                                                                                                                                                                                                                                    | M618D Ⓢ      | 6714DB       | ■ M-Series    | YP         |                                                          |        |
|  <p><b>6 Compartments</b><br/>(L x W): A= 1-11/16" x 6-1/4" (4.29 x 15.88 cm)</p>                                                                                                | A606D Ⓢ      | 6658DB       | ■ A-Series    | Styrene    | 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)  | 24/ctn |
|                                                                                                                                                                                                                                                                    | T606D ⬢      | 6711DB       | ■ T-Series    | TP         |                                                          |        |
|                                                                                                                                                                                                                                                                    | K606D Ⓢ      | 6658DK       | ■ K-Series    | SBC        |                                                          |        |
|                                                                                                                                                                                                                                                                    | M606D Ⓢ      | 6710DB       | ■ M-Series    | YP         |                                                          |        |
|  <p><b>1 Compartment</b></p>                                                                                                                                                     | A601D Ⓢ      | 6652DB       | ■ A-Series    | Styrene    | 10-1/2" x 6-3/16" x 2-1/4"<br>(26.67 x 15.72 x 5.72 cm)  | 24/ctn |
|                                                                                                                                                                                                                                                                    | K601D Ⓢ      | 6652DK       | ■ K-Series    | SBC        |                                                          |        |
|  <p><b>24 Compartments</b> (L x W): A= 1-11/16" x 2" (4.29 x 5.08 cm), Box has Sliding Lid (Non-Hinged)</p>                                                                      | A924-2       | 6684CB       | ■ A-Series    | Styrene    | 10-9/16" x 8-1/4" x 1-9/16"<br>(26.83 x 20.96 x 3.97 cm) | 10/ctn |
|  <p><b>6 Compartments, Black Mechanical Latches (Ref. page 13) &amp; 12 Removable Dividers</b> (L x W): A= 1-11/16" x 6-1/4" (4.29 x 15.87 cm)</p>                               | T4007 ⬢      | 6747TE       | ■ Tuff Tainer | TP         | 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)  | 6/ctn  |
|  <p><b>6 Compartments, Silver Mechanical Latches (Ref. pg 13) &amp; 12 Removable Tarnish Inhibitor Dividers (Ref. pg 34)</b> (L x W): A= 1-11/16" x 6-1/4" (4.29 x 15.87 cm)</p> | T4007AT      | 6748TE       | ■ Tuff Tainer | TP         | 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)  | 6/ctn  |

Boxes 10-5/8" x 6-5/8" x 1-9/16" through 11-15/16" x 5-15/16" x 1-7/16"  
(26.99 x 16.83 x 3.97 cm) through (30.32 x 15.08 x 3.65 cm)

# COMPARTMENTED BOXES

| BOX MATERIAL KEY               |                           |                                              | SYMBOL KEY        |
|--------------------------------|---------------------------|----------------------------------------------|-------------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       | ◆ = Blue Diamond  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            | Ⓢ = Special Order |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |                   |

| Box Diagram                                                                                                                                                                                                                      | Model Number | Stock Number | Family        | Material | Dimensions (Inside, L x W x D)                              | Packed |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|--------------|---------------|----------|-------------------------------------------------------------|--------|
|                                                                                                                                                 | T4007E ◆     | 6746TE       | ■ Tuff Tainer | TP       | 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)     | 6/ctn  |
| 6 Compartments, Integral Latches (Ref. page 13) & 12 Removable Dividers<br>(L x W): A= 1-11/16" x 6-1/4" (4.29 x 15.87 cm)                                                                                                       |              |              |               |          |                                                             |        |
|                                                                                                                                                 | T4000        | 6734TE       | ■ Tuff Tainer | TP       | 10-5/8" x 6-5/8" x 1-9/16"<br>(26.99 x 16.83 x 3.97 cm)     | 6/ctn  |
| 1 Compartment                                                                                                                                                                                                                    |              |              |               |          |                                                             |        |
|                                                                                                                                                 | DB606        | 6758CD       | ■ Diamondback | Styrene  | 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | 12/ctn |
| 6 Compartments<br>(L x W): A= 1-3/4" x 6-3/8" (4.45 x 16.19 cm)                                                                                                                                                                  |              |              |               |          |                                                             |        |
|                                                                                                                                                 | DB613 ◆      | 6764CD       | ■ Diamondback | Styrene  | 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | 12/ctn |
| 13 Compartments<br>(L x W): A= 1-7/8" x 2-1/16" (4.76 x 5.24 cm), B= 1-3/4" x 4-1/8" (4.45 x 10.48 cm), C= 3-9/16" x 4-1/8" (9.05 x 10.48 cm)                                                                                    |              |              |               |          |                                                             |        |
|                                                                                                                                               | DB601 Ⓢ      | 6752CD       | ■ Diamondback | Styrene  | 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | 12/ctn |
| 1 Compartment                                                                                                                                                                                                                    |              |              |               |          |                                                             |        |
|                                                                                                                                               | DB618        | 6766CD       | ■ Diamondback | Styrene  | 11" x 6-3/8" x 1-9/16"<br>(27.94 x 16.19 x 3.97 cm)         | 12/ctn |
| 18 Compartments<br>(L x W): A= 1-3/4" x 2-1/16" (4.45 x 5.24 cm)                                                                                                                                                                 |              |              |               |          |                                                             |        |
|                                                                                                                                               | 5129-1       | 6789CH       | ■ Mighty-Tuff | TCP      | 11-15/16" x 5-15/16" x 1-7/16"<br>(30.32 x 15.08 x 3.65 cm) | 6/ctn  |
| 1 Compartment                                                                                                                                                                                                                    |              |              |               |          |                                                             |        |
|                                                                                                                                               | 5129CL       | 6226MT       | ■ Mighty-Tuff | TCP      | 11-15/16" x 5-15/16" x 1-7/16"<br>(30.32 x 15.08 x 3.65 cm) | 6/ctn  |
| 24 Compartments<br>(L x W): A= 1-7/16" x 1-7/8" (3.65 x 4.76 cm)                                                                                                                                                                 |              |              |               |          |                                                             |        |
|                                                                                                                                               | 5130CL       | 6228MT       | ■ Mighty-Tuff | TCP      | 11-15/16" x 5-15/16" x 1-7/16"<br>(30.32 x 15.08 x 3.65 cm) | 6/ctn  |
| 6 Compartments<br>(L x W): A= 1-7/16" x 3-15/16" (3.65 x 10.00 cm), B= 8-7/8" x 1-7/8" (22.54 x 4.76 cm), C= 1-7/16" x 1-7/8" (3.65 x 4.76 cm),<br>D= 10-3/8" x 1-7/8" (26.35 x 4.76 cm), E= 5-15/16" x 1-7/8" (15.08 x 4.76 cm) |              |              |               |          |                                                             |        |










\* Adding color to the resins effects the clarity of the finished product

For Customer Service Inquiries Call 1-800-344-5716

# COMPARTMENTED BOXES

Boxes 12-3/4" x 8-1/2" x 2-1/8" through 13-1/8" x 8-7/8" x 1-15/16"  
(32.39 x 21.59 x 5.40 cm) through (33.34 x 22.54 x 4.92 cm)

| BOX MATERIAL KEY               |                           |                                              |  |  | SYMBOL KEY        |
|--------------------------------|---------------------------|----------------------------------------------|--|--|-------------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       |  |  | ⬠ = Blue Diamond  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            |  |  | Ⓢ = Special Order |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |  |  |                   |







| Box Diagram                                                                                                                                                                                                                     | Model Number                             | Stock Number                                   | Family                                                     | Material                                 | Dimensions (Inside, L x W x D)                           | Packed |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------|------------------------------------------------|------------------------------------------------------------|------------------------------------------|----------------------------------------------------------|--------|
| <br>1 Compartment                                                                                                                               | A801<br>K801 ⬠<br>C801                   | 6672CB<br>6672KB<br>6734TC                     | ■ A-Series<br>■ K-Series<br>--                             | Styrene<br>SBC<br>Conductive             | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)   | 12/ctn |
| <br>12 Compartments<br>(L x W): A= 2-1/16" x 4-3/16" (5.24 x 12.22 cm)                                                                          | A812<br>K812<br>M812                     | 6676CB<br>6676KB<br>6722TF                     | ■ A-Series<br>■ K-Series<br>■ M-Series                     | Styrene<br>SBC<br>YP                     | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)   | 12/ctn |
| <br>24 Compartments<br>(L x W): A= 2-1/16" x 2-1/16" (5.24 x 5.24 cm)                                                                           | A824<br>T824 ⬠<br>K824 ⬠<br>M824<br>C824 | 6680CB<br>6726TE<br>6680KB<br>6726TF<br>6726TC | ■ A-Series<br>■ T-Series<br>■ K-Series<br>■ M-Series<br>-- | Styrene<br>TP<br>SBC<br>YP<br>Conductive | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)   | 12/ctn |
| <br>18 Compartments<br>(L x W): A= 2-1/16" x 2-1/16" (5.24 x 5.24 cm), B= 2-1/16" x 4-3/16" (5.24 x 12.22 cm)                                  | A818 Ⓢ<br>K818<br>M818                   | 6678CB<br>6678KB<br>6724TF                     | ■ A-Series<br>■ K-Series<br>■ M-Series                     | Styrene<br>SBC<br>YP                     | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)   | 12/ctn |
| <br>6 Compartments<br>(L x W): A= 2-1/16" x 8-1/2" (5.24 x 21.59 cm)                                                                          | A806 Ⓢ<br>T806 ⬠<br>K806<br>M806         | 6674CB<br>6718TE<br>6674KB<br>6718TF           | ■ A-Series<br>■ T-Series<br>■ K-Series<br>■ M-Series       | Styrene<br>TP<br>SBC<br>YP               | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)   | 12/ctn |
| <br>8 Compartments<br>(L x W): A= 2-1/16" x 8-1/2" (5.24 x 21.59 cm), B= 2-1/16" x 4-1/8" (5.24 x 10.48 cm), C= 2-1/16" x 2" (5.24 x 5.08 cm) | M808 Ⓢ                                   | 6720TF                                         | ■ M-Series                                                 | YP                                       | 12-3/4" x 8-1/2" x 2-1/8"<br>(32.39 x 21.59 x 5.40 cm)   | 12/ctn |
| <br>1 Compartment                                                                                                                             | T901 Ⓢ                                   | 6727ID                                         | ■ T-Series                                                 | TP                                       | 13-1/8" x 8-7/8" x 1-15/16"<br>(33.34 x 22.54 x 4.92 cm) | 6/ctn  |
| <br>4 Compartments, with Handle & 16 IDS Dividers (Ref. page 13)<br>(L x W): A= 13-1/8" x 2-1/8" (33.34 x 5.40 cm)                            | 999-2                                    | 6726ID                                         | ■ IDS                                                      | TP                                       | 13-1/8" x 8-7/8" x 1-15/16"<br>(33.34 x 22.54 x 4.92 cm) | 6/ctn  |
| <br>4 Compartments & 16 IDS Dividers (Ref. page 13) (L x W): A= 13-1/8" x 2-1/8" (33.34 x 5.40 cm)                                            | T900 ⬠                                   | 6725ID                                         | ■ IDS                                                      | TP                                       | 13-1/8" x 8-7/8" x 1-15/16"<br>(33.34 x 22.54 x 4.92 cm) | 6/ctn  |

\* Adding color to the resins effects the clarity of the finished product

Boxes 13-1/2" x 5-3/4" x 2" through 17" x 7-1/8" x 2"  
(34.29 x 14.61 x 5.08 cm) through (43.18 x 18.10 x 5.08 cm)

# COMPARTMENTED BOXES

| BOX MATERIAL KEY               |                           |                                              | SYMBOL KEY        |
|--------------------------------|---------------------------|----------------------------------------------|-------------------|
| TP = Translucent Polypropylene | YP = Yellow Polypropylene | TCP = Transparent Cellulose Propionate       | ◆ = Blue Diamond  |
| SP = Taupe Polypropylene       | WP = White Polypropylene  | SBC = Styrene-Butadiene Copolymer            | Ⓢ = Special Order |
| OP = Orange Polypropylene      |                           | SBMM = Styrene Butadiene Methyl Methacrylate |                   |

| Box Diagram                                                                                                                                                                                                                                                                                       | Model Number | Stock Number | Family      | Material | Dimensions (Inside, L x W x D)                            | Packed |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|--------------|-------------|----------|-----------------------------------------------------------|--------|
| <br>1 Compartment                                                                                                                                                                                                | V601 ◆       | 6667VB       | V-Series    | SP       | 13-1/2" x 5-3/4" x 2"<br>(34.29 x 14.61 x 5.08 cm)        | 12/ctn |
| <br>4 Compartments, Black Mechanical Latches (Ref. page 13) & 20 Removable Dividers<br>(L x W): A= 13-11/16" x 2" (34.77 x 5.08 cm), B= 13-11/16" x 1-11/16" (34.77 x 4.29 cm)                                   | T5007 ◆      | 6757TE       | Tuff Tainer | TP       | 13-11/16" x 8-3/16" x 1-3/4"<br>(34.77 x 20.80 x 4.45 cm) | 6/ctn  |
| <br>4 Compartments, Silver Mechanical Latches (Ref. page 13) & 15 Removable Tarnish Inhibitor Dividers (Ref. page 34)<br>(L x W): A= 13-11/16" x 2" (34.77 x 5.08 cm), B= 13-11/16" x 1-11/16" (34.77 x 4.29 cm) | T5007AT      | 6758TE       | Tuff Tainer | TP       | 13-11/16" x 8-3/16" x 1-3/4"<br>(34.77 x 20.80 x 4.45 cm) | 6/ctn  |
| <br>4 Compartments, Integral Latches (Ref. page 13) & 20 Removable Dividers<br>(L x W): A= 13-11/16" x 2" (34.77 x 5.08 cm), B= 13-11/16" x 1-11/16" (34.77 x 4.29 cm)                                           | T5007E ◆     | 6756TE       | Tuff Tainer | TP       | 13-11/16" x 8-3/16" x 1-3/4"<br>(34.77 x 20.80 x 4.45 cm) | 6/ctn  |
| <br>6 Compartments & 16 Removable Dividers<br>(L x W): A= 15-5/16" x 2" (38.89 x 5.08 cm), B= 3-1/4" x 2" (8.26 x 5.08 cm), C= 8-1/2" x 2" (21.59 x 5.08 cm)                                                   | T6004 ◆      | 6760TE       | Tuff Tainer | TP       | 15-1/4" x 8-7/8" x 1-3/8"<br>(38.74 x 22.54 x 3.49 cm)    | 6/ctn  |
| <br>6 Compartments & 9 Removable Dividers (L x W): A= 15-1/4" x 4-1/2" (38.74 x 11.43 cm), B= 15-1/4" x 2-1/8" (38.74 x 5.40 cm), C= 3-3/4" x 2-1/8" (9.53 x 5.40 cm), D= 3-3/4" x 1-1/2" (9.53 x 3.81 cm)     | T7003/4      | 6773TE       | Tuff Tainer | TP       | 15-1/4" x 8-7/8" x 3"<br>(38.74 x 22.54 x 7.62 cm)        | 6/ctn  |
| <br>7 Compartments & 9 Removable Dividers<br>(L x W): A= 15-1/4" x 2-3/16" (38.74 x 5.56 cm), B= 3-3/4" x 2-1/8" (9.52 x 5.40 cm), C= 3-3/4" x 2-1/8" (9.52 x 5.40 cm)                                         | T7004 ◆      | 6774TE       | Tuff Tainer | TP       | 15-1/4" x 8-7/8" x 3"<br>(38.74 x 22.54 x 7.62 cm)        | 6/ctn  |
| <br>1 Compartment                                                                                                                                                                                              | T7000 ◆      | 6770TE       | Tuff Tainer | TP       | 15-1/4" x 8-7/8" x 3"<br>(38.74 x 22.54 x 7.62 cm)        | 6/ctn  |
| <br>1 Compartment                                                                                                                                                                                              | V701 ◆       | 6172VB       | V-Series    | SP       | 17" x 7-1/8" x 2"<br>(43.18 x 18.10 x 5.08 cm)            | 6/ctn  |

\* Adding color to the resins effects the clarity of the finished product

For Customer Service Inquiries Call 1-800-344-5716


# COMPARTMENTED BOXES

## Deep & Slim Super Satchels

The Super Satchel has a proven record when it comes to accommodating parts. Used in many industries as a kit for replacement parts or as a salesperson's sidekick, you won't need to worry about being organized. All Super Satchels are made out of "Acid Free" translucent polypropylene, with a positive contact latch system. The Deep Super Satchels are available in one compartment, six fixed compartments or six fixed compartments with removable dividers. The Slim Super Satchels are available in one compartment or eight fixed compartments and can accommodate up to 40 removable dividers.

The Deep Super Satchel Boxes are stackable and made from "Acid Free" Polypropylene with black handle and positive contact latches.


- **T9001 Deep Super Satchel**
  - Accommodates 12" x 12" (30.48 x 30.48 cm) documents
- **T9006 Deep Super Satchel**
  - 6 fixed extra deep compts
- **T9007 Deep Super Satchel**
  - 6 fixed extra deep compts with 12 removable dividers included
  - Divider packs sold separately (See page 34)



| Model Number | Stock Number | Description inch (centimeter)                                                                                          | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|--------|
| T9001        | 6991TE       | 1 compt w/black handle & latches<br>Outside Dimensions: 14 x 15 x 3-1/2 (35.56 x 38.10 x 8.89)                         | 13-1/8" x 13-1/8" x 3"<br>(33.34 x 33.34 x 7.62 cm) | 6/ctn  |
| T9006        | 6996TE       | 6 compt w/black handle & latches<br>Outside Dimensions: 14 x 15 x 3-1/2 (35.56 x 38.10 x 8.89)                         | 13-1/8" x 13-1/8" x 3"<br>(33.34 x 33.34 x 7.62 cm) | 6/ctn  |
| T9007        | 6997TE       | 6 compt w/black handle & latches & 12 removable dividers<br>Outside Dimensions: 14 x 15 x 3-1/2 (35.56 x 38.10 x 8.89) | 13-1/8" x 13-1/8" x 3"<br>(33.34 x 33.34 x 7.62 cm) | 6/ctn  |

The Slim Super Satchel Boxes are stackable and made from "Acid Free" Polypropylene with black (T9100 & T9101) or silver (T9101AT) positive contact latches.

- **T9100 Slim Super Satchel**
  - Accommodates 12" x 12" (30.48 x 30.48 cm) documents
- **T9101 / T9101AT Slim Super Satchels**
  - 8 fixed compts with 20 removable dividers included
  - T9101AT includes the Tarnish Inhibitor dividers (See page 34)
  - Accommodates up to 40 dividers for up to 48 compts
  - Divider 12-packs sold separately (See page 34)



| Model Number | Stock Number | Description inch (centimeter)                                                                                                 | Dimensions (Inside, L x W x D)                          | Packed |
|--------------|--------------|-------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------|--------|
| T9100        | 6990TE       | 1 compt w/black latches<br>Outside Dimensions: 14 x 15 x 2 (35.56 x 38.10 x 5.08)                                             | 13-1/8" x 13-1/8" x 1-3/4"<br>(33.34 x 33.34 x 4.45 cm) | 6/ctn  |
| T9101        | 6998TE       | 8 compt w/black latches, & 20 removable dividers<br>Outside Dimensions: 14 x 15 x 2 (35.56 x 38.10 x 5.08)                    | 13-1/8" x 13-1/8" x 1-3/4"<br>(33.34 x 33.34 x 4.45 cm) | 6/ctn  |
| T9101AT      | 6999TE       | 8 compt w/silver latches, & 20 removable Tarnish Inhibitor dividers<br>Outside Dimensions: 14 x 15 x 2 (35.56 x 38.10 x 5.08) | 13-1/8" x 13-1/8" x 1-3/4"<br>(33.34 x 33.34 x 4.45 cm) | 6/ctn  |


# COMPARTMENTED BOXES

## Deluxe & Double Deep Super Satchels

Like the Deep and Slim Super Satchels, the Deluxe and Double Deep Super Satchels are made out of "Acid Free" translucent polypropylene, with a positive contact latch system.

### Deluxe Super Satchel™ Boxes


The Deluxe Super Satchel is the "Ultimate Storage Unit" - essentially four boxes in one - and is available in three different configurations: Open Top / Divided Bottom, Divided Top / Open Bottom, and Divided Top / Divided Bottom. The divided sections of the Deluxe Super Satchel include removable dividers.



| Model Number | Stock Number | Description                                                                                                  | Dimensions (Outside, L x W x D)                      | Packed |
|--------------|--------------|--------------------------------------------------------------------------------------------------------------|------------------------------------------------------|--------|
| T9500        | 6787TE       | Color: Translucent with Black Handle & Latches<br>Open Top & Divided Bottom. Includes removable dividers.    | 17-1/4" x 16-3/4" x 5"<br>(43.82 x 42.55 x 12.70 cm) | 3/ctn  |
| T9501        | 6788TE       | Color: Translucent with Black Handle & Latches<br>Divided Top & Open Bottom. Includes removable dividers.    | 17-1/4" x 16-3/4" x 5"<br>(43.82 x 42.55 x 12.70 cm) | 3/ctn  |
| T9502        | 6789TE       | Color: Translucent with Black Handle & Latches<br>Divided Top & Divided Bottom. Includes removable dividers. | 17-1/4" x 16-3/4" x 5"<br>(43.82 x 42.55 x 12.70 cm) | 3/ctn  |

### Double Deep Super Satchel™

The Double Deep Super Satchel has extra depth for tall items and can be used one of two ways: Open Core (without dividers) or customized to up to eight compartments using removable dividers.



T9200 Compartments (L x W)  
 w/o Dividers = 12-7/16 x 12-9/16 (31.57 x 31.93 cm)  
 A = [1 row 2 compts] 6-1/4" x 3" (15.88 x 7.62 cm)  
 B = [2 rows 4 compts] 6-1/4" x 3-1/4" (15.88 x 8.26 cm)  
 C = [1 row 2 compts] 6-1/4" x 2-3/4" (15.88 x 6.99 cm)

T9200

| Model Number | Stock Number | Description                                                                                 | Dimensions (Outside, L x W x D)                          | Packed |
|--------------|--------------|---------------------------------------------------------------------------------------------|----------------------------------------------------------|--------|
| T9200        | 6784TE       | Color: Translucent with Black Handle & Latches<br>Double Deep. Includes removable dividers. | 15-7/32 x 14-5/32 x 6-7/32<br>(38.66 x 35.96 x 15.80 cm) | 3/ctn  |

# COMPARTMENTED BOXES

## Compartmented Box / Super Satchel Case Divider Packs



**Tarnish Inhibitor by Flambeau** provides safe, long-term protective storage for sterling silver items. The patented Tarnish Inhibitor additive forms a harmless protective layer around silver surfaces that prevents tarnishing for up to five years.

To order Tarnish Inhibitor dividers for your specific Tuff Tainer or Super Satchel, see below:

|                |           |         |         |        |
|----------------|-----------|---------|---------|--------|
| <b>T4007AT</b> | (page 28) | 12/pack | Order#  | 4812DP |
| <b>T5007AT</b> | (page 31) | 12/pack | Order#  | 5812DP |
| <b>T9101AT</b> | (page 32) | 12/pack | Order # | 5812DP |



**Zerust®**, a new advanced polymer technology that creates a harmless vapor barrier around your parts inhibiting corrosion for up to five years, is now an option available in Tuff Tainer dividers.

To order Zerust dividers for your specific Tuff Tainer or Super Satchel, see below:


|              |           |         |         |        |
|--------------|-----------|---------|---------|--------|
| <b>T2003</b> | (page 22) | 15/pack | Order#  | 2012ZP |
| <b>T3003</b> | (page 26) | 12/pack | Order # | 3012ZP |
| <b>T4007</b> | (page 28) | 12/pack | Order # | 4712ZP |
| <b>T5007</b> | (page 31) | 12/pack | Order # | 5712ZP |
| <b>T6004</b> | (page 31) | 12/pack | Order # | 6012ZP |
| <b>T7003</b> | (page 31) | 12/pack | Order # | 7012ZP |
| <b>T7004</b> | (page 31) | 12/pack | Order # | 7012ZP |
| <b>T9101</b> | (page 32) | 12/pack | Order # | 5712ZP |
| <b>T9007</b> | (page 32) | 12/pack | Order # | 9012ZP |



Zerust is a registered trademark of Northern Technologies International Corporation.

To order Non-Zerust dividers for your specific Tuff Tainer or Super Satchel, see below:

|              |           |         |         |        |              |        |
|--------------|-----------|---------|---------|--------|--------------|--------|
| <b>T1002</b> | (page 20) | 12/pack | Order # | 1012DP | Order Bulk # | 601331 |
| <b>T2003</b> | (page 22) | 15/pack | Order # | 2012DP | Order Bulk # | 601321 |
| <b>T3003</b> | (page 26) | 12/pack | Order # | 3412DP | Order Bulk # | 601320 |
| <b>T4007</b> | (page 28) | 12/pack | Order # | 4712DP | Order Bulk # | 601370 |
| <b>T5007</b> | (page 31) | 12/pack | Order # | 5712DP | Order Bulk # | 601365 |
| <b>T6004</b> | (page 31) | 12/pack | Order # | 6012DP | Order Bulk # | 601329 |
| <b>T7003</b> | (page 31) | 12/pack | Order # | 7012DP | Order Bulk # | 601332 |
| <b>T7004</b> | (page 31) | 12/pack | Order # | 7012DP | Order Bulk # | 601332 |
| <b>T9101</b> | (page 32) | 12/pack | Order # | 5712DP | Order Bulk # | 601365 |
| <b>T9007</b> | (page 32) | 12/pack | Order # | 9012DP | Order Bulk # | 601372 |



To order IDS (Infinite Divider System) dividers, see below:

|             |           |        |         |        |              |        |
|-------------|-----------|--------|---------|--------|--------------|--------|
| <b>T300</b> | (page 22) | 8/pack | Order # | 3108DP | Order Bulk # | 601316 |
| <b>T600</b> | (page 27) | 8/pack | Order # | 6108DP | Order Bulk # | 601308 |
| <b>T900</b> | (page 30) | 8/pack | Order # | 9108DP | Order Bulk # | 601310 |



Compartment ribbed at 1/16" (0.16 cm) increments.  
US Patent 4,838,445

# CASES: TRADESMAN & MERCHANT<sup>™</sup> X STYLES

## Tradesman<sup>™</sup> Case

The original! Any other case resembling this style is a knock-off! Flambeau Tradesman Cases are built in the USA! These professional hand-held carrying cases are very functional. Commonly used to protect; store; and attractively merchandise hundreds of products. Tradesman cases are easy to customize with different color options; adhesive or in-mold labels; logo plates; interior foam sets; vacuum trays or just "plain open!" Made from tough polypropylene resin, the Tradesman Series cases incorporate slide open/shut lockable latches with overlapping lid to base closure providing natural dust barrier and moisture resistance. Available in three sizes (10", 14" and 17") with more new sizes coming soon!



## Customization of the Tradesman<sup>™</sup> Case

Customize your Tradesman case with options that include engraving, printing, labeling, die-cut foam and the in-mold labeling process which is nearly indestructible and impervious to chemicals.



Custom Foam:  
Convuluted, or  
Diced Available.

Tradesman case stock colors include Black, and Translucent Clear. Custom colors are available. Please call Customer Service at 1-800-344-5716 for stock and custom colors.

## Custom Options Enhance Interest

Point-of-Purchase has become more important than ever before as companies look for ways to reduce cost and improve sales. Using the Flambeau Tradesman<sup>™</sup>, options such as in-mold decorating, labeling, engraving, & custom foam interiors enhance consumer interest.



## Merchant X Case

**NEW**

Merchant X is the next generation styled case beyond Tradesman. The Merchant Case design is truly innovative! U S Design Patent D633,294 granted March 1, 2011. All Merchant X Cases employ shallow lid with deep base functionality.



The deep base allows greater capacity for storage and less cost when lid foam is required. The Merchant X10 and Merchant X15 case handles are designed to provide excellent balance by off-setting the handle for center



grasp between the lid and base. Slide open/shut lockable latches with a bead-line seal fit complete this exquisite line. Available in 7, 10, 12, and 15 inch size ranges!!

## Custom Foam

Merchant cases offer the best solution when foam is the desired choice for protecting and merchandising your products. The shallow lid design in all Merchants minimizes the required use of foam there by minimizing cost. The Merchant's deep base versus Tradesman style cases is excellent for storing multiple contoured parts.



**NEW**

Introducing the  
7" Merchant X



# CASES: TRADESMAN & MERCHANT X

## Flambeau Tradesman™ Cases

- All are available in black, translucent clear and blue
- Black case is available with or without foam



| Model Number | Stock Number | Description                                                           | Dimensions (Inside, L x W x D)                         | Packed |
|--------------|--------------|-----------------------------------------------------------------------|--------------------------------------------------------|--------|
| 6775TC       | 6775TC       | 10-1/2" (26.67 cm) Black - without Foam                               | 9-1/2" x 5-3/4" x 2-3/4"<br>(24.13 x 14.61 x 6.99 cm)  | 14/ctn |
| 6775TB       | 6775TB       | 10-1/2" (26.67 cm) Black - without Foam - Biodegradable               |                                                        |        |
| 6776TC       | 6776TC       | 10-1/2" (26.67 cm) Black - with Convuluted Foam                       |                                                        |        |
| 6775WF       | 6775WF       | 10-1/2" (26.67 cm) Black - with Convuluted Foam Lid & Diced Foam Base |                                                        |        |
| 6775TF       | 6775TF       | 10-1/2" (26.67 cm) Translucent Clear                                  |                                                        |        |
| 6775TD       | 6775TD       | 10-1/2" (26.67 cm) Translucent Blue                                   |                                                        |        |
| 6780TC       | 6780TC       | 14" (35.56 cm) Black - without Foam                                   | 13-1/4" x 7-3/8" x 3"<br>(33.66 x 18.73 x 7.62 cm)     | 14/ctn |
| 6780TB       | 6780TB       | 14" (35.56 cm) Black - without Foam - Biodegradable                   |                                                        |        |
| 6781TC       | 6781TC       | 14" (35.56 cm) Black - with Convuluted Foam                           |                                                        |        |
| 6780XG       | 6780XG       | 14" (35.56 cm) Black - with Convuluted Foam Lid & Diced Foam Base     |                                                        |        |
| 6780TN       | 6780TN       | 14" (35.56 cm) Translucent Clear                                      |                                                        |        |
| 6780TP       | 6780TP       | 14" (35.56 cm) Translucent Blue                                       |                                                        |        |
| 6785TC       | 6785TC       | 17" (43.18 cm) Black - without Foam                                   | 16-3/8" x 9-1/4" x 3-1/2"<br>(41.59 x 23.50 x 8.89 cm) | 6/ctn  |
| 6785TB       | 6785TB       | 17" (43.18 cm) Black - without Foam - Biodegradable                   |                                                        |        |
| 6785TE       | 6785TE       | 17" (43.18 cm) Black - with Convuluted Foam                           |                                                        |        |
| 6785UP       | 6785UP       | 17" (43.18 cm) Black - with Convuluted Foam Lid & Diced Foam Base     |                                                        |        |
| 6785TI       | 6785TI       | 17" (43.18 cm) Translucent Clear                                      |                                                        |        |

## Merchant X Cases

*An Xcellent complement to our Tradesman Case Line*

- The Merchant X cases feature integral handle, mechanical hinge and lockable sliding latches
- Designed with deep base/shallow lid for greater storage area





| Model Number | Stock Number | Description                                                  | Dimensions (Inside, L x W x D)                        | Packed |
|--------------|--------------|--------------------------------------------------------------|-------------------------------------------------------|--------|
| 6767TC       | 6767TC       | 7" (17.78 cm) Black - without Foam                           | 6-1/2" x 4-1/5" x 3-1/5"<br>(16.51 x 10.67 x 8.13 cm) | 12/ctn |
| 6767TN       | 6767TN       | 7" (17.78 cm) Translucent Clear - without Foam               |                                                       |        |
| 6772TC       | 6772TC       | 10" (25.4 cm) Black - without Foam                           | 9-5/8" x 7-1/8" x 2-4/5"<br>(24.45 x 18.10 x 7.11 cm) | 12/ctn |
| 6772TB       | 6772TB       | 10" (25.4 cm) Black - without Foam - Biodegradable           |                                                       |        |
| 6772TF       | 6772TF       | 10" (25.4 cm) Black - with Flat Foam Lid and Convuluted Base |                                                       |        |
| 6772TD       | 6772TD       | 10" (25.4 cm) Translucent Clear - without Foam               |                                                       |        |
| 6777TC       | 6777TC       | 12" (30.48 cm) Black - without Foam                          | 11" x 7-1/4" x 3-1/4"<br>(27.94 x 18.41 x 8.25 cm)    | 12/ctn |
| 6777TB       | 6777TB       | 12" (30.48 cm) Black - without Foam - Biodegradable          |                                                       |        |
| 6777TF       | 6777TF       | 12" (30.48 cm) Black - with Flat Foam Lid & Diced Foam Base  |                                                       |        |
| 6777TD       | 6777TD       | 12" (30.48 cm) Translucent Clear - without Foam              |                                                       |        |
| 6782TC       | 6782TC       | 15" (38.1 cm) Black - without Foam                           | 14" x 11" x 3-1/8"<br>(35.56 x 27.94 x 7.94 cm)       | 12/ctn |
| 6783TC       | 6783TC       | 15" (38.1 cm) Black - with Divided Base & 12 Dividers        |                                                       |        |
| 6786TC       | 6786TC       | 15" (38.1 cm) Black - with Tray, Divided Base & 16 Dividers  |                                                       |        |



## The Defender...Just in Case!

The combination of high-density homopolymer material and double-wall construction offer increased product protection. This case is water- and chemical-resistant. Can be customized through logo engraving, Spectra-Molding™ permanent labeling, custom colors, foam or molded interior.

- ProTech™ Latches
- Rear Feet Detail (Offers increased stability for upright display)
- Exterior Banding Strap Detail (Allows case to be used as a shipping container)
- Interior Gasket Seal
- Water- and Chemical-resistant
- Crush-resistant and Stackable



| Model Number       | Stock Number | Description                                    | Inside Dimensions<br>(L x W x D) inches (cm)   | Outside Dimensions<br>(L x W x D) inches (cm)         |
|--------------------|--------------|------------------------------------------------|------------------------------------------------|-------------------------------------------------------|
| Defender 12 (DQ 6) | 50641        | Defender 12                                    | 12 x 9 x 5<br>(30.48 x 22.86 x 12.70)          | 15-15/16 x 13-1/4 x 6-7/16<br>(40.48 x 33.65 x 16.35) |
| Defender 12 (DQ 6) | 50641F       | Defender 12 with Diced Foam                    | 12 x 9 x 5<br>(30.48 x 22.86 x 12.70)          | 15-15/16 x 13-1/4 x 6-7/16<br>(40.48 x 33.65 x 16.35) |
| Defender 17 (DW 6) | 50514        | Defender 17                                    | 15 x 12 x 5<br>(38.10 x 30.48 x 12.70)         | 18-1/2 x 15 x 6-3/16<br>(21.59 x 38.10 x 15.72)       |
| Defender 17 (DW 6) | 50514F       | Defender 17 with Diced Foam                    | 15 x 12 x 5<br>(38.10 x 30.48 x 12.70)         | 18-1/2 x 15 x 6-3/16<br>(21.59 x 38.10 x 15.72)       |
| Defender 18 (DX 7) | 50642        | Defender 18                                    | 15-1/2 x 10-1/4 x 6<br>(39.37 x 26.03 x 15.24) | 20-3/4 x 15-3/4 x 7-5/16<br>(52.70 x 40.00 x 18.57)   |
| Defender 18 (DX 7) | 50642F       | Defender 18 with Diced Foam                    | 15-1/2 x 10-1/4 x 6<br>(39.37 x 26.03 x 15.24) | 20-3/4 x 15-3/4 x 7-5/16<br>(52.70 x 40.00 x 18.57)   |
| Defender 23 (DY 9) | 50720        | Defender 23                                    | 19-1/2 x 15 x 7-3/4<br>(49.53 x 38.10 x 19.68) | 25-1/4 x 21 x 9-3/16<br>(64.13 x 53.34 x 23.34)       |
| Defender 23 (DY 9) | 50720F       | Defender 23 with Diced Foam                    | 19-1/2 x 15 x 7-3/4<br>(49.53 x 38.10 x 19.68) | 25-1/4 x 21 x 9-3/16<br>(64.13 x 53.34 x 23.34)       |
| Defender 23 (DY 9) | 50720W       | Defender 23 with Wheel Assembly                | 19-1/2 x 15 x 7-3/4<br>(49.53 x 38.10 x 19.68) | 25-1/4 x 21 x 9-3/16<br>(64.13 x 53.34 x 23.34)       |
| Defender 23 (DY 9) | 50720FW      | Defender 23 with Diced Foam and Wheel Assembly | 19-1/2 x 15 x 7-3/4<br>(49.53 x 38.10 x 19.68) | 25-1/4 x 21 x 9-3/16<br>(64.13 x 53.34 x 23.34)       |
| Defender 26 (DZ 9) | 50721        | Defender 26                                    | 22-3/4 x 17-3/4 x 8<br>(57.78 x 44.04 x 20.32) | 28-3/4 x 24 x 9-5/16<br>(73.02 x 60.96 x 23.65)       |
| Defender 26 (DZ 9) | 50721F       | Defender 26 with Diced Foam                    | 22-3/4 x 17-3/4 x 8<br>(57.78 x 44.04 x 20.32) | 28-3/4 x 24 x 9-5/16<br>(73.02 x 60.96 x 23.65)       |
| Defender 26 (DZ 9) | 50721W       | Defender 26 with Wheel Assembly                | 22-3/4 x 17-3/4 x 8<br>(57.78 x 44.04 x 20.32) | 28-3/4 x 24 x 9-5/16<br>(73.02 x 60.96 x 23.65)       |
| Defender 26 (DZ 9) | 50721WF      | Defender 26 with Diced Foam and Wheel Assembly | 22-3/4 x 17-3/4 x 8<br>(57.78 x 44.04 x 20.32) | 28-3/4 x 24 x 9-5/16<br>(73.02 x 60.96 x 23.65)       |

# CASES: INFINITY™

## Infinity™ Case



With flair, style and professional presence, the Infinity is designed to give you a high level of protection with a modern look.



Offered with or without foam, the Infinity is available in a variety of sizes and depths.



The Infinity lends itself to customization including engraving, printing, labeling, die-cut foam, custom colors and the in-mold labeling/decorating process (see pages 8 & 9). Made of high-density polyethylene (HDPE) the case is impervious to most chemicals, gasoline & is an excellent case for most applications.



The Infinity features a natural dust seal and double wall protection in the lid and base that naturally creates an interior impact barrier helping the case become crush resistant and withstand a 30 pound impact test. The dual latch system provides easy latching with confidence of security even in the harshest conditions.



Infinity Pin Hinge



Infinity Locking Hole

Some Size Samples of Infinity Cases



**NEW**



Infinity 14 (FV 6.5)  
50380


## Infinity™ Cases

This blow molded case with double wall construction gives you the highest protection level possible.

- Offered with or without foam
- Select styles available in integral or pin hinge

### Drawing Key

a = Exterior Length    b = Exterior Width    c = Overall Exterior Depth  
d = Interior Length    e = Interior Width    f = Overall Interior Depth  
g = Interior Lid Depth    h = Interior Base Depth



| Stock Number              | Style                   | Interior Dimensions:<br>L x W x overall D<br>(d x e x f) inches (cm) | Interior Depth:<br>Lid = g Base = h<br>inches (cm) | Exterior Dimensions:<br>L x W x overall D<br>(a x b x c) inches (cm) | Standard<br>Handle / Latch | Description                             |
|---------------------------|-------------------------|----------------------------------------------------------------------|----------------------------------------------------|----------------------------------------------------------------------|----------------------------|-----------------------------------------|
| 20190<br>50190            | Infinity 10<br>FH 4     | 8-1/4 x 5-7/16 x 3-5/16<br>(20.96 x 13.81 x 8.41)                    | g = 1-5/16 (3.33)<br>h = 1-15/16 (4.92)            | 10-1/8 x 8-1/8 x 4<br>(25.72 x 20.64 x 10.16)                        | H052 / L089                | foam option available                   |
| 20250<br>50250            | Infinity 12<br>FQ 2-1/2 | 9-1/2 x 6-5/8 x 1-3/4<br>(24.13 x 16.83 x 4.45)                      | g = 3/8 (0.95)<br>h = 1-3/8 (3.49)                 | 12 x 9 x 2-1/2<br>(30.48 x 22.86 x 6.35)                             | none / L089                | foam option available                   |
| 20290<br>50290            | Infinity 12<br>FQ 4-1/2 | 9-1/2 x 6-5/8 x 3-3/16<br>(24.13 x 16.83 x 8.10)                     | g = 2-7/16 (6.19)<br>h = 2-3/8 (6.03)              | 12 x 9 x 4-1/2<br>(30.48 x 22.86 x 11.43)                            | H052 / L089                | foam option available                   |
| 20330<br>50330            | Infinity 14<br>FV 4     | 11-1/2 x 8-1/2 x 3-3/16<br>(29.21 x 21.59 x 8.10)                    | g = 1-3/8 (3.49)<br>h = 1-13/16 (4.60)             | 14 x 10-1/2 x 4<br>(35.56 x 26.67 x 10.16)                           | H052 / L089                | foam option available                   |
| 20350<br>50350            | Infinity 14<br>FV 5     | 11-1/2 x 8-1/2 x 4-1/4<br>(29.21 x 21.59 x 10.80)                    | g = 1-7/8 (4.76)<br>h = 2-3/8 (6.03)               | 14 x 10-1/2 x 5<br>(35.56 x 26.67 x 12.70)                           | H052 / L089                | Integral Hinge<br>foam option available |
| 20351<br>50351            | Infinity 14<br>FV 5     | 11-1/2 x 8-1/2 x 4-1/4<br>(29.21 x 21.59 x 10.80)                    | g = 1-7/8 (4.76)<br>h = 2-3/8 (6.03)               | 14 x 10-1/2 x 5<br>(35.56 x 26.67 x 12.70)                           | H052 / L089                | Pin Hinge<br>foam option available      |
| <b>NEW</b> 20380<br>50380 | Infinity 14<br>FV 6-1/2 | 11 x 7-11/16 x 5-3/4<br>(27.94 x 19.53 x 14.61)                      | g = 2-1/8 (5.41)<br>h = 3-1/2 (8.90)               | 14 x 11 x 7<br>(35.6 x 28 x 17.8)                                    | H0230M / L089              | foam option available                   |
| 20410<br>50410            | Infinity 17<br>FW 4-1/2 | 14-3/8 x 10 x 3-7/16<br>(36.51 x 25.40 x 8.73)                       | g = 1-1/4 (3.18)<br>h = 2-3/16 (5.56)              | 17 x 14-1/2 x 4-1/2<br>(43.18 x 36.83 x 11.43)                       | H0230M / L085              | foam option available                   |
| 20430<br>50430            | Infinity 17<br>FW 6-1/2 | 14-3/8 x 10 x 5-9/16<br>(36.51 x 25.40 x 14.13)                      | g = 2-5/16 (5.87)<br>h = 3-1/4 (8.26)              | 17 x 14-1/2 x 6-1/2<br>(43.18 x 36.83 x 16.51)                       | H0230M / L085              | foam option available                   |
| 20470<br>50470            | Infinity 20<br>FX 5-1/2 | 17-3/4 x 12-5/8 x 4-1/16<br>(45.09 x 32.07 x 11.75)                  | g = 1-13/16 (4.60)<br>h = 2-1/4 (5.72)             | 20 x 15 x 5-1/2<br>(50.80 x 38.10 x 13.97)                           | H0230M / L095              | foam option available                   |
| 20500<br>50500            | Infinity 20<br>FX 8-1/2 | 17-3/4 x 12-5/8 x 7-1/2<br>(45.09 x 32.07 x 19.05)                   | g = 3-1/4 (8.26)<br>h = 4-1/4 (10.80)              | 20 x 15 x 8-1/2<br>(50.80 x 38.10 x 21.59)                           | H0230M / L095              | foam option available                   |
| 50817                     | Infinity 27<br>FZ 8-1/2 | 24-15/16 x 14-3/16 x 7-1/2<br>(63.33 x 36.03 x 19.05)                | g = 1-1/2 (3.81)<br>h = 6 (15.24)                  | 27-3/8 x 18 x 8-1/2<br>(69.53 x 45.72 x 21.59)                       | H074 / L115                | foam option available                   |
| 50845                     | Infinity 43<br>FZ 7     | 40-5/8 x 14-7/16 x 6<br>(103.18 x 36.67 x 15.24)                     | g = 1-1/2 (3.81)<br>h = 4-1/2 (11.43)              | 43 x 18-15/16 x 7<br>(109.22 x 46.51 x 17.78)                        | H074 / L116                | foam option available                   |

# CASES: “P” SERIES

## “P” Series - Pin Hinge Case



The “P” Series case is a Flambeau original and has a proven track record in most industries and applications.

This pin-hinge style high-density polyethylene (HDPE) blow molded case features heavy-duty latches, double-wall lid protection and is impervious to most chemicals and gasoline.




The routed base option is designed to accommodate our standard solid sheet or diced foam and is available in a variety of sizes and depths. Please call Customer Service for size availability.



The “P” Series is easily customized through engraving, printing, labeling, custom colors, die-cut foam, molded interiors and in-mold decorating/labeling process (molded into the case) which is nearly indestructible.

### Drawing Key

- a = Exterior Length
- b = Exterior Width
- c = Overall Exterior Depth
- d = Interior Length
- e = Interior Width
- f = Overall Interior Depth
- g = Interior Lid Depth
- h = Interior Base Depth
- i = Routed Depth



\* Number of weld posts may vary.

| Stock Number | Style    | Interior Dimensions: L x W x overall D<br>(d x e x f) inches (cm) | Routed Depth = i<br>inches (cm) | Interior Depth:<br>Lid = g Base = h inches (cm) | Exterior Dimensions: L x W x overall D<br>(a x b x c) inches (cm) | Standard<br>Handle / Latch | Comments<br>inches (cm) |
|--------------|----------|-------------------------------------------------------------------|---------------------------------|-------------------------------------------------|-------------------------------------------------------------------|----------------------------|-------------------------|
| 18673        | PB 1-5/8 | 6-13/16 x 3-3/16 x 1-5/16<br>(17.30 x 8.10 x 3.33)                | 1/4 (0.64)                      | g = 1/8 (0.32)<br>h = 1-3/16 (3.02)             | 7-1/2 x 4-1/2 x 1-5/8<br>(19.05 x 11.43 x 4.13)                   | none / L089                | foam option available   |
| 17873        | PC 3-1/8 | 7-1/4 x 5-7/8 x 2-13/16<br>(18.42 x 14.92 x 7.14)                 | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-3/16 (5.56)             | 8-1/2 x 7-13/16 x 3-1/8<br>(21.59 x 19.84 x 7.94)                 | H001 / L089                | foam option available   |

“P” Series Cases Continued on page 41

# CASES: "P" SERIES

| Stock Number       | Style      | Interior Dimensions: L x W x overall D<br>(d x e x f) inches (cm) | Routed Depth = i<br>inches (cm) | Interior Depth:<br>Lid = g Base = h inches (cm) | Exterior Dimensions: L x W x overall D<br>(a x b x c) inches (cm) | Standard<br>Handle / Latch | Comments<br>inches (cm)                                      |
|--------------------|------------|-------------------------------------------------------------------|---------------------------------|-------------------------------------------------|-------------------------------------------------------------------|----------------------------|--------------------------------------------------------------|
| 16887<br>50032 [E] | PC 3-9/16  | 7-1/4 x 5-7/8 x 3-1/4<br>(18.42 x 14.92 x 8.26)                   | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-5/8 (6.67)              | 8-1/2 x 7-13/16 x 3-9/16<br>(21.59 x 19.84 x 9.05)                | H001 / L089                | 4-7/8 x 1-7/8 (12.38 x 4.76)<br>label recess, foam opt. avl. |
| 15865              | PC 3-9/16  | 7-1/4 x 5-7/8 x 3-1/4<br>(18.42 x 14.92 x 8.26)                   | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-5/8 (6.67)              | 8-1/2 x 7-13/16 x 3-9/16<br>(21.59 x 19.84 x 9.05)                | H001 / L089                | 3-1/4 x 1-1/2 (8.26 x 3.81)<br>label recess                  |
| 16070              | PF 1-3/4   | 8-5/8 x 4 x 1-7/16<br>(21.91 x 10.16 x 3.65)                      | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 13/16 (2.06)              | 9-1/2 x 5-3/4 x 1-3/4<br>(24.13 x 14.61 x 4.45)                   | none / L089                |                                                              |
| 16716              | PF 3-1/8   | 8-5/8 x 4 x 2-13/16<br>(21.91 x 10.16 x 7.14)                     | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 3-3/16 (8.10)             | 9-1/2 x 5-3/4 x 3-1/8<br>(24.13 x 14.61 x 7.94)                   | H001 / L089                |                                                              |
| 17474<br>50048 [E] | PH 3-1/8   | 9-1/8 x 6-1/2 x 2-13/16<br>(23.18 x 16.51 x 7.14)                 | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-3/16 (5.56)             | 10 x 8-5/16 x 3-1/8<br>(25.40 x 21.11 x 7.94)                     | H001 / L089                | foam option available                                        |
| 18964              | PH 3-7/16  | 9-1/8 x 6-1/2 x 3-1/8<br>(23.18 x 16.51 x 7.94)                   | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 2-3/16 (5.56)           | 10 x 8-5/16 x 3-7/16<br>(25.40 x 21.11 x 8.73)                    | H001 / L089                |                                                              |
| 17383              | PH 3-9/16  | 9-1/8 x 6-1/2 x 3-1/4<br>(23.18 x 16.51 x 8.26)                   | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-5/8 (6.67)              | 10 x 8-5/16 x 3-9/16<br>(25.40 x 21.11 x 9.05)                    | H001 / L089                |                                                              |
| 18290              | PH 3-7/8   | 9-1/8 x 6-1/2 x 3-9/16<br>(23.18 x 16.51 x 9.05)                  | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 2-5/8 (6.67)            | 10 x 8-5/16 x 3-7/8<br>(25.40 x 21.11 x 9.84)                     | H001 / L089                |                                                              |
| 16615              | PQ 2-3/8   | 11-3/8 x 7 x 2-1/16<br>(28.89 x 17.78 x 5.24)                     | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 1-1/8 (2.86)            | 12-1/4 x 8-13/16 x 2-3/8<br>(31.12 x 22.38 x 6.03)                | none / L089                |                                                              |
| 18924              | PQ 3-7/16  | 11-3/8 x 7 x 3-1/8<br>(28.89 x 17.78 x 7.94)                      | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 2-3/16 (5.56)           | 12-1/4 x 8-13/16 x 3-7/16<br>(31.12 x 22.38 x 8.73)               | H052 / L089                |                                                              |
| 12349              | PQ 3-13/16 | 11-3/8 x 7 x 3-7/16<br>(28.89 x 17.78 x 8.73)                     | 7/16 (1.11)                     | g = 1-1/4 (3.18)<br>h = 2-3/16 (5.56)           | 12-1/4 x 8-13/16 x 3-13/16<br>(31.12 x 22.38 x 9.68)              | H052 / L089                |                                                              |
| 12347<br>50025 [E] | PQ 3-7/8   | 11-3/8 x 7 x 3-9/16<br>(28.89 x 17.78 x 9.05)                     | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 2-5/8 (6.67)            | 12-1/4 x 8-13/16 x 3-7/8<br>(31.12 x 22.38 x 9.84)                | H052 / L089                | foam option available                                        |
| 15658              | PV 3-1/8   | 12-11/16 x 8-15/16 x 2-13/16<br>(32.23 x 22.70 x 7.14)            | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-3/16 (5.56)             | 13-1/2 x 10-13/16 x 3-1/8<br>(34.29 x 27.46 x 7.94)               | H052 / L089                |                                                              |
| 16952              | PV 3-7/16  | 12-11/16 x 8-15/16 x 3-1/8<br>(32.23 x 22.70 x 7.94)              | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 2-3/16 (5.56)           | 13-1/2 x 10-13/16 x 3-7/16<br>(34.29 x 27.46 x 8.73)              | H052 / L089                |                                                              |
| 16541              | PV 3-11/16 | 12-11/16 x 8-15/16 x 3-3/8<br>(32.23 x 22.70 x 8.57)              | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-3/4 (6.99)              | 13-1/2 x 10-13/16 x 3-11/16<br>(34.29 x 27.46 x 9.37)             | H052 / L089                |                                                              |
| 17976<br>50024 [E] | PV 4       | 12-11/16 x 8-15/16 x 3-11/16<br>(32.23 x 22.70 x 9.37)            | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 2-3/4 (6.99)            | 13-1/2 x 10-13/16 x 4<br>(34.29 x 27.46 x 10.16)                  | H052 / L089                | foam option available                                        |
| 12276<br>50026 [E] | PV 5-1/8   | 12-11/16 x 8-15/16 x 4-3/4<br>(32.23 x 22.70 x 12.07)             | 7/16 (1.11)                     | g = 1-1/2 (3.81)<br>h = 3-1/4 (8.26)            | 13-1/2 x 10-13/16 x 5-1/8<br>(34.29 x 27.46 x 13.02)              | H052 / L089                | foam option available                                        |
| 16965              | PV 6-1/8   | 12-11/16 x 8-15/16 x 5-5/8<br>(32.23 x 22.70 x 14.29)             | 7/16 (1.11)                     | g = 1-7/8 (4.76)<br>h = 3-3/4 (9.53)            | 13-1/2 x 10-13/16 x 6-1/8<br>(34.29 x 27.46 x 15.56)              | H052 / L089                |                                                              |
| 11583<br>50030 [E] | PW 4       | 14 x 10-3/4 x 3-1/2<br>(35.56 x 27.31 x 8.89)                     | 1-1/4 (3.18)                    | g = 5/8 (1.59)<br>h = 2-7/8 (7.30)              | 15-1/2 x 13-5/16 x 4<br>(39.37 x 33.81 x 10.16)                   | H0230M / L085              | foam option available                                        |
| 11585              | PW 4-3/4   | 14 x 10-3/4 x 4-1/4<br>(35.56 x 27.31 x 10.80)                    | 1-1/4 (3.18)                    | g = 1-3/8 (3.49)<br>h = 2-7/8 (7.30)            | 15-1/2 x 13-5/16 x 4-3/4<br>(39.37 x 33.81 x 12.07)               | H0230M / L085              |                                                              |
| 11598              | PW 4-3/4   | 14 x 10-3/4 x 4<br>(35.56 x 27.31 x 10.16)                        | 1-1/4 (3.18)                    | g = 1-3/8 (3.49)<br>h = 2-5/8 (6.67)            | 15-1/2 x 13-5/16 x 4-3/4<br>(39.37 x 33.81 x 12.07)               | H0230M / L085              | double wall base                                             |
| 11664              | PW 5-1/2   | 14 x 10-3/4 x 5<br>(35.56 x 27.31 x 12.70)                        | 1-1/4 (3.18)                    | g = 2-1/8 (5.40)<br>h = 2-7/8 (7.30)            | 15-1/2 x 13-5/16 x 5-1/2<br>(39.37 x 33.81 x 13.97)               | H0230M / L085              |                                                              |
| 17977<br>50053 [E] | PW 6-1/4   | 14 x 10-3/4 x 5-3/4<br>(35.56 x 27.31 x 14.61)                    | 1-1/4 (3.18)                    | g = 2-1/8 (5.40)<br>h = 3-5/8 (9.21)            | 15-1/2 x 13-5/16 x 6-1/4<br>(39.37 x 33.81 x 15.88)               | H0230M / L026              | foam option available<br>17977 uses latch L085               |
| 11588              | PW 6-1/4   | 14 x 10-3/4 x 5-5/8<br>(35.56 x 27.31 x 14.29)                    | 1-1/4 (3.18)                    | g = 2-3/4 (6.98)<br>h = 2-7/8 (7.30)            | 15-1/2 x 13-5/16 x 6-1/4<br>(39.37 x 33.81 x 15.88)               | H0230M / L085              |                                                              |
| 12090              | PX 3-1/2   | 17 x 13 x 3<br>(43.18 x 33.02 x 7.62)                             | 15/16 (2.38)                    | g = 1-3/8 (3.49)<br>h = 1-5/8 (4.13)            | 18-1/2 x 15-9/16 x 3-1/2<br>(46.99 x 39.53 x 8.89)                | Integral / L037            |                                                              |
| 16607<br>50050 [E] | PX 5       | 17 x 13 x 4-1/2<br>(43.18 x 33.02 x 11.43)                        | 15/16 (2.38)                    | g = 1-3/8 (3.49)<br>h = 3-1/8 (7.94)            | 18-1/2 x 15-9/16 x 5<br>(46.99 x 39.53 x 12.70)                   | H0230M / L026              |                                                              |
| 12097              | PX 6-1/4   | 17 x 13 x 5-5/8<br>(43.18 x 33.02 x 14.29)                        | 15/16 (2.38)                    | g = 1-3/4 (4.45)<br>h = 3-7/8 (9.84)            | 18-1/2 x 15-9/16 x 6-1/4<br>(46.99 x 39.53 x 15.88)               | Integral / L037            |                                                              |
| 12101<br>50051 [E] | PX 8       | 17 x 13 x 7-3/8<br>(43.18 x 33.02 x 18.73)                        | 15/16 (2.38)                    | g = 3-1/2 (8.89)<br>h = 3-7/8 (9.84)            | 18-1/2 x 15-9/16 x 8<br>(46.99 x 39.53 x 20.32)                   | H0230M / L026              |                                                              |
| 12023              | PX 8       | 17 x 13 x 7-3/8<br>(43.18 x 33.02 x 18.73)                        | 15/16 (2.38)                    | g = 3-1/2 (8.89)<br>h = 3-7/8 (9.84)            | 18-1/2 x 15-9/16 x 8<br>(46.99 x 39.53 x 20.32)                   | H0230M / L085              |                                                              |
| 18925              | PX 8       | 17 x 13 x 7<br>(43.18 x 33.02 x 17.78)                            | 15/16 (2.38)                    | g = 3-1/2 (8.89)<br>h = 3-1/2 (8.89)            | 18-1/2 x 15-9/16 x 8<br>(46.99 x 39.53 x 20.32)                   | H0230M / L085              |                                                              |
| 12211<br>50045 [E] | PZ 4-1/2   | 24-1/2 x 13 x 3-5/8<br>(62.23 x 33.02 x 9.21)                     | 1-1/8 (2.86)                    | g = 7/8 (2.22)<br>h = 2-3/4 (6.99)              | 26 x 15-9/16 x 4-1/2<br>(66.04 x 39.53 x 11.43)                   | H0230M / L095              |                                                              |
| 12414<br>50088 [E] | PZ 8       | 24-1/2 x 13 x 7-3/8<br>(62.23 x 33.02 x 18.73)                    | 1-1/8 (2.86)                    | g = 3-1/2 (8.89)<br>h = 3-7/8 (9.84)            | 26 x 15-9/16 x 8<br>(66.04 x 39.53 x 20.32)                       | H0230M / L095              | foam option available<br>optional integral handle            |
| 12415<br>50415 [E] | PZ 9       | 24-1/2 x 13 x 8-3/8<br>(62.23 x 33.02 x 21.27)                    | 1-1/8 (2.86)                    | g = 3-1/2 (8.89)<br>h = 4-7/8 (12.38)           | 26 x 15-9/16 x 9<br>(66.04 x 39.53 x 22.86)                       | H0230M / L095              | foam option available<br>optional integral handle            |

# CASES: AIRMOLD® “R” SERIES


## Airmold® “R” Series - Integral Hinge Case



Expect performance from the Flambeau “R” series cases. With a wide range of cases to choose from, this case family features an integral hinge and latch system. This case is simple and reliable and is our most economical blow molded case offering.



Constructed from high-density polyethylene (HDPE) this case is tough enough for almost any challenge. Available as a double-wall case, or with a routed base to accommodate foam, this case offers maximum protection. A broad range of sizes and depths are available.



Airmold “R” Series Cases Continued on page 43

# CASES: AIRMOLD® “R” SERIES

| Stock Number | Style     | Interior Dimensions: L x W x overall D<br>(d x e x f) inches (cm) | Routed Depth = i<br>inches (cm) | Interior Depth:<br>Lid = g Base = h inches (cm) | Exterior Dimensions: L x W x overall D<br>(a x b x c) inches (cm) | Standard<br>Handle / Latch | Comments<br>inches (cm) |
|--------------|-----------|-------------------------------------------------------------------|---------------------------------|-------------------------------------------------|-------------------------------------------------------------------|----------------------------|-------------------------|
| 2504         | RA 2-1/16 | 6-5/8 x 4-3/4 x 1-3/4<br>(16.83 x 12.07 x 4.45)                   | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 1-1/8 (2.86)              | 7-1/2 x 5-3/4 x 2-1/16<br>(19.05 x 14.61 x 5.24)                  | none / Integral            |                         |
| 9431         | RA 2-5/8  | 6-5/8 x 4-3/4 x 2-5/16<br>(16.83 x 12.07 x 5.87)                  | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 1-3/8 (3.49)            | 7-1/2 x 5-3/4 x 2-5/8<br>(19.05 x 14.61 x 6.67)                   | none / Integral            |                         |
| 2505         | RA 3-7/16 | 6-5/8 x 4-3/4 x 3-1/8<br>(16.83 x 12.07 x 7.94)                   | 7/16 (1.11)                     | g = 1 (2.54)<br>h = 2-3/16 (5.56)               | 7-1/2 x 5-3/4 x 3-7/16<br>(19.05 x 14.61 x 8.73)                  | none / Integral            |                         |
| 48-9411      | RB 1-1/4  | 6-13/16 x 3-3/16 x 15/16<br>(17.30 x 8.10 x 2.38)                 | 1/4 (0.64)                      | g = 1/8 (0.32)<br>h = 13/16 (2.06)              | 7-1/2 x 4 x 1-1/4<br>(19.05 x 10.16 x 3.18)                       | none / Integral            |                         |
| 48-9512      | RB 1-5/8  | 6-13/16 x 3-3/16 x 1-5/16<br>(17.30 x 8.10 x 3.33)                | 1/4 (0.64)                      | g = 1/8 (0.32)<br>h = 1-3/16 (3.02)             | 7-1/2 x 4 x 1-5/8<br>(19.05 x 10.16 x 1.59)                       | none / Integral            |                         |
| 48-9513      | RB 1-5/8  | 6-13/16 x 3-3/16 x 1-5/16<br>(17.30 x 8.10 x 3.33)                | 1/4 (0.64)                      | g = 1/2 (1.27)<br>h = 13/16 (2.06)              | 7-1/2 x 4 x 1-5/8<br>(19.05 x 10.16 x 1.59)                       | none / Integral            |                         |
| 48-9514      | RB 2      | 6-13/16 x 3-3/16 x 1-11/16<br>(17.30 x 8.10 x 4.29)               | 1/4 (0.64)                      | g = 1/2 (1.27)<br>h = 1-3/16 (3.02)             | 7-1/2 x 4 x 2<br>(19.05 x 10.16 x 5.08)                           | none / Integral            |                         |
| 48-9515      | RB 2      | 6-13/16 x 3-3/16 x 1-11/16<br>(17.30 x 8.10 x 4.29)               | 1/4 (0.64)                      | g = 7/8 (2.22)<br>h = 13/16 (2.06)              | 7-1/2 x 4 x 2<br>(19.05 x 10.16 x 5.08)                           | none / Integral            |                         |
| 48-9516      | RB 2-3/8  | 6-13/16 x 3-3/16 x 2-1/16<br>(17.30 x 8.10 x 5.24)                | 1/4 (0.64)                      | g = 1/2 (1.27)<br>h = 1-9/16 (3.97)             | 7-1/2 x 4 x 2-3/8<br>(19.05 x 10.16 x 6.03)                       | none / Integral            |                         |
| 48-9517      | RB 2-3/8  | 6-13/16 x 3-3/16 x 2-1/16<br>(17.30 x 8.10 x 5.24)                | 1/4 (0.64)                      | g = 7/8 (2.22)<br>h = 1-3/16 (3.02)             | 7-1/2 x 4 x 2-3/8<br>(19.05 x 10.16 x 6.03)                       | none / Integral            |                         |
| 48-9518      | RB 2-3/4  | 6-13/16 x 3-3/16 x 2-7/16<br>(17.30 x 8.10 x 6.19)                | 1/4 (0.64)                      | g = 1/2 (1.27)<br>h = 1-15/16 (4.92)            | 7-1/2 x 4 x 2-3/4<br>(19.05 x 10.16 x 6.99)                       | none / Integral            |                         |
| 48-9519      | RB 2-3/4  | 6-13/16 x 3-3/16 x 2-7/16<br>(17.30 x 8.10 x 6.19)                | 1/4 (0.64)                      | g = 7/8 (2.22)<br>h = 1-9/16 (3.97)             | 7-1/2 x 4 x 2-3/4<br>(19.05 x 10.16 x 6.99)                       | none / Integral            |                         |
| 48-9520      | RB 3-1/8  | 6-13/16 x 3-3/16 x 2-13/16<br>(17.30 x 8.10 x 7.14)               | 1/4 (0.64)                      | g = 7/8 (2.22)<br>h = 1-15/16 (4.92)            | 7-1/2 x 4 x 3-1/8<br>(19.05 x 10.16 x 7.94)                       | none / Integral            |                         |
| 2500         | RC 1-3/4  | 7-9/16 x 5-7/8 x 1-7/16<br>(19.21 x 14.92 x 3.65)                 | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 13/16 (2.06)              | 8-1/2 x 7 x 1-3/4<br>(21.59 x 17.78 x 4.45)                       | none / Integral            |                         |
| 2509         | RC 2-3/8  | 7-9/16 x 5-7/8 x 2-1/16<br>(19.21 x 14.92 x 5.24)                 | 7/16 (1.11)                     | g = 1 (2.54)<br>h = 1-1/8 (2.86)                | 8-1/2 x 7 x 2-3/8<br>(21.59 x 17.78 x 6.03)                       | none / Integral            |                         |
| 2513         | RC 3-7/8  | 7-9/16 x 5-7/8 x 3-9/16<br>(19.21 x 14.92 x 9.05)                 | 7/16 (1.11)                     | g = 1 (2.54)<br>h = 2-5/8 (6.67)                | 8-1/2 x 7 x 3-7/8<br>(21.59 x 17.78 x 9.84)                       | H001 / Integral            |                         |
| 2524         | RF 1-3/4  | 8-5/8 x 4 x 1-7/16<br>(21.91 x 10.16 x 3.65)                      | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 13/16 (2.06)              | 9-1/2 x 5 x 1-3/4<br>(24.13 x 12.70 x 4.45)                       | none / Integral            |                         |
| 2527         | RF 3-1/8  | 8-5/8 x 4 x 2-13/16<br>(21.91 x 10.16 x 7.14)                     | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-3/16 (5.56)             | 9-1/2 x 5 x 3-1/8<br>(24.13 x 12.70 x 7.94)                       | H001 / Integral            |                         |
| 2532         | RH 1-3/4  | 9-1/8 x 6-1/2 x 1-7/16<br>(23.18 x 16.51 x 3.65)                  | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 13/16 (2.06)              | 10 x 7-1/2 x 1-3/4<br>(25.40 x 19.05 x 4.45)                      | none / Integral            |                         |
| 2533         | RH 2-3/8  | 9-1/8 x 6-1/2 x 2-1/16<br>(23.18 x 16.51 x 5.24)                  | 7/16 (1.11)                     | g = 1 (2.54)<br>h = 1-1/8 (2.86)                | 10 x 7-1/2 x 2-3/8<br>(25.40 x 19.05 x 6.03)                      | none / Integral            |                         |
| 2534         | RH 3-1/8  | 9-1/8 x 6-1/2 x 2-13/16<br>(23.18 x 16.51 x 7.14)                 | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-3/16 (5.56)             | 10 x 7-1/2 x 3-1/8<br>(25.40 x 19.05 x 7.94)                      | H001 / Integral            |                         |
| 2541         | RH 3-7/16 | 9-1/8 x 6-1/2 x 3-1/8<br>(23.18 x 16.51 x 7.94)                   | 7/16 (1.11)                     | g = 1 (2.54)<br>h = 2-3/16 (5.56)               | 10 x 7-1/2 x 3-7/16<br>(25.40 x 19.05 x 7.94)                     | H001 / Integral            |                         |
| 2537         | RH 3-7/8  | 9-1/8 x 6-1/2 x 3-9/16<br>(23.18 x 16.51 x 9.05)                  | 7/16 (1.11)                     | g = 1 (2.54)<br>h = 2-5/8 (6.67)                | 10 x 7-1/2 x 3-7/8<br>(25.40 x 19.05 x 9.84)                      | H001 / Integral            |                         |
| 2547         | RK 2-3/8  | 10-1/8 x 4-1/4 x 2-1/16<br>(25.72 x 10.80 x 5.34)                 | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 1-1/8 (2.86)            | 11 x 5-1/4 x 2-3/8<br>(27.94 x 13.34 x 6.03)                      | none / Integral            |                         |
| 2549         | RK 3-1/8  | 10-1/8 x 4-1/4 x 2-13/16<br>(25.72 x 10.80 x 7.14)                | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-3/16 (5.56)             | 11 x 5-1/4 x 3-1/8<br>(27.94 x 13.34 x 7.94)                      | H001 / Integral            |                         |
| 9624         | RK 3-9/16 | 10-1/8 x 4-1/4 x 3-1/4<br>(25.72 x 10.80 x 8.26)                  | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-5/8 (6.67)              | 11 x 5-1/4 x 3-9/16<br>(27.94 x 13.34 x 9.05)                     | H001 / Integral            |                         |
| 2560         | RN 1-3/4  | 11-3/8 x 5-1/4 x 1-7/16<br>(28.89 x 13.34 x 3.65)                 | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 13/16 (2.06)              | 12-1/4 x 6-1/4 x 1-3/4<br>(31.12 x 15.88 x 4.45)                  | none / Integral            |                         |
| 2569         | RN 3-7/16 | 11-3/8 x 5-1/4 x 3-1/8<br>(28.89 x 13.34 x 7.94)                  | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 2-3/16 (5.56)           | 12-1/4 x 6-1/4 x 3-7/16<br>(31.12 x 15.88 x 8.73)                 | H001 / Integral            |                         |
| 2565         | RN 3-7/8  | 11-3/8 x 5-1/4 x 3-9/16<br>(28.89 x 13.34 x 9.05)                 | 7/16 (1.11)                     | g = 15/16 (2.38)<br>h = 2-5/8 (6.67)            | 12-1/4 x 6-1/4 x 3-7/8<br>(31.12 x 15.88 x 9.84)                  | H001 / Integral            |                         |
| 2574         | RQ 1-3/4  | 11-3/8 x 7 x 1-7/16<br>(28.89 x 17.78 x 3.65)                     | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 13/16 (2.06)              | 12-1/4 x 8 x 1-3/4<br>(31.12 x 20.32 x 4.45)                      | none / Integral            |                         |
| 2581         | RQ 2-1/16 | 11-3/8 x 7 x 1-3/4<br>(28.89 x 17.78 x 4.45)                      | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 1-1/8 (2.86)              | 12-1/4 x 8 x 2-1/16<br>(31.12 x 20.32 x 5.24)                     | none / Integral            |                         |
| 2575         | RQ 2-3/8  | 11-3/8 x 7 x 2-1/16<br>(28.89 x 17.78 x 5.24)                     | 7/16 (1.11)                     | g = 1 (2.54)<br>h = 1-1/8 (2.86)                | 12-1/4 x 8 x 2-3/8<br>(31.12 x 20.32 x 6.03)                      | none / Integral            |                         |

“R” Series Cases Continued on page 44

# CASES: AIRMOLD® “R” SERIES

| Stock Number | Style     | Interior Dimensions: L x W x overall D<br>(d x e x f) inches (cm) | Routed Depth = i<br>inches (cm) | Interior Depth:<br>Lid = g Base = h inches (cm) | Exterior Dimensions: L x W x overall D<br>(a x b x c) inches (cm) | Standard<br>Handle / Latch | Comments<br>inches (cm)  |
|--------------|-----------|-------------------------------------------------------------------|---------------------------------|-------------------------------------------------|-------------------------------------------------------------------|----------------------------|--------------------------|
| 7144         | RQ 2-3/4  | 11-3/8 x 7 x 2-3/8<br>(28.89 x 17.78 x 6.03)                      | 7/16 (1.11)                     | g = 1-1/4 (3.18)<br>h = 1-1/8 (2.86)            | 12-1/4 x 8 x 2-3/4<br>(31.12 x 20.32 x 6.99)                      | none / Integral            |                          |
| 2577         | RQ 3-1/8  | 11-3/8 x 7 x 2-13/16<br>(28.89 x 17.78 x 7.14)                    | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-3/16 (5.56)             | 12-1/4 x 8 x 3-1/8<br>(31.12 x 20.32 x 7.94)                      | H052 / Integral            |                          |
| 2579         | RQ 3-7/8  | 11-3/8 x 7 x 3-9/16<br>(28.89 x 17.78 x 9.05)                     | 7/16 (1.11)                     | g = 1 (2.54)<br>h = 2-5/8 (6.67)                | 12-1/4 x 8 x 3-7/8<br>(31.12 x 20.32 x 9.84)                      | H001 / Integral            |                          |
| 2585         | RQ 4-1/4  | 11-3/8 x 7 x 3-7/8<br>(28.89 x 17.78 x 9.84)                      | 7/16 (1.11)                     | g = 1-1/4 (3.18)<br>h = 2-5/8 (6.67)            | 12-1/4 x 8 x 4-1/4<br>(31.12 x 20.32 x 10.80)                     | H001 / Integral            |                          |
| 2588         | RT 1-3/4  | 11-5/8 x 3-1/4 x 1-7/16<br>(29.53 x 8.26 x 3.65)                  | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 13/16 (2.06)              | 12-1/2 x 4-1/4 x 1-3/4<br>(31.75 x 10.80 x 4.45)                  | none / Integral            |                          |
| 2590         | RT 3-1/8  | 11-5/8 x 3-1/4 x 2-13/16<br>(29.53 x 8.26 x 7.14)                 | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-3/16 (5.56)             | 12-1/2 x 4-1/4 x 3-1/8<br>(31.75 x 10.80 x 7.94)                  | none / Integral            |                          |
| 2618         | RV 2-1/16 | 12-11/16 x 8-15/16 x 1-3/4<br>(32.23 x 22.70 x 4.45)              | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 1-1/8 (2.86)              | 13-1/2 x 10 x 2-1/16<br>(34.29 x 25.40 x 5.24)                    | none / Integral            |                          |
| 2596         | RV 2-3/8  | 12-11/16 x 8-15/16 x 2-1/16<br>(32.23 x 22.70 x 5.24)             | 7/16 (1.11)                     | g = 1 (2.54)<br>h = 1-1/8 (2.86)                | 13-1/2 x 10 x 2-3/8<br>(34.29 x 25.40 x 6.03)                     | none / Integral            |                          |
| 2597         | RV 3-1/8  | 12-11/16 x 8-15/16 x 2-13/16<br>(32.23 x 22.70 x 7.14)            | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-3/16 (5.56)             | 13-1/2 x 10 x 3-1/8<br>(34.29 x 25.40 x 7.94)                     | none / Integral            |                          |
| 2611         | RV 3-7/16 | 12-11/16 x 8-15/16 x 2-13/16<br>(32.23 x 22.70 x 7.14)            | 7/16 (1.11)                     | g = 5/8 (1.59)<br>h = 2-13/16 (7.14)            | 13-1/2 x 10 x 3-7/16<br>(34.29 x 25.40 x 8.73)                    | H024 / Integral            |                          |
| 2600         | RV 4      | 12-11/16 x 8-15/16 x 3-11/16<br>(32.23 x 22.70 x 9.67)            | 7/16 (1.11)                     | g = 1 (2.54)<br>h = 2-3/4 (6.99)                | 13-1/2 x 10 x 4<br>(34.29 x 25.40 x 10.16)                        | H052 / Integral            |                          |
| 2605         | RV 5-1/8  | 12-11/16 x 8-15/16 x 4-3/4<br>(32.23 x 22.70 x 12.07)             | 7/16 (1.11)                     | g = 1-1/2 (3.81)<br>h = 3-1/4 (8.26)            | 13-1/2 x 10 x 5-1/8<br>(34.29 x 25.40 x 13.02)                    | H024 / Integral            |                          |
| 2619         | RV 6-1/8  | 12-11/16 x 8-15/16 x 5-5/8<br>(32.23 x 22.70 x 14.29)             | 7/16 (1.11)                     | g = 1-7/8 (4.76)<br>h = 3-3/4 (9.53)            | 13-1/2 x 10 x 6-1/8<br>(34.29 x 25.40 x 15.56)                    | H024 / Integral            |                          |
| 7205         | RW 4-3/4  | 14 x 10-3/4 x 4-1/4<br>(35.56 x 27.31 x 10.80)                    | 1-1/4 (3.18)                    | g = 1-3/8 (3.49)<br>h = 2-7/8 (7.30)            | 15-1/2 x 12-1/4 x 4-3/4<br>(39.37 x 31.12 x 12.07)                | H0230M/Integral            | optional integral handle |
| 7279         | RW 5-1/2  | 14 x 10-3/4 x 5<br>(35.56 x 27.31 x 12.70)                        | 1-1/4 (3.18)                    | g = 2-1/8 (5.40)<br>h = 2-7/8 (7.30)            | 15-1/2 x 12-1/4 x 5-1/2<br>(39.37 x 31.12 x 13.97)                | H0230M/Integral            | optional integral handle |
| 7207         | RW 5-1/2  | 14 x 10-3/4 x 5<br>(35.56 x 27.31 x 12.70)                        | 1-1/4 (3.18)                    | g = 1-3/8 (3.49)<br>h = 3-5/8 (9.21)            | 15-1/2 x 12-1/4 x 5-1/2<br>(39.37 x 31.12 x 13.97)                | H0230M/Integral            | optional integral handle |
| 7203         | RW 6-1/4  | 14 x 10-3/4 x 5-3/4<br>(35.56 x 27.31 x 14.61)                    | 1-1/4 (3.18)                    | g = 2-1/8 (5.40)<br>h = 3-5/8 (9.21)            | 15-1/2 x 12-1/4 x 6-1/4<br>(39.37 x 31.12 x 15.88)                | H0230M/Integral            | optional integral handle |
| 14523        | RX 3      | 17 x 13 x 2-1/2<br>(43.18 x 33.02 x 6.35)                         | 15/16 (2.38)                    | g = 7/8 (2.22)<br>h = 1-5/8 (4.13)              | 18-1/2 x 14-1/2 x 3<br>(46.99 x 36.83 x 7.62)                     | H0230M/Integral            | optional integral handle |
| 2725         | RX 5      | 17 x 13 x 4-1/2<br>(43.18 x 33.02 x 11.43)                        | 15/16 (2.38)                    | g = 1-3/8 (3.49)<br>h = 3-1/8 (7.94)            | 18-1/2 x 14-1/2 x 5<br>(46.99 x 36.83 x 12.70)                    | H0230M/Integral            | optional integral handle |
| 2728         | RX 6-1/4  | 17 x 13 x 5-5/8<br>(43.18 x 33.02 x 14.29)                        | 15/16 (2.38)                    | g = 1-3/4 (4.45)<br>h = 3-7/8 (9.84)            | 18-1/2 x 14-1/2 x 6-1/4<br>(46.99 x 36.83 x 12.70)                | H0230M/Integral            | optional integral handle |
| 2742         | RX 8      | 17 x 13 x 7-3/8<br>(43.18 x 33.02 x 18.73)                        | 15/16 (2.38)                    | g = 3-1/2 (8.89)<br>h = 3-7/8 (9.84)            | 18-1/2 x 14-1/2 x 8<br>(46.99 x 36.83 x 20.32)                    | H0230M / L037              | optional integral handle |

## Beta Case

Durability is built into this case! Made of high-density polyethylene (HDPE), this case is impervious to most common chemicals. Featuring an integral handle, hinge and latch system, the Beta Case is built tough.



| Model Number | Stock Number | Description inches (centimeters)                                                                           | Dimensions (Inside, L x W x D)                     | Packed |
|--------------|--------------|------------------------------------------------------------------------------------------------------------|----------------------------------------------------|--------|
| 21496        | 21496        | Color: Black, double-wall case<br>Lid Depth = 1-1/2 (3.81) Base Depth = 1-1/2 (3.81)                       | 13" x 8-1/2" x 2-3/4"<br>(33.02 x 21.59 x 6.99 cm) | 16/ctn |
| 50237        | 50237        | Color: Black, double-wall case with small logo plate<br>Lid Depth = 1-1/2 (3.81) Base Depth = 1-1/2 (3.81) | 13" x 8-1/2" x 2-3/4"<br>(33.02 x 21.59 x 6.99 cm) | 16/ctn |

# CASES: BLACK RIBBON™

## Black Ribbon™ Cases

Flambeau introduces a new product line of **water resistant cases** available in four sizes! Each precision Black Ribbon™ case features a 360 degree. These extremely durable cases also feature a metal front cam locking mechanical latch system and external rubber bumpers for impact absorption, skid resistance, and greater durability. Cases are made of tough impact resistant ABS plastic.

Flambeau Black Ribbon Cases (shown below) are sold with "open" core or flat foam lid and base. Cases can easily be outfitted with die cut foam inserts when required for added nesting and protection of your valuables. These cases are excellent for outdoor use in demanding environments. They are ideal for storing and protecting cell phones, iPods, electronic devices, jewelry, small tools and components.

### Sample usage

Rugged and water resistant!



**6734PF**

Shown with flat foam lid & base



**6735PC**

Shown without foam



**Sample usage**  
Customized case



| Model Number  | Stock Number | Description                                         | Dimensions (Inside, L x W x D)                         | Packed |
|---------------|--------------|-----------------------------------------------------|--------------------------------------------------------|--------|
| <b>6734PC</b> | 6734PC       | 4-3/8" (11.11 cm) Black - without Foam              | 3-7/8" x 2-3/8" x 1-3/8"<br>(9.84 x 6.03 x 3.49 cm)    | 4/ctn  |
| <b>6734PF</b> | 6734PF       | 4-3/8" (11.11 cm) Black - with Flat Foam Lid & Base |                                                        |        |
| <b>6735PC</b> | 6735PC       | 5" (12.70 cm) Black - without Foam                  | 4-3/8" x 2-7/8" x 1-3/8"<br>(11.11 x 7.30 x 3.49 cm)   | 4/ctn  |
| <b>6735PF</b> | 6735PF       | 5" (12.70 cm) Black - with Flat Foam Lid & Base     |                                                        |        |
| <b>6736PC</b> | 6736PC       | 6-1/4" (15.56 cm) Black - without Foam              | 5-7/8" x 2-3/4" x 1-1/2"<br>(14.92 x 6.99 x 3.81 cm)   | 4/ctn  |
| <b>6736PF</b> | 6736PF       | 6-1/4" (15.56 cm) Black - with Flat Foam Lid & Base |                                                        |        |
| <b>6737PC</b> | 6737PC       | 7-3/4" (19.69 cm) Black - without Foam              | 7-1/8" x 3-5/8" x 1-11/16"<br>(18.10 x 9.21 x 4.29 cm) | 4/ctn  |
| <b>6737PF</b> | 6737PF       | 7-3/4" (19.69 cm) Black - with Flat Foam Lid & Base |                                                        |        |
| <b>6738PC</b> | 6737PC       | 8-3/4" (22.23 cm) Black - without Foam              | 8-1/2" x 5-1/4" x 2-1/4"<br>(21.59 x 13.34 x 5.72 cm)  | 4/ctn  |

# CASES: ACCESSORIES

## Flambeau Case Handles & Latches

Infinity (Reference Chart on page 38)



**Handle - H052**

Styles: FH, FQ (4-1/2 only) & FV



**Handle - H023**

Styles: FW & FX



**Over Mold Grip Handle - H0230M**

Styles: FH, FQ, FV, FW, FX & FZ




**Latch - L085**

Style: FW



**Latch - L115**

Style: FZ (8-1/2)



**Handle - H074**

Style: FZ



**Latch - L089**

Styles: FH, FQ & FV



**Latch - L095**

Style: FX



**Latch - L116**

Style: FZ (7)

## "P" Series (Reference Chart on page 40-41)

Some cases do not have a handle option available, please see **page 40-41** to see which specific cases they are.



**Handle - H001**

Styles: PC, PF (3-1/8 only), PH



**Handle - H052**

Styles: PQ (3-7/16, 3-13/16 & 3-7/8 only), PV



**Handle - H023**

Styles: PW (4, 4-3/4, 5-1/2 & 6-1/4 only), PX (8 only), PZ



**Handle - Integral**

Styles: PW, PX & PZ



**Latch - L089**

Styles: PB, PC, PF, PH, PQ, PV



**Latch - L085**

Styles: PW (4, 4-3/4, 5-1/2 & 6-1/4 only), PX (8 only)



**Latch - L026**

Styles: PW (6-1/4 only)  
PX (5 & 8 only)



**Latch - L037**

Styles: PX (3-1/2, 5, 6-1/4 & 8 only)



**Latch - L095**

Use with Style: PZ

## Airmold® "R" Series (Reference Chart on page 42-44)

Some cases do not have a handle option available, please see **page 42-44** to see which specific cases they are.



**Handle - H001**

Styles: RA (3-1/8 & 3-7/16 only),  
RC (3-7/8 only), RF (3-1/8 only),  
RH (3-1/8, 3-7/16 & 3-7/8 only),  
RK (3-1/8 & 3-9/16 only),  
RN (3-7/16 & 3-7/8 only)  
& RQ (3-7/8 & 4-1/4 only)




**Handle - H024**

Style: RV (3-7/16, 5-1/8 & 6-1/8 only)



**Handle - H023**

Styles: RW, RX



**Latch - Integral**

Styles: RA, RB, RC, RF, RH,  
RK, RN, RQ, RT, RV, RW,  
& RX (3, 5 & 6-1/4 only)



**Latch - L037**

Styles: RX (8 only)

## Optional Handles and Latches



**Handle - Integral**  
P Series Case Styles  
PW, PX & PZ  
R Series Case Styles  
RW & RX



**Handle - H074**  
Gear Box & Custom Case  
Applications Only



**Handle - H040**  
Custom Case Applications  
Only



**Infinity Metal  
Latch - L078**  
Styles FW, FX & Custom  
Case Applications



**Latch - L115**  
Custom Case Applications  
Only



**Latch - L0110**  
Custom Case Applications  
Only

## Display Windows

The windows are manufactured from a clear plastic resin and can be hot stamped with your company name or logo. Four sizes of windows are available and are custom fitted to our pin hinge style cases.



**AR1466 (L x W)**  
7-1/2" x 3-1/2"  
(19.05 x 8.89 cm)



**AR1536 (L x W)**  
10-1/4" x 3"  
(26.04 x 7.62 cm)



**X-1191 Small (L x W)**  
5-15/16" x 1-15/16"  
(15.08 x 4.92 cm)



**X-1193 Large (L x W)**  
8-7/16" x 2-3/16"  
(21.43 x 5.56 cm)

## Additional Options



**Flambeau Purge Valve**



**Perimeter Gasket**



**Custom Small & Large  
Exterior Logo Plate**  
additional tooling expense



**Lid Stays**



**Interior Door(s)**  
additional tooling expense



**Interior Tray(s)**  
additional tooling expense



**Security Feature**



**Removable Lid**



**Literature Holder  
Routed Slot**



**Literature Holder  
Plastic Clip - X893**



**Literature Holder  
Elastic Strap**



**Pallets and/or File Folders**

*For information on Flambeau's Custom Capabilities see the Custom Capabilities Section starting on page 8.*

# CASES: BLOW MOLDED TRADESMAN™ & MAILERS

## Blow Molded Tradesman™ Case

Featuring extra thick walls the Blow Molded Tradesman is one of our most durable cases. This high-density polyethylene (HDPE) case is resistant to most common chemicals, gasoline and the harshest conditions. Simply, this case is built to be abused! The sleek design includes an integral handle, hinge and latch system.

*We encourage you to challenge this case!*



Features a logo area for customization



19978

| Model Number                                                                            | Stock Number | Description                                 | Dimensions (Inside, L x W x D)                     | Packed |
|-----------------------------------------------------------------------------------------|--------------|---------------------------------------------|----------------------------------------------------|--------|
| 19978  | 19978        | Black double-wall case with logo plate area | 15" x 8-1/2" x 3-1/2"<br>(38.10 x 21.59 x 8.89 cm) | 16/ctn |

## Mailers

Reusable shipping containers from Flambeau will help you save money and give you the durability needed to protect your cargo while in transit. Our blow molded mailers feature double-wall construction and are stackable. Offered with our standard convoluted foam they are designed to protect even the most sensitive cargo. Lids and bases are separate pieces for loading convenience and feature overlapping positive edges to reduce lid movement and provide a natural dust barrier. Lids and bases must be secured for transit. Made of high-density polyethylene (HDPE) our mailers are impervious to most common chemicals and gasoline.



mailer with convoluted foam



| Model Number                                                                                            | Stock Number | Outside Dimensions<br>(L x W x D) inches (cm)    | Inside Dimensions<br>(L x W x D) inches (cm)       | Maximum Load Size<br>(L x W x D) inches (cm)       | Packed |
|---------------------------------------------------------------------------------------------------------|--------------|--------------------------------------------------|----------------------------------------------------|----------------------------------------------------|--------|
| 8792<br>8792-PI04    | 8792-PI04    | 12" x 10" x 3"<br>(30.48 x 25.40 x 7.62 cm)      | 9-1/2" x 7" x 1-5/8"<br>(24.13 x 17.78 x 4.13 cm)  | 8-1/2" x 6" x 1"<br>(21.59 x 15.24 x 2.54 cm)      | 32/ctn |
| 8793<br>8793-PI05    | 8793-PI05    | 12" x 10" x 5"<br>(30.48 x 25.40 x 12.70 cm)     | 9-1/2" x 7" x 4"<br>(24.13 x 17.78 x 10.16 cm)     | 8-1/2" x 6" x 3-1/4"<br>(21.59 x 15.24 x 8.26 cm)  | 32/ctn |
| 8794<br>8794-PI06    | 8794-PI07    | 14" x 12" x 3"<br>(35.56 x 30.48 x 7.62 cm)      | 11-1/2" x 9" x 1-5/8"<br>(29.21 x 22.86 x 4.13 cm) | 10-1/2" x 8" x 1"<br>(26.67 x 20.32 x 2.54 cm)     | 32/ctn |
| 8286<br>8286-PI07    | 8286-PI06    | 14" x 12" x 5"<br>(35.56 x 30.48 x 12.70 cm)     | 11-1/2" x 9" x 4"<br>(29.21 x 22.86 x 10.16 cm)    | 10-1/2" x 8" x 3-1/4"<br>(26.67 x 20.32 x 8.26 cm) | 32/ctn |
| 8162<br>8162-PI14    | 8162-PI14    | 8" x 6" x 3"<br>(20.32 x 15.24 x 7.62 cm)        | 6" x 4" x 1-5/8"<br>(15.24 x 10.16 x 4.13 cm)      | 5" x 3" x 1"<br>(12.70 x 7.62 x 2.54 cm)           | 48/ctn |
| 8161<br>8161-PI19    | 8161-PI19    | 21" x 15" x 5"<br>(53.34 x 38.10 x 12.70 cm)     | 18" x 12" x 4"<br>(45.72 x 30.48 x 10.16 cm)       | 17" x 11" x 2-1/2"<br>(43.18 x 27.94 x 6.35 cm)    | 6/ctn  |
| 10133<br>10133-PI20  | 10133-PI20   | 27" x 14-1/2" x 7"<br>(68.58 x 36.83 x 17.78 cm) | 24" x 12" x 6"<br>(60.96 x 30.48 x 15.24 cm)       | 23" x 11" x 2-5/8"<br>(58.42 x 27.94 x 6.67 cm)    | 3/ctn  |


## Stationary & Mobile Storage

Flambeau's mobile and stationary storage systems can help you improve your space utilization and increase your productivity. Our wide variety of products gives you the flexibility to quickly select a system that works for your specific needs. With some of the most durable products in the industry, our extra heavy-duty products are constructed with copolymer resins, that are dent-proof, rust-proof, chemical-, scratch-, and impact-resistant and built to last! Many products feature brass pin hinges, positive cam-over latches, tongue and groove construction and other structural features that any professional would expect.

### IDS™ Cabinets - Infinite Divider Storage System

A hybrid between mobile and stationary storage, these cabinets have interlocking grooves for easy and secure stacking. The IDS system truly gives you mastery over your storage space with (5) IDS translucent cases featuring dividers that can be placed every 1/16" (0.16 cm) throughout the compartments! From 1 compartment to 100 compartments, each individual case fits into its own tray within the cabinet and can be easily and quickly removed to be taken to a remote site while keeping the parts secure.

- Dent-proof polypropylene housing
- Interlocking stackable cabinets
- Easily moved
- Fully extendable drawers
- Removable cases
- Infinite Divider System



IDS Cabinet with 5 trays, no boxes




IDS Cabinet with 5 trays and (5) T900 Boxes



IDS Cabinet with 5 trays and (5) 999-2 Boxes



Special interlocking grooves on the cabinets allow them to be stacked on top of each other.



T900 Inside Dimensions (L x W x D)  
13-1/8" x 8-7/8" x 1-15/16" (33.34 x 22.54 x 4.92 cm)



999-2 Inside Dimensions (L x W x D)  
13-1/8" x 8-7/8" x 1-15/16" (33.34 x 22.54 x 4.92 cm)

| Model Number | Stock Number | Description inch (centimeter)                                                   | Dimensions (Outside, L x W x D)                       | Packed |
|--------------|--------------|---------------------------------------------------------------------------------|-------------------------------------------------------|--------|
| 8500NT       | 8500NT       | Cabinet with (5) trays, no boxes                                                | 15-1/4" x 14-3/4" x 16"<br>(13.34 x 37.47 x 40.64 cm) | 1/ctn  |
| 8500ST       | 8500ST       | Cabinet with (5) trays and (5) T900 boxes<br>T900 boxes come with 16 dividers   | 15-1/4" x 14-3/4" x 16"<br>(13.34 x 37.47 x 40.64 cm) | 1/ctn  |
| 8500JT       | 8500JT       | Cabinet with (5) trays and (5) 999-2 boxes<br>999-2 boxes come with 16 dividers | 15-1/4" x 14-3/4" x 16"<br>(13.34 x 37.47 x 40.64 cm) | 1/ctn  |

See the Compartmented Box Section (pages 14-34) for additional boxes that will work within the IDS Cabinet and for replacement T900 & 999-2 IDS boxes.

# SPECIALTY STORAGE

## Parts Station™ Storage Cabinets & Rototower™

High density storage, maximum organization and cost savings efficiency can be achieved with our generous selection of reinforced durable plastic frame storage cabinets and expandable Rototower. Each drawer cabinet features styrene translucent drawers and drawer stops to prevent accidental spills while our tower has a heavy-duty tip-resistant steel base with slip-proof feet. Easy rotation is aided by our extra large ball-bearing rotating system.



Holds 16 Cabinets.


Uses the C26P and U45P Cabinets.

Not shown to scale, with cabinets to left.

All cabinets include (10) 35/52 dividers, all other dividers are optional


| Model Number | Stock Number | Description                                                                          | Uses Drawer                           | Uses Divider                       | Dimensions (Outside, L x W x H)                             | Packed |
|--------------|--------------|--------------------------------------------------------------------------------------|---------------------------------------|------------------------------------|-------------------------------------------------------------|--------|
| <b>C20P</b>  | 6575PC       | Color: Gray<br>Clear Styrene Drawers<br>Clear Styrene Dividers                       | (15) TW<br>(4) TQ<br>(1) TF           | 35/52<br>50/64<br>57/275           | 12" x 6-1/4" x 11-1/4"<br>(30.48 x 15.88 x 28.58 cm)        | 4/ctn  |
| <b>C26P</b>  | 6576PC       | Color: Gray<br>Clear Styrene Drawers<br>Clear Styrene Dividers                       | (15) TW<br>(8) TQ<br>(2) TJ<br>(1) TF | 35/52<br>50/64<br>57/135<br>57/275 | 12" x 6-1/4" x 16-1/2"<br>(30.48 x 15.88 x 41.91 cm)        | 4/ctn  |
| <b>U30P</b>  | 6573PC       | Color: Gray<br>Clear Styrene Drawers<br>Clear Styrene Dividers                       | (30) TW                               | 35/52                              | 12" x 6-1/4" x 11-1/4"<br>(30.48 x 15.88 x 28.58 cm)        | 4/ctn  |
| <b>U45P</b>  | 6574PC       | Color: Gray<br>Clear Styrene Drawers<br>Clear Styrene Dividers                       | (45) TW                               | 35/52                              | 12" x 6-1/4" x 16-1/2"<br>(30.48 x 15.88 x 41.91 cm)        | 4/ctn  |
| <b>160RT</b> | 6798RT       | Gray Rototower<br>Holds 16 Cabinets.<br>Uses C26P & U45P<br>Cabinets Sold Separately | -                                     | -                                  | 18-1/2" x 18-1/2" x 72-1/2"*<br>(46.99 x 46.99 x 184.15 cm) | 1/ctn  |

\* from floor to top of cabinet



160RT Rototower™

## Replacement Drawers & Dividers\* (Plastic Frame Cabinets)



| Model Number | Stock Number | Description                                                                                | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|--------------------------------------------------------------------------------------------|-----------------------------------------------------|--------|
| <b>TW</b>    | 6062DP       | Uses (3) 35/52 dividers, dividers sold separately                                          | 2" x 5-3/8" x 1-3/8" (5.08 x 13.65 x 3.49 cm)       | 6/pk   |
| <b>TQ</b>    | 6063DP       | Uses (3) 50/64 dividers, dividers sold separately                                          | 2-1/2" x 5-3/8" x 2-1/4" (6.35 x 13.65 x 5.72 cm)   | 6/pk   |
| <b>TJ</b>    | 6066DP       | Uses (3) 57/135 dividers, dividers sold separately                                         | 5-3/8" x 5-3/8" x 2-1/4" (13.65 x 13.65 x 5.72 cm)  | 6/pk   |
| <b>TF</b>    | 6068DP       | Uses (3) 57/135 or (1) 57/275 or (1) 57/275 & (6) 50/64 dividers, dividers sold separately | 10-7/8" x 5-3/8" x 2-1/4" (27.62 x 13.65 x 5.72 cm) | 6/pk   |

| Model Number  | Stock Number | Description                                                              | Dimensions (Inside, L x W x D)               | Packed |
|---------------|--------------|--------------------------------------------------------------------------|----------------------------------------------|--------|
| <b>35/52</b>  | 6770DV       | Divider fits in Drawer TW, Divider wall thickness 1/16" (1.588 cm)       | 2" x 1-1/4" x 1/8" (5.08 x 3.18 x 0.32 cm)   | 48/pk  |
| <b>50/64</b>  | 6775DV       | Divider fits in Drawer TQ & TF, Divider wall thickness 1/16" (1.588 cm)  | 2-1/2" x 2" x 1/8" (6.35 x 5.08 x 0.32 cm)   | 24/pk  |
| <b>57/135</b> | 6778DV       | Divider fits in Drawers TJ & TF, Divider wall thickness 1/16" (1.588 cm) | 5-3/8" x 2" x 1/8" (13.65 x 5.08 x 0.32 cm)  | 12/pk  |
| <b>57/275</b> | 6779DV       | Divider fits in Drawers TF, Divider wall thickness 1/16" (1.588 cm)      | 10-7/8" x 2" x 1/8" (27.62 x 5.08 x 0.32 cm) | 6/pk   |


\* Contact Customer Service for large quantity divider purchases at 1-800-344-5716.

## Satchel-Style Cases

A fantastic heavy-duty professional case! The Satchel case is commonly used as a parts or sales sample kit. The tinted lid is made of a high impact, scratch-resistant terpolymer, that gives you a quick view of parts. The case base, dividers, handle and catches are all molded from impact resistant polypropylene. Satchel Cases – a popular pick due to its durability, ease of use and an esthetic value. Large and small sizes available.

- Comfortable fold-down handle
- Can be customized (color or company logo)
- Tinted “quick-view” lid
- Rust-proof heavy-duty hinges





## Small Satchel-Style Cases



| Model Number | Stock Number | Description inch (centimeter)                                                              | Dimensions (Outside, L x W x D)                         | Packed |
|--------------|--------------|--------------------------------------------------------------------------------------------|---------------------------------------------------------|--------|
| 711-2        | 6771UA       | Tinted translucent lid, 1 compartment                                                      | 15-1/2" x 11-3/4" x 2-1/2"<br>(39.37 x 28.85 x 6.35 cm) | 12/ctn |
| 724-2        | 6770PA       | Tinted translucent lid, 9-24 compartments, includes 15 movable dividers                    | 15-1/2" x 11-3/4" x 2-1/2"<br>(39.37 x 28.85 x 6.35 cm) | 12/ctn |
| 725-2        | 6773AB       | Double sided with tinted translucent lid, 10-25 compartments, includes 15 movable dividers | 15-1/2" x 11-3/4" x 5"<br>(39.37 x 28.85 x 12.70 cm)    | 6/ctn  |
| 748-2        | 6772AD       | Double sided with tinted translucent lid, 18-48 compartments, includes 30 movable dividers | 15-1/2" x 11-3/4" x 5"<br>(39.37 x 28.85 x 12.70 cm)    | 6/ctn  |

Divider Packs Available (sold separately): 12pk of dividers for 724-2, 725-2 & 748-2 is order #6020DP. Bulk pks of dividers for 724-2, 725-2 & 748-2 is order #602025

## Large Satchel-Style Cases



| Model Number | Stock Number | Description inch (centimeter)                                          | Dimensions (Outside, L x W x D)                 | Packed |
|--------------|--------------|------------------------------------------------------------------------|-------------------------------------------------|--------|
| 1016-2       | 6745AB       | Tinted translucent lid, 4-16 compartments Includes 12 movable dividers | 18-1/2" x 13" x 3"<br>(46.99 x 33.02 x 7.62 cm) | 6/ctn  |
| 1021-2       | 6745AG       | Tinted translucent lid, 21 compartments                                | 18-1/2" x 13" x 3"<br>(46.99 x 33.02 x 7.62 cm) | 6/ctn  |
| 1024-2       | 6745AA       | Tinted translucent lid, 24 compartments                                | 18-1/2" x 13" x 3"<br>(46.99 x 33.02 x 7.62 cm) | 6/ctn  |
| 1032-2       | 6745AC       | Tinted translucent lid, 8-32 compartments Includes 24 movable dividers | 18-1/2" x 13" x 3"<br>(46.99 x 33.02 x 7.62 cm) | 6/ctn  |


Divider Packs Available (sold separately): 12 pk of dividers for 1016-2 is order #6014DP. Bulk pks of dividers for 1016-2 is order #601312. 12 pk of dividers for 1032-2 is order #6013DP. Bulk pks of dividers for 1032-2 is order #601303.

# SPECIALTY STORAGE

## Carry Packs™


Only from Flambeau! Carry Packs give your storage compartments mobility! From the shelf or wall (mountable), this system gives you the high density storage and organization you need and the freedom to easily get your parts to the work site.

- Each Carry Pack is stocked with specific compartmented boxes
- Boxes lock in place for ease of folding and carrying
- Each box can be quickly disengaged for part access
- Carry Pack frames are available with or without boxes
- Other boxes available for each Carry Pack\*



21210-2 Folded


21210-2 Flat



20220-2 Diagram (flat)

Comes with (2) T221 &


(2) T220 Translucent Polypropylene Boxes\*\*



21210-2 Diagram (flat)

Comes with (2) T210 &

(2) T215 Translucent Polypropylene Boxes\*\*



21600-2 Diagram (flat)

Comes with (1) T618 &

(1) T612 Translucent Polypropylene Boxes\*\*

| Model Number | Stock Number | Description inch (centimeter)                                                                             | Dimensions (Overall, L x W x D)                          | Packed |
|--------------|--------------|-----------------------------------------------------------------------------------------------------------|----------------------------------------------------------|--------|
| 20220-2      | 6701VU       | Comes with (2) T220 & (2) T221 Boxes<br>Box (L x W x D) = 4-3/8 x 2-5/8 x 1 (11.11 x 6.67 x 2.54)         | 9-3/4" x 8-3/4" x 1-1/2"<br>(24.77 x 22.23 x 3.81 cm)    | 6/ctn  |
| 6701NB       | 6701NB       | Frame Only                                                                                                | 9-3/4" x 8-3/4" x 1-1/2"<br>(24.77 x 22.23 x 3.81 cm)    | 6/ctn  |
| 21210-2      | 6709VU       | Comes with (2) T210 & (2) T215 Boxes<br>Box (L x W x D) = 6-3/4 x 3-3/16 x 1-3/16 (17.15 x 8.10 x 3.02)   | 14-1/4" x 10-3/4" x 1-1/2"<br>(36.20 x 27.31 x 3.81 cm)  | 6/ctn  |
| 6709NB       | 6709NB       | Frame Only                                                                                                | 14-1/4" x 10-3/4" x 1-1/2"<br>(36.20 x 27.31 x 3.81 cm)  | 6/ctn  |
| 21600-2      | 6728VU       | Comes with (1) T612 & (1) T618 Boxes<br>Box (L x W x D) = 10-1/2 x 6-3/16 x 1-9/16 (26.67 x 15.72 x 3.97) | 13-7/16" x 13-1/2" x 2-1/8"<br>(34.13 x 34.29 x 5.40 cm) | 6/ctn  |
| 6728NB       | 6728NB       | Frame Only                                                                                                | 13-7/16" x 13-1/2" x 2-1/8"<br>(34.13 x 34.29 x 5.40 cm) | 6/ctn  |

\*Additional boxes (sold separately) available for the 20220-2 are: A220, K220, M220, A221, M221, A226, K226, and A228.

Additional boxes (sold separately) available for the 21210-2 are: A210, K210, M210, A211, A212, A213, A214, A215, K215, M215, A216, K216, A217, A219, K219, and T219

Additional boxes (sold separately) available the 21600-2 are: A601, K601, A602, K602, M602, A603, A606, K606, M606, T606, A607, K607, A612, M612, A613, K616R, M616R, T616R, A618, K618, M618, A623, K623, and M623. Information on these boxes can be found in the Compartmented Box Section starting on **page 20**

## Step 'N Store™ Stool

A cross between a tool box and a step stool, the Step 'N Store makes a great companion for tool portability and that often needed "little extra reach" on any job site.

- Engineered to support 300 pounds (136.08 kg)
- Heavy-duty riveted fold-down handle
- Lift-out center tray



22500-3

| Model Number | Stock Number | Description inch (centimeter)                                                                 | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|-----------------------------------------------------------------------------------------------|-----------------------------------------------------|--------|
| 22500-3      | 6759TC       | Color: Safety Yellow<br>Tray Dimensions (L x W x D) 14 x 8-1/4 x 1-5/8 (35.56 x 20.96 x 4.13) | 15-1/2" x 9" x 7-1/2"<br>(39.37 x 22.86 x 19.05 cm) | 2/ctn  |

## Expandable Tube

- Contoured, blow molded construction - won't bend, crush or break
- Hinged door makes it easy to load and unload
- Molded-in handle for maximum durability
- Completely lockable for added security
- Telescopes from 63" (160.02 cm) to 87" (220.99 cm) for maximum versatility



50077

| Model Number | Stock Number | Description                   | Dimensions (Inside, L x W x D)                         | Packed |
|--------------|--------------|-------------------------------|--------------------------------------------------------|--------|
| 50077        | 50077        | Color: Black, expandable tube | 3-1/4" x 61-1/2" x 85-1/2" (8.26 x 156.21 x 217.17 cm) | 1/ctn  |

**NEW**

# SPECIALTY STORAGE: GUN CASES

## Protective Gun Cases

These cases protect your guns from bumps & bruises while preventing unwanted trespassers into the case. The guns are blanketed with egg-shell foam padding, four locking points and piano style hinge to prevent opening during transport.

### Economy Single Gun Case

- Largest economy single available
- Four locking points and piano style hinge
- keeps children out when properly locked
- Durable egg-shell foam

Patent #D498,052, #6,874,628



### Single Gun Case

- Four locking points for extra security
- Combination of piano style hinge and brass hinge provide durability, safety and protection
- Oversized single fits most scoped rifles
- Durable egg-shell foam

Patent #D498,052, #6,874,628



### Double Gun Case

- Four locking points for extra security
- Combination of piano style hinge and brass hinge provide durability, safety & protection
- Oversized double will accommodate two scoped rifles
- Durable egg-shell foam

Patent #D498,052, #6,874,628



### Pistol Pack Series

- Sliding, lockable latches
- Stackable
- Contemporary high profile design
- Full egg-shell foam




# SPECIALTY STORAGE

## Utility Workstation™ Cart

A lot of thought went into the design of the Utility Workstation and, as a result, it is the most user friendly, most versatile cart on the market! Stress tested for weight up to 300 pounds (136.08 kg) you can easily integrate this cart into almost any application. Many other Flambeau products can be integrated into this Workstation to increase your organization & efficiency. Can be customized with your company name or logo. Assembles in less than 5 minutes!

- Locking tabs for lid
- Lockable lid compartment
- Sliding removable lid
- Drain plugs (each tray)
- Customizable (logo area)
- Bin Rail
- Heavy-duty locking casters - Holds up to 300 lbs (136.08 kg)
- Ergonomic handle with tool receiver



Interior Tray Dimensions:  
25-1/2" x 18" x 3-5/25"  
(64.77 x 45.72 x 8.13 cm)  
Work Surface Dimensions:  
28-1/2" x 7-1/2"  
(72.39 x 44.45 cm)  
Bottom Tray Dimensions:  
20" x 17" x 3"  
(50.80 x 43.18 x 7.62 cm)  
Logo Area:  
14" x 3-5/25" (35.56 x 8.13 cm)

Workstation shown with bins. For more information on the bins see below.




| Model Number | Stock Number | Description          | Dimensions (Overall, L x W x H)             | Packed |
|--------------|--------------|----------------------|---------------------------------------------|--------|
| 8510ST       | 8510ST       | Color: Two-Tone Gray | 43" x 22" x 39" (109.22 x 55.55 x 99.06 cm) | 1/ctn  |

## Bin Storage Systems

Mix and match our four (4) sizes of bins to your liking. Our polypropylene bins are extra heavy-duty and can be stacked or wall-mounted with a rail. Our bins are impervious to rust, oil and most common chemicals.

- Locking rail (back of bin)
- Stackable
- Mountable
- Available in Conductive material **page 65**
- Use with Utility Workstation™ above



## Bin Storage Bin Rail

Locking rail that attaches to the back of the bins.

- Sold separately



| Model Number         | Stock Number               | Description                                              | Dimensions (Inside, L x W x D)                      | Packed |
|----------------------|----------------------------|----------------------------------------------------------|-----------------------------------------------------|--------|
| 60R<br>60B<br>60Y    | 6794RB<br>6794BB<br>6794YB | Red<br>Blue<br>Yellow                                    | 4-1/4" x 4" x 1-1/2" (10.80 x 10.16 x 3.81 cm)      | 24/ctn |
| 120R<br>120B<br>120Y | 6795RB<br>6795BB<br>6795YB | Red<br>Blue<br>Yellow                                    | 4-1/4" x 5" x 2-1/2" (10.80 x 12.70 x 6.35 cm)      | 24/ctn |
| 240R<br>240B<br>240Y | 6796RB<br>6796BB<br>6796YB | Red<br>Blue<br>Yellow                                    | 4-1/4" x 6-1/2" x 3-1/4" (10.80 x 16.51 x 8.26 cm)  | 12/ctn |
| 480R<br>480B<br>480Y | 6797RB<br>6797BB<br>6797YB | Red<br>Blue<br>Yellow                                    | 4-1/4" x 8-3/4" x 5-1/4" (10.80 x 22.23 x 13.34 cm) | 12/ctn |
| 351BA                | 6794BA                     | set includes: (16) 60Y, (24) 120R, (24) 240Y & (16) 480B | see each individual bin size                        | 1/ctn  |
| SR4                  | 6796RL                     | Bin Rail holds 4 bins                                    | 19-1/2" long (49.53 cm long)                        | 12/ctn |

\* Width is measured from back to front straight edge before flare out.

## Rolling Tote Storage Cabinet **NEW**

The Rolling Tote is designed for light commercial parts storage and transport. Excellent for storing and transporting hand held tools; MRO items; or single unit storage for multiple uses. Features side extension pull handle with grip and lift out removable tray including lid stays. The large interior storage area, approx. 31" X 20" provides ample area to organize.

### Dimensions

Inside: 30-1/2" x 19" x 19-1/4" (77.47 x 48.26 x 48.90 cm)

Outside: 31" x 19-1/4" x 19-1/2" (78.74 x 48.90 x 49.53 cm)

Packed: 1/ctn

Weight: 23.0 lbs per carton

Cu ft/carton: 6-3/4 (17.14)

6531BK



## Utility Series – Industrial Grade

Flambeau Utility Series boxes are engineered tough. With thick wall construction and interior "I" beam support structures, you can expect the Utility Series boxes to out-perform most any other box! Features include: tongue-and-groove positive lid to base fit and heavy-duty riveted handles to handle even the heaviest load. Our positive cam-over latches and locking tabs give you added security. Finally, our heavy-duty cantilever trays are secured by rust-resistant hardware for extra longevity.

- Resistant to oil and common chemicals
- Lockable
- Dent-proof
- Tip-Guard™ (cantilever trays only)
- Scratch resistant
- Removable Interior Trays

## Blow Molded Tool Boxes

### Small Tool Box

- Lift-out tray sits on a "lip" at the top of the tool box base
- Tray size is larger than bottom dimension of tool box
- Available in red or black
- Has injection molded hardware
- Routed base for more storage space



50040  
Open



50043  
Open

### Large Tool Box

- Lift-out tray sits on a "lip" at the top of the tool box base
- Tray size is larger than bottom dimension of tool box
- Available in red or black
- Has injection molded handle with large single integral latch
- Double wall construction for extra strength



50043

21470

50040

50042

| Models        | Lid Depth        | Base Depth         | Tray Dimensions                                       |
|---------------|------------------|--------------------|-------------------------------------------------------|
| 50040 & 50042 | 1-7/8" (4.76 cm) | 2-13/16" (7.14 cm) | 16-5/8" x 4-15/16" x 1-1/4" (42.23 x 12.54 x 3.18 cm) |
| 21470 & 50043 | 3-1/2" (8.89 cm) | 3-1/2" (8.89 cm)   | 19-1/2" x 8-9/16" x 1-3/4" (49.53 x 21.75 x 4.45 cm)  |

| Model Number | Stock Number       | Description inch (centimeter)                                                                           | Dimensions (Inside, L x W x D)                          | Packed |
|--------------|--------------------|---------------------------------------------------------------------------------------------------------|---------------------------------------------------------|--------|
| 50040        | 50040<br>21469Y140 | Color: Red, Small tool box<br>Outside* L x W x D = 15-5/8 x 4-15/16 x 4-11/16 (39.69 x 12.54 x 11.91)   | 15-1/2" x 4-3/4" x 4"<br>(39.37 x 12.07 x 10.16 cm)     | 30/ctn |
| 50042        | 50042<br>21470Y500 | Color: Black, Small tool box<br>Outside* L x W x D = 15-5/8 x 4-15/16 x 4-11/16 (39.69 x 12.54 x 11.91) | 15-1/2" x 4-3/4" x 4"<br>(39.37 x 12.07 x 10.16 cm)     | 30/ctn |
| 21470        | 21470              | Color: Red, Large tool box<br>Outside* L x W x D = 19-7/8 x 8-5/16 x 7 (50.48 x 21.11 x 17.78)          | 18-1/4" x 7-1/2" x 5-3/4"<br>(46.36 x 19.05 x 14.61 cm) | 8/ctn  |
| 50043        | 50043<br>21470Y500 | Color: Black, Large tool box<br>Outside* L x W x D = 19-7/8 x 8-5/16 x 7 (50.48 x 21.11 x 17.78)        | 18-1/4" x 7-1/2" x 5-3/4"<br>(46.36 x 19.05 x 14.61 cm) | 8/ctn  |

\*Includes lid overlap and hinges

# TOOL BOXES

## Utility Boxes

Flambeau Utility Boxes feature spacious open interiors and are manufactured from light-weight copolymer resins that are non-conductive, dent-proof, rust-proof and scratch-resistant.

- Brass hinge and latch pins & Tough recessed handles
- Positive action latches
- Models 1800 & 2100 have (2) 3/16" (2.06 cm) Lock Tabs
- Textured finish & Tongue-and-groove construction



| Model Number | Stock Number | Description inch (centimeter)                                                                        | Dimensions (Outside*, L x W x D)                         | Dimensions (Inside, L x W x D)                          | Packed |
|--------------|--------------|------------------------------------------------------------------------------------------------------|----------------------------------------------------------|---------------------------------------------------------|--------|
| <b>1100</b>  | 6734UB       | Color: Gray<br>Lid Depth: 1-3/4 (4.45) Base Depth: 2-3/4 (6.99)                                      | 12-1/8" x 7-1/4" x 4-1/2"<br>(30.80 x 18.42 x 11.43 cm)  | 11-1/8" x 5-3/4" x 4"<br>(28.26 x 14.61 x 10.16 cm)     | 6/ctn  |
| <b>1200</b>  | 6736UB       | Color: Gray<br>Lid Depth: 2-3/4 (6.99) Base Depth: 2-3/4 (6.99)                                      | 12-1/8" x 7-1/4" x 5-1/2"<br>(30.80 x 18.42 x 13.97 cm)  | 11-1/8" x 5-3/4" x 5-1/4"<br>(28.26 x 14.61 x 13.34 cm) | 6/ctn  |
| <b>1400</b>  | 6742UB       | Color: Gray<br>Lid Depth: 3-1/2 (8.89) Base Depth: 3-1/2 (8.89)                                      | 14-3/8" x 8" x 7"<br>(36.51 x 20.32 x 17.78 cm)          | 13" x 6" x 6-1/4"<br>(33.02 x 15.24 x 15.88 cm)         | 6/ctn  |
| <b>1700</b>  | 6746UB       | Color: Gray<br>Lid Depth: 3-1/2 (8.89) Base Depth: 3-1/2 (8.89)                                      | 16-3/8" x 8-5/8" x 7"<br>(41.59 x 21.91 x 17.78 cm)      | 15" x 6-3/4" x 6-1/2"<br>(38.10 x 17.14 x 16.51 cm)     | 4/ctn  |
| <b>1800</b>  | 6752UB       | Color: Gray, has 3/16 (2.06) diameter lock tab<br>Lid Depth: 4-1/4 (10.80) Base Depth: 4-1/4 (10.80) | 17-1/2" x 10-1/4" x 8-1/2"<br>(44.45 x 26.04 x 21.59 cm) | 15-5/8" x 6-1/2" x 7-3/4"<br>(39.69 x 16.51 x 19.69 cm) | 4/ctn  |
| <b>2100</b>  | 6760UB       | Color: Gray, has 3/16 (2.06) diameter lock tab<br>Lid Depth: 5-1/4 (13.34) Base Depth: 5-1/4 (13.34) | 19" x 11-1/2" x 10-1/2"<br>(48.26 x 29.21 x 26.67 cm)    | 17-1/8" x 8-5/8" x 9-1/4"<br>(43.50 x 21.91 x 23.50 cm) | 2/ctn  |

## Utility/Tool Boxes with Lift-Out Trays and Lock Tabs - Trays not sold separately



| Model Number   | Stock Number | Description inch (centimeter)                                                                                                                                          | Dimensions (Outside*, L x W x D)                        | Dimensions (Inside, L x W x D)                          | Packed |
|----------------|--------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------|---------------------------------------------------------|--------|
| <b>14800-2</b> | 6744HS       | Color: Gray, has 3/16 (2.06) diameter lock tab<br>Lid Depth: 1-1/2 (3.81) Base Depth: 3-1/2 (8.89)<br>Tray (L x W x D): 12-1/4 x 4-3/4 x 1-1/2 (31.12 x 12.07 x 3.81)  | 14-1/2" x 7-1/2" x 5-1/4"<br>(36.83 x 19.05 x 13.34 cm) | 13" x 5-3/8" x 4-1/4"<br>(33.02 x 13.65 x 10.80 cm)     | 6/ctn  |
| <b>17800-2</b> | 6748HS       | Color: Gray, has 3/16 (2.06) diameter lock tab<br>Lid Depth: 2-1/8 (5.40) Base Depth: 4-3/4 (12.07)<br>Tray (L x W x D): 13-3/4 x 5-5/8 x 1-7/8 (34.93 x 14.29 x 4.76) | 16-5/8" x 8-3/4" x 7-1/8"<br>(42.23 x 22.23 x 18.10 cm) | 14-1/2" x 6-1/8" x 6"<br>(36.83 x 15.56 x 15.24 cm)     | 4/ctn  |
| <b>6518TH</b>  | 6518TH       | Color: Gray, has 1/4 (0.64) diameter molded lock tabs<br>Lid Depth: 2 (5.08) Base Depth: 7 (17.78)<br>Tray (L x W x D): 16 x 7-1/2 x 2 (40.64 x 19.05 x 5.08)          | 17" x 8-1/2" x 8-1/2"<br>(43.20 x 20.40 x 20.40 cm)     | 16-1/4" x 7-3/4" x 7-3/4"<br>(41.28 x 19.68 x 19.68 cm) | 4/ctn  |
| <b>19800-2</b> | 6757HS       | Color: Gray, has 3/16 (2.06) diameter lock tab<br>Lid Depth: 2-3/8 (6.03) Base Depth: 7 (17.78)<br>Tray (L x W x D): 17-5/8 x 6-3/8 x 2-3/16 (44.77 x 16.19 x 5.56)    | 20-1/4" x 8-7/8" x 8-3/8"<br>(51.44 x 22.54 x 21.27 cm) | 18-1/8" x 6-1/2" x 7-1/8"<br>(46.36 x 16.51 x 18.10 cm) | 4/ctn  |
| <b>19804</b>   | 6757TY       | Color: Yellow, has 3/16 (2.06) diameter lock tab<br>Lid Depth: 2-3/8 (6.03) Base Depth: 7 (17.78)<br>Tray (L x W x D): 17-5/8 x 6-3/8 x 2-3/16 (44.77 x 16.19 x 5.56)  | 20-1/4" x 8-7/8" x 8-3/8"<br>(51.44 x 22.54 x 21.27 cm) | 18-1/8" x 6-1/2" x 7-1/8"<br>(46.36 x 16.51 x 18.10 cm) | 4/ctn  |
| <b>6520TH</b>  | 6520TH       | Color: Gray, has two 1/4 (0.64) diameter molded lock tabs<br>Lid Depth: 2 (5.08) Base Depth: 8 (20.32)<br>Tray (L x W x D): 17-3/4 x 8 x 2 (45.09 x 20.32 x 5.08)      | 20" x 9-3/4" x 9-3/4"<br>(50.80 x 24.80 x 24.80 cm)     | 17-1/4" x 9" x 9"<br>(43.82 x 22.86 x 22.86 cm)         | 4/ctn  |
| <b>23800-2</b> | 6759HS       | Color: Gray, has 3/16 (2.06) diameter lock tab<br>Lid Depth: 2-1/2 (6.35) Base Depth: 8-3/8 (21.27)<br>Tray (L x W x D): 20-5/8 x 7-1/2 x 2 (52.39 x 19.05 x 5.08)     | 23" x 10-1/2" x 11-3/8"<br>(58.42 x 26.67 x 28.89 cm)   | 20-5/8" x 7-1/2" x 10"<br>(52.39 x 19.05 x 25.40 cm)    | 2/ctn  |
| <b>27800-2</b> | 6754TC       | Color: Gray, has 3/16 (2.06) diameter lock tab<br>Lid Depth: 3-1/2 (8.89) Base Depth: 10-3/8 (26.35)<br>Tray (L x W x D): 11-1/2 x 2-1/4 x 11 (29.21 x 5.72 x 27.94)   | 27-1/2" x 13-3/4" x 14"<br>(69.85 x 35.93 x 35.56 cm)   | 23" x 12-1/2" x 12"<br>(58.42 x 31.75 x 30.48 cm)       | 2/ctn  |

\*Includes lid overlap and hinges

## Utility Boxes with Cantilever Trays

Rugged Utility Boxes featuring Tip-Guard™ cantilever trays make it easy to organize tools and parts, repair kits, samples or sports equipment in a small space. Manufactured from light-weight copolymer resins that are dent-proof, rust-proof and scratch-resistant, these Utility Boxes are also resistant to oils and most common chemicals.


- Tough recessed handles
- Cantilever Tip-Guard tray supports
- Brass hinge and latch pins
- Positive-action latches
- Tongue-and-groove construction
- Trays are a light gray
- 3/16" (2.06 cm) diameter lock tab on models 18090-2 and 19060-2

## 2 Tray Boxes




17090-2

17090-2 Tray Configuration



Top Tray (from front of box)




Bottom Tray (from front of box)

17090-2 Tray Compartments (Inside L x W x D)  
**A**= 14-1/4" x 1-7/8" x 1-5/16" (36.20 x 4.76 x 3.33 cm)  
**B**= 3-1/2" x 3-3/16" x 1-5/16" (8.89 x 8.10 x 3.33 cm)  
**C**= 7" x 1-7/8" x 1-5/16" (17.78 x 4.76 x 3.33 cm)  
**D**= 1-11/16" x 1-7/8" x 1-5/16" (4.29 x 4.76 x 3.33 cm)  
**E**= 6" x 5-3/4" x 1-5/16" (15.24 x 14.61 x 3.33 cm)  
**F**= 4" x 5-3/4" x 1-5/16" (10.16 x 14.61 x 3.33 cm)



18090-2

18090-2 Tray Configuration



Top Tray (from front of box)



Bottom Tray (from front of box)

18090-2 Tray Compartments (Inside L x W x D)  
**A**= 9" x 7" x 1-3/4" (22.86 x 17.78 x 4.45 cm)  
**B**= 9" x 2-1/4" x 1-3/4" (22.86 x 5.72 x 4.45 cm)  
**C**= 5-1/2" x 7" x 1-3/4" (13.97 x 17.78 x 4.45 cm)  
**D**= 2-7/16" x 7" x 1-3/4" (6.19 x 17.78 x 4.45 cm)  
**E**= 6-1/4" x 7" x 1-3/4" (15.88 x 17.78 x 4.45 cm)


| Model Number | Stock Number | Description inch (centimeter)                                                                         | Dimensions (Outside*, L x W x D)                         | Dimensions (Inside, L x W x D)                          | Packed |
|--------------|--------------|-------------------------------------------------------------------------------------------------------|----------------------------------------------------------|---------------------------------------------------------|--------|
| 17090-2      | 6749HS       | Color: Gray, 2 cantilever trays, 11 compartments<br>Lid Depth: 3-1/2 (8.89) Base Depth: 3-1/2 (8.89)  | 16-3/8" x 8-5/8" x 7"<br>(41.59 x 21.91 x 17.78 cm)      | 15" x 6-3/4" x 6-1/2"<br>(38.10 x 17.15 x 16.51 cm)     | 4/ctn  |
| 18090-2      | 6755HS       | Color: Gray, 2 cantilever trays, 8 compartments<br>Lid Depth: 4-1/4 (10.80) Base Depth: 4-1/4 (10.80) | 17-1/2" x 10-1/4" x 8-1/2"<br>(44.45 x 26.04 x 21.59 cm) | 15-5/8" x 6-1/2" x 7-3/4"<br>(39.69 x 16.51 x 19.69 cm) | 4/ctn  |

## 6 Tray Box



19060-2

19060-2 Tray Configuration



Top Tray - Right Bank  
(from front of box)



Middle Tray - Right Bank  
(from front of box)



Bottom Tray - Right Bank  
(from front of box)



Top Tray - Left Bank  
(from front of box)



Middle Tray - Left Bank  
(from front of box)



Bottom Tray - Left Bank  
(from front of box)

19060-2 Tray Compartments (Inside L x W x D)  
**A**= 14-1/2" x 2-3/4" x 1" (36.83 x 6.99 x 2.54 cm)  
**B**= 1-3/4" x 2-3/4" x 1" (4.45 x 6.99 x 2.54 cm)  
**C**= 1-7/8" x 2-7/8" x 1-5/16" (4.76 x 7.30 x 3.33 cm)

**D**= Slant divider wall 12-1/2" x 1-5/8" & 2-3/8" x 1-5/16" (31.75 x 4.13 & 6.03 x 3.33 cm)  
**E**= 14-1/2" x 1-3/8" x 1-5/16" (36.83 x 3.49 x 3.33 cm)  
**F**= 1-1/2" x 4-3/8" x 1-5/16" (3.81 x 11.11 x 3.33 cm)  
**G**= 8-1/8" x 4-3/8" x 1-5/16" (20.64 x 11.11 x 3.33 cm)

| Model Number | Stock Number | Description inch (centimeter)                                                                      | Dimensions (Outside*, L x W x D)                          | Dimensions (Inside, L x W x D)                          | Packed |
|--------------|--------------|----------------------------------------------------------------------------------------------------|-----------------------------------------------------------|---------------------------------------------------------|--------|
| 19060-2      | 6756HS       | Color: Gray, 6 cantilever trays, 35 compartments<br>Lid Depth: 4-3/4 (12.07) Base Depth: 4 (10.16) | 18-1/2" x 10-3/4" x 10-3/8"<br>(46.99 x 27.31 x 26.35 cm) | 15-1/2" x 7-1/4" x 8-1/2"<br>(39.37 x 18.42 x 21.59 cm) | 1/ctn  |

\*Includes lid overlap and hinges

# TOOL BOXES

## Low Boy™ Tool Box

This low profile tool box has an ergonomic handle and is manufactured from light-weight copolymer resins that are non-conductive, dent-proof, rust-proof & scratch-resistant.

- Spacious 17" x 10-1/2" x 3-5/8" (43.18 x 26.67 x 9.21 cm) interior
- Stand-alone tool box does not accommodate expansion kit.



18192-2

| Model Number | Stock Number | Description   | Dimensions (Outside*, L x W x D)                  | Dimensions (Inside, L x W x D)                   | Packed |
|--------------|--------------|---------------|---------------------------------------------------|--------------------------------------------------|--------|
| 18192-2      | 6735HS       | Color: Yellow | 18-1/2" x 12-1/2" x 6" (46.99 x 31.75 x 15.24 cm) | 17" x 10-1/2" x 3-5/8" (43.18 x 26.67 x 9.21 cm) | 4/ctn  |

## Expandable Building Box

Manufactured from light-weight copolymer resins that are non-conductive, dent-proof, rust-proof & scratch-resistant.

- Ergonomic handle
- Spacious 17" x 10-1/2" x 3-5/8" (43.18 x 26.67 x 9.21 cm) top interior
- Includes (2), 999-2 Infinite Divider System™ Boxes
- Additional trays available with Expansion Kit



13901-2



999-2 Inside Dimensions (L x W x D)  
13-1/8" x 8-7/8" x 1-15/16"  
(33.34 x 22.54 x 4.92 cm)




13900-2

| Model Number | Stock Number | Description                 | Dimensions (Outside*, L x W x D)                       | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|-----------------------------|--------------------------------------------------------|-----------------------------------------------------|--------|
| 13900-2      | 6730HS       | Colors: Yellow and Black    | 18-1/2" x 12-1/2" x 11-3/4" (46.99 x 31.75 x 28.85 cm) | 18" x 11" x 3-1/2" (45.72 x 27.94 x 8.89 cm)        | 4/ctn  |
| 13901-2      | 6731HS       | Expansion Kit, Color: Black | 16-3/16" x 10-1/16" x 3-1/4" (41.12 x 25.56 x 8.26 cm) | 13-1/2" x 9-1/4" x 2-3/4" (34.29 x 23.50 x 6.99 cm) | 6/ctn  |

## Versatile Utility Tool Box

This Kwik-Change Series tool box comes complete with a large, bulk storage area with removable small tool and fastener organization. Features interchangeable Tuff Tainer® storage to allow for "quick-changes", depending on the job and supplies needed. Exterior rack on each side for quick access to frequently-used tools.


- Heavy-duty, fold-down handle and cam-over latches
- Bulk storage beneath lid
- Bulk capacity featuring interchangeable Tuff Tainer® Boxes
- Includes (3) T4007E, and (2) T1002 removable Tuff Tainer\* Boxes



(3) T4007E



(2) T1002



7040-2

\* Tuff Tainers are adjustable compartmented boxes; for dimensions of T4007E (Ref. page 16), and T1002 (Ref. page 14).

| Model Number | Stock Number | Description       | Bulk Storage (L x W x D)                 | Dimensions (Outside*, L x W x D)                | Packed |
|--------------|--------------|-------------------|------------------------------------------|-------------------------------------------------|--------|
| 7040-2       | 6767HS       | Color: Black/Gray | 14" x 8" x 4" (35.56 x 20.32 x 10.16 cm) | 14" x 8-1/2" x 3-1/4" (35.56 x 21.59 x 8.26 cm) | 2/ctn  |

## Tailgator™

- Removable dividers allow items to be stored upright
- Prop-rod holds lid upright for easy access
- Handle on each side allows Tailgator to be moved easily
- Two large Power Latches™ hold Tailgator's lid securely in place
- Lockable
- Removable floor panel can lock in place or side-to-side for easy access
- Strong construction allows stacking on top
- Front panel opens independently
- Removable lid doubles as a tabletop



38000



| Model Number | Stock Number | Description  | Dimensions (Inside, L x W x D)                         | Packed |
|--------------|--------------|--------------|--------------------------------------------------------|--------|
| 38000        | 6542TG       | Color: Taupe | 35-3/4" x 16-3/4" x 10-1/4" (90.81 x 42.55 x 26.04 cm) | 1/ctn  |

## Flambeau Packaging Solutions Gear Boxes - Whether hauling it, protecting it, or storing it, these Gear Boxes do it all!

Flambeau offers two sizes of Gear Boxes – the T1408B with a 13" (33.02 cm) interior length and the T1418 with a 17-1/2" (44.45 cm) interior length. Both are perfect for a variety of uses, with features like a deep open interior, snap-open lid, lift-out tray, oversized handle and latch. These Gear Boxes are perfect for Medical Supplies, Safety Equipment, Automotive Repair Kits, Test Equipment, Toys, Art Supplies, Maintenance & Repair Supplies, Gaming, Industrial Supplies, Firearm Supplies and much more.

### Features

- Deep open interior
- Gasket in lid
- Cam-over latch design
- Large carry handle
- Tongue-and-groove design
- Snap-open lid with storage
- Lift-out tray
- Lockable

### Benefits

- Accommodates large, tall parts and equipment
- Keeps contents dry and protected in extreme environments
- Provides added strength
- Better ergonomics makes hauling easier
- Helps keep dust and contaminants out
- Perfect for storing small parts
- Keeps everything organized and at your fingertips
- Secures contents in main compartment



**T1408B**

Top compartment "U" shaped 1" (2.54 cm) Deep



**T1418**

Top compartment "U" shaped 1-1/4" (3.18 cm) Deep



All models include a 360° gasket in the lid which keeps contents dry and protected from some of the most extreme environments.



As an option, both sizes can be molded in Zerust® Corrosion Inhibitor creating an invisible barrier to fight against corrosion.



Both sizes available in custom colors contact Customer Service for more information.

| Model Number  | Stock Number | Description inch (centimeter)                                                       | Tray Dimensions (L x W x D)                            | Dimensions (Inside, L x W x D)                        | Packed |
|---------------|--------------|-------------------------------------------------------------------------------------|--------------------------------------------------------|-------------------------------------------------------|--------|
| <b>T1408B</b> | 6430TD       | Color: Black with Lift-Out Tray<br>Inside Box Clearance Under Tray is 5-1/4 (13.33) | 12-3/4" x 6-1/2" x 2"<br>(32.39 x 16.51 x 5.08 cm)     | 13" x 6-3/4" x 7-1/4"<br>(33.02 x 17.15 x 18.42 cm)   | 4/ctn  |
| <b>T1418</b>  | 6917GB       | Color: Black with Lift-Out Tray<br>Inside Box Clearance Under Tray is 7 (17.78)     | 13-1/4" x 8-1/4" x 2-3/4"<br>(33.66 x 20.96 x 6.99 cm) | 17-1/2" x 10-1/2" x 12"<br>(44.45 x 26.67 x 30.48 cm) | 2/ctn  |

# TOOL BOXES

## Lil' Brute™ Utility/Tool Box

The Lil' Brute Utility Tool Box is redesigned! New added features include upgraded Super Satchel style handle with new L-089 "quick-snap" latches. Available with or without lift out tray! Customize with colors or hot stamp options. A fantastic value!

- Available with or without trays - trays not sold separately

\*Includes lid overlap and hinges



| Model Number | Stock Number | Description inch (centimeter)                                                                                                  | Dimensions (Outside*, L x W x D)                | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|--------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------|-----------------------------------------------------|--------|
| 13805-2      | 6743HS       | Color: Black, with tray (L x W x D) 12 x 4-3/8 x 1 (30.48 x 11.11 x 2.54)<br>Lid Depth: 1/2" (1.27), Base Depth: 4-1/4 (10.80) | 13" x 6" x 5-3/8"<br>(33.02 x 15.24 x 13.65 cm) | 12" x 4-3/4" x 4-3/4"<br>(30.48 x 12.07 x 12.07 cm) | 6/ctn  |
| 13815-2      | 6742HS       | Color: Black, without tray                                                                                                     | 13" x 6" x 5-3/8"<br>(33.02 x 15.24 x 13.65 cm) | 12" x 4-3/4" x 4-3/4"<br>(30.48 x 12.07 x 12.07 cm) | 6/ctn  |

## Utility Tote

- Copolymer resins resist scratching, fading and rusting
- Has a large built-in handle and pull-out tray on bottom can be opened from either side
- Ideal for service areas or vehicles
- Drawer with 12 compartments & dimensions of 13-3/4" x 9" x 1-1/2" (34.93 x 22.86 x 3.81 cm)

16500-2



| Model Number | Stock Number | Description                          | Dimensions (Outside, L x W x D)                       | Dimensions (Inside, L x W x D)               | Packed |
|--------------|--------------|--------------------------------------|-------------------------------------------------------|----------------------------------------------|--------|
| 16500-2      | 6769HS       | Color: Black, with light gray drawer | 16-5/8" x 10-1/4" x 6-7/8" (42.23 x 26.04 x 17.46 cm) | 13-3/4" x 9" x 4" (34.93 x 22.86 x 10.16 cm) | 6/ctn  |

## Utility Bench Box

- Spacious 20" x 8" x 4" (50.8 x 20.32 x 10.16 cm) top
- Two large pull-out drawers with 2 compartments in drawer one & 2 compartments in drawer two
- Drawer dimensions are 18-3/8" x 5-7/8" x 1-7/8" (46.67 x 14.92 x 4.76 cm)
- Drawers can be secured from accidental opening
- Includes two (2) removable dividers for each drawer
- Fold-down handle

\*Includes lid overlap and hinges

21800-2



| Model Number | Stock Number | Description                             | Dimensions (Outside, L x W x D)                       | Dimensions (Inside, L x W x D)           | Packed |
|--------------|--------------|-----------------------------------------|-------------------------------------------------------|------------------------------------------|--------|
| 21800-2      | 6758HS       | Color: Black, with 2 light gray drawers | 21-3/4" x 10-3/4" x 9-3/8" (55.25 x 27.31 x 23.81 cm) | 20" x 8" x 4" (50.80 x 20.32 x 10.16 cm) | 1/ctn  |

## Tool Chests

Flambeau Tool Chests are also designed to organize, store and protect precision tools, hardware and small parts. They feature a unique front panel design that allows drawer access when the front panel is down. A unique lock prevents accidental spills and allows the lid and drawers to lift as a unit, providing access to the large lower storage area.

- Molded in high-impact resins
- Resistant to most common chemicals, solvents and oils
- Positive-action latches
- Lockable
- Brass hinges and latch pins
- Light gray interchangeable drawers with adjustable compartment sizes
- Model 22030-2 is molded in industrial-grade ABS plastic



For Drawer Dimensions and Compartment Dimensions, Please See Below.

| Model Number | Stock Number | Description                         | Drawer Configuration | Dimensions (Outside, L x W x D)                        | Packed |
|--------------|--------------|-------------------------------------|----------------------|--------------------------------------------------------|--------|
| 22030-2      | 6759CH       | Color: Gray with light gray drawers | (2) B & (1) F        | 19-1/2" x 11-1/2" x 11-3/4" (49.53 x 29.21 x 29.85 cm) | 1/ctn  |

## Drawer Cabinets


Flambeau Drawer Cabinets are designed to organize, store and protect precision tools, hardware and small parts. They feature a self-storing door panel providing all-weather protection for the contents inside.

- Molded in industrial grade ABS plastic
- Resistant to most common chemicals, solvents and oils
- Positive-action latches
- Lockable
- Brass hinges and latch pins
- Light gray interchangeable drawers with adjustable compartment sizes, see below for drawer details




| Model Number       | Stock Number | Description                         | Drawer Configuration        | Dimensions (Outside, L x W x D)                        | Packed |
|--------------------|--------------|-------------------------------------|-----------------------------|--------------------------------------------------------|--------|
| 22060              | 6596DH       | Color: Gray with light gray drawers | (4) B, (1) C & (1) F        | 19-1/2" x 11-1/2" x 11-3/4" (49.53 x 29.21 x 29.85 cm) | 1/ctn  |
| 2275-2             | 6763DB       | Color: Gray with light gray drawers | (2) B, (2) D & (1) E        | 19-1/2" x 10-3/8" x 15" (49.53 x 26.35 x 38.10 cm)     | 1/ctn  |
| 2276-2 (not shown) | 6764DB       | Color: Gray with light gray drawers | (1) A, (3) B, (1) C & (1) D | 19-1/2" x 10-3/8" x 15" (49.53 x 26.35 x 38.10 cm)     | 1/ctn  |
| 2277-2             | 6765DB       | Color: Gray with light gray drawers | (1) A, (2) B & (4) D        | 19-1/2" x 10-3/8" x 15" (49.53 x 26.35 x 38.10 cm)     | 1/ctn  |


## Drawer Cabinets & Tool Chests Drawer Dimensions




**Drawer A** - #AR839-45 - inches (centimeters)  
 Overall L x W x D: 15-9/16 x 8-13/16 x 1-3/8 (39.53 x 22.84 x 3.49)  
 Compartments L x W x D  
 A= 1-15/16 x 6-3/16 x 1-1/4 (4.92 x 15.72 x 3.18)  
 B= 7-5/16 x 6-3/16 x 1-1/4 (18.57 x 15.72 x 3.18)  
 C= 15-1/8 x 2-7/16 x 1-1/4 (5.08 x 7.94 x 3.18)



**Drawer B** - #AR841-45 - inches (centimeters)  
 Overall L x W x D: 15-9/16 x 8-13/16 x 1-3/8 (39.53 x 22.84 x 3.49)  
 Compartments L x W x D  
 A= 1-15/16 x 4-1/2 x 1-1/4 (4.92 x 11.43 x 3.18)  
 B= 3-3/16 x 8-7/8 x 1-1/4 (8.10 x 22.54 x 3.18)




**Drawer C** - #AR869-45 - inches (centimeters)  
 Overall L x W x D: 15-9/16 x 8-13/16 x 2-7/8 (39.53 x 22.84 x 7.30)  
 Compartment L x W x D  
 A= 15-1/8 x 8-5/8 x 2-5/8 (38.42 x 21.91 x 6.67)



**Drawer D** - #AR840-45 - inches (centimeters)  
 Overall L x W x D: 15-9/16 x 8-13/16 x 1-3/8 (39.53 x 22.84 x 3.49)  
 Compartments L x W x D  
 A= 1-3/8 x 5-1/16 x 1-1/4 (3.49 x 12.86 x 3.18)  
 B= 1-3/8 x 3-9/16 x 1-1/4 (3.49 x 9.05 x 3.18)  
 C= 3-3/16 x 3-9/16 x 1-1/4 (8.10 x 9.05 x 3.18)



**Drawer E** - #AR928-45 - inches (centimeters)  
 Overall L x W x D: 15-9/16 x 8-13/16 x 4-7/16 (39.53 x 22.84 x 11.27)  
 Compartment L x W x D  
 A= 15-1/8 x 8-5/8 x 4-5/16 (38.42 x 21.91 x 10.95)




**Drawer F** - #AR897-45 - inches (centimeters)  
 Overall L x W x D: 15-9/16 x 8-13/16 x 1-3/8 (39.53 x 22.84 x 3.49)  
 Compartments L x W x D  
 A= 15-1/8 x 6-3/16 x 1-1/4 (38.42 x 15.72 x 3.18)  
 B= 15-1/8 x 2-7/16 x 1-1/4 (38.42 x 6.19 x 3.18)


## Drawer Cabinets & Tool Chests Replacement Drawer Packs

Each replacement drawer pack includes 6 drawers.


| Model Number | Stock Number | Description | Packed |
|--------------|--------------|-------------|--------|
| AR839-45     | 6073DP       | Drawer A    | 6/pk   |
| AR841-45     | 6069DP       | Drawer B    | 6/pk   |
| AR869-45     | 6071DP       | Drawer C    | 6/pk   |
| AR840-45     | 6072DP       | Drawer D    | 6/pk   |
| AR928-45     | 6060DP       | Drawer E    | 6/pk   |
| AR897-45     | 6070DP       | Drawer F    | 6/pk   |




**Drawer A**  
 L= 15-9/16" (39.53 cm)  
 W= 8-13/16" (22.84 cm)  
 D= 1-3/8" (3.49 cm)



**Drawer B**  
 L= 15-9/16" (39.53 cm)  
 W= 8-13/16" (22.84 cm)  
 D= 1-3/8" (3.49 cm)




**Drawer C**  
 L= 15-9/16" (39.53 cm)  
 W= 8-13/16" (22.84 cm)  
 D= 2-7/8" (7.30 cm)



**Drawer D**  
 L= 15-9/16" (39.53 cm)  
 W= 8-13/16" (22.84 cm)  
 D= 1-3/8" (3.49 cm)



**Drawer E**  
 L= 15-9/16" (39.53 cm)  
 W= 8-13/16" (22.84 cm)  
 D= 4-7/16" (11.27 cm)



**Drawer F**  
 L= 15-9/16" (39.53 cm)  
 W= 8-13/16" (22.84 cm)  
 D= 1-3/8" (3.49 cm)

Dimensions Listed are Overall Dimensions

# MEDICAL

## Maximum Versatility - Built to Last

Our extensive line of medical boxes and cases are the most durable in the field. Constructed of copolymer resins, our medical line is light-weight, rust-proof, scratch- and chemical-resistant. Flambeau medical cases, chests, and instrument boxes are built to last with extra thick walls for long-lasting durability and impact resistance. Used by EMS personnel, rescue, first-responders, trainers, triage staff and other respected medical professionals around the globe, our variety of products will meet your needs in most any application.

### Features

- Thick-wall Construction
  - Maximum Physical Protection
- Locking Tabs (select items)
- Positive Contact Cam-over Latches
- Rust-proof Hinges
- Heavy-duty Cantilever Drawer Stays
- Heavy-duty Riveted Fold-down Handles
- Autoclave Safe (select items)

## Medical Device Box

Store, transport, and protect cardiac implant devices and most other small wafer type implantable devices. Sterilize with ETO; Gamma; or E-Beam process. Made of tough Polypropylene material. Box can be easily customized with logo or name plate.

- Lid top fits over base



| Model Number | Stock Number | Description inch (centimeter) | Tray Dimensions (L x W x D)                             | Dimensions (Inside, L x W x D)                          | Packed |
|--------------|--------------|-------------------------------|---------------------------------------------------------|---------------------------------------------------------|--------|
| 6528MD       | 6528MD       | Color: Natural                | 5-3/10" x 5-3/10" x 1.1/2"<br>(13.46 x 13.46 x 3.81 cm) | 5-3/10" x 5-3/10" x 1-1/2"<br>(13.46 x 13.46 x 3.81 cm) | 24/ctn |

## Paramedic Gear Box - Water-resistant

Light-weight, rust-proof, scratch- and chemical-resistant and lockable! The Gear Box features a 360° water-resistant rubber lid seal with an easy access heavy-duty cam-over latch so you can be sure that your contents will be secure and protected from adverse weather conditions.

- Lockable with a heavy-duty large comfort handle
- Top compartment "U" shaped 1" (2.54 cm) deep
- Positive-touch, double-latch system (top storage area)
- Lift-out tray has a center handle - Additional 3/4" (1.91 cm) above tray under lid



Gasket Picture



PM1408

| Model Number | Stock Number | Description inch (centimeter)                                                         | Tray Dimensions (L x W x D)                        | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|---------------------------------------------------------------------------------------|----------------------------------------------------|-----------------------------------------------------|--------|
| PM1408       | 6430PM       | Color: Orange with Lift-Out Tray<br>Inside Box Clearance Under Tray is 5-1/4" (13.33) | 12-3/4" x 6-1/2" x 2"<br>(32.39 x 16.51 x 5.08 cm) | 13" x 6-3/4" x 7-1/4"<br>(33.02 x 17.15 x 18.42 cm) | 4/ctn  |

## Paramedic Case

Our most complete Paramedic cases yet! These cases combine bulk storage with compartmentalization to give you the convenience and flexibility you need.

### PM8040 - Heavy-duty fold-down handle

- Includes (4) 6004R, and (2) T2003 removable, Tuff Tainer™ boxes
- Interior slotted to hold up to (3) additional removable, T2003 Tuff Tainer™ boxes



PM8040

\* Tuff Tainers are adjustable compartmented boxes; for dimensions of T2003 (Ref. page 14), T6004 (Ref. page 16), T4007E (Ref. page 16), T4000 (Ref. page 16), and T1002 (Ref. page 14).

| Model Number | Stock Number | Description   | Bulk Storage (L x W x D)                  | Dimensions (Inside, L x W x D)                  | Packed |
|--------------|--------------|---------------|-------------------------------------------|-------------------------------------------------|--------|
| PM7040       | 6049PM       | Color: Orange | 14" x 8" x 4" (35.56 x 20.32 x 10.16 cm)  | 14" x 8-1/2" x 3-1/4" (35.56 x 21.59 x 8.26 cm) | 2/ctn  |
| PM8040       | 6778PM       | Color: Orange | 18" x 11" x 4" (45.72 x 27.94 x 10.16 cm) | 17" x 11" x 3-1/2" (43.18 x 27.94 x 8.89 cm)    | 2/ctn  |

## First Aid Cases



| Model Number | Stock Number | Description                                                                          | Tray(s) Dimensions (L x W x D)                         | Dimensions (Inside, L x W x D)                          | Packed |
|--------------|--------------|--------------------------------------------------------------------------------------|--------------------------------------------------------|---------------------------------------------------------|--------|
| PM1702       | 6768PM       | Color: Orange with white tray<br>1 compartment and removable tray                    | 14-3/8" x 6-5/8" x 2"<br>(36.51 x 16.83 x 5.08 cm)     | 15" x 6-3/4" x 6-1/2"<br>(38.10 x 17.14 x 16.51 cm)     | 4/ctn  |
| PM1772       | 6770PM       | Color: Orange with white trays<br>2 tip-proof cantilever trays, 8 large compartments | 14-1/4" x 5-3/4" x 1-3/8"<br>(36.20 x 14.61 x 3.49 cm) | 15" x 6-3/4" x 6-1/2"<br>(38.10 x 17.14 x 16.51 cm)     | 4/ctn  |
| PM1872       | 6772PM       | Color: Orange with white trays<br>2 tip-proof cantilever trays, 8 large compartments | 14-3/4" x 7-1/8" x 1-3/4"<br>(37.47 x 18.10 x 4.45 cm) | 15-5/8" x 6-1/2" x 7-3/4"<br>(39.69 x 16.51 x 19.69 cm) | 4/ctn  |

## Paramedic Box

The standard in emergency care cases.

- Lockable
- Heavy-duty trays - Riveted cantilever rust-resistant hardware




| Model Number | Stock Number | Description                                                                     | Tray(s) Dimensions (L x W x D)                     | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|---------------------------------------------------------------------------------|----------------------------------------------------|-----------------------------------------------------|--------|
| PM2072       | 6774PM       | Color: Orange with white trays<br>2 tip-proof cantilever trays, 10 compartments | 16-3/8" x 7-3/8" x 2"<br>(41.59 x 18.73 x 5.08 cm) | 17-1/8" x 9-1/2" x 5"<br>(43.50 x 24.13 x 12.70 cm) | 1/ctn  |

## Instrument Boxes

Ideal for small or delicate equipment.

- Integral hinge
- Positive latch
- Durable polypropylene construction
- Safe for autoclaving



| Model Number | Stock Number | Description                                   | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|-----------------------------------------------|-----------------------------------------------------|--------|
| V301         | 6142VB       | Color: Orange, 1 Compartment with hanging tab | 7" x 3-1/4" x 1" (17.78 x 8.26 x 2.54 cm)           | 36/ctn |
| V301PT       | 6650VC       | Color: Taupe, 1 Compartment                   | 7" x 3-1/4" x 1" (17.78 x 8.26 x 2.54 cm)           | 36/ctn |
| V401         | 6152VB       | Color: Taupe, 1 Compartment                   | 8-1/8" x 4-1/8" x 1-3/16" (20.64 x 10.48 x 3.02 cm) | 24/ctn |
| V401D-2      | 6654DV       | Color: Taupe, Deep, 1 Compartment             | 8-1/8" x 4-1/8" x 2-5/8" (20.64 x 10.48 x 6.67 cm)  | 24/ctn |
| V501         | 6160VB       | Color: Taupe, 1 Compartment                   | 10" x 4-1/4" x 1-1/2" (25.40 x 10.80 x 3.81 cm)     | 24/ctn |
| V601         | 6667VB       | Color: Taupe, 1 Compartment                   | 13-1/2" x 5-3/4" x 2" (34.29 x 14.61 x 5.08 cm)     | 12/ctn |
| V701         | 6172VB       | Color: Taupe, 1 Compartment                   | 17" x 7-1/8" x 2" (43.18 x 18.10 x 5.08 cm)         | 6/ctn  |

# MEDICAL

## Command Center Box

Excellent for bulk storage. With two built-in handles on each end, this box gives you the flexibility and ease of quick transport from your rig to the scene. This box is durable, but light-weight and has become a favorite!

- Lockable with 2 power latches



PM27800

| Model Number | Stock Number | Description   | Removable Interior Tray Dimensions (L x W x D) | Dimensions (Inside, L x W x D)                 | Packed |
|--------------|--------------|---------------|------------------------------------------------|------------------------------------------------|--------|
| PM27800      | 6754PM       | Color: Orange | 12" x 11-3/4" x 2" (30.48 x 29.85 x 5.08 cm)   | 23" x 12-1/2" x 12" (58.42 x 31.75 x 30.48 cm) | 2/ctn  |

## Trauma Drug Kits

Our trauma drug kits have a drop-front panel for easy access to the storage bin below, a positive cam-over latch, and are lockable for protection of contents. The ABS drawers can be sterilized. All drawers are removable and interchangeable. *See Drawer Configuration in table for drawers included with the PM2272 and PM2273.*



PM2272



Closed view of models  
PM2272 and PM2273



PM2273

| Model Number | Stock Number | Description                                     | Drawer Configuration | Dimensions (Inside, L x W x D)                   | Packed |
|--------------|--------------|-------------------------------------------------|----------------------|--------------------------------------------------|--------|
| PM2272       | 6776PM       | Color: Orange with White Drawers, 8-14 compts.  | (1) B & (1) C        | 17-3/8" x 9-3/4" x 5" (44.13 x 24.77 x 12.70 cm) | 1/ctn  |
| PM2273       | 6777PM       | Color: Orange with White Drawers, 21-39 compts. | (3) B                | 17-3/8" x 9-3/4" x 5" (44.13 x 24.77 x 12.70 cm) | 1/ctn  |

## Drawer Cabinets

Our drawer cabinets have a front panel that easily drops down for use of all drawers, a positive cam-over latch, and are lockable for protection of contents. The ABS drawers can be sterilized. All drawers are removable and interchangeable. *See Drawer Configuration in table for drawers included with the PM2274 and PM2275.*



PM2274

closed  
view




PM2275


closed  
view

| Model Number | Stock Number | Description                                     | Drawer Configuration        | Dimensions (Outside, L x W x D)                    | Packed |
|--------------|--------------|-------------------------------------------------|-----------------------------|----------------------------------------------------|--------|
| PM2274       | 6762PM       | Color: Orange with White Drawers, 27 compts.    | (1) A, (1) C, (1) D & (1) E | 19-1/2" x 10-3/8" x 15" (49.53 x 26.35 x 38.10 cm) | 1/ctn  |
| PM2275       | 6763PM       | Color: Orange with White Drawers, 53-65 compts. | (2) B, (2) D & (1) E        | 19-1/2" x 10-3/8" x 15" (49.53 x 26.35 x 38.10 cm) | 1/ctn  |


## Trauma Drug Kits & Drawer Cabinets Drawer Dimensions




**Drawer A** - #AR839-10 - inches (centimeters)  
Overall L x W x D: 15-9/16 x 8-13/16 x 1-3/8 (39.53 x 22.84 x 3.49)  
Compartments L x W x D  
A= 1-15/16 x 6-3/16 x 1-1/4 (4.92 x 15.72 x 3.18)  
B= 7-5/16 x 6-3/16 x 1-1/4 (18.57 x 15.72 x 3.18)  
C= 15-1/8 x 2-7/16 x 1-1/4 (5.08 x 7.94 x 3.18)



**Drawer B** - #AR841-10 - inches (centimeters)  
Overall L x W x D: 15-9/16 x 8-13/16 x 1-3/8 (39.53 x 22.84 x 3.49)  
Compartments L x W x D  
A= 1-15/16 x 4-1/2 x 1-1/4 (4.92 x 11.43 x 3.18)  
B= 3-3/16 x 8-7/8 x 1-1/4 (8.10 x 22.54 x 3.18)



**Drawer C** - #AR869-10 - inches (centimeters)  
Overall L x W x D: 15-9/16 x 8-13/16 x 2-7/8 (39.53 x 22.84 x 7.30)  
Compartments L x W x D  
A= 15-1/8 x 8-5/8 x 2-5/8 (38.42 x 21.91 x 6.67)



**Drawer D** - #AR840-10 - inches (centimeters)  
Overall L x W x D: 15-9/16 x 8-13/16 x 1-3/8 (39.53 x 22.84 x 3.49)  
Compartments L x W x D  
A= 1-3/8 x 5-1/16 x 1-1/4 (3.49 x 12.86 x 3.18)  
B= 1-3/8 x 3-9/16 x 1-1/4 (3.49 x 9.05 x 3.18)  
C= 3-3/16 x 3-9/16 x 1-1/4 (8.10 x 9.05 x 3.18)



**Drawer E** - #AR928-10 - inches (centimeters)  
Overall L x W x D: 15-9/16 x 8-13/16 x 4-7/16 (39.53 x 22.84 x 11.27)  
Compartments L x W x D  
A= 15-1/8 x 8-5/8 x 4-5/16 (38.42 x 21.91 x 10.95)

To order replacement drawers, please call Customer Service at 1-800-344-5716. Be sure to give them the Drawer letter (A, B, etc.) and number listed after "#" in this section for easier ordering.

## Guard Against Expensive Damage

A leader in the industry, Flambeau's reusable conductive product line significantly reduces electrical resistance and provides an extremely high permanent level of conductivity to dissipate static charge buildup, alleviating electrostatic discharge (ESD). Our proprietary blend of carbon loaded HDPE materials are a guarantee that Flambeau conductive products will protect the most sensitive equipment and perform in the harshest environment.

### Technical Data

- Surface Resistivity  $10^{10}$ - $10^{11}$  (ASTM D 257 / ESD S11.11)
- Static Decay <2.0 Seconds (MIL-PRF-81705D)

### Features

- Double-wall Construction - Maximum Physical Protection
- Locking Tabs (select items)
- Reusable & Stackable
- Secure Positive, Integral Double Latches
- ESD Protection
- Permanently Anti-Static

## Conductive Cases

### Options:

- Clear Conductive Window (Special order styles only)
  - Easy part identification without compromise of Faraday Cage protection
- Grounding Snap
  - Reduces surface charges so the case can be safely opened without damaging contents
- Antistatic or Conductive Foam
  - (Conductive quoted separately)
  - (Antistatic included upon request, foam is glued into case)
  - Provides physical shock resistance, reduces the potential for static build-up and arc potential due to the low friction coefficient of the foam



| Model Number                                                                              | Stock Number   | Description                                   | Dimensions (Inside, L x W x D**) *B = Base; L = Lid **Depth = Base + Lid                                          | Packed  |
|-------------------------------------------------------------------------------------------|----------------|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------|---------|
| 50019  | 50019<br>21460 | 5 x 3 Conductive Case                         | 5-1/16" x 2-3/4" B*, 2-5/8" L* x 1"<br>(13.49 x 6.99 B*, 6.67 L* x 2.54 cm)                                       | 341/ctn |
| 21463  | 21463          | 6 x 5 Conductive Case                         | 6-3/4" B*, 6-1/2" L* x 5" B*, 4-3/4" L* x 1-3/16"<br>(17.15 B*, 16.51 L* x 12.70 B*, 12.07 L* x 3.02 cm)          | 135/ctn |
| 50014  | 50014          | 9 x 7 Conductive Case with wire tie feature   | 8-15/16" B*, 9-1/16" L* x 6-5/8" B*, 6-1/2" L* x 1-1/4"<br>(22.70 B*, 23.02 L* x 16.83 B*, 16.51 L* x 3.18 cm)    | 96/ctn  |
| 50015  | 50015          | 12 x 8 Conductive Case with wire tie feature  | 11-7/8" B*, 11-15/16" L* x 8-3/16" B*, 8-7/16" L* x 1-1/4"<br>(30.16 B*, 30.32 L* x 20.80 B*, 21.43 L* x 3.18 cm) | 54/ctn  |
| 21458  | 21458          | 13 x 11 Conductive Case with wire tie feature | 12-3/4" x 10-1/2" x 1-3/4"<br>(32.39 x 26.67 x 4.45 cm)                                                           | 30/ctn  |
| 21459  | 21459          | 15 x 6 Conductive Case                        | 15" x 6-1/2" x 2"<br>(38.10 x 16.51 x 5.08 cm)                                                                    | 24/ctn  |
| 21462  | 21462          | 18 x 14 Conductive Case with wire tie feature | 17-1/2" x 13-1/2" x 1-5/16"<br>(44.45 x 34.29 x 3.33 cm)                                                          | 7/ctn   |
| 21461  | 21461          | 18 x 18 Conductive Case with wire tie feature | 18-7/16" x 17-11/16" x 1-15/16"<br>(46.83 x 44.93 x 4.92 cm)                                                      | 10/ctn  |

# CONDUCTIVE PRODUCTS

## Conductive Tool Box

- 14" (35.56 cm) Storage Box with full-length tray



14800-2C

| Model Number | Stock Number | Description  | Tray Dimensions (L x W x D)                            | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|--------------|--------------------------------------------------------|-----------------------------------------------------|--------|
| 14800-2C     | 6744HC       | Color: Black | 12-1/4" x 4-3/4" x 1-1/2"<br>(31.12 x 12.07 x 3.81 cm) | 13" x 5-3/8" x 4-1/4"<br>(33.02 x 13.65 x 10.80 cm) | 6/ctn  |

## 600/800 Series Conductive Boxes



C601





C618





C801



C824



Compartments (L x W)  
A= 2-1/16" x 1-3/4" (5.24 x 4.45 cm)



Compartments (L x W)  
A= 2-1/16" x 2-1/16" (5.24 x 5.24 cm)

| Model Number | Stock Number | Description     | Dimensions (Inside, L x W x D)                        | Packed |
|--------------|--------------|-----------------|-------------------------------------------------------|--------|
| C601         | 6707TC       | 1 compartment   | 10-1/2" x 6-3/16" x 1-9/16" (26.67 x 15.72 x 3.97 cm) | 24/ctn |
| C618         | 6714TC       | 18 compartments | 10-1/2" x 6-3/16" x 1-9/16" (26.67 x 15.72 x 3.97 cm) | 24/ctn |
| C801         | 6734TC       | 1 compartment   | 12-3/4" x 8-1/2" x 2-1/8" (32.39 x 21.59 x 5.40 cm)   | 12/ctn |
| C824         | 6726TC       | 24 compartments | 12-3/4" x 8-1/2" x 2-1/8" (32.39 x 21.59 x 5.40 cm)   | 12/ctn |

## Conductive Storage Bins



3006C



3007C



3008C



3005C

| Model Number | Stock Number | Description  | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|--------------|-----------------------------------------------------|--------|
| 3006C        | 6771BC       | Color: Black | 4-1/4" x 4" x 1-1/2" (10.80 x 10.16 x 3.81 cm)      | 24/ctn |
| 3007C        | 6772BC       | Color: Black | 4-1/4" x 5" x 2-1/2" (10.80 x 12.70 x 6.35 cm)      | 24/ctn |
| 3008C        | 6773BC       | Color: Black | 4-1/4" x 6-1/2" x 3-1/4" (10.80 x 16.51 x 8.26 cm)  | 12/ctn |
| 3005C        | 6774BC       | Color: Black | 4-1/4" x 8-3/4" x 5-1/4" (10.80 x 22.23 x 13.34 cm) | 12/ctn |

\* Width is measured from back to front straight edge before flare out.

# CONDUCTIVE PRODUCTS

## Conductive Storage Cabinets/Rototower™



Holds 16 Cabinets.

Uses the C26P-C and U45P-C Cabinets.

Not shown to scale, with cabinets to left.




161 CRT Rototower™

*All cabinets include (10) 35/52C dividers, all other dividers are optional*

| Model Number | Stock Number | Description                                                                               | Uses Drawer                                   | Uses Divider                           | Dimensions (Outside, L x W x H)                                                                   | Packed |
|--------------|--------------|-------------------------------------------------------------------------------------------|-----------------------------------------------|----------------------------------------|---------------------------------------------------------------------------------------------------|--------|
| C20P-C       | 6575CD       | Color: Black<br>Black Drawers<br>Black Dividers                                           | (15) TW-C<br>(4) TQ-C<br>(1) TF-C             | 35/52C<br>50/64C<br>57/275C            | 12" x 6-1/4" x 11-1/4"<br>(30.48 x 15.88 x 28.58 cm)                                              | 4/ctn  |
| C26P-C       | 6576CD       | Color: Black<br>Black Drawers<br>Black Dividers                                           | (15) TW-C<br>(8) TQ-C<br>(2) TJ-C<br>(1) TF-C | 35/52C<br>50/64C<br>57/135C<br>57/275C | 12" x 6-1/4" x 16-1/2"<br>(30.48 x 15.88 x 41.91 cm)                                              | 4/ctn  |
| U30P-C       | 6573CD       | Color: Black<br>Black Drawers<br>Black Dividers                                           | (30) TW-C                                     | 35/52C                                 | 12" x 6-1/4" x 11-1/4"<br>(30.48 x 15.88 x 28.58 cm)                                              | 4/ctn  |
| U45P-C       | 6574CD       | Color: Black<br>Black Drawers<br>Black Dividers                                           | (45) TW-C                                     | 35/52C                                 | 12" x 6-1/4" x 16-1/2"<br>(30.48 x 15.88 x 41.91 cm)                                              | 4/ctn  |
| 161 CRT      | 6797RT       | Black Rototower<br>Holds 16 Cabinets.<br>Uses C26P-C & U45P-C<br>Cabinets Sold Separately | -                                             | -                                      | 18-1/2" x 18-1/2" x 72-1/2"*<br>(46.99 x 46.99 x 184.15 cm)<br><br>* from floor to top of cabinet | 1/ctn  |

## Conductive Replacement Drawers & Dividers\* (Plastic Frame Cabinets)



| Model Number | Stock Number | Description                                                                                    | Dimensions (Inside, L x W x D)                      | Packed |
|--------------|--------------|------------------------------------------------------------------------------------------------|-----------------------------------------------------|--------|
| TW-C         | 6061DP       | Uses (3) 35/52C dividers, dividers sold separately                                             | 2" x 5-3/8" x 1-3/8" (5.08 x 13.65 x 3.49 cm)       | 6/pk   |
| TQ-C         | 6064DP       | Uses (3) 50/64C dividers, dividers sold separately                                             | 2-1/2" x 5-3/8" x 2-1/4" (6.35 x 13.65 x 5.72 cm)   | 6/pk   |
| TJ-C         | 6065DP       | Uses (3) 57/135C dividers, dividers sold separately                                            | 5-3/8" x 5-3/8" x 2-1/4" (13.65 x 13.65 x 5.72 cm)  | 6/pk   |
| TF-C         | 6067DP       | Uses (3) 57/135C or (1) 57/275C or (1) 57/275C & (6) 50/64C dividers, dividers sold separately | 10-7/8" x 5-3/8" x 2-1/4" (27.62 x 13.65 x 5.72 cm) | 6/pk   |

| Model Number | Stock Number | Description                                                                  | Dimensions (Inside, L x W x D)               | Packed |
|--------------|--------------|------------------------------------------------------------------------------|----------------------------------------------|--------|
| 35/52C       | 6780CD       | Divider fits in Drawer TW-C, Divider wall thickness 1/16" (1.588 cm)         | 2" x 1-1/4" x 1/8" (5.08 x 3.18 x 0.32 cm)   | 25/pk  |
| 50/64C       | 6785CD       | Divider fits in Drawer TQ-C & TF-C, Divider wall thickness 1/16" (1.588 cm)  | 2-1/2" x 2" x 1/8" (6.35 x 5.08 x 0.32 cm)   | 24/pk  |
| 57/135C      | 6782CD       | Divider fits in Drawers TJ-C & TF-C, Divider wall thickness 1/16" (1.588 cm) | 5-3/8" x 2" x 1/8" (13.65 x 5.08 x 0.32 cm)  | 12/pk  |
| 57/275C      | 6784CD       | Divider fits in Drawers TF-C, Divider wall thickness 1/16" (1.588 cm)        | 10-7/8" x 2" x 1/8" (27.62 x 5.08 x 0.32 cm) | 6/pk   |

\* Contact Customer Service for large quantity divider purchases at 1-800-344-5716.

For Customer Service Inquiries Call 1-800-344-5716

# TABLE OF CONTENTS

## OVERVIEW & CAPABILITIES

Pages 2 - 13

- 2..... Company Overview - What's New From Flambeau
- 3..... Biodegradable
- 4..... Custom Soft-side
- 5..... Special Programs & Offerings
- 6..... Capabilities
- 7..... Zerust® & Tarnish Inhibitor
- 8-10..... Custom Manufacturing, Stock & Options
- 11..... FAQ's

## COMPARTMENTED BOXES

Pages 14 - 34

- 12-13 .... Compartmented Box Families Available
- 14-17 .... Reference Charts – Box Size
- 18-19 .... Reference Chart – Number of Compartments
- 20-31 .... Boxes Listed from Smallest to Largest Dimension
- 32..... Deep Super Satchel™, Slim Super Satchel™  
& Tarnish Inhibitor Slim Super Satchel™ Boxes
- 33..... Deluxe Super Satchel™ Boxes  
Double Deep Super Satchel™ Box
- 34..... Tuff Tainer® & Super Satchel, Tarnish Inhibitor  
Zerust® & Non-Zerust Divider Packs  
IDS (Infinite Divider System) Divider Packs

## CASES

Pages 35 - 48

- 35..... Tradesman™ & Merchant X Cases
- 36..... More Tradesman & Merchant X Cases
- 37..... Defender™ Case Series
- 38-39 .... Infinity™ Cases
- 40-41 .... "P" Series Cases
- 42-44 .... Airmold® "R" Series Cases
- 44..... Beta Case
- 45..... Black Ribbon Cases
- 46-47.... Accessories: Handles & Latches
- 48..... Blow Molded Tradesman & Mailers

## SPECIALTY STORAGE

Pages 49 - 54

- 49..... IDS™ Cabinets
- 50..... Parts Station™ Storage Cabinets  
Parts Station Rototower™  
Parts Station Replacement Drawers & Dividers
- 51..... Large Satchel-Style Cases
- 52 ..... Carry Packs™, Step 'N Store™ Stool & Expandable Tube
- 53 **NEW** Gun Cases: Economy Single Gun Case, Single Gun Case,  
Double Gun Case & Pistol Pack Series
- 54..... Utility Workstation™ Cart & Bin Storage Systems

## TOOL BOXES

Pages 55 - 61

- 55 **NEW** Rolling Tote Storage Cabinet & Blow Molded Tool Boxes
- 56..... Utility Boxes & Utility Boxes with Lift-Out Trays
- 57..... Utility Boxes with Cantilever Trays
- 58..... Low Boy™ Tool Box, Expandable Building Box &  
Versatile Utility Tool Box, Tailgator™
- 59..... Gear Boxes
- 60..... Lil' Brute™ Utility/Tool Box, Utility Tote,  
Utility Bench Box, Tool Chests
- 61..... Drawer Cabinets, Drawer Cabinet Replacement  
Drawer Packs & Tool Chest Replacement Drawer Packs

## MEDICAL

Pages 62 - 64

- 62 **NEW** Medical Device Box, Paramedic Gear Box &  
Paramedic Case
- 63..... First Aid Cases, Paramedic Case & Instrument Boxes
- 64..... Command Center Box, Trauma Drug Kits &  
Drawer Cabinets

## CONDUCTIVE

Pages 65 - 67

- 65..... Conductive Cases
- 66..... Conductive Tool Box, 600/800 Series Boxes &  
Conductive Storage Bins
- 67..... Conductive Storage Cabinets, Conductive Cabinet  
Rototower™ & Conductive Cabinet Replacement  
Drawers & Dividers



**Flambeau®** INC.

A MEMBER OF THE NORDIC GROUP OF COMPANIES

**Customer Service: (800) 344-5716**

15981 Valplast Street, Middlefield, Ohio 44062

PH: (440) 632-1631 • Fax: (440) 632-1581

Check us out at: [www.flambeaucases.com](http://www.flambeaucases.com)



© 2011 Flambeau® Inc. All Rights Reserved. Zerust® is a registered trademark of Northern Technologies International Corporation.