


F



**CONNECTOR
SPECIFICATION:**

VOLTAGE RATING	600V AC/DC
AMPERAGE RATING	2P: 25 AMPS, 3P: 25 AMPS, 4P: 20 AMPS
PROTECTION	IP67
OPERATING TEMP.	-20°C TO 105°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237

POLES	MATERIAL NO.	ENGINEERING NO.	FINISHED LENGTH
4	1300000088	32678	6.0 FT. +2.19"-0 [183CM+56mm-0]
4	1300000090	32679	12.0 FT. +3.50"-0 [366 CM +89mm-0]

5	LABEL	VINYL	YELLOW
4	COUPLING	THERMOPLASTIC	BLACK
3	CONTACT SOCKET	COPPER ALLOY	UN-PLATED
2	OVERMOLD	RUBBER	YELLOW
1	CABLE-12 AWG SOW	CPE JACKET	YELLOW
ITEM	COMPONENT	MATERIAL	FINISH

RELEASED		QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
EC NO:	DRWN:		mm	INCH	DRAWN BY	DATE			
EC NO: IPG2013-0663	DRWN: RSTONE 2012/11/26	1	4 PLACES	±---	±---	RSTONE	2012/11/26	MOLEX INCORPORATED	QUICK CHANGE CABLE ASSY 2-4P FEMALE, 12 AWG
CH'K'D: K JOZWIK	APPR: JFMURPHY 2013/02/07	2	3 PLACES	±---	±---	CHECKED BY	DATE		
		3	2 PLACES	±---	±.01	K JOZWIK	2012/11/28		
		4	1 PLACE	±0.3	±---	APPROVED BY	DATE		
		5	ANGULAR ±2°			JFMURPHY	2013/02/07		
ITEM	COMPONENT	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		MATERIAL NO.	DOCUMENT NO.	SHEET NO.
		A			SD-130000-005				1 OF 1
			SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				