

Wiha 3K Series Screwdrivers and Sets



460 95 Set 5 Pcs. Slotted & Phillips

Blade chrome-vanadium-molybdenum steel, chrome nickel-plated.
Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item							
No.	mm	mm		Size	mm		lbs.
460 95	450 55	4.5	100	451 35	0	60	1.04
	450 60	6.0	100	451 37	1	80	Each
				451 42	2	100	\$21.94



460 94 Set 6 Pcs. Slotted & Phillips

Blade chrome-vanadium-molybdenum steel, chrome nickel-plated.
Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item No.							
	mm	mm	Size	mm	lbs.		
460 94	450 50	3.0	100	451 37	1	80	.91
	450 55	4.5	100	451 44	2	150	
	450 58	5.5	125				Each
	450 65	6.5	150				\$26.48



460 97 Set 8 Pcs. Slotted & Phillips Blade CVM steel, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item							
No.	mm	mm		Size	mm		lbs.
460 97	450 50	3.0	100	451 37	1	80	1.70
	450 55	4.5	100	451 42	2	100	
	450 60	6.0	100	451 50	2	40	Each
	450 67	8.0	150	451 52	3	150	\$40.54



452 Pozidriv® Screwdriver, With Wiha-3K Series Handle

Blade chrome-vanadium-molybdenum steel, hard chromed shaft.
Wiha-3k Ergo handle, cushion grip. Black tip.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.	Each
452 05	0	60	2.3	146	5.7	.06	10	\$3.00
452 07	0	100	3.9	186	7.3	.07	10	\$3.00
452 15	1	80	3.1	187	7.3	.13	10	\$4.14
452 20	1	100	3.9	207	8.1	.14	10	\$4.14
452 25	2	100	3.9	219	8.6	.21	10	\$5.50
452 30	2	150	5.9	269	10.6	.23	10	\$6.12
452 35	3	150	5.9	269	10.6	.31	10	\$7.26



451 Phillips Screwdriver, With Wiha-3K Series Handle & Hanger

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.	Each
451 62	1	80	3.1	187	7.3	.14	1	\$4.02
451 64	1	200	8.0	307	12.0	.17	1	\$4.94
451 65	2	100	4.0	218	8.5	.22	1	\$5.36
451 66	2	150	6.0	268	10.5	.24	1	\$5.58
451 67	2	200	8.0	318	12.5	.26	1	\$7.64
451 71	3	150	6.0	268	10.5	.32	1	\$6.82



450 Slotted Screwdriver, With Wiha-3K Series Handle & Hanger

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	Each
450 23*	4.0	.157	100	4.0	0.8	.031	206	8.1	.13	1	\$4.12
450 24	4.5	.177	100	4.0	1.0	.039	207	8.1	.14	1	\$3.80
450 25	4.5	.177	150	6.0	1.0	.039	257	10.1	.15	1	\$4.54
450 26	4.5	.177	200	8.0	1.0	.039	306	12.0	.16	1	\$4.84
450 27	5.5	.216	125	5.0	1.0	.039	243	9.5	.20	1	\$4.22
450 28	6.0	.236	100	4.0	0.9	.035	218	8.5	.21	1	\$4.74
450 29	6.0	.236	150	6.0	0.9	.035	268	10.5	.24	1	\$5.26
450 30	6.0	.236	200	8.0	0.9	.035	318	12.5	.26	1	\$5.46
450 33	8.0	.315	150	6.0	1.2	.047	268	10.5	.27	1	\$6.82
450 34	10.0	.393	200	8.0	1.6	.063	318	12.5	.36	1	\$7.14

* Cabinet Tip



455 TORX® Screwdriver, With Wiha-3K Series Handle & Hanger

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.	Each
455 57	T15	80	4.0	190	7.5	.12	1	\$4.12
455 58	T20	100	4.5	215	8.4	.12	1	\$4.32
455 59	T25	100	4.5	215	8.4	.21	1	\$4.64
455 60	T27	115	5.1	240	9.4	.29	1	\$5.16
455 62	T30	115	6.0	233	9.1	.32	1	\$5.78