

PRODUCT FAMILIES

Pin Headers and Sockets

Clips and Insulators

Banana Plugs and Wires

Grabbers, Probes and Spade Terminals

Test Leads and Patch Cords

Coaxial Cable Assemblies

Coaxial Test Leads

Coaxial Break-Outs

DMM Kits

Coaxial Break-Outs

Mini-Micro-Plunger to BNC Male

TOOL SEARCH TOOLS

MUELLER OR DISTRIBUTOR STOCK SEARCH

PART #

SEARCH

CROSS COMPETITOR PART #

Choose a Brand

PART #

SEARCH

TOOL MeterMate® DMM ACCESSORY SELECTOR

Select Meter Make

Select a Make First

TOOL BUILDS A PCB HEADER OR SOCKET OVER 15,000 IN STOCK

GD

Model# BU-1450-C-**-0

- Material: BNC Male Connector: MIL-C-39012, gold-plated center contact and silver-plated body; Coaxial Cable: shielded RG58C/U, MIL-C-17F, 50 ohm; Plunger: nylon housing, stainless steel spring and beryllium copper contact
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 300 VRMS on center conductor

Insulated Alligator Clips to BNC Male With RG58



Model# BU-5030-C-**-0

- Material: Alligator Clip: nickel-plated steel with PVC insulator; BNC Male Connector: MIL-C-39012, gold-plated center contact and silver-plated body (RG174/U BNC is a commercial connector with nickel-plated body); Coaxial Cable: shielded RG58C/U, MIL-C-17F, 50 ohm or shielded RG174/U, MIL-C-17D, 50 ohm
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 300 VRMS on center conductor

BNC Male Breakout to Tinned End Wires



Model# BU-5100-A-4-0

- Material: BNC Male Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS on center conductor

BNC Male Breakout to Mini-Micro-Grabbers



Model# BU-5114-A-4-0

- Material: BNC Male Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Mini-Micro-Grabbers (No.208) conductor and abrasion resistant, nylon housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 150 VRMS, 5 Amp

Insulated BNC Male to BNC Female



Model# BU-5659-B-**-0

- Material: BNC Male/Female Connector: fully insulated nylon housing; nickel-plated brass body, gold/nickel plated brass center contact; polyethylene dielectric; Coaxial Cable: RG58, 50 ohm
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 500 VRMS on center conductor


BNC Male Breakout to Stackable Single Banana Plugs



Model# BU-5120-A-4-0

- Material: BNC Male Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Banana Plug: premium nine-leaf, nickel-plated beryllium copper springs and copper alloy 360 bodies for minimum stacked in multiples, ABS housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amp

BNC Male Breakout to Insulated Mini-Alligator Clips



Model# BU-5131-A-4-0

- Material: BNC Male Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Clip: Mueller No. 30BL with No. 31 insulators; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 10 Amp

BNC Male Breakout to Stackable 0.080" (2.0mm) Pin Plugs



Model# BU-5144-A-4-0

- Material: BNC Male Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Pin Tip: nickel-plated brass 0.080" (2.0mm) dia; 0.500" (12.7mm) long; Tip Jack: Accepts 0.080" (2.0mm) dia. pin, nickel-plated, alloy 360 copper body; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amps

BNC Female Breakout Style to Tinned End Wires



Model# BU-5200-A-4-0

- Material: BNC Female Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amps

BNC Female Breakout to Mini-Micro-Grabbers



Model# BU-5214-A-4-0

- Material: BNC Female Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Mini-Micro-Grabbers (No.208) conductor and abrasion resistant, nylon housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amps

BNC Female Breakout to Stackable Single Banana Plugs



Model# BU-5220-A-4-0

- Material: BNC Female Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Banana Plug: premium nine-leaf, nickel-plated beryllium copper springs and copper alloy 360 bodies for minimum stacked in multiples, ABS housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 10 Amps

BNC Female Breakout to Insulated Mini-Alligator Clips



Model# BU-5231-A-4-0

- Material: BNC Female Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Clip: Mueller No. 30BL with No. 31 insulators; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amps

BNC Female Breakout to Stackable 0.080" (2.0mm) Pin Plugs



Model# BU-5244-A-4-0

- Material: BNC Female Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Pin Tip: nickel-plated brass 0.080" (2.0mm) dia; 0.500" (12.7mm) long; Tip Jack: accepts 0.080" (2.0mm) dia. pin, nickel-plated, alloy 360 copper body; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amps

Insulated Alligator Clips to BNC Male With RG174



Model# BU-5330-F-**-0

- Material: Alligator Clip: nickel-plated steel with PVC insulator; BNC Male Connector: MIL-C-39012, gold-plated center contact and silver-plated body (RG174/U BNC is a commercial connector with nickel-plated body); Coaxial Cable: shielded RG58C/U, MIL-C-17F, 50 ohm or shielded RG174/U, MIL-C-17D, 50 ohm
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 300 VRMS on center conductor