




- 1 TIN PL .000150 MIN THK
MIL-T-10727
- 2 PART NO: 324460; .052 LB.
PART NO: 1-324460-0; .052 LB.
PART NO: 1-324460-3; .061 LB.
- 3 PRELIMINARY - NOT FOR PRODUCTION
- 4 .045 MAX BURR ALLOWED INSIDE THE WIRE
BARREL ID IN AREA OF SIGHT HOLE.

.66	.91	1.77	△	150,500-	COPPER	△ 1-324460-3
.66	.66	1.52	CLEANED	190,000	ASTM-B-75	1-324460-0
			△	CM	ANNEALED	324460
"C"	"B"	"A"	FINISH	WIRE RANGE	MATERIAL	PART No

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 4/24/89	TE Connectivity	
		CHK MS FEHER 4/24/89		
DIMENSIONS: INCHES		APVD WJ VOCKROTH 11/8/89	NAME	
		PRODUCT SPEC	SPLICE, BUTT, AMPPOWER WIRE SIZE: 3/0 AWG	
MATERIAL SEE TABLE		APPLICATION SPEC	SIZE A3	
FINISH SEE TABLE		WEIGHT △ 2	CAGE CODE 00779	DRAWING NO C=324460
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1
			REV R	