

DESCRIPTION: DIP SOLDER FEMALE/STAMPED

SPECIFICATIONS:



MATERIALS:

SHELL: STEEL, NICKEL PLATED
INSULATOR: UL 94V-0 RATED BLACK NYLON 9T
CONTACTS: BRASS, GOLD PLATED
RoHS COMPLIANT

ELECTRICALS:

CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: 15 mOHMS MAX
INSULTOR RESISTANCE: 1000 MOHMS MIN
VOLTAGE: 500V AC FOR 1 MINUTE
TEMPERATURE: -50°C TO +100°C

POS.	A	B	C	D	E	F	G
09	1.213	0.984	0.642	0.756	0.311	0.109	0.496
	30.80	24.99	16.30	19.20	7.90	2.77	12.60
15	1.541	1.312	0.971	1.091	0.311	0.109	0.496
	39.14	33.32	24.65	27.70	7.90	2.77	12.60
25	2.087	1.852	1.512	1.618	0.311	0.109	0.496
	53.00	47.04	38.40	41.10	7.90	2.77	12.60
37	2.728	2.500	2.157	2.256	0.311	0.109	0.496
	69.29	63.50	54.80	57.30	7.90	2.77	12.60
50	2.638	2.406	2.055	2.169	0.429	0.109	0.602
	67.00	61.00	52.20	55.10	10.90	2.77	15.30



171-YYY-213RYY1

SERIES _____
POSITIONS _____
009
015
025
037
050
GENDER _____
1 = MALE
2 = FEMALE
TERMINATION _____
1 = DIP SOLDER
SHELL PLATING _____
3 = NICKEL
HARDWARE OPTIONS _____
00 = NO HARDWARE
01 = .098" 4-40 CLINCH NUT BOARD SIDE
02 = .236" 4-40 CLINCH NUT BOARD SIDE
03 = .236" 4-40 CLINCH NUT MATING SIDE
05 = .237" 4-40 BOARD LOCK
08 = .228" 4-40 BOARD LOCK
91 = .237" 4-40 SPACER/BOARD LOCK
PLATING OPTIONS _____
1 = GOLD FLASH
2 = 30 MICRO-INCH GOLD

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS

DATE:
8-12-98

CHECKED:

DATE:

SCALE:

SHEET

OF

1

3

REV
10






DWG NO.

171-YYY-213RYY1

RoHS COMPLIANT

NorComp

DESCRIPTION: PCB LAYOUT - STANDARD "D" - MALE & FEMALE



* TYP. ON ALL SIZES


DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: C. SMITH		DATE: 03-08-06		
			CHECKED:		DATE:		
			SCALE: FULL		SHEET 2 OF 3		REV 10
			DWG NO. 171-YYY-213RYY1				


TOLERANCE:
ALL DIMENSIONS ARE ±0.010

ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS


01X 0.098" (BOARD SIDE) - CN1




02X 0.236" (BOARD SIDE) - CN2




03X..... 0.236" (MATING SIDE) - CN8




05X 0.237" (BOARD SIDE) - CN10



08X 0.228" (BOARD SIDE) - CN3



91X 0.237" BOARD SIDE
0.197 MATING SIDE
CN10/SFSO4404



NOTE: 4-40 FEMALE SCREW LOCK IS REMOVABLE

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS

DATE:
11-28-05

CHECKED:

DATE:

SCALE:

SHEET **3** OF **3**

REV **10**

DWG NO.

171-YYY-213RYY1

RoHS COMPLIANT

NorComp

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

<u>171-015-213R031</u>	<u>171-025-213R031</u>	<u>171-009-213R011</u>	<u>171-009-213R021</u>	<u>171-009-213R031</u>	<u>171-009-213R911</u>
<u>171-015-213R011</u>	<u>171-015-213R021</u>	<u>171-025-213R011</u>	<u>171-025-213R021</u>	<u>171-025-213R911</u>	<u>171-037-213R011</u>
<u>171-037-213R021</u>	<u>171-037-213R031</u>	<u>171-037-213R911</u>	<u>171-050-213R011</u>	<u>171-050-213R021</u>	<u>171-050-213R031</u>
<u>171-050-213R911</u>	<u>171-015-213R911</u>	<u>171-050-213R051</u>			