

Protective covers - HC-B16-BCSFS-P-BK - 1414626

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON protective covers, B16, for HC-EVO-B16... supporting base element, for single locking latch, with retaining cord with combination eyelet, IP54



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
Custom tariff number	85389099
Country of origin	Germany

Technical data

Environmental Product Compliance

China RoHS	No hazardous substances above threshold values
------------	------------------------------------------------

Ambient conditions

Ambient temperature (operation)	-20 °C ... 100 °C
---------------------------------	-------------------

General

Size	B16
Material	PA
Flammability rating according to UL 94	HB
Seal present	no
Note	Protective cover for supporting base element with single locking latch
Connection	Plastic protective cover for short-term protection


Standards and Regulations

Flammability rating according to UL 94	HB
----------------------------------------	----

Protective covers - HC-B16-BCSFS-P-BK - 1414626

Drawings

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 5.1	23110102
eCl@ss 6.0	23110102
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

ETIM

ETIM 5.0	EC002314
----------	----------

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
