

DIALIGHT PART NUMBER	DIM "A"	TERMINAL TYPE	COLLAR & FLANGE NUT FINISH
508-7438-504	.865 [21,74]	FIG. 1	BLACK ANODIZE
508-7438-604	.865 [21,74]	FIG. 1	CLEAR ANODIZE
508-7445-504	.942 [23,92]	FIG. 1	BLACK ANODIZE
508-7445-604	.942 [23,92]	FIG. 1	CLEAR ANODIZE
508-7538-504	.834 [21,18]	FIG. 2	BLACK ANODIZE
508-7538-604	.834 [21,18]	FIG. 2	CLEAR ANODIZE
508-7545-504	.920 [23,37]	FIG. 2	BLACK ANODIZE
508-7545-604	.920 [23,37]	FIG. 2	CLEAR ANODIZE
508-8738-504	.848 [21,54]	FIG. 3	BLACK ANODIZE
508-8738-604	.848 [21,54]	FIG. 3	CLEAR ANODIZE
508-8745-504	.934 [23,72]	FIG. 3	BLACK ANODIZE
508-8745-604	.934 [23,72]	FIG. 3	CLEAR ANODIZE





FIG.1 - SOLDER BLADE TERMINALS

NOTES:

- 1. DIALIGHT PART NUMBERS: 508-74XX-504, 508-74XX-604, 508-75XX-504, 508-75XX-604, 508-87XX-504 & 508-87XX-604.
- 2. MAXIMUM PANEL THICKNESS: .156"
- 3. RECOMMENDED MOUNTING HOLE SIZE: .380±.002".

REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	—	NEW RELEASE	AJF	KLJ	NO	12-20-10




FIG.2 - SOLDER CUP TERMINALS




FIG.3 - TURRET TERMINALS

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.				
SCALE: 4.000		DRAWING NUMBER C-17895		REV A
ALL DIM'S IN: INCHES (MM)				
TOLERANCES: UNLESS OTHERWISE SPECIFIED		TITLE 508 SERIES DATALAMP HOLDER		
FRACTIONS: ±1/64				
DECIMALS (.XX): ±.01		MATERIAL		
DECIMALS (.XXX): ±.005				
DECIMALS (.XXXX): ±.0005		Dialight 1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727		
ANGLES: ±1°				
FINISH:		SHEET 1 OF 1		
FSCM 83330				
		FAMILY TABLE:		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[508-7538-604](#) [508-7545-504](#) [508-7445-504](#) [508-8745-604](#) [508-8738-604](#)