



Units:mm



P1	P2	P3	COLOR
1	1	1	RED
2	1	1	WHITE
3	2	2	DRAIN(RED)
		2	DRAIN(WHITE)

Electrical test:
1.100% short,open,miswire test
2.Conduct resistance: 2 0hm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



⑪	TIE	2	BLACK L=80mm
⑩	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑨	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"
⑧	TUBE	3	HEAT SHRINK TUBE BLACK OD1.5*10mm
⑦	S/R	1.5g	BLACK PVC 40P (Mould NO.:SR-048)
⑥	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)
⑤	OUT JACKET	3.3g	PVC-40P RED(RD-35),(Mould NO.:WM-009)
④	OUT JACKET	3.3g	CLEAR LD-PE (Mould NO.:NM-006)
③	OUT JACKET	3.3g	PVC-40P WHITE(W-100)(Mould NO.:WM-009)
②	CABLE	1	NOUL [(10/0.10)*S(28/0.10)*2F JACKET BLACK OD2.8*5.6mm
①	CONN	2	RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN
①	CONN	1	3.55T MALE Tray6.0mm L=26mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK
NO.	NAME	QTY	SPECIFICATION

NOTE:
1.小PE袋/大PE袋对应料号,包袋数量及时间印刷样式:


CnC Tech, LLC	Industrial Cable and Connector Technology
770-10043-00100	10 PCS
529	RoHS
770-10043-00100	10 PCS
529	RoHS

2.外箱两个侧唛ITEM NO后面各贴一个35*22mm RoHS标签。

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY	LICHENG	DRAWING NO.	V6/LJ0-094-080-A
CHECKED BY		CUSTOMER	CNC
APPROVAL BY		ITEM NO.	770-10043-00100
DECIDE BY		DATE	2012-12-28
VERSIONS/EDITION	A/0	PROJECTION	


Units:mm



PIN ASSIGNMENT:

P1	P2	P3	COLOR
1	1	1	RED
2	1	1	WHITE
3	2	2	DRAIN(RED)
		2	DRAIN(WHITE)

Electrical test:
1.100% short,open,miswire test
2.Conduct resistance:2 Ohm(max)
3.Insulation resistance:10Mohm(min)
4.dielectric test:DC 300V



⑪	TIE	2	BLACK L=80mm
⑩	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑨	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"
⑧	TUBE	3	HEAT SHRINK TUBE BLACK OD1.5*10mm
⑦	S/R	1.5g	BLACK PVC 40P (Mould NO.:SR-048)
⑥	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	3.3g	PVC-40P RED(RD-35),(Mould NO.:WM-009)
⑤	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	3.3g	PVC-40P WHITE(W-100)(Mould NO.:WM-009)
④	OUT JACKET	3.0g	BLACK PVC-40P (Mould NO.:WM-020)
③	CABLE	1	NOUL [(10/0.10)+S(28/0.10)]*2F JACKET BLACK OD2.8*5.6mm
②	CONN	2	RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN
①	CONN	1	3.55T MALE Tray6.0mm L=26mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK
NO.	NAME	QTY	SPECIFICATION

NOTE:
1.小PE袋/大PE袋对应料号,包袋数量及时间印刷样式:


CnC Tech, LLC	Industrial Cable and Connector Technology
770-10043-00150	10 PCS
10 PCS	529
10 PCS	529

2.外箱两个侧吸ITEM NO.后面各贴一个35*22mm ROHS标签。

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY	LICHENG	DRAWING NO.	V6/LJQ-094-080-B
CHECKED BY		CUSTOMER	CNC
APPROVAL BY		ITEM NO.	770-10043-00150
DECIDE BY		DATE	2012-12-28
VERSIONS/EDITION	A/0	PROJECTION	


Units:mm



PIN ASSIGNMENT:

P1	P2	P3	COLOR
1	1	1	RED
2	1	1	WHITE
3	2	2	DRAIN(RED)
		2	DRAIN(WHITE)

Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2.0hm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



⑪	TIE	2	BLACK L=80mm
⑩	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑨	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"
⑧	TUBE	3	HEAT SHRINK TUBE BLACK OD1.5*10mm
⑦	S/R	1.5g	BLACK PVC 40P (Mould NO.:SR-048)
⑥	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	3.3g	PVC-40P RED(RD-35),(Mould NO.:WM-009)
⑤	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	3.3g	PVC-40P WHITE(W-100)(Mould NO.:WM-009)
④	OUT JACKET	3.0g	BLACK PVC-40P (Mould NO.:WM-020)
③	CABLE	1	NOUL [(10/0.10)+S(28/0.10)]*2F JACKET BLACK OD2.8*5.6mm
②	CONN	2	RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN
①	CONN	1	3.5ST MALE Tray6.0mm L=26mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK
NO.	NAME	QTY	SPECIFICATION


NOTE:
1.小PE袋/大PE袋对应料号,包袋数量及时间印刷样式:
Cnc Tech, LLC
Industrial Cable and Connector Technology
770-10043-00200
10 PCS
ROHS
529
印袋人/产品料号
印对应的袋袋数量
表示529/09年(按海关产品生产牌照印)

2.外箱两个侧面ITEM NO.后面各贴一个35*22mm ROHS标签。

Cnc Tech, LLC
Industrial Cable and Connector Technology


DRAWN BY	LICHENG	DRAWING NO.	V6/LJQ-094-080-C
CHECKED BY		CUSTOMER	CNC
APPROVAL BY		ITEM NO.	770-10043-00200
DECIDE BY		DATE	2012-12-28
VERSION/EDITION	A/0	PROJECTION	

Units:mm



P1	P2	P3	COLOR
1	1		RED
2	1		WHITE
3	2		DRAIN(RED)
		2	DRAIN(WHITE)

Electrical test:
1.100% short,open, miswire test
2. Conduct resistance: 5 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



⑪	TIE	2	BLACK L=120mm
⑩	PE BAG	1/5	CLEAR SIZE: 280*330*0.05mm PRINT BLACK*MADE IN CHINA*+*5PCS*
⑨	PE BAG	1	CLEAR SIZE: 150*280*0.05mm PRINT BLACK*MADE IN CHINA*+*1PC*
⑧	TUBE	3	HEAT SHRINK TUBE BLACK OD1.5*10mm
⑦	S/R	1.5g	BLACK PVC 40P (Mould NO.:SR-048)
⑥	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	3.3g	PVC-40P RED(RD-35),(Mould NO.:WM-009)
⑤	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	3.3g	PVC-40P WHITE(W-100)(Mould NO.:WM-009)
④	OUT JACKET	3.0g	BLACK PVC-40P (Mould NO.:WM-020)
③	CABLE	1	NOUL TC(100.10)*S(280.10)*2F JACKET BLACK OD2.8*5.6mm
②	CONN	2	RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN
①	CONN	1	3.55T MALE Tray6.0mm L=26mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK
NO.	NAME	QTY	SPECIFICATION

NOTE:
1.小PE袋/大PE袋对应料号,包袋数量及时间印刷样式:

CnC Tech, LLC	770-10043-00500	5 PCS.	ROHS	529
Industrial Cable and Connector Technology				
印袋人产料号	印袋人产料号	印袋人产料号	印袋人产料号	印袋人产料号
印袋人产料号	印袋人产料号	印袋人产料号	印袋人产料号	印袋人产料号

2. 外箱两个侧面ITEM NO.后面各贴一个35*22mm ROHS标签。

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY	LICHENG	DRAWING NO.	V6/LJQ-094-080-D
CHECKED BY		CUSTOMER	CNC
APPROVAL BY		ITEM NO.	770-10043-00500
DECIDE BY		DATE	2012-12-28
VERSIONS/EDITION	A/0	PROJECTION	

