

Digital Sound Level Meter



Features

- USB interface with datalogging software
- Internal datalogging
- A and C weighting
- Selectable fast / slow response time
- Large 1999 count backlit LCD display
- Analog bargraph display and numerous on-screen icons
- AC/DC outputs for level recorder
- Self calibration with internal oscillator
- Selectable MIN or MAX hold and data hold function
- Three measurement ranges
- 0.1dB resolution
- Selectable auto-power-off
- Threaded insert which accepts standard tripod mount
- Removable windscreen
- AC adaptor (included) or battery operation
- Includes manual, 9V battery and rugged blow molded carry case

This Flagship of the Tenma sound level meter line provides features normally exclusive to units costing much more. It is perfect for sound system testing, speaker system measurement and environmental noise level monitoring.

Specifications

Standard applied	: IEC61672-1 Class 2
Frequency range	: 31.5Hz ~ 8KHz
Measuring level range	: 30dB ~ 130dB
Frequency weighting	: A/C
Microphone	: 1/2 inch electret condenser
Calibration	: External potentiometer for use with external calibrated source
Display	: 1999 count LCD, plus analog bargraph Resolution: 0.1dB Refresh rate: 0.5 sec.
Accuracy	: ± 1.4 dB, @1KHz, 94dB (under reference conditions)
Time weighting	: FAST (125ms), SLOW (1 sec.)



Digital Sound Level Meter



Level ranges	: Lo: 30dB ~ 80dB Med: 50dB ~ 100dB Hi: 80dB ~ 130dB
Alarm function	: Displays "OVER" when input exceeds maximum level of selected range Displays "UNDER" when input falls below minimum level of selected range
AC output	: 1.0Vrms at full scale, output impedance approximately 100Ω
DC output	: 10mV / dB, output impedance approx 1KΩ
Data output	: USB data traffic
Internal datalogging memory	: 32,700
Auto power off	: Meter automatically shuts down after approx. 15 minutes of inactivity
Power supply	: One 9V battery, 006P or NEDA1604 or IEC 6F22, or included AC adaptor
Battery life	: Approximately 30 hours
Operation temperature	: 0°C ~ 40°C, (32°F ~ 104°F)
Operation humidity	: 10 ~ 90% RH
Storage temperature	: -10°C ~ 60°C
Dimension	: 9 3/4" (L) × 2 1/2" (W) × 1" (D)
Weight	: 350g (including battery)
Accessories	: Instruction manual, battery, windscreen, case, USB cable and software

Part Number Table

Description	Part Number
Digital Sound Level Meter	72-947

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

