

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200210006](#)
Status: **Active**
Overview: [Brad Ultra-Lock Connection System](#)
Description: Micro-Change (M12) Ultra-Lock (M12) Double-Ended Cordset, 12 Poles, Female (Straight) to Male (Straight), PUR Cable Shielded, Black, 3.0m (9.84') Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Industrial Cordsets
Series [120021](#)
Connector End A Ultra-Lock (M12)
Connector End B Ultra-Lock (M12)
IP Rating IP68
Material - Contact Copper Alloy
Overview [Brad Ultra-Lock Connection System](#)
Product Name Ultra-Lock (M12)
Protocol N/A
Region Europe
Type Double Ended
UPC 883906197742

Physical
Cable Diameter 6.50mm (.256")
Cable Length 3.0m (9.84')
Color - Cable Jacket Black
Coupling Style Push to Lock
Gender Female-Male
Keyway Single
LED Indicator No
Material - Cable Jacket PUR
Material - Connector Body PUR
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold
Orientation Straight to Straight
Poles 12
Temperature Range - Operating -25°C to +80°C
Wire Size AWG 26
Wire/Cable Type UL 20549

Electrical
Current - Maximum per Contact 1.5A
Voltage - Maximum 30V AC/DC

Material Info
Engineering Number WWCS30P45M030G

Reference - Drawing Numbers
Sales Drawing SD-WWCS30P45MXXX



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[120021](#) Series