



# International Components Corporation

A reputation of excellence in the field of quality electronic components.

Product: **ELECTRO-ACOUSTIC TRANSDUCER**

Description: **ROHS COMPLIANT**

Part Number: **BRT2821P-24**

## SPECIFICATIONS:


RATED VOLTAGE:	24 VDC
OPERATING VOLTAGE:	15 ~ 28
MAX CURRENT:	25 mA
SOUND OUTPUT LEVEL:	95dB @ 30 cm
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	2800 ± 200
OPERATING TEMPERATURE:	-20 TO +60°C
tone MODE:	CONTINUOUS
PULSE RATE:	N/A
COIL RESISTANCE:	NOT APPLIC
COIL IMPEDANCE:	WITH BUILT
FRAME DIAMETER:	28.0 mm
FRAME DEPTH:	20.0 mm
MOUNTING DIMENSIONS:	14.0 mm

## COMMENTS:


\*VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY,

\*\*VALUE APPLYING (RESONANT FREQUENCY, SINE WAVE, M

## DIMENSIONS:



## FREQUENCY RESPONSE:



\*\*Note - Frequency is 2.8 KHz. + 0.2 KHz. from 3 to 8 VDC