


SOLISTA LED



Specification

Voltage	9 - 28Vdc
Current	3mA / 6mA @ 24Vdc (user selectable)
Flash Rate	0.5Hz / 1Hz (user selectable)
Temperature	-10°C to + 55°C
Monitoring	Reverse polarity
Construction	ABS Body / Polycarbonate Lens
IP Rating	IP54 (Shallow Base) IP65 (Deep / U Base)
Lens Colour	Red or Amber
Body Colour	Red or White
Weight	0.1Kg

LED beacons are available to complement audible alarms for use in areas where people may be present who have impaired hearing or areas with high ambient noise levels. LED technology offers a greatly reduced current consumption compared to Xenon types making them ideal for use with fire panels with restricted sounder circuit current capacity.

- ULTRA LOW CURRENT – LED TECHNOLOGY
- HIGH RELIABILITY
- LONG SERVICE LIFE
- STANDARD BAYONET BASE FITTING
- COMPACT SIZE