

Temperature Dataloggers

TEMPERATURE LOGGER -5 to +15° C

HI-140G

HANNA INSTRUMENTS

- Accuracy: $\pm 0.3^{\circ}\text{C}$
- IP rating: IP65
- Resolution: 0.1°C
- Temperature measuring ranges, -5 to $+15^{\circ}\text{C}$



A range of datalogging thermometer modules that can be left unattended and will take temperature readings at set intervals, without the need for external probes.

The modules are housed in fully waterproof cases that are not much larger than a computer mouse. The Windows software allows the modules to be programmed with C or F readings, high/low temperature alarms and sample time intervals, and displays the downloaded results in chart or graph form.

7,600 temperature readings that are stored in the non-volatile memory

1min to 24 hour reading frequency

Delayed start facility

High and low temperature LED alarms

Infrared downloading via RS232 interface and Windows software

4 years battery life from a standard AA type battery

Selectable ID number

Suitable for food applications

Integral moulded eye hook hanger