




## Network and Electrical Solutions

UNIFIED PHYSICAL INFRASTRUCTURE<sup>SM</sup>

Worldwide | 

### FS78-8-DSL2



- Polypropylene insulation housing available in DIN standard colors in strips of 50
- Continuously molded design provides consistent placement of ferrules in tool to ensure fast, reliable terminations
- Available in #20 – #14 AWG featuring a seamless barrel design to contain loose wire strands for superior terminations
- Designed for use with the Semiautomatic Ferrule Crimping Tool CT-1000 for medium volume applications

|                                 |                                                                                                   |
|---------------------------------|---------------------------------------------------------------------------------------------------|
| ▪ Part Number                   | FS78-8-DSL2                                                                                       |
| ▪ RoHS Compliancy Status        | Compliant                                                                                         |
| ▪ Part Description              | Insulated ferrules, single wire French end sleeve on strip.                                       |
| ▪ Color                         | Red                                                                                               |
| ▪ Length (In.)                  | .60                                                                                               |
| ▪ Length (mm)                   | 15.2                                                                                              |
| ▪ CE Compliant                  | No                                                                                                |
| ▪ CE Marking                    | No                                                                                                |
| ▪ Inside Diameter (In.)         | .07                                                                                               |
| ▪ Inside Diameter (mm)          | 1.8                                                                                               |
| ▪ Max. Wire Insul. Dia. (In.)   | .13                                                                                               |
| ▪ Pin Length (In.)              | .31                                                                                               |
| ▪ Pin Length (mm)               | 8.0                                                                                               |
| ▪ Pricing Description           | Insulated Ferrules on Strips, single wire, 16 AWG (1.5mm), .31"(8.0mm) pin length, red end sleeve |
| ▪ Tool                          | CT-1000                                                                                           |
| ▪ Wire Range                    | 16 AWG                                                                                            |
| ▪ Wire Range (mm <sup>2</sup> ) | 1.50                                                                                              |
| ▪ Wire Strip Length (In.)       | 13/32                                                                                             |
| ▪ Wire Strip Length (mm)        | 10                                                                                                |