

4, 5 and 8-Wire M12 eurofast® Field Wireable Connectors, Standard and Reverse Key

- Straight Male Connectors
- IEC IP 67 Protection



Drawing	Part Number	Housing Specs.	Application	Pinout
	BS 8141-0	PBT, Black PG 7 cable gland accepts 4-6 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 60 V, 4 A	Mates with standard key 4-pin cordsets and receptacles	
	BS 8141-0/PG 9	PBT, Black PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 60 V, 4 A	Mates with standard key 4-pin cordsets and receptacles	
	BS 8151-0/PG 9	PBT, Black PG 9 cable gland, accepts 6-8 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 60 V, 4 A	Mates with standard key 5-pin cordsets and receptacles	
	BS 8157-0/PG 9	PBT, Black PG 9 cable gland, accepts 6-8 mm cable diameter Spring clamp accepts up to 20 AWG conductors 85°C 125 V, 4 A	Mates with standard key 5-pin cordsets and receptacles, spring clamp	
	BSWS 8141-0	PBT, Black PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 250 V, 4 A	Mates with <u>reverse</u> key 4-pin cordsets and receptacles	
	BSWS 8151-0	PBT, Black PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 125 V, 4 A	Mates with <u>reverse</u> key 5-pin cordsets and receptacles	
	BS 8181-0	Nylon, Black PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 30 VAC/75 VDC, 2 A	Mates with standard key 8-pin cordsets and receptacles	