



**One smart printer to print it all**



|                                                         |          |
|---------------------------------------------------------|----------|
| <b>BMP™71 Label Printer &amp; Accessories . . . . .</b> | <b>2</b> |
|---------------------------------------------------------|----------|



|                                                                                     |           |
|-------------------------------------------------------------------------------------|-----------|
| <b>High Performance Industrial Identification / Safety Identification . . . . .</b> | <b>10</b> |
|-------------------------------------------------------------------------------------|-----------|



|                                                               |           |
|---------------------------------------------------------------|-----------|
| <b>General and Industrial Identification Labels . . . . .</b> | <b>11</b> |
|---------------------------------------------------------------|-----------|



|                                         |           |
|-----------------------------------------|-----------|
| <b>Wire And Cable Marking . . . . .</b> | <b>16</b> |
|-----------------------------------------|-----------|



|                                               |           |
|-----------------------------------------------|-----------|
| <b>Electrical Component Marking . . . . .</b> | <b>22</b> |
|-----------------------------------------------|-----------|



|                                 |           |
|---------------------------------|-----------|
| <b>Datacom Labels . . . . .</b> | <b>23</b> |
|---------------------------------|-----------|



|                                                                    |           |
|--------------------------------------------------------------------|-----------|
| <b>Circuit Board and Component Identification Labels . . . . .</b> | <b>27</b> |
|--------------------------------------------------------------------|-----------|



|                                                 |           |
|-------------------------------------------------|-----------|
| <b>Security Identification Labels . . . . .</b> | <b>29</b> |
|-------------------------------------------------|-----------|



|                                                   |           |
|---------------------------------------------------|-----------|
| <b>Laboratory Identification Labels . . . . .</b> | <b>29</b> |
|---------------------------------------------------|-----------|



Brady products are sold on the condition that the purchaser will test them in actual use and determine for himself/herself their suitability to his/her intended purpose. Brady warrants to the purchaser that Brady products are free from defects in material and workmanship but limits its obligation under this warranty to the replacement of the product which has been shown to Brady's satisfaction to have been defective at the time of its purchase.

The warranty does not extend to any persons who have acquired the product from the purchaser. It is in lieu of any other warranty, including every warranty of sale-ability, marketability or suitability for the intended purpose, and is also in lieu of any other obligation or liability on the part of Brady.

Under no circumstances will Brady be liable for losses, damage, costs or subsequent damage of whatever nature which may arise in connection with the use of, or inability to use, Brady's products.

## BMP™71 LABEL PRINTER



The BMP71 mobile label printer can print on more than 30 different types of label material – all designed with Brady's industrial-strength durability. Whether you need heat shrink sleeves, die-cut labels or indoor/outdoor vinyl, you can be confident that the BMP71 printer has the right label material for your application.

### Speed up your labelling

The powerful BMP71 prints faster than any other printer in its class (38 mm/sec). Don't wait longer than necessary for your labels.

### The full keyboard lets you type labels in less time

The BMP71 has a full keyboard, available in 4 different versions: QWERTY, AZERTY, QWERTZ and CYRILLIC. Use both your hands to type your label instead of one finger and save time!

### The enlarged full colour screen makes your label printing so much easier

The enlarged screen of the BMP71 enables to see the whole label at once, helping you to compose the label in the most efficient way, eliminating trial and error!

### One smart printer to print it all

The BMP71 is your essential tool that handles all your label printing needs.



| Order Reference   | Description                                                                                                                                                                                                                                                                    |
|-------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| BMP71-QWERTY-UK   | Printer, Hard Carry Case, 2 Label Rolls, 1 Black Ribbon Cartridge, Rechargeable Battery Pack, AC Adaptor, USB Communications Cable, TLS2200® / HandiMark™ Material Roll Adaptor, Quick Start Guide, Product CD (w/ Printer Driver, Tutorials, Full User's Guide), Cleaning Kit |
| BMP71-QWERTY-EU   | As above but with European Power Supply                                                                                                                                                                                                                                        |
| BMP71-AZERTY-EU   | As above but with AZERTY Keyboard and European Power Supply                                                                                                                                                                                                                    |
| BMP71-QWERTZ-EU   | As above but with QWERTZ Keyboard and European Power Supply                                                                                                                                                                                                                    |
| BMP71-CYRILLIC-EU | As above but with CYRILLIC Keyboard and European Power Supply                                                                                                                                                                                                                  |
| M71-AC-EU         | BMP71 European AC                                                                                                                                                                                                                                                              |
| M71-AC-UK         | BMP71 UK AC                                                                                                                                                                                                                                                                    |
| M71-QC-EU         | BMP71 European Quick Charger                                                                                                                                                                                                                                                   |
| M71-QC-UK         | BMP 71 UK Quick Charger                                                                                                                                                                                                                                                        |
| M71-HC            | BMP71 Hard Carry Case                                                                                                                                                                                                                                                          |
| M71-SC            | BMP 71 Soft Carry Case                                                                                                                                                                                                                                                         |
| M71-AC-BC         | BMP71 AC/BATTERY CHARGER                                                                                                                                                                                                                                                       |
| M71-BATT          | BMP71 SPARE BATTERY                                                                                                                                                                                                                                                            |
| M71-CLEAN         | BMP71 CLEANING KIT                                                                                                                                                                                                                                                             |
| M71-ADAPT         | BMP71 ROLL ADAPTER FOR TLS/HM                                                                                                                                                                                                                                                  |

# Features – Printing Options

## Printer

- Large full colour graphic LCD screen
- Display communicates important status information:
  - Installed label part
  - Label size and colour
  - Amount of material remaining
  - Remaining battery charge
  - Label and area status
  - Current font size and rotation
- Thermal transfer printing mechanism - 300 dpi
- High print speed of 38 mm/sec
- Weight : 2.5kg (w/battery)
- Handle to easily carry the printer anywhere you need it
- Built in industrial label cutter
- Print width 46 mm - Print length up to 1016 mm
- Stand alone or PC connectivity via USB
- Durable hard carry case
- Operating temperature range: 4° to 49°C

## Labels

- The pre-defined application templates and wizards save time and make it easy to print the exact label you need
- Adjustable to six different widths of labels
- Can print up to 25 lines per label
- Batch label printing or print multiple copies of one label
- Ability to serialise data
- Prints mirror image
- Built-in Smart Cell Technology in labels and ribbons

## Memory



- Ability to store, retrieve and delete label files
- Save over 100,000 labels!
- Built in time/date stamp

## Battery

- Prints 4000 labels per battery charge (25, 40 to 50 mm labels)
- Rechargeable Battery and AC power/battery charger
- Sleep mode conserves battery power when printer is not in use
- UL and CUL listed battery charger

## Symbols & Barcodes

- Standard electrical and datacom symbols included
- Barcode symbologies: Code 39 and Code 128
- Over 500 built in graphics



## Text

- Auto font sizing
- Custom True Type Font
- Text size 4 pt to 174pt (scaleable)



**Prints all TLS2000® and Handimark™ label parts including bulk rolls. Users interested in upgrading to BMP™71 Printer, do not need to invest in a new set of consumables.**

## Easy way to create labels on your PC with LabelMark™ Labelling Software

Brady's LabelMark™ software lets you easily create labels for Asset ID, Component Marking, Telecom/Datacom Labelling, Wire Markers and more. It allows users to design, edit and print their Brady labels. Integrates completely with Microsoft® Office, AutoCAD® applications and more.

**LabelMark™**  
LABELING SOFTWARE



## Easy to Use Graphical Interface Label Design

- Option for line-edit or free-form mode for label design
- Several common barcode symbologies available
- Ability to import graphical images
- Data import support including spreadsheets, ASCII, ODBC and OLE DB

## Label Editing

- Easy to use single screen editing
- Multiple document interface for working with different labels at the same time
- Ability to flip/flop data on label (i.e. flip/flop "to"/"from" order)

## Label Printing

- Compatible with all Brady media, stock and custom formats
- Works with a variety of different printers to suit various applications



## Enhance your labels with advanced graphics and symbols with MarkWare™ software

With Brady's MarkWare™ software you can combine text with graphics, symbols and barcodes. Labels can be used as visual tools throughout your facility. For lean enterprises, Brady's MarkWare™ software provides additional graphics and templates for Signs, Labels, Pipe Markers and Tags - perfect for 5S, TPM and lean visuals.



## Quick & Easy Label Design

- Includes label template designs. The size of the template adjusts automatically to the size of the installed material, regardless of width
- Over 600 standardised symbols available
- Ability to import drawings, signs and diagrams
- Supports European CLP Hazardous Substances Identification labels containing GHS and ADR graphics
- Creation of pipe markers guaranteeing compliance based on your choice of national standard
- 5 Barcode protocols and 19 languages

## Label Editing


- Advanced functions allow quick label creation ("align objects", "group objects", foreground/background, zoom, rotation...)
- Employs all the basic functions of Windows® applications (copy/paste within the application print preview, etc ...).

## Label Printing

- Windows®-compatible print driver included
- Windows® print driver adds the Brady printer to your printer list. This authorises printing directly from other software such as drawing and other widely used creative programs

# Applications

## Patch Panel ID



## Electrical Panel ID



## Face Plate ID




## Wire & Cable Self-Laminating Labels




## Wire & Cable Sleeves



## Terminal Block Markers



## Wire & Cable Wrap Around Labels



## Tag Printing



## Desi-Strip Inserts



## Flag Labels



## Logistics Labelling



## Safety Identification



## Pipe Marking



## Asset ID



## Laboratory ID



## Information Signs




## Circuit Board & Component Labelling



## Industrial Barcode Labelling



## Security ID



# Materials and Ribbons Cross Reference Chart

| Material Number     | Material Description                                                 | Colour                                   | Finish | Min./Max. Service Temperature | Application                                                                                | Special Properties                                                                                              | Agency Approvals/ Compliance                                                                                                                                                                                                                                | Recommended Ribbons                               |
|---------------------|----------------------------------------------------------------------|------------------------------------------|--------|-------------------------------|--------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------|
| <b>Nylon Cloth</b>  |                                                                      |                                          |        |                               |                                                                                            |                                                                                                                 |                                                                                                                                                                                                                                                             |                                                   |
| B-499               | Nylon Cloth with permanent acrylic pressure sensitive adhesive       | White                                    | Matt   | -70° to 90°C<br>30 days       | Low profile through-conduit wire marking, component and general labelling                  | High adhesion makes all-purpose wire marker ideal for environments where heat, oil and dirt are present         |   <b>HF</b>                                                                           | M71-R4300                                         |
| <b>Paper</b>        |                                                                      |                                          |        |                               |                                                                                            |                                                                                                                 |                                                                                                                                                                                                                                                             |                                                   |
| B-424               | General Purpose Paper with permanent latex adhesive                  | White                                    | Matt   | -40° to 50°C<br>30 days       | Barcode and general labelling                                                              | Good contrast and smear resistance                                                                              |                                                                                                                                                                                                                                                             | M71-R4300                                         |
| <b>Polyester</b>    |                                                                      |                                          |        |                               |                                                                                            |                                                                                                                 |                                                                                                                                                                                                                                                             |                                                   |
| B-422               | Polyester with permanent acrylic adhesive                            | White                                    | Gloss  | -40° C to 100°C<br>30 days    | Electronic PCB ID and component, barcode label and rating plate, outlet and patch panel ID | 2 mil adhesive recommended for application on textured surfaces                                                 |                                                                                       | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-423               | Polyester with permanent acrylic adhesive                            | White                                    | Gloss  | -40°C to 120°C<br>30 days     | Electronic PCB ID and component, barcode label, rating plates and outlets                  |                                                                                                                 |   <b>HF</b>                                                                           | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-428               | Metallised polyester with permanent acrylic adhesive                 | Silver                                   | Matt   | -40°C to 120°C<br>30 days     | Rating plates, electronic component marking                                                |                                                                                                                 |   <b>HF</b>                                                                           | M71-R4300                                         |
| B-430               | Clear polyester with permanent acrylic adhesive                      | Clear                                    | Gloss  | -70°C to 100°C<br>30 days     | General labelling rating/name plates, outlet and general communications                    | High adhesion make it ideal for highly textured and other surfaces that are difficult to adhere to; Translucent |                                                                                       | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-459               | Polyester with permanent acrylic adhesive                            | White                                    | Matt   | -40°C to 110°C<br>30 days     | Electronic PCB ID and component, barcode labelling and rating plates                       |                                                                                                                 |                                                                                       | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-461               | Self-laminating polyester with permanent acrylic adhesive            | White/<br>Translucent                    | Matt   | -196°C to 130°C<br>30 days    | Laboratory ID                                                                              | Excellent abrasion and smudge resistance                                                                        | <b>HF</b>                                                                                                                                                                                                                                                   | M71-R4300<br>M71-R6200                            |
| B-473               | Polyester with static dissipative permanent acrylic adhesive         | White                                    | Gloss  | -40°C to 120°C<br>30 days     | Electronic PCB ID and component, barcode labelling and rating plates                       | Static dissipative adhesive and liner                                                                           |    | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-483               | Polyester with permanent rubber adhesive                             | White                                    | Gloss  | -40°C to 120°C<br>30 days     | General labelling; barcode label and rating plates                                         | Ultra-aggressive adhesive for thermal transfer printing, designed for powder coated surfaces                    |                                                                                       | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-486               | Polyester with permanent rubber adhesive                             | Silver                                   | Matt   | -40°C to 120°C<br>30 days     | General labelling; barcode label and rating plates                                         | Metallised polyester with ultra-aggressive adhesive for oily, greasy and powder-coated surfaces                 |                                                                                       | M71-R4300                                         |
| B-488               | Polyester with permanent acrylic adhesive                            | White                                    | Matt   | -40°C to 160°C<br>30 days     | Electronic PCB and component; barcode label and rating plates                              | High performance matt white                                                                                     |                                                                                   | M71-R4300<br>M71-R6200                            |
| B-489               | Polyester with permanent rubber adhesive                             | White                                    | Matt   | -40°C to 120°C<br>30 days     | General labelling, barcode labelling and rating plates                                     | Ultra-aggressive adhesive for oily, greasy and powder coated surfaces; UL/CSA approval pending                  |                                                                                                                                                                                                                                                             | M71-R6200                                         |
| B-582               | BradyGlo™ Polyester with acrylic adhesive                            | Phosphorescent                           | Gloss  | -40°C to 80°C                 | Photoluminescent safety identification                                                     |                                                                                                                 |                                                                                                                                                                                                                                                             | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-7593              | EPREP: polyester tag on foam carrier with permanent acrylic adhesive | White, Yellow, Red, Green, Silver, Black | Gloss  | -40°C to 100°C<br>30 days     | Electrical components, switches, push buttons, rack and patch panels                       | 650 µm thick material with foam tape to replace engraved name plates; colour match available on demand          |                                                                                                                                                                                                                                                             | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| <b>Polyethylene</b> |                                                                      |                                          |        |                               |                                                                                            |                                                                                                                 |                                                                                                                                                                                                                                                             |                                                   |
| B-109               | Polyethylene tag                                                     | White                                    | Matt   | -40°C to 80°C<br>30 days      | Multi-purpose identification tag, where durability is required                             | Cross-laminated polyethylene provides extreme tear resistance and excellent cold-weather performance            |                                                                                                                                                                                                                                                             | M71-R4300                                         |
| B-145               | Polyethylene tag                                                     | Grey                                     | Matt   | -40°C to 100°C<br>30 days     | Power and ground labels                                                                    | Tear-resistant 2-sided printable tag                                                                            |                                                                                                                                                                                                                                                             | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-145FR             | Flame retardant rigid polyethylene tag                               | Grey                                     | Matt   | -40°C to 100°C<br>30 days     | Power and ground labels                                                                    | Tear-resistant 2-sided printable tag                                                                            |                                                                                                                                                                        | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-7599              | Polyethylene tag                                                     | White                                    | Matt   | -40°C to 50°C<br>30 days      | Multi-purpose identification tag                                                           | 250 µm polyethylene tag                                                                                         | <b>HF</b>                                                                                                                                                                                                                                                   | M71-R6200                                         |
| <b>Polymide</b>     |                                                                      |                                          |        |                               |                                                                                            |                                                                                                                 |                                                                                                                                                                                                                                                             |                                                   |
| B-426               | Polymide with permanent acrylic adhesive                             | Amber                                    | Matt   | -70°C to 330°C<br>80 sec.     | Underside PCB and other high temperature, high performance applications                    | Withstands extremely high temperatures                                                                          |                                                                                                                                                                                                                                                             | M71-R4300                                         |
| B-477               | Polymide with static dissipative permanent acrylic adhesive          | White                                    | Gloss  | -70°C to 300°C<br>80 sec.     | Top- or bottom-side board application for SMT or Through hole                              | Static dissipative adhesive and liner                                                                           |                                                                                   | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-478               | Polymide with static dissipative permanent acrylic adhesive          | White                                    | Gloss  | -70°C to 300°C<br>80 sec.     | 1 mil low profile top- or bottom-side board application for SMT or Through hole            | Static dissipative adhesive and liner                                                                           |   <b>HF</b>                                                                       | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |



These materials have static dissipative adhesives



These materials are UL recognised



These materials are CSA approved.



Halogen-Free (DIN VDE 0472/parts 815)

\*R-6900 ribbon comes in red, green, magenta, yellow and blue

# Materials and Ribbons Cross Reference Chart

| Material Number                                   | Material Description                                   | Colour                                                                                                                   | Finish     | Min./Max. Service Temperature | Application                                                             | Special Properties                                                                                                                                             | Agency Approvals/ Compliance  | Recommended Ribbons                               |
|---------------------------------------------------|--------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|------------|-------------------------------|-------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------|---------------------------------------------------|
| <b>Polyolefin</b>                                 |                                                        |                                                                                                                          |            |                               |                                                                         |                                                                                                                                                                |                               |                                                   |
| B-341                                             | PermaSleeve™ heat shrink polyolefin sleeves            | White, Yellow                                                                                                            | Matt       | -40°C to 130°C<br>1000 hours  | Wire marking                                                            | 2-to-1 shrink ratio, self-extinguishing, meets the material and physical property of AMS-DTL-23053/5 Class 1, SAE AS-81531, MIL-STD-202, Method 215 and UL 224 |                               | M71-R4300                                         |
| B-342                                             | PermaSleeve™ heat shrink polyolefin sleeves            | White, Yellow                                                                                                            | Matt       | -55°C to 130°C<br>1000 hours  | Wire marking                                                            | 3-to-1 shrink ratio, self-extinguishing, meets the material and physical property of AMS-DTL-23053/5 Class 1, SAE AS-81531, MIL-STD-202, Method 215 and UL 224 |                               | M71-R4300                                         |
| <b>Polypropylene</b>                              |                                                        |                                                                                                                          |            |                               |                                                                         |                                                                                                                                                                |                               |                                                   |
| B-412                                             | Polypropylene tag                                      | White                                                                                                                    | Matt       | -40°C to 100°C<br>30 days     | Wire, cable and product inventory information                           | Designed where tensile strength is needed                                                                                                                      | <b>HF</b>                     | M71-R6200                                         |
| B-425                                             | Polypropylene with acrylic adhesive                    | White                                                                                                                    | Matt       | -40°C to 100°C<br>30 days     | Cable and wire markers, P- and T-labels                                 | Excellent abrasion and smudge resistance                                                                                                                       | <b>UL</b> <b>SP</b> <b>HF</b> | M71-R4300                                         |
| B-529                                             | Economy polypropylene with acrylic adhesive            | Whit                                                                                                                     | Gloss      | -40°C to 100°C                | Low-cost choice for indoor use                                          |                                                                                                                                                                |                               | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| <b>Tedlar®</b>                                    |                                                        |                                                                                                                          |            |                               |                                                                         |                                                                                                                                                                |                               |                                                   |
| B-437                                             | Tedlar® with permanent acrylic adhesive                | White, Yellow                                                                                                            | Matt       | -70°C to 135°C<br>30 days     | Aerospace and military cable marking                                    | Self-extinguishing                                                                                                                                             |                               | M71-R4300                                         |
| B-642                                             | Tedlar® with permanent acrylic adhesive                | White                                                                                                                    | Matt       | -70°C to 120°C<br>30 days     | Self-laminating, wire and cable marking                                 | Self-extinguishing, low smoke and flame spread, excellent abrasion and smudge resistance                                                                       |                               | M71-R4300                                         |
| <b>Thermoplastic Polyether-polyurethane (PUR)</b> |                                                        |                                                                                                                          |            |                               |                                                                         |                                                                                                                                                                |                               |                                                   |
| B-7643                                            | Thermoplastic polyether polyurethane tag               | White, Yellow                                                                                                            | Matt       | -40°C to 90°C<br>30 days      | Wire & cable marking                                                    | Zero halogen, more colours available                                                                                                                           |                               | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| <b>Vinyl</b>                                      |                                                        |                                                                                                                          |            |                               |                                                                         |                                                                                                                                                                |                               |                                                   |
| B-352                                             | Vinyl with permanent acrylic adhesive                  | Silver                                                                                                                   | Matt       | -40°C to 80°C<br>30 days      | Tamper-resistant labels for security ID; asset ID                       | Metallised vinyl, designed to fracture easily                                                                                                                  |                               | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-427                                             | Self-laminating vinyl with permanent acrylic adhesive  | White                                                                                                                    | Matt       | -70°C to 70°C<br>30 days      | Self-laminating wire and cable marking                                  | Excellent abrasion and smudge resistance                                                                                                                       | <b>UL</b>                     | M71-R4300                                         |
| B-530                                             | Tamper evident vinyl with acrylic adhesive             | White                                                                                                                    | Gloss      | -40°C to 90°C                 | Tamper-resistant labels for security ID; asset ID                       | Designed to fracture easily                                                                                                                                    |                               | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-580                                             | High Performance vinyl with permanent acrylic adhesive | Red, Yellow, Blue, Green, White, Orange, Grey, Black, Brown, Purple, Clear, Gold, Ochre, Sky Blue, Light Blue, Pink, Tan | Gloss      | -40°C to 82°C                 | Safety identification, pipe marking                                     | 5-year average outdoor durability                                                                                                                              |                               | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-584                                             | Reflective vinyl with acrylic adhesive                 | White, Yellow, Orange                                                                                                    | Gloss      | -40°C to 82°C                 | Reflective quality makes material ideal for use in low-light conditions | 5-year average outdoor durability                                                                                                                              |                               | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-581                                             | Repositionable vinyl with acrylic adhesive             | White, Yellow                                                                                                            | Gloss      | -40°C to 82°C                 | Indoor labels where frequent repositioning is required                  |                                                                                                                                                                |                               | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| B-7696                                            | Rigid vinyl tag, Rigid Durasleeve                      | White                                                                                                                    | Gloss      | -40° C to 70°C<br>30 days     | Sleeves, inserts, tags, terminal block markers                          | Rigid construction                                                                                                                                             |                               | M71-R6000<br>M71-R4400-WT<br>M71-R6900 (colours*) |
| <b>Vinyl Cloth</b>                                |                                                        |                                                                                                                          |            |                               |                                                                         |                                                                                                                                                                |                               |                                                   |
| B-498                                             | Vinyl cloth with repositionable rubber based adhesive  | White                                                                                                                    | Semi-gloss | -40°C to 82°C<br>30 days      | Wire and electronic component marking                                   | Repositionable adhesive                                                                                                                                        | <b>UL</b>                     | M71-R6200                                         |

 These materials have static dissipative adhesives

 These materials are UL recognised

 These materials are CSA approved.

**HF** Halogen-Free (DIN VDE 0472/parts 815)

Tedlar® is a registered trademark of DuPont

\*R-6900 ribbon comes in red, green, magenta, yellow and blue



Brady has hundreds of RoHS compliant materials for you to choose from and we are committed to provide you with the latest information. Simply go to [www.weee.rohs.bradyeurope.com](http://www.weee.rohs.bradyeurope.com) for the latest up-date.



For more information on our materials or to help you choose, visit [www.bradyeurope.com](http://www.bradyeurope.com)

# Ribbons

## Ribbons

| Order Reference | Colour  | Ribbon Width (mm) | Ribbon Length (m) | Special property                                                                                                                     |
|-----------------|---------|-------------------|-------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| M71-R4300       | Black   | 50.80             | 46                | Strong environmental resistance against smearing and chemicals. Reliable, sharp-edge print quality to maximize bar code readability. |
| M71-R4400-WT    | White   | 50.80             | 46                | High density ribbon with excellent solvent resistance, high heat resistance, and super scratch resistance.                           |
| M71-R6000       | Black   | 50.80             | 46                | High density ribbon with excellent solvent resistance, high heat resistance, and super scratch resistance.                           |
| M71-R6200       | Black   | 50.80             | 46                | Designed for harsh environment labeling applications. Superior abrasion, chemical and heat resistance.                               |
| M71-R6400       | Black   | 50.80             | 46                | High density ribbon with excellent solvent resistance, high heat resistance, and super scratch resistance.                           |
| M71-R6800-WT    | White   | 50.80             | 46                | Strong environmental resistance against smearing and chemicals. Reliable, sharp-edge print quality to maximize bar code readability. |
| M71-R6900-BL    | Blue    | 50.80             | 46                | High density ribbon with excellent solvent resistance, high heat resistance, and super scratch resistance.                           |
| M71-R6900-GN    | Green   | 50.80             | 46                | High density ribbon with excellent solvent resistance, high heat resistance, and super scratch resistance.                           |
| M71-R6900-MA    | Magenta | 50.80             | 46                | High density ribbon with excellent solvent resistance, high heat resistance, and super scratch resistance.                           |
| M71-R6900-RD    | Red     | 50.80             | 46                | High density ribbon with excellent solvent resistance, high heat resistance, and super scratch resistance.                           |
| M71-R6900-YL    | Yellow  | 50.80             | 46                | High density ribbon with excellent solvent resistance, high heat resistance, and super scratch resistance.                           |



## Bulk Packaging

Bulk labels are designed for the BMP™71 Label Printer as a cost-effective solution for high volume labelling needs. Order references beginning with “B” indicate bulk rolls.





# High Performance Industrial Identification / Safety Identification

## B-580 Indoor/Outdoor Vinyl:

- Brady's indoor/outdoor grade vinyl tape adheres well to pipes, walls, equipment, windows – most clean, dry surfaces.
- Conforms well to irregular, curved or rough surfaces – it even stands up to grease, oil and most industrial chemicals.
- Five year average outdoor durability in temperatures from 82°C to -40°C, can be applied as low as -18°C.

| Diagram | Order Reference  | Width A (mm) | Length B (m) | Colour     |
|---------|------------------|--------------|--------------|------------|
| ●       | M71C-500-580-WT  | 12.70        | 15.24        | White      |
| ●       | M71C-500-580-YL  | 12.70        | 15.24        | Yellow     |
| ●       | M71C-500-580-GN  | 12.70        | 15.24        | Green      |
| ●       | M71C-500-580-RD  | 12.70        | 15.24        | Red        |
| ●       | M71C-500-580-BL  | 12.70        | 15.24        | Blue       |
| ●       | M71C-500-580-LB  | 12.70        | 15.24        | Light Blue |
| ●       | M71C-500-580-SB  | 12.70        | 15.24        | Sky Blue   |
| ●       | M71C-500-580-OR  | 12.70        | 15.24        | Orange     |
| ●       | M71C-500-580-BK  | 12.70        | 15.24        | Black      |
| ●       | M71C-500-580-GY  | 12.70        | 15.24        | Grey       |
| ●       | M71C-500-580-BR  | 12.70        | 15.24        | Brown      |
| ●       | M71C-500-580-GD  | 12.70        | 15.24        | Gold       |
| ●       | M71C-500-580-OC  | 12.70        | 15.24        | Ochre      |
| ●       | M71C-500-580-PL  | 12.70        | 15.24        | Purple     |
| ●       | M71C-500-580-PK  | 12.70        | 15.24        | Pink       |
| ●       | M71C-500-580-TN  | 12.70        | 15.24        | Tan        |
| ●       | M71C-500-580-CL  | 12.70        | 15.24        | Clear      |
| ●       | M71C-1000-580-WT | 25.40        | 15.24        | White      |
| ●       | M71C-1000-580-YL | 25.40        | 15.24        | Yellow     |
| ●       | M71C-1000-580-GN | 25.40        | 15.24        | Green      |
| ●       | M71C-1000-580-RD | 25.40        | 15.24        | Red        |
| ●       | M71C-1000-580-BL | 25.40        | 15.24        | Blue       |
| ●       | M71C-1000-580-LB | 25.40        | 15.24        | Light Blue |
| ●       | M71C-1000-580-SB | 25.40        | 15.24        | Sky Blue   |
| ●       | M71C-1000-580-OR | 25.40        | 15.24        | Orange     |
| ●       | M71C-1000-580-BK | 25.40        | 15.24        | Black      |
| ●       | M71C-1000-580-GY | 25.40        | 15.24        | Grey       |
| ●       | M71C-1000-580-BR | 25.40        | 15.24        | Brown      |
| ●       | M71C-1000-580-GD | 25.40        | 15.24        | Gold       |
| ●       | M71C-1000-580-OC | 25.40        | 15.24        | Ochre      |
| ●       | M71C-1000-580-PL | 25.40        | 15.24        | Purple     |
| ●       | M71C-1000-580-PK | 25.40        | 15.24        | Pink       |
| ●       | M71C-1000-580-TN | 25.40        | 15.24        | Tan        |
| ●       | M71C-1000-580-CL | 25.40        | 15.24        | Clear      |
| ●       | M71C-2000-580-WT | 50.80        | 15.24        | White      |
| ●       | M71C-2000-580-YL | 50.80        | 15.24        | Yellow     |
| ●       | M71C-2000-580-GN | 50.80        | 15.24        | Green      |
| ●       | M71C-2000-580-RD | 50.80        | 15.24        | Red        |
| ●       | M71C-2000-580-BL | 50.80        | 15.24        | Blue       |
| ●       | M71C-2000-580-LB | 50.80        | 15.24        | Light Blue |
| ●       | M71C-2000-580-SB | 50.80        | 15.24        | Sky Blue   |
| ●       | M71C-2000-580-OR | 50.80        | 15.24        | Orange     |
| ●       | M71C-2000-580-BK | 50.80        | 15.24        | Black      |
| ●       | M71C-2000-580-GY | 50.80        | 15.24        | Grey       |
| ●       | M71C-2000-580-BR | 50.80        | 15.24        | Brown      |
| ●       | M71C-2000-580-GD | 50.80        | 15.24        | Gold       |
| ●       | M71C-2000-580-OC | 50.80        | 15.24        | Ochre      |
| ●       | M71C-2000-580-PL | 50.80        | 15.24        | Purple     |
| ●       | M71C-2000-580-PK | 50.80        | 15.24        | Pink       |
| ●       | M71C-2000-580-TN | 50.80        | 15.24        | Tan        |
| ●       | M71C-2000-580-CL | 50.80        | 15.24        | Clear      |






Order references with "C" (e.g. M71C) indicate continuous.

# General and Industrial Identification Labels


## Repositionable Labels

### • B-581 Repositionable Vinyl:

- Special adhesive allows easy removal of label to re-apply again and again.
- Best choice for indoor marking where frequent repositioning is required, such as shelves.

| Diagram                                                                               | Order Reference  | Width A (mm) | Length B (m) | Colour |
|---------------------------------------------------------------------------------------|------------------|--------------|--------------|--------|
|    | M71C-500-581-YI  | 12.70        | 15.24        | Yellow |
|    | M71C-500-581-WT  | 12.70        | 15.24        | White  |
|    | M71C-1000-581-YL | 25.40        | 15.24        | Yellow |
|   | M71C-1000-581-WT | 25.40        | 15.24        | White  |
|  | M71C-2000-581-YL | 50.80        | 15.24        | Yellow |
|  | M71C-2000-581-WT | 50.80        | 15.24        | White  |




Order references with "C" (e.g. M71C) indicate continuous.




## Reflective Labels

### • B-584 Reflective Vinyl:

- Ideal for reading labels in low light conditions.

| Diagram                                                                               | Order Reference  | Width A (mm) | Length B (m) | Colour |
|---------------------------------------------------------------------------------------|------------------|--------------|--------------|--------|
|  | M71C-500-584-YI  | 12.70        | 15.24        | Yellow |
|  | M71C-500-584-WT  | 12.70        | 15.24        | White  |
|  | M71C-1000-584-YL | 25.40        | 15.24        | Yellow |
|  | M71C-1000-584-WT | 25.40        | 15.24        | White  |
|  | M71C-2000-584-YL | 50.80        | 15.24        | Yellow |
|  | M71C-2000-584-WT | 50.80        | 15.24        | White  |

Order references with "C" (e.g. M71C) indicate continuous.



For more information on our materials or to help you choose, visit [www.bradyeurope.com](http://www.bradyeurope.com)

# General and Industrial Identification Labels

## Material to Surface Cross Reference Guide


| Brady material number (B-number) |         |        |         | Smooth<br>(Examples: Uncoated Metal,<br>Plastic, Glass) | Textured/Rough<br>(Examples: Textured ABS,<br>Cast Metal, Polycarbonate) | Highly Textured / Low Surface Energy<br>(Examples: Powder Coated,<br>Low Surface Energy ABS, Polypropylene) |
|----------------------------------|---------|--------|---------|---------------------------------------------------------|--------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|
| B-7351                           | B-352** | B-422* | B-432*  | ✓ YES                                                   | ✓ YES                                                                    | NO                                                                                                          |
| B-435*                           | B-427** | B-580  |         |                                                         |                                                                          |                                                                                                             |
| B-483*                           | B-486*  | B-489* | B-499*  | ✓ YES                                                   | ✓ YES                                                                    | ✓ YES                                                                                                       |
| B-423*                           | B-424   | B-428* | B-430*  |                                                         |                                                                          |                                                                                                             |
| B-459*                           | B-473*  | B-488* | B-7546* | ✓ YES                                                   | NO                                                                       | NO                                                                                                          |
| B-7566                           | B-7576* |        |         |                                                         |                                                                          |                                                                                                             |

\*Material UL recognised / CSA approved

\*\*Material UL recognised

## Rating, Name Plate Labels

- B-422, B-423 Permanent Glossy Polyester
- B-424 General Purpose White Paper
- B-428 Permanent Metallised Polyester
- B-430 Permanent Clear Polyester
- B-483 Ultra-Aggressive Glossy Polyester
- B-486 Ultra-Aggressive Metallised Polyester
- B-489 Ultra-Aggressive Matt Polyester
- B-488 Matt Polyester
- B-499 Nylon Cloth



| Diagram | Order Reference | Labels Per Roll | Width A (mm) | Height B (mm) | Applications/Descriptions                       | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points | Surface Suitability |
|---------|-----------------|-----------------|--------------|---------------|-------------------------------------------------|---------------------------------------|---------------------------------|---------------------|
| ▲       | M71-16-483      | 500             | 25.40        | 9.53          | Asset ID for textured surfaces                  | 24                                    | 3                               | ✓                   |
| ▲       | BM71-17-428     | 5000            | 25.40        | 12.70         | General Purpose over-laminated ID               | 24                                    | 5                               | ✓                   |
| ▲       | M71-17-428      | 500             | 25.40        | 12.70         | General Purpose over-laminated ID               | 24                                    | 5                               | ✓                   |
| ▲       | M71-17-483      | 500             | 25.40        | 12.70         | Asset ID for textured surfaces                  | 24                                    | 5                               | ✓                   |
| ▲       | M71-17-486      | 500             | 25.40        | 12.70         | Asset ID for oily, greasy and textured surfaces | 24                                    | 5                               | ✓                   |
| ▲       | M71-17-489      | 500             | 25.40        | 12.70         | Asset ID for oily, greasy and textured surfaces | 24                                    | 5                               | ✓                   |
| ▲       | M71-19-423      | 250             | 25.40        | 25.40         | Rating plate                                    | 24                                    | 10                              | ✓                   |
| ▲       | BM71-19-423     | 2500            | 25.40        | 25.40         | Rating plate                                    | 24                                    | 10                              | ✓                   |
| ▲       | M71-19-483      | 250             | 25.40        | 25.40         | Asset ID for textured surfaces                  | 24                                    | 10                              | ✓                   |
| ▲       | M71-20-424      | 100             | 50.80        | 25.40         | General ID and Asset ID                         | 46                                    | 10                              | ✓                   |
| ▲       | BM71-20-424     | 1000            | 50.80        | 25.40         | General ID and Asset ID                         | 46                                    | 10                              | ✓                   |
| ▲       | M71-20-428      | 100             | 50.80        | 25.40         | Asset ID, silver finish                         | 46                                    | 10                              | ✓                   |
| ▲       | BM71-20-428     | 1000            | 50.80        | 25.40         | Asset ID, silver finish                         | 46                                    | 10                              | ✓                   |
| ▲       | M71-20-483      | 100             | 50.80        | 25.40         | Asset ID for textured surfaces                  | 46                                    | 10                              | ✓                   |
| ▲       | M71-20-486      | 100             | 50.80        | 25.40         | Asset ID for oily, greasy and textured surfaces | 46                                    | 10                              | ✓                   |
| ▲       | M71-22-423      | 100             | 76.20        | 25.40         | General ID                                      | 50                                    | 10                              | ✓                   |
| ▲       | M71-22-428      | 100             | 76.20        | 25.40         | Rating plate                                    | 50                                    | 10                              | ✓                   |
| ▲       | M71-23-423      | 100             | 101.60       | 25.40         | General ID                                      | 50                                    | 9                               | ✓                   |
| ▲       | M71-23-483      | 100             | 101.60       | 25.40         | Asset ID for textured surfaces                  | 50                                    | 9                               | ✓                   |
| ▶       | M71-24-423-BK   | 500             | 28.70        | 12.70         | 1.60 mm Black-bordered component ID             | 24                                    | 3                               | ✓                   |
| ▲       | M71-26-423      | 100             | 69.85        | 31.75         | General ID and Asset ID                         | 50                                    | 13                              | ✓                   |
| ▲       | M71-26-428      | 100             | 69.85        | 31.75         | General ID and Asset ID                         | 50                                    | 13                              | ✓                   |
| ▲       | M71-29-428      | 500             | 38.10        | 12.70         | Face plates, panels, equipment, silver finish   | 37                                    | 5                               | ✓                   |

\*Any label 50.80 mm or larger is rotated on liner

Order references beginning with "B" indicate bulk rolls.

Continued on next page >>

✓ Material suitable for smooth surfaces.


✓ Material suitable for smooth and textured surfaces.

✓ Material suitable for smooth, textured and highly textured surfaces.

# General and Industrial Identification Labels

## Rating, Name Plate Labels (continued)

- B-422, B-423 Permanent Glossy Polyester
- B-428 Permanent Metallised Polyester
- B-430 Permanent Clear Polyester
- B-483 Ultra-Aggressive Glossy Polyester
- B-486 Ultra-Aggressive Metallised Polyester
- B-489 Ultra-Aggressive Matt Polyester
- B-488 Matt Polyester
- B-499 Nylon Cloth



| Diagram | Order Reference | Labels Per Roll | Width A (mm) | Height B (mm) | Applications/Descriptions                       | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points | Surface Suitability |
|---------|-----------------|-----------------|--------------|---------------|-------------------------------------------------|---------------------------------------|---------------------------------|---------------------|
| ▲       | M71-29-483      | 500             | 38.10        | 12.70         | Asset ID for textured surfaces                  | 37                                    | 5                               | ✓                   |
| ▲       | M71-29-486      | 500             | 38.10        | 12.70         | Asset ID for oily, greasy and textured surfaces | 37                                    | 5                               | ✓                   |
| ▲       | M71-29-489      | 500             | 38.10        | 12.70         | Asset ID for oily, greasy and textured surfaces | 37                                    | 5                               | ✓                   |
| ▲       | M71-30-422      | 250             | 38.10        | 19.05         | Asset ID for textured surfaces                  | 37                                    | 8                               | ✓                   |
| ▲       | M71-30-483      | 250             | 38.10        | 19.05         | Asset ID for oily, greasy and textured surfaces | 37                                    | 8                               | ✓                   |
| ▲       | M71-30-486      | 250             | 38.10        | 19.05         | Asset ID for oily, greasy and textured surfaces | 37                                    | 8                               | ✓                   |
| ▲       | M71-30-499      | 250             | 19.05        | 38.10         | Asset ID for oily, greasy and textured surfaces | 18                                    | 16                              | ✓                   |
| ▲       | M71-31-423      | 250             | 38.10        | 25.40         | General ID                                      | 37                                    | 10                              | ✓                   |
| ▲       | M71-31-483      | 250             | 38.10        | 25.40         | Asset ID for textured surfaces                  | 37                                    | 10                              | ✓                   |
| ▲       | M71-32-423      | 250             | 38.10        | 38.10         | General ID                                      | 37                                    | 16                              | ✓                   |
| ▲       | M71-32-489      | 250             | 38.10        | 38.10         | Asset ID for oily, greasy and textured surfaces | 37                                    | 16                              | ✓                   |
| ▲       | M71-37-422      | 100             | 76.20        | 48.26         | Asset ID for textured surfaces                  | 50                                    | 20                              | ✓                   |
| ▲       | M71-37-423      | 100             | 76.20        | 48.26         | General ID and Asset ID                         | 50                                    | 20                              | ✓                   |
| ▲       | M71-37-483      | 100             | 76.20        | 48.26         | Asset ID for oily, greasy and textured surfaces | 50                                    | 20                              | ✓                   |
| ▲       | M71-37-486      | 100             | 76.20        | 48.26         | Asset ID for oily, greasy and textured surfaces | 50                                    | 20                              | ✓                   |
| ▲       | M71-38-423      | 100             | 101.60       | 48.26         | General ID and Asset ID                         | 50                                    | 20                              | ✓                   |
| ▲       | M71-38-428      | 100             | 101.60       | 48.26         | Asset ID, silver finish                         | 50                                    | 20                              | ✓                   |
| ▲       | M71-38-483      | 100             | 101.60       | 48.26         | Asset ID for oily, greasy and textured surfaces | 50                                    | 20                              | ✓                   |
| ▲       | M71-38-489      | 100             | 101.60       | 48.26         | Asset ID for oily, greasy and textured surfaces | 50                                    | 20                              | ✓                   |
| ▲       | M71-78-499      | 250             | 48.26        | 25.40         | General ID                                      | 46                                    | 10                              | ✓                   |
| ▲       | M71-80-488      | 250             | 19.05        | 22.86         | Asset ID with print durability                  | 18                                    | 10                              | ✓                   |
| ▲       | M71-81-488      | 750             | 48.26        | 6.35          | Asset ID with print durability                  | 46                                    | 10                              | ✓                   |
| ▲       | M71-81-499      | 750             | 48.26        | 6.35          | General ID                                      | 46                                    | 10                              | ✓                   |
| ▲       | M71-84-499      | 500             | 22.86        | 12.70         | General ID                                      | 22                                    | 2                               | ✓                   |
| ▲       | M71-97-488      | 250             | 22.86        | 22.86         | Asset ID with print durability                  | 18                                    | 9                               | ✓                   |
| ●       | M71C-375-422    | 1 (cont.)       | 9.53         | 15.24 m       | General ID                                      | 50                                    | 3                               | ✓                   |
| ●       | M71C-375-430    | 1 (cont.)       | 9.53         | 15.24 m       | General ID                                      | 50                                    | 3                               | ✓                   |
| ●       | M71C-475-422    | 1 (cont.)       | 12.07        | 15.24 m       | General ID                                      | 50                                    | 5                               | ✓                   |
| ●       | M71C-500-423    | 1 (cont.)       | 12.70        | 15.24 m       | Small ICs                                       | 50                                    | 5                               | ✓                   |
| ●       | M71C-500-428    | 1 (cont.)       | 12.70        | 15.24 m       | Small ICs, silver finish                        | 50                                    | 5                               | ✓                   |
| ●       | M71C-500-483    | 1 (cont.)       | 12.70        | 15.24 m       | Small IC's, silver finish                       | 50                                    | 5                               | ✓                   |
| ●       | M71C-625-422    | 1 (cont.)       | 15.88        | 15.24 m       | General ID                                      | 50                                    | 6                               | ✓                   |
| ●       | M71C-1000-422   | 1 (cont.)       | 25.40        | 15.24 m       | General ID                                      | 50                                    | 10                              | ✓                   |
| ●       | M71C-1000-430   | 1 (cont.)       | 25.40        | 15.24 m       | General ID                                      | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-483   | 1 (cont.)       | 25.40        | 15.24 m       | General ID                                      | 50                                    | 10                              | ✓                   |
| ●       | M71C-1900-422   | 1 (cont.)       | 48.26        | 15.24 m       | General ID                                      | 50                                    | 10                              | ✓                   |
| ●       | M71C-1900-430   | 1 (cont.)       | 48.26        | 15.24 m       | General ID                                      | 50                                    | 10                              | ✓                   |
| ●       | M71C-1900-483   | 1 (cont.)       | 48.26        | 15.24 m       | General ID                                      | 50                                    | 10                              | ✓                   |

\*Any label 50.80 mm or larger is rotated on liner

✓ Material suitable for smooth surfaces.


✓ Material suitable for smooth and textured surfaces.

✓ Material suitable for smooth, textured and highly textured surfaces.

# General and Industrial Identification Labels

## General Industrial Labels

- B-422 Permanent Glossy Polyester
- B-430 Permanent Clear Polyester
- B-483 Ultra-Aggressive Glossy Polyester
- B-489 Ultra-Aggressive Matt Polyester
- B-580 Indoor/Outdoor Vinyl



| Diagram | Order Reference  | Labels Per Roll | Colour     | Width A (mm) | Height B (mm) | Max. Characters per line for 7 points | Max. Lines of Text for 7 points | Surface Suitability |
|---------|------------------|-----------------|------------|--------------|---------------|---------------------------------------|---------------------------------|---------------------|
| ▲       | M71-16-483       | 500             | White      | 25.40        | 9.53          | 14                                    | 2                               | ✓                   |
| ▲       | M71-17-483       | 500             | White      | 25.40        | 12.70         | 10                                    | 2                               | ✓                   |
| ▲       | M71-17-489       | 500             | White      | 25.40        | 12.70         | 10                                    | 2                               | ✓                   |
| ▲       | M71-19-483       | 250             | White      | 25.40        | 25.40         | 14                                    | 7                               | ✓                   |
| ▲       | M71-20-483       | 100             | White      | 50.80        | 25.40         | 50                                    | 4                               | ✓                   |
| ▲       | M71-23-483       | 100             | White      | 101.60       | 25.40         | 38                                    | 4                               | ✓                   |
| ▲       | M71-29-483       | 500             | White      | 38.10        | 12.70         | 14                                    | 2                               | ✓                   |
| ▲       | M71-29-489       | 500             | White      | 38.10        | 12.70         | 14                                    | 2                               | ✓                   |
| ▲       | M71-30-422       | 250             | White      | 38.10        | 19.05         | 14                                    | 3                               | ✓                   |
| ▲       | M71-30-483       | 250             | White      | 38.10        | 19.05         | 14                                    | 3                               | ✓                   |
| ▲       | M71-31-483       | 250             | White      | 38.10        | 25.40         | 14                                    | 4                               | ✓                   |
| ▲       | M71-32-489       | 250             | White      | 38.10        | 38.10         | 14                                    | 4                               | ✓                   |
| ▲       | M71-37-422       | 100             | White      | 76.20        | 48.26         | 28                                    | 9                               | ✓                   |
| ▲       | M71-37-483       | 100             | White      | 76.20        | 48.26         | 28                                    | 9                               | ✓                   |
| ▲       | M71-38-483       | 100             | White      | 101.60       | 48.26         | 38                                    | 9                               | ✓                   |
| ▲       | M71-38-489       | 100             | White      | 101.60       | 48.26         | 39                                    | 9                               | ✓                   |
| ●       | M71C-375-422     | 1 (cont.)       | White      | 9.53         | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-375-430     | 1 (cont.)       | Clear      | 9.53         | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-475-422     | 1 (cont.)       | White      | 12.07        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-422     | 1 (cont.)       | White      | 12.07        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-483     | 1 (cont.)       | White      | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-BK  | 1 (cont.)       | Black      | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-BL  | 1 (cont.)       | Blue       | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-BR  | 1 (cont.)       | Brown      | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-CL  | 1 (cont.)       | Clear      | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-GD  | 1 (cont.)       | Gold       | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-GN  | 1 (cont.)       | Green      | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-GY  | 1 (cont.)       | Grey       | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-LB  | 1 (cont.)       | Light Blue | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-OC  | 1 (cont.)       | Ochre      | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-OR  | 1 (cont.)       | Orange     | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-PK  | 1 (cont.)       | Pink       | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-PL  | 1 (cont.)       | Purple     | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-RD  | 1 (cont.)       | Red        | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-SB  | 1 (cont.)       | Sky Blue   | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-TN  | 1 (cont.)       | Tan        | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-WT  | 1 (cont.)       | White      | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-500-580-YL  | 1 (cont.)       | Yellow     | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-625-422     | 1 (cont.)       | White      | 15.88        | 15.24 m       | 50                                    | 3                               | ✓                   |
| ●       | M71C-1000-580-BK | 1 (cont.)       | Black      | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-BL | 1 (cont.)       | Blue       | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-BR | 1 (cont.)       | Brown      | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-CL | 1 (cont.)       | Clear      | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-GD | 1 (cont.)       | Gold       | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-GN | 1 (cont.)       | Green      | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-GY | 1 (cont.)       | Grey       | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-LB | 1 (cont.)       | Light Blue | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |

\*Any label 50.80 mm or larger is rotated on liner

Continued on next page >>

✓ Material suitable for smooth surfaces.

✓ Material suitable for smooth and textured surfaces.

✓ Material suitable for smooth, textured and highly textured surfaces.




# General and Industrial Identification Labels

## General Industrial Labels (continued)




- B-422 Permanent Glossy Polyester
- B-430 Permanent Clear Polyester
- B-483 Ultra-Aggressive Glossy Polyester
- B-580 Indoor/Outdoor Vinyl

| Diagram | Order Reference  | Labels Per Roll | Colour     | Width A (mm) | Height B (mm) | Max. Characters per line for 7 points | Max. Lines of Text for 7 points | Surface Suitability |
|---------|------------------|-----------------|------------|--------------|---------------|---------------------------------------|---------------------------------|---------------------|
| ●       | M71C-1000-580-OC | 1 (cont.)       | Ochre      | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-OR | 1 (cont.)       | Orange     | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-PK | 1 (cont.)       | Pink       | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-PL | 1 (cont.)       | Purple     | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-RD | 1 (cont.)       | Red        | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-SB | 1 (cont.)       | Sky Blue   | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-TN | 1 (cont.)       | Tan        | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-WT | 1 (cont.)       | White      | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-580-YL | 1 (cont.)       | Yellow     | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-422    | 1 (cont.)       | White      | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-430    | 1 (cont.)       | Clear      | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1000-483    | 1 (cont.)       | White      | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-1900-422    | 1 (cont.)       | White      | 48.26        | 15.24 m       | 50                                    | 9                               | ✓                   |
| ●       | M71C-1900-430    | 1 (cont.)       | Clear      | 48.26        | 15.24 m       | 50                                    | 9                               | ✓                   |
| ●       | M71C-1900-483    | 1 (cont.)       | White      | 48.26        | 15.24 m       | 50                                    | 9                               | ✓                   |
| ●       | M71C-2000-580-BK | 1 (cont.)       | Black      | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-BL | 1 (cont.)       | Blue       | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-BR | 1 (cont.)       | Brown      | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-CL | 1 (cont.)       | Clear      | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-GD | 1 (cont.)       | Gold       | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-GN | 1 (cont.)       | Green      | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-GY | 1 (cont.)       | Grey       | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ▲       | M71C-2000-580-LB | 1 (cont.)       | Light Blue | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ▲       | M71C-2000-580-OC | 1 (cont.)       | Ochre      | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-OR | 1 (cont.)       | Orange     | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-PK | 1 (cont.)       | Pink       | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-PL | 1 (cont.)       | Purple     | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-RD | 1 (cont.)       | Red        | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-SB | 1 (cont.)       | Sky Blue   | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-TN | 1 (cont.)       | Tan        | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-WT | 1 (cont.)       | White      | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |
| ●       | M71C-2000-580-YL | 1 (cont.)       | Yellow     | 50.80        | 15.24 m       | 50                                    | 8                               | ✓                   |



## Pre-Printed Labels

- B-423 Permanent Glossy Polyester
- B-428 Permanent Metallised Polyester



| Order Reference | Labels Per Roll | Colours         | Width A (mm) | Height B (mm) | Pre- Printed Legend | Surface Suitability |
|-----------------|-----------------|-----------------|--------------|---------------|---------------------|---------------------|
| M71-30-423-TEST | 250             | Green on White  | 38.10        | 19.05         | Tested              | ✓                   |
| M71-30-428-CALI | 250             | Green on Silver | 38.10        | 19.05         | Calibration         | ✓                   |
| M71-35-428-PROP | 250             | Black on Silver | 41.40        | 19.05         | Property Tag        | ✓                   |



✓ Material suitable for smooth surfaces.

✓ Material suitable for smooth and textured surfaces.

✓ Material suitable for smooth, textured and highly textured surfaces.

## Wrap Around Labels

- **B-498 Vinyl cloth:** repositionable rubber based adhesive
- **B-499 Nylon Cloth:** permanent adhesive, pliable for rough and smooth surfaces.



| Diagram                                                         | Order Reference | Labels Per Roll | Label Width A (mm) | Label Height B (mm) | Max. Wire Diameter (mm) | Approx. Wire Gauge* | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|-----------------------------------------------------------------|-----------------|-----------------|--------------------|---------------------|-------------------------|---------------------|---------------------------------------|---------------------------------|
| <b>9 AWG Based on Type of Wire – Max Wire Diam. 3.03 mm</b>     |                 |                 |                    |                     |                         |                     |                                       |                                 |
| ▲                                                               | M71-7-498       | 500             | 12.70              | 12.70               | 3.03                    | 9                   | 11                                    | 5                               |
| ▲                                                               | M71-7-499       | 500             | 12.70              | 12.70               | 3.03                    | 9                   | 11                                    | 5                               |
| ▲                                                               | M71-81-499      | 750             | 48.26              | 6.35                | 10.00                   | 9                   | 46                                    | 10                              |
| ▲                                                               | M71-84-499      | 500             | 22.86              | 12.70               | 6.00                    | 9                   | 22                                    | 2                               |
| <b>6 AWG Based on Type of Wire – Max Wire Diam. 4.55 mm</b>     |                 |                 |                    |                     |                         |                     |                                       |                                 |
| ▲                                                               | M71-10-498      | 750             | 6.35               | 19.05               | 4.55                    | 6                   | 5                                     | 3                               |
| ▲                                                               | M71-11-498      | 500             | 12.70              | 19.05               | 4.55                    | 6                   | 11                                    | 8                               |
| ▲                                                               | BM71-11-498     | 5000            | 12.70              | 19.05               | 4.55                    | 6                   | 11                                    | 8                               |
| ▲                                                               | M71-11-499      | 500             | 12.70              | 19.05               | 4.55                    | 6                   | 11                                    | 8                               |
| ▲                                                               | BM71-11-499     | 5000            | 12.70              | 19.05               | 4.55                    | 6                   | 11                                    | 8                               |
| <b>3 AWG Based on Type of Wire – Max Wire Diam. 6.06 mm</b>     |                 |                 |                    |                     |                         |                     |                                       |                                 |
| ▲                                                               | M71-16-498      | 500             | 9.53               | 25.40               | 6.06                    | 3                   | 8                                     | 10                              |
| ▲                                                               | M71-16-499      | 500             | 9.53               | 25.40               | 6.06                    | 3                   | 8                                     | 10                              |
| ▲                                                               | M71-17-498      | 500             | 25.40              | 12.70               | 6.06                    | 3                   | 24                                    | 5                               |
| ▲                                                               | M71-18-498      | 250             | 19.05              | 25.40               | 6.06                    | 3                   | 18                                    | 10                              |
| ▲                                                               | M71-18-499      | 250             | 19.05              | 25.40               | 6.06                    | 3                   | 18                                    | 10                              |
| ▲                                                               | BM71-18-498     | 2500            | 19.05              | 25.40               | 6.06                    | 3                   | 18                                    | 10                              |
| ▲                                                               | M71-19-498      | 250             | 25.40              | 25.40               | 6.06                    | 3                   | 24                                    | 10                              |
| ▲                                                               | BM71-19-498     | 2500            | 25.40              | 25.40               | 6.06                    | 3                   | 24                                    | 10                              |
| ▲                                                               | M71-19-499      | 250             | 25.40              | 25.40               | 6.06                    | 3                   | 24                                    | 10                              |
| ▲                                                               | M71-78-499      | 250             | 48.26              | 25.40               | 10.00                   | 3                   | 46                                    | 10                              |
| <b>0 AWG Based on Type of Wire – Max Wire Diam. 9.10 mm</b>     |                 |                 |                    |                     |                         |                     |                                       |                                 |
| ▲                                                               | M71-28-499      | 750             | 38.10              | 6.35                | 9.10                    | 0                   | 5                                     | 16                              |
| ▲                                                               | M71-29-498      | 500             | 38.10              | 12.70               | 9.10                    | 0                   | 11                                    | 16                              |
| ▲                                                               | BM71-29-498     | 5000            | 12.70              | 38.10               | 9.10                    | 0                   | 11                                    | 16                              |
| ▲                                                               | M71-29-499      | 500             | 12.70              | 38.10               | 9.10                    | 0                   | 11                                    | 16                              |
| ▲                                                               | M71-30-498      | 250             | 19.05              | 38.10               | 9.10                    | 0                   | 18                                    | 16                              |
| ▲                                                               | M71-30-499      | 250             | 19.05              | 38.10               | 9.10                    | 0                   | 18                                    | 16                              |
| ▲                                                               | M71-31-498      | 250             | 25.40              | 38.10               | 9.10                    | 0                   | 24                                    | 16                              |
| ▲                                                               | M71-31-499      | 250             | 25.40              | 38.10               | 9.10                    | 0                   | 24                                    | 16                              |
| ▲                                                               | M71-32-498      | 250             | 38.10              | 38.10               | 9.10                    | 0                   | 37                                    | 16                              |
| <b>0000 AWG Based on Type of Wire – Max Wire Diam. 15.16 mm</b> |                 |                 |                    |                     |                         |                     |                                       |                                 |
| ▲                                                               | M71-21-498      | 100             | 25.40              | 63.50               | 15.6                    | 0000                | 24                                    | 23                              |
| ▲                                                               | M71-21-499      | 100             | 25.40              | 63.50               | 15.6                    | 0000                | 24                                    | 23                              |
| <b>0000 AWG Based on Type of Wire – Max Wire Diam. 24.26 mm</b> |                 |                 |                    |                     |                         |                     |                                       |                                 |
| ▲                                                               | M71-33-498      | 100             | 38.10              | 101.60              | 24.26                   | 0000                | 37                                    | 16                              |



\*Based on National Electric Code insulation measurement of THHN Wire.

Order references beginning with "B" indicate bulk rolls.

# Wire and Cable Marking

## Self-Laminating Labels

- **B-427 Vinyl:** resistant to water, oil, solvents and abrasion.
- **B-642 Tedlar®:** excellent abrasion and smudge resistance, self-extinguishing



| Diagram                                                              | Order Reference | Labels Per Roll | Colour | Label Width A (mm) | Label Height B (mm) | Write-on Height C (mm) | Min. Wire Diameter (mm) | Max. Wire Diameter (mm) | Approx. Wire Gauge* | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|----------------------------------------------------------------------|-----------------|-----------------|--------|--------------------|---------------------|------------------------|-------------------------|-------------------------|---------------------|---------------------------------------|---------------------------------|
| <b>10 to 0 AWG Based on Type of Wire – Maximum Wire Diam 10.00</b>   |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ✗                                                                    | M71-104-427     | 250             | White  | 38.10              | 25.40               | 9.53                   | 3.00                    | 8.00                    | 10 to 0             | 37                                    | 3                               |
| <b>10 to 4 AWG Based on Type of Wire – Maximum Wire Diam 5.00</b>    |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ⊗                                                                    | BM71-17-427     | 5000            | White  | 12.70              | 25.40               | 9.53                   | 3.00                    | 5.00                    | 10 to 4             | 11                                    | 3                               |
| ⊗                                                                    | M71-17-427      | 500             | White  | 12.70              | 25.40               | 9.53                   | 3.00                    | 5.00                    | 10 to 4             | 11                                    | 3                               |
| ⊗                                                                    | BM71-18-427     | 2500            | White  | 19.05              | 25.40               | 9.53                   | 3.00                    | 5.00                    | 10 to 4             | 18                                    | 3                               |
| ⊗                                                                    | M71-18-427      | 250             | White  | 19.05              | 25.40               | 9.53                   | 3.00                    | 5.00                    | 10 to 4             | 18                                    | 3                               |
| ✗                                                                    | BM71-19-427     | 2500            | White  | 25.40              | 25.40               | 9.53                   | 3.00                    | 5.00                    | 10 to 4             | 24                                    | 3                               |
| ✗                                                                    | M71-19-427      | 250             | White  | 25.40              | 25.40               | 9.53                   | 3.00                    | 5.00                    | 10 to 4             | 24                                    | 3                               |
| ✗                                                                    | M71-19-427-YL   | 250             | Yellow | 25.40              | 25.40               | 9.53                   | 3.00                    | 5.00                    | 10 to 4             | 24                                    | 3                               |
| ✗                                                                    | M71-19-642      | 250             | White  | 25.40              | 25.40               | 9.53                   | 3.00                    | 5.00                    | 10 to 4             | 24                                    | 3                               |
| ✗                                                                    | M71-96-427      | 250             | White  | 25.40              | 19.05               | 9.53                   | 3.00                    | 5.00                    | 10 to 4             | 24                                    | 3                               |
| <b>10 to 10 AWG Based on Type of Wire – Maximum Wire Diam 3.00</b>   |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ⊗                                                                    | M71-10-427      | 750             | White  | 6.35               | 19.05               | 9.53                   | 3.00                    | 3.00                    | 10 to 10            | 5                                     | 3                               |
| ⊗                                                                    | BM71-11-427     | 5000            | White  | 12.70              | 19.05               | 9.53                   | 3.00                    | 3.00                    | 10 to 10            | 11                                    | 3                               |
| ⊗                                                                    | M71-11-427      | 500             | White  | 12.70              | 19.05               | 9.53                   | 3.00                    | 3.00                    | 10 to 10            | 11                                    | 3                               |
| <b>7 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 12.00</b> |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ⊗                                                                    | BM71-107-427    | 1000            | White  | 50.80              | 38.10               | 12.70                  | 4.00                    | 12.00                   | 7 to 0000           | 46                                    | 5                               |
| ⊗                                                                    | M71-107-427     | 100             | White  | 50.80              | 38.10               | 12.70                  | 4.00                    | 12.00                   | 7 to 0000           | 46                                    | 5                               |
| <b>7 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 10.00</b> |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ✗                                                                    | M71-88-427      | 250             | White  | 44.45              | 38.10               | 12.70                  | 4.00                    | 10.00                   | 7 to 0000           | 40                                    | 5                               |
| <b>7 to 0 AWG Based on Type of Wire – Maximum Wire Diam 8.00</b>     |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ⊗                                                                    | M71-28-427      | 750             | White  | 6.35               | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 5                                     | 5                               |
| ⊗                                                                    | BM71-29-427     | 5000            | White  | 12.70              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 11                                    | 5                               |
| ⊗                                                                    | M71-29-427      | 500             | White  | 12.70              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 11                                    | 5                               |
| ⊗                                                                    | BM71-30-427     | 2500            | White  | 19.05              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 18                                    | 5                               |
| ⊗                                                                    | M71-30-427      | 250             | White  | 19.05              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 18                                    | 5                               |
| ⊗                                                                    | M71-30-427-BL   | 250             | Blue   | 19.05              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 18                                    | 5                               |
| ⊗                                                                    | M71-30-427-PL   | 250             | Purple | 19.05              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 18                                    | 5                               |
| ⊗                                                                    | M71-30-427-RD   | 250             | Red    | 19.05              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 18                                    | 5                               |
| ⊗                                                                    | BM71-31-427     | 2500            | White  | 25.40              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 24                                    | 5                               |
| ⊗                                                                    | M71-31-427      | 250             | White  | 25.40              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 24                                    | 5                               |
| ⊗                                                                    | M71-31-427-GN   | 250             | Green  | 25.40              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 24                                    | 5                               |
| ⊗                                                                    | M71-31-427-RD   | 250             | Red    | 25.40              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 24                                    | 5                               |
| ⊗                                                                    | M71-31-427-YL   | 250             | Yellow | 25.40              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 24                                    | 5                               |
| ⊗                                                                    | M71-31-642      | 250             | White  | 25.40              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 24                                    | 5                               |
| ⊗                                                                    | BM71-32-427     | 1000            | White  | 38.10              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 37                                    | 5                               |
| ⊗                                                                    | M71-32-427      | 250             | White  | 38.10              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 37                                    | 5                               |
| ⊗                                                                    | M71-32-427-YL   | 250             | Yellow | 38.10              | 38.10               | 12.70                  | 4.00                    | 8.00                    | 7 to 0              | 37                                    | 5                               |
| <b>7 to 4 AWG Based on Type of Wire – Maximum Wire Diam 5.00</b>     |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ✗                                                                    | M71-103-427     | 250             | White  | 25.40              | 31.75               | 12.70                  | 4.00                    | 5.00                    | 7 to 4              | 24                                    | 5                               |


\*Based on National Electric Code insulation measurement of THHN Wire.

Order references beginning with "B" indicate bulk rolls.

Continued on next page >>

## Self-Laminating Labels (continued)

- **B-427 Vinyl:** resistant to water, oil, solvents and abrasion.
- **B-642 Tedlar®:** excellent abrasion and smudge resistance, self-extinguishing



| Diagram                                                              | Order Reference | Labels Per Roll | Colour | Label Width A (mm) | Label Height B (mm) | Write-on Height C (mm) | Min. Wire Diameter (mm) | Max. Wire Diameter (mm) | Approx. Wire Gauge* | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|----------------------------------------------------------------------|-----------------|-----------------|--------|--------------------|---------------------|------------------------|-------------------------|-------------------------|---------------------|---------------------------------------|---------------------------------|
| <b>3 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 14.00</b> |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ⊗                                                                    | BM71-21-427     | 1000            | White  | 25.40              | 63.50               | 19.05                  | 6.00                    | 14.00                   | 3 to 0000           | 24                                    | 8                               |
| ⊗                                                                    | M71-21-427      | 100             | White  | 25.40              | 63.50               | 19.05                  | 6.00                    | 14.00                   | 3 to 0000           | 24                                    | 8                               |
| ⊗                                                                    | M71-21-427-YL   | 100             | Yellow | 25.40              | 63.50               | 19.05                  | 6.00                    | 14.00                   | 3 to 0000           | 24                                    | 8                               |
| ⊗                                                                    | M71-21-642      | 100             | White  | 25.40              | 63.50               | 19.05                  | 6.00                    | 14.00                   | 3 to 0000           | 24                                    | 8                               |
| <b>1 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 24.00</b> |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ⊗                                                                    | BM71-23-427     | 1000            | White  | 25.40              | 101.60              | 25.40                  | 8.00                    | 24.00                   | 1 to 0000           | 24                                    | 10                              |
| ⊗                                                                    | M71-23-427      | 100             | White  | 25.40              | 101.60              | 25.40                  | 8.00                    | 24.00                   | 1 to 0000           | 24                                    | 10                              |
| ⊗                                                                    | BM71-33-427     | 500             | White  | 38.10              | 101.60              | 25.40                  | 8.00                    | 24.00                   | 1 to 0000           | 37                                    | 10                              |
| ⊗                                                                    | M71-33-427      | 100             | White  | 38.10              | 101.60              | 25.40                  | 8.00                    | 24.00                   | 1 to 0000           | 37                                    | 10                              |
| ⊗                                                                    | M71-33-427-YL   | 100             | Yellow | 38.10              | 101.60              | 25.40                  | 8.00                    | 24.00                   | 1 to 0000           | 37                                    | 10                              |
| <b>1 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 17.00</b> |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ⊗                                                                    | BM71-34-427     | 500             | White  | 38.10              | 152.40              | 38.10                  | 8.00                    | 17.00                   | 1 to 0000           | 37                                    | 16                              |
| ⊗                                                                    | M71-66-427      | 100             | White  | 49.23              | 80.01               | 25.40                  | 8.00                    | 17.00                   | 1 to 0000           | 46                                    | 10                              |
| <b>1 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 36.00</b> |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ⊗                                                                    | M71-34-427      | 50              | White  | 38.10              | 152.40              | 38.10                  | 12.00                   | 36.00                   | 1 to 0000           | 37                                    | 16                              |
| <b>1 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 20.00</b> |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ⊗                                                                    | BM71-109-427    | 500             | White  | 38.10              | 101.60              | 38.10                  | 12.00                   | 20.00                   | 1 to 0000           | 37                                    | 16                              |
| ⊗                                                                    | M71-109-427     | 100             | White  | 38.10              | 101.60              | 38.10                  | 12.00                   | 20.00                   | 1 to 0000           | 37                                    | 16                              |
| <b>1 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 17.00</b> |                 |                 |        |                    |                     |                        |                         |                         |                     |                                       |                                 |
| ⊗                                                                    | BM71-64-427     | 1000            | White  | 25.40              | 85.73               | 28.58                  | 9.00                    | 17.00                   | 1 to 0000           | 24                                    | 12                              |
| ⊗                                                                    | M71-64-427      | 100             | White  | 25.40              | 85.73               | 28.58                  | 9.00                    | 17.00                   | 1 to 0000           | 24                                    | 12                              |

\*Based on National Electric Code insulation measurement of THHN Wire.

Order references beginning with "B" indicate bulk rolls.

## Applying Self-laminating Labels



Apply the printed area to your wire.



Wrap the clear area around the wire, covering the printed area.





Once applied the clear laminate will protect your legend for years to come.

# Wire and Cable Marking

## PermaSleeve™ Heat-Shrink Sleeve Markers

- **B-342 Polyolefin:** 3:1 Shrink ratio, self-extinguishing, meets requirements of SAE AMS-DTL-23053/5 Class 1, SAE-AS-81531, MIL-STD-202 method 215K, is UL224 recognised, CSA acceptance pending
- **B-341 Polyolefin:** 2:1 Shrink ratio, same properties as B-342




| Diagram                     | Order Reference    | Sleeves Per Roll | Colour | Sleeve Width A (mm) | Sleeve Height B (mm) | Min. Wire Diameter (mm) | Max. Wire Diameter (mm) | Approx. Wire Gauge* | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|-----------------------------|--------------------|------------------|--------|---------------------|----------------------|-------------------------|-------------------------|---------------------|---------------------------------------|---------------------------------|
| <b>3:1 SHRINK RATIO</b>     |                    |                  |        |                     |                      |                         |                         |                     |                                       |                                 |
| <b>25.78mm marker width</b> |                    |                  |        |                     |                      |                         |                         |                     |                                       |                                 |
| ✓                           | M71-94-1-342       | 100              | White  | 25.78               | 4.62                 | 0.58                    | 2.03                    | 28 to 18            | 22                                    | 1                               |
| ✓                           | BM71-94-1-342      | 2500             | White  | 25.78               | 4.62                 | 0.58                    | 2.03                    | 28 to 18            | 22                                    | 1                               |
| ✓                           | M71-94-1-342YL     | 100              | Yellow | 25.78               | 4.62                 | 0.58                    | 2.03                    | 28 to 18            | 22                                    | 1                               |
| ✓                           | BM71-94-1-342YL    | 2500             | Yellow | 25.78               | 4.62                 | 0.58                    | 2.03                    | 28 to 18            | 22                                    | 1                               |
| ✓                           | M71-125-1-342      | 100              | White  | 25.78               | 5.97                 | 1.17                    | 2.79                    | 22 to 16            | 22                                    | 1                               |
| ✓                           | BM71-125-1-342     | 1000             | White  | 25.78               | 5.97                 | 1.17                    | 2.79                    | 22 to 16            | 22                                    | 1                               |
| ✓                           | M71-125-1-342YL    | 100              | Yellow | 25.78               | 5.97                 | 1.17                    | 2.79                    | 22 to 16            | 22                                    | 1                               |
| ✓                           | M71-187-1-342      | 100              | White  | 25.78               | 8.51                 | 1.57                    | 3.81                    | 18 to 12            | 22                                    | 2                               |
| ✓                           | BM71-187-1-342     | 1000             | White  | 25.78               | 8.51                 | 1.57                    | 3.81                    | 18 to 12            | 22                                    | 2                               |
| ✓                           | M71-187-1-342YL    | 100              | Yellow | 25.78               | 8.51                 | 1.57                    | 3.81                    | 18 to 12            | 22                                    | 2                               |
| ✓                           | BM71-187-1-342YL   | 1000             | Yellow | 25.78               | 8.51                 | 1.57                    | 3.81                    | 18 to 12            | 22                                    | 2                               |
| ✓                           | M71-250-1-342      | 100              | White  | 25.78               | 11.15                | 2.39                    | 5.46                    | 16 to 10            | 22                                    | 3                               |
| ✓                           | BM71-250-1-342     | 1000             | White  | 25.78               | 11.15                | 2.39                    | 5.46                    | 16 to 10            | 22                                    | 3                               |
| ✓                           | M71-250-1-342YL    | 100              | Yellow | 25.78               | 11.15                | 2.39                    | 5.46                    | 16 to 10            | 22                                    | 3                               |
| ✓                           | M71-375-1-342      | 100              | White  | 25.78               | 16.38                | 3.18                    | 8.13                    | 12 to 6             | 22                                    | 5                               |
| ✓                           | BM71-375-1-342     | 1000             | White  | 25.78               | 16.38                | 3.18                    | 8.13                    | 12 to 6             | 22                                    | 5                               |
| ✓                           | M71-375-1-342YL    | 100              | Yellow | 25.78               | 16.38                | 3.18                    | 8.13                    | 12 to 6             | 22                                    | 5                               |
| ✓                           | M71-500-1-342      | 100              | White  | 25.78               | 21.62                | 4.75                    | 11.43                   | 8 to 1              | 22                                    | 7                               |
| ✓                           | BM71-500-1-342     | 1000             | White  | 25.78               | 21.62                | 4.75                    | 11.43                   | 8 to 1              | 22                                    | 7                               |
| ✓                           | M71-500-1-342YL    | 100              | Yellow | 25.78               | 21.62                | 4.75                    | 11.43                   | 8 to 1              | 22                                    | 7                               |
| ✓                           | BM71-500-1-342YL   | 1000             | Yellow | 25.78               | 21.62                | 4.75                    | 11.43                   | 8 to 1              | 22                                    | 7                               |
| <b>44.83mm marker width</b> |                    |                  |        |                     |                      |                         |                         |                     |                                       |                                 |
| ✓                           | M71-94-175-342     | 100              | White  | 44.83               | 4.62                 | 0.58                    | 2.03                    | 28 to 18            | 41                                    | 1                               |
| ✓                           | BM71-94-175-342    | 2500             | White  | 44.83               | 4.62                 | 0.58                    | 2.03                    | 28 to 18            | 41                                    | 1                               |
| ✓                           | M71-94-175-342YL   | 100              | Yellow | 44.83               | 4.62                 | 0.58                    | 2.03                    | 28 to 18            | 41                                    | 1                               |
| ✓                           | BM71-94-175-342YL  | 2500             | Yellow | 44.83               | 4.62                 | 0.58                    | 2.03                    | 28 to 18            | 41                                    | 1                               |
| ✓                           | M71-125-175-342    | 100              | White  | 44.83               | 5.97                 | 1.17                    | 2.79                    | 22 to 16            | 41                                    | 1                               |
| ✓                           | BM71-125-175-342   | 1000             | White  | 44.83               | 5.97                 | 1.17                    | 2.79                    | 22 to 16            | 41                                    | 1                               |
| ✓                           | M71-125-175-342YL  | 100              | Yellow | 44.83               | 5.97                 | 1.17                    | 2.79                    | 22 to 16            | 41                                    | 1                               |
| ✓                           | BM71-125-175-342YL | 1000             | Yellow | 44.83               | 5.97                 | 1.17                    | 2.79                    | 22 to 16            | 41                                    | 1                               |
| ✓                           | M71-187-175-342    | 100              | White  | 44.83               | 8.51                 | 1.57                    | 3.81                    | 18 to 12            | 41                                    | 3                               |
| ✓                           | BM71-187-175-342   | 1000             | White  | 44.83               | 8.51                 | 1.57                    | 3.81                    | 18 to 12            | 41                                    | 3                               |
| ✓                           | M71-187-175-342YL  | 100              | Yellow | 44.83               | 8.51                 | 1.57                    | 3.81                    | 18 to 12            | 41                                    | 3                               |
| ✓                           | BM71-187-175-342YL | 1000             | Yellow | 44.83               | 8.51                 | 1.57                    | 3.81                    | 18 to 12            | 41                                    | 3                               |
| ✓                           | M71-250-175-342    | 100              | White  | 44.83               | 11.15                | 2.39                    | 5.46                    | 16 to 10            | 41                                    | 3                               |
| ✓                           | BM71-250-175-342   | 1000             | White  | 44.83               | 11.15                | 2.39                    | 5.46                    | 16 to 10            | 41                                    | 3                               |
| ✓                           | M71-250-175-342YL  | 100              | Yellow | 44.83               | 11.15                | 2.39                    | 5.46                    | 16 to 10            | 41                                    | 3                               |
| ✓                           | BM71-250-175-342YL | 1000             | Yellow | 44.83               | 11.15                | 2.39                    | 5.46                    | 16 to 10            | 41                                    | 3                               |
| ✓                           | M71-375-175-342    | 100              | White  | 44.83               | 16.38                | 3.18                    | 8.13                    | 12 to 6             | 41                                    | 5                               |
| ✓                           | BM71-375-175-342   | 1000             | White  | 44.83               | 16.38                | 3.18                    | 8.13                    | 12 to 6             | 41                                    | 5                               |
| ✓                           | M71-375-175-342YL  | 100              | Yellow | 44.83               | 16.38                | 3.18                    | 8.13                    | 12 to 6             | 41                                    | 5                               |
| ✓                           | BM71-375-175-342YL | 1000             | Yellow | 44.83               | 16.38                | 3.18                    | 8.13                    | 12 to 6             | 41                                    | 5                               |
| ✓                           | M71-500-175-342    | 100              | White  | 44.83               | 21.62                | 4.75                    | 11.43                   | 8 to 1              | 41                                    | 7                               |
| ✓                           | BM71-500-175-342   | 1000             | White  | 44.83               | 21.62                | 4.75                    | 11.43                   | 8 to 1              | 41                                    | 7                               |
| ✓                           | M71-500-175-342YL  | 100              | Yellow | 44.83               | 21.62                | 4.75                    | 11.43                   | 8 to 1              | 41                                    | 7                               |
| ✓                           | BM71-500-175-342YL | 1000             | Yellow | 44.83               | 21.62                | 4.75                    | 11.43                   | 8 to 1              | 41                                    | 7                               |
| <b>Continuous marker</b>    |                    |                  |        |                     |                      |                         |                         |                     |                                       |                                 |
| ♥                           | BM71C-125-342      | 1 (cont.)        | White  | 15.24 m             | 5.97                 | 1.17                    | 2.79                    | 22 to 16            | NA                                    | NA                              |
| ♥                           | BM71C-187-342      | 1 (cont.)        | White  | 15.24 m             | 8.51                 | 1.57                    | 3.81                    | 18 to 12            | NA                                    | NA                              |
| ♥                           | BM71C-250-342      | 1 (cont.)        | White  | 15.24 m             | 11.15                | 2.39                    | 5.46                    | 16 to 10            | NA                                    | NA                              |
| ♥                           | BM71C-375-342      | 1 (cont.)        | White  | 15.24 m             | 16.38                | 3.18                    | 8.13                    | 12 to 6             | NA                                    | NA                              |
| ♥                           | BM71C-500-342      | 1 (cont.)        | White  | 15.24 m             | 21.62                | 4.75                    | 11.43                   | 8 to 1              | NA                                    | NA                              |
| <b>2:1 SHRINK RATIO</b>     |                    |                  |        |                     |                      |                         |                         |                     |                                       |                                 |
| <b>25.78mm marker width</b> |                    |                  |        |                     |                      |                         |                         |                     |                                       |                                 |
| ✓                           | M71-1000-1-341     | 50               | White  | 25.78               | 42.16                | 11.43                   | 24.13                   | 1 to 500            | 22                                    | 16                              |
| ✓                           | M71-1000-1-341YL   | 50               | Yellow | 25.78               | 42.16                | 11.43                   | 24.13                   | 1 to 500            | 22                                    | 16                              |
| <b>44.83mm marker width</b> |                    |                  |        |                     |                      |                         |                         |                     |                                       |                                 |
| ✓                           | M71-1000-175-341   | 50               | White  | 44.83               | 42.16                | 11.43                   | 24.13                   | 1 to 500            | 41                                    | 16                              |
| ✓                           | BM71-1000-175-341  | 500              | White  | 44.83               | 42.16                | 11.43                   | 24.13                   | 1 to 500            | 41                                    | 16                              |
| ✓                           | M71-1000-175-341YL | 50               | Yellow | 44.83               | 42.16                | 11.43                   | 24.13                   | 1 to 500            | 41                                    | 16                              |
| <b>Continuous marker</b>    |                    |                  |        |                     |                      |                         |                         |                     |                                       |                                 |
| ♥                           | BM71C-1000-341     | 1 (cont.)        | White  | 15.24 m             | 42.16                | 11.43                   | 24.13                   | 1 to 500            | NA                                    | NA                              |

\*Based on National Electric Code insulation measurement of THHN Wire.

Order references beginning with "B" indicate bulk rolls.

## Rigid Durasleeve Inserts

- **B-7696:** Rigid vinyl tag



| Order Reference | Tags Per Roll | Colour | Width (mm) | Height (mm) | Carrier | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|-----------------|---------------|--------|------------|-------------|---------|---------------------------------------|---------------------------------|
| BM71D-3-7696    | 2500          | White  | 16.00      | 4.40        | AC*-L16 | 11                                    | 1                               |
| BM71D-3-7696-YL | 5000          | Yellow | 16.00      | 4.40        | AC*-L16 | 11                                    | 1                               |
| BM71D-5-7696    | 2500          | White  | 30.00      | 4.40        | AC*-L30 | 21                                    | 1                               |
| BM71D-5-7696-YL | 5000          | Yellow | 30.00      | 4.40        | AC*-L30 | 21                                    | 1                               |

Order references beginning with "B" indicate bulk rolls.

## Ademark Tag Carrier

Ademark carriers are produced in transparent PVC. The special shape of the carrier means that it can be adapted to cables of various diameters. This means that there are only seven different sizes of carriers which cater for cables with external diameters from 1.3 mm up to 24 mm.

- Temperature range: -40° to 60°C
- Material: PVC
- Self extinguishing: UL94V0



| Order Reference | Carriers per pack | Length (mm) | Wire O.D. (mm) |
|-----------------|-------------------|-------------|----------------|
| AC-0-L16        | 2000              | 16.00 mm    | 1.30 - 2.00    |
| AC-1-L16        | 2000              | 16.00 mm    | 1.80 - 2.50    |
| AC-2-L16        | 2000              | 16.00 mm    | 2.50 - 4.00    |
| AC-3-L16        | 1000              | 16.00 mm    | 4.00 - 6.50    |
| AC-4-L16        | 1000              | 16.00 mm    | 6.00 - 10.00   |
| AC-5-L16        | 750               | 16.00 mm    | 9.00 - 15.00   |
| AC-6-L16        | 500               | 16.00 mm    | 15.00 - 24.00  |


| Order Reference | Carriers per pack | Length (mm) | Wire O.D. (mm) |
|-----------------|-------------------|-------------|----------------|
| AC-0-L30        | 2000              | 30.00 mm    | 1.30 - 2.00    |
| AC-1-L30        | 2000              | 30.00 mm    | 1.80 - 2.50    |
| AC-2-L30        | 2000              | 30.00 mm    | 2.50 - 4.00    |
| AC-3-L30        | 1000              | 30.00 mm    | 4.00 - 6.50    |
| AC-4-L30        | 1000              | 30.00 mm    | 6.00 - 10.00   |
| AC-5-L30        | 750               | 30.00 mm    | 9.00 - 15.00   |
| AC-6-L30        | 500               | 30.00 mm    | 15.00 - 24.00  |

## Rapido™

- **B-7599:** Yellow coated polyethylene tag suitable for durable terminated wire marking for electrical devices and fibre installations.

| Order Reference | Tags Per Roll | Colour | Width A (mm) | Height B (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|-----------------|---------------|--------|--------------|---------------|---------------------------------------|---------------------------------|
| BM71R-1-7599-YL | 2500          | Yellow | 22.90        | 5.20          | 11                                    | 1                               |
| BM71R-2-7599-YL | 2500          | Yellow | 23.00        | 5.20          | 8                                     | 1                               |
| BM71R-3-7599-YL | 2500          | Yellow | 25.00        | 5.70          | 7                                     | 2                               |
| BM71R-4-7599-YL | 2500          | Yellow | 26.00        | 7.00          | 7                                     | 2                               |
| BM71R-5-7599-YL | 2500          | Yellow | 41.00        | 11.00         | 17                                    | 3                               |

Order references beginning with "B" indicate bulk rolls.




# Wire and Cable Marking

## Heatex™ Cable Markers

- **B-7643:** Zero halogen polyether polyurethane tag material


| Order Reference | Tags Per Roll | Colour | Width A (mm) | Height B (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|-----------------|---------------|--------|--------------|---------------|---------------------------------------|---------------------------------|
| BM71H-1-7643-WT | 250           | White  | 60.00        | 10.00         | 40                                    | 4                               |
| BM71H-1-7643-YL | 250           | Yellow | 60.00        | 10.00         | 40                                    | 4                               |
| BM71H-2-7643-WT | 250           | White  | 75.00        | 10.00         | 51                                    | 4                               |
| BM71H-2-7643-YL | 250           | Yellow | 75.00        | 10.00         | 51                                    | 4                               |
| BM71H-3-7643-WT | 250           | White  | 75.00        | 25.00         | 51                                    | 10                              |
| BM71H-3-7643-YL | 250           | Yellow | 75.00        | 25.00         | 51                                    | 10                              |

Order references beginning with "B" indicate bulk rolls.



## Tear Resistant Cable Markers

- **B-109 Polyethylene:** Provides extreme tear resistance and excellent cold-weather performance; meets requirements of DIN VDE 0472/parts 815
- **B-145 Polyethylene:** Tear resistant and 2-side printable, is UL94 V2 recognised



| Diagram | Order Reference | Tags Per Roll | Colour | Width A (mm) | Height B (mm) | Write-on Area W x H (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points | Cable Type                           |
|---------|-----------------|---------------|--------|--------------|---------------|--------------------------|---------------------------------------|---------------------------------|--------------------------------------|
|         | M71-12-109      | 100           | White  | 19.05        | 76.20         | 17.78 x 52.07            | 45                                    | 6                               | Cable Bundles; Power & Ground Cables |
|         | BM71-12-109     | 1,000         | White  | 19.05        | 76.20         | 17.78 x 52.07            | 45                                    | 6                               | Cable Bundles                        |
|         | M71-36-109      | 250           | White  | 44.45        | 28.58         | 44.45 x 28.57            | 40                                    | 15                              | Power & Ground Cables                |
|         | BM71-111-145-GY | 1,000         | Grey   | 19.25        | 30.63         | 19.25 x 30.63            | 16                                    | 14                              | 145C Tag; Power & Ground Cables      |
|         | BM71-110-145-GY | 1,000         | Grey   | 44.45        | 25.40         | 44.45 x 25.40            | 28                                    | 20                              | 145P Tag; Power & Ground Cables      |

Order references beginning with "B" indicate bulk rolls.



## Coloured Nylon Ties

Perfect for colour coded applications.

**Size:** 200 x 4 mm

**Material:** Nylon

**Packing:** 100 pieces

| Order Reference | Colour | Order Reference | Colour |
|-----------------|--------|-----------------|--------|
| 229955          | White  | 229959          | Yellow |
| 229956          | Blue   | 229960          | Green  |
| 229957          | Red    | 229961          | Violet |
| 229958          | Orange | 229962          | Black  |

|           |                                                                                            |
|-----------|--------------------------------------------------------------------------------------------|
| <b>BL</b> | Blue, for horizontal cable terminations                                                    |
| <b>BR</b> | Brown, for campus backbone cable terminations                                              |
| <b>GR</b> | Green, network connections                                                                 |
| <b>GY</b> | Grey, for backbone cable between intermediate cross-connect and telecommunications cabinet |
| <b>OR</b> | Orange, central office termination                                                         |
| <b>PL</b> | Purple, major switching and data equipment terminations                                    |
| <b>RD</b> | Red, for all key telephone equipment terminations                                          |
| <b>YL</b> | Yellow, for auxiliary, maintenance, alarms, security, etc.                                 |



## Terminal Block Repositionable Markers

### • B-498: Repositionable vinyl cloth

| Order Reference | Label Width A (mm) | Label Length B (m) (continuous) | Max. Characters per line for 5 Points |
|-----------------|--------------------|---------------------------------|---------------------------------------|
| M71C-240-498    | 6.10               | 9.14                            | 4                                     |
| M71C-318-498    | 8.08               | 9.14                            | 7                                     |
| BM71C-318-498   | 8.08               | 91.44                           | 7                                     |
| M71C-375-498    | 9.53               | 9.14                            | 7                                     |
| BM71C-375-498   | 9.53               | 91.44                           | 7                                     |

Order references beginning with "B" indicate bulk rolls.

Order references with "C" (e.g. M71C) indicate continuous.





## EPREP Labels – Engraved Plate Replacement Labels

### • B-7593: Polyethylene Foam Laminate


BRADY EPREP labels are innovative labels specifically designed to replace engraved and plotted plates for identification of electrical components, electrical cabinets, push buttons, patch panels etc.

| Diagram | Order Reference | Tags Per Roll | Colour | Width A (mm) | Height B (mm) | Diameter D (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points | Format    |
|---------|-----------------|---------------|--------|--------------|---------------|-----------------|---------------------------------------|---------------------------------|-----------|
| ▲       | M71EP-1-7593-SL | 250           | Silver | 27.00        | 8.00          |                 | 22                                    | 3                               | Roll      |
| ▲       | M71EP-1-7593-WT | 250           | White  | 27.00        | 8.00          |                 | 22                                    | 3                               | Roll      |
| ▲       | M71EP-2-7593-SL | 250           | Silver | 27.00        | 12.50         |                 | 22                                    | 5                               | Roll      |
| ▲       | M71EP-2-7593-WT | 250           | White  | 27.00        | 12.50         |                 | 22                                    | 5                               | Roll      |
| ▲       | M71EP-3-7593-SL | 150           | Silver | 27.00        | 15.00         |                 | 22                                    | 6                               | Roll      |
| ▲       | M71EP-3-7593-WT | 150           | White  | 27.00        | 15.00         |                 | 22                                    | 6                               | Roll      |
| ▲       | M71EP-4-7593-SL | 150           | Silver | 27.00        | 18.00         |                 | 22                                    | 7                               | Roll      |
| ▲       | M71EP-4-7593-WT | 150           | White  | 27.00        | 18.00         |                 | 22                                    | 7                               | Roll      |
| ◻       | M71EP-5-7593-BK | 100           | Black  | 30.00        | 40.00         | 24.00           | 24                                    | 5                               | Fanfolded |
| ◻       | M71EP-5-7593-GN | 100           | Green  | 30.00        | 40.00         | 24.00           | 24                                    | 5                               | Fanfolded |
| ◻       | M71EP-5-7593-RD | 100           | Black  | 30.00        | 40.00         | 24.00           | 24                                    | 5                               | Fanfolded |
| ◻       | M71EP-5-7593-SL | 100           | Silver | 30.00        | 40.00         | 24.00           | 24                                    | 5                               | Fanfolded |
| ◻       | M71EP-5-7593-WT | 100           | White  | 30.00        | 40.00         | 24.00           | 24                                    | 5                               | Fanfolded |
| ◻       | M71EP-5-7593-YL | 100           | Yellow | 30.00        | 40.00         | 24.00           | 24                                    | 5                               | Fanfolded |
| ▲       | M71EP-6-7593-BK | 100           | Black  | 45.00        | 15.00         |                 | 36                                    | 6                               | Fanfolded |
| ▲       | M71EP-6-7593-RD | 100           | Black  | 45.00        | 15.00         |                 | 36                                    | 6                               | Fanfolded |
| ▲       | M71EP-6-7593-YL | 100           | Yellow | 45.00        | 15.00         |                 | 36                                    | 6                               | Fanfolded |
| ▲       | BM71E-6-7593-SL | 500           | Silver | 45.00        | 15.00         |                 | 36                                    | 6                               | Bulk roll |
| ▲       | BM71E-6-7593-WT | 500           | White  | 45.00        | 15.00         |                 | 36                                    | 6                               | Bulk roll |
| ▲       | M71EP-7-7593-SL | 100           | Silver | 35.00        | 18.00         |                 | 28                                    | 7                               | Roll      |
| ▲       | M71EP-7-7593-WT | 100           | White  | 35.00        | 18.00         |                 | 28                                    | 7                               | Roll      |
| ▲       | M71EP-7-7593-YL | 100           | Yellow | 35.00        | 18.00         |                 | 28                                    | 7                               | Roll      |
| ▲       | M71EP-8-7593-SL | 125           | Silver | 48.00        | 19.00         |                 | 39                                    | 7                               | Roll      |
| ▲       | M71EP-8-7593-WT | 125           | White  | 48.00        | 19.00         |                 | 39                                    | 7                               | Roll      |


Order references beginning with "B" indicate bulk rolls.





Roll



Fanfolded




Bulk roll



## Nylon Cloth Labels

### • B-499: White nylon cloth with high adhesion



| Order Reference | Tags Per Roll | Label Diameter C (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|-----------------|---------------|-----------------------|---------------------------------------|---------------------------------|
| M71-82-499      | 500           | 9.52                  | 7                                     | 2                               |
| M71-83-499      | 250           | 12.70                 | 9                                     | 3                               |



# Datacom Labels

## Self-Laminating Labels

- **B-427 Vinyl:** excellent abrasion and smudge resistance.



| Diagram | Order Reference | Labels Per Roll | Label Width A (mm) | Label Height B (mm) | Write-on Height C (mm) | Application                                                           | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|---------|-----------------|-----------------|--------------------|---------------------|------------------------|-----------------------------------------------------------------------|---------------------------------------|---------------------------------|
| ✗       | BM71-19-427     | 2500            | 25.40              | 25.40               | 9.53                   | 2 Pair Fibre                                                          | 24                                    | 3                               |
| ✗       | M71-19-427      | 250             | 25.40              | 25.40               | 9.53                   | 2 Pair Fibre                                                          | 24                                    | 3                               |
| ✗       | M71-19-427-YL   | 250             | 25.40              | 25.40               | 9.53                   | 2 Pair Fibre                                                          | 24                                    | 3                               |
| ✗       | BM71-21-427     | 1000            | 25.40              | 63.50               | 19.05                  | 4 Pair STP, 25 Pair Copper, 4-12 Pair Fibre                           | 24                                    | 8                               |
| ✗       | M71-21-427      | 100             | 25.40              | 63.50               | 19.05                  | 4 Pair STP, 25 Pair Copper, 4-12 Pair Fibre                           | 24                                    | 8                               |
| ✗       | M71-21-427-YL   | 100             | 25.40              | 63.50               | 19.05                  | 4 Pair STP, 25 Pair Copper, 4-12 Pair Fibre                           | 24                                    | 8                               |
| ✗       | BM71-23-427     | 1000            | 25.40              | 101.60              | 25.40                  | 50 Pair Copper, 24 Pair Fibre, Backbone cable                         | 24                                    | 10                              |
| ✗       | M71-23-427      | 100             | 25.40              | 101.60              | 25.40                  | 50 Pair Copper, 24 Pair Fibre, Backbone cable                         | 24                                    | 10                              |
| ⊗       | BM71-29-427     | 5000            | 12.70              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 11                                    | 5                               |
| ⊗       | M71-29-427      | 500             | 12.70              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 11                                    | 5                               |
| ⊗       | BM71-30-427     | 2500            | 19.05              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 18                                    | 5                               |
| ⊗       | M71-30-427      | 250             | 19.05              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 18                                    | 5                               |
| ⊗       | M71-30-427-BL   | 250             | 19.05              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 18                                    | 5                               |
| ⊗       | M71-30-427-PL   | 250             | 19.05              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 18                                    | 5                               |
| ⊗       | M71-30-427-RD   | 250             | 19.05              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 18                                    | 5                               |
| ⊗       | BM71-31-427     | 2500            | 25.40              | 38.10               | 12.70                  | 4 Pair UTP, CAT 5, CAT 5E, RG-6 Coax, RG-59 Coax                      | 24                                    | 5                               |
| ⊗       | M71-31-427      | 250             | 25.40              | 38.10               | 12.70                  | 4 Pair UTP, CAT 5, CAT 5E, CAT 6, Silver Satin, RG-6 Coax, RG-59 Coax | 24                                    | 5                               |
| ⊗       | M71-31-427-GN   | 250             | 25.40              | 38.10               | 12.70                  | 4 Pair UTP, CAT 5, CAT 5E, CAT 6, Silver Satin, RG-6 Coax, RG-59 Coax | 24                                    | 5                               |
| ⊗       | M71-31-427-RD   | 250             | 25.40              | 38.10               | 12.70                  | 4 Pair UTP, CAT 5, CAT 5E, CAT 6, Silver Satin, RG-6 Coax, RG-59 Coax | 24                                    | 5                               |
| ⊗       | M71-31-427-YL   | 250             | 25.40              | 38.10               | 12.70                  | 4 Pair UTP, CAT 5, CAT 5E, CAT 6, Silver Satin, RG-6 Coax, RG-59 Coax | 24                                    | 5                               |
| ⊗       | BM71-32-427     | 1000            | 38.10              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 37                                    | 5                               |
| ⊗       | M71-32-427      | 250             | 38.10              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 37                                    | 5                               |
| ⊗       | M71-32-427-YL   | 250             | 38.10              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 37                                    | 5                               |
| ✗       | BM71-33-427     | 500             | 38.10              | 101.60              | 25.40                  | 50 Pair Copper, 24 Pair Fibre, Backbone cable                         | 37                                    | 10                              |
| ✗       | M71-33-427      | 100             | 38.10              | 101.60              | 25.40                  | 50 Pair Copper, 24 Pair Fibre, Backbone cable                         | 37                                    | 10                              |
| ✗       | M71-33-427-YL   | 100             | 38.10              | 101.60              | 25.40                  | 50 Pair Copper, 24 Pair Fibre, Backbone cable                         | 37                                    | 10                              |
| ✗       | BM71-34-427     | 500             | 38.10              | 152.40              | 38.10                  | 100 Pair Copper, 36 Pair Fibre                                        | 37                                    | 16                              |
| ✗       | M71-34-427      | 50              | 38.10              | 152.40              | 38.10                  | 100 Pair Copper                                                       | 37                                    | 16                              |
| ✗       | BM71-64-427     | 1000            | 25.40              | 85.73               | 28.58                  | Fibre/Coax                                                            | 24                                    | 12                              |
| ✗       | M71-64-427      | 100             | 25.40              | 85.73               | 28.58                  | Fibre/Coax                                                            | 24                                    | 12                              |
| ✗       | M71-66-427      | 100             | 49.23              | 80.01               | 25.40                  | 50 Pair Copper, 24 Pair Fibre, Backbone cable                         | 46                                    | 10                              |
| ✗       | M71-88-427      | 250             | 44.45              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 40                                    | 5                               |
| ✗       | M71-103-427     | 250             | 25.40              | 31.75               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 24                                    | 5                               |
| ✗       | M71-104-427     | 250             | 38.10              | 25.40               | 9.53                   | 2 Pair Fibre, Single/Multi-Mode                                       | 37                                    | 3                               |
| ✗       | BM71-107-427    | 1000            | 50.80              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 46                                    | 5                               |
| ⊗       | M71-107-427     | 100             | 50.80              | 38.10               | 12.70                  | CAT 5, 4 Pair UTP                                                     | 46                                    | 5                               |
| ✗       | BM71-109-427    | 500             | 38.10              | 101.60              | 38.10                  | 50 Pair Copper, 24 Pair Fibre, Backbone cable                         | 37                                    | 16                              |
| ✗       | M71-109-427     | 100             | 38.10              | 101.60              | 38.10                  | 50 Pair Copper, 24 Pair Fibre, Backbone cable                         | 37                                    | 16                              |

Order references beginning with "B" indicate bulk rolls.

## TubeSleeve Carriers


Brady TubeSleeve Carriers are the ideal complement to self-laminating labels, where the cables are thin and available space for text is small. Apply the tubesleeve to the cable and then apply the self-lam. The limited available space is increased significantly, giving you the possibility of printing more text.

| Order Reference | Sleeves Per Pack | Min. Cable Diameter (mm) | Max. Cable Diameter (mm) | Recommended Label |
|-----------------|------------------|--------------------------|--------------------------|-------------------|
| BTS1426         | 1000             | 1.00                     | 4.00                     | M71-31-427        |
| BTS4626         | 1000             | 4.00                     | 6.00                     | M71-31-427        |
| BTS6826         | 400              | 6.00                     | 8.00                     | M71-23-423        |
| BTS81226        | 250              | 8.00                     | 12.00                    | M71-23-423        |



## Fibre Optic Labels/Flags


### • B-425 Polypropylene



| Diagram | Order Reference | Labels Per Roll | Label Width A (mm) | Label Height B (mm) | Application  | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|---------|-----------------|-----------------|--------------------|---------------------|--------------|---------------------------------------|---------------------------------|
| T       | M71FT-1-425     | 250             | 30.00              | 20.00               | Fibre Strand | 24                                    | 8                               |
| P       | M71FP-1-425     | 250             | 30.00              | 20.00               | Fibre Strand | 24                                    | 8                               |
| P       | M71FP-2-425     | 250             | 44.45              | 25.40               | Fibre Strand | 35                                    | 10                              |

## Power and Ground Cable Tags

- **B-109 Polyethylene:** Extreme tear resistance
- **B-145 Polyethylene:** Tear resistant and 2-side printable
- **B145FR Polyethylene:** Tear resistant, 2-side printable and flame retardant




| Diagram | Order Reference  | Tags Per Roll | Colour | Width A (mm) | Height B (mm) | Write-on Area W x H (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points | Application                                  |
|---------|------------------|---------------|--------|--------------|---------------|--------------------------|---------------------------------------|---------------------------------|----------------------------------------------|
| ⊙       | BM71-12-109      | 1000          | White  | 19.05        | 76.20         | 17.78 x 52.07            | 45                                    | 6                               | Communications Cables, Power & Ground Cables |
| ⊙       | M71-12-109       | 100           | White  | 19.05        | 76.20         | 17.78 x 52.07            | 45                                    | 6                               | Communications Cables                        |
| ●       | M71-36-109       | 250           | White  | 44.45        | 28.58         | 44.45 x 28.57            | 40                                    | 15                              | Cable Labels                                 |
| ●       | BM71-111-145-GY  | 1000          | Grey   | 30.63        | 19.25         | 19.25 x 30.63            | 16                                    | 14                              | Cable Labels                                 |
| ●       | M71-111-145FR-GY | 100           | Grey   | 30.63        | 19.25         | 19.25 x 30.63            | 16                                    | 14                              | Cable Labels                                 |
| ●       | M71-111-145-GY   | 100           | Grey   | 30.63        | 19.25         | 19.25 x 30.63            | 16                                    | 14                              | Cable Labels                                 |
| ●       | M71-110-145FR-GY | 100           | Grey   | 44.45        | 25.40         | 44.45 x 25.40            | 28                                    | 20                              | Cable Labels                                 |
| ●       | BM71-110-145-GY  | 1000          | Grey   | 44.45        | 25.40         | 44.45 x 25.40            | 28                                    | 20                              | Cable Labels                                 |
| ●       | M71-110-145-GY   | 100           | Grey   | 44.45        | 25.40         | 44.45 x 25.40            | 28                                    | 20                              | Cable Labels                                 |

Order references beginning with "B" indicate bulk rolls.

# Datacom Labels

## Workstation Labels

- B-412 Polypropylene
- B-422 Permanent Glossy Polyester
- B-430 Clear Polyester




| Diagram | Order Reference | Labels Per Roll | Label Width A (mm) | Label Height B (mm) | Application                        | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|---------|-----------------|-----------------|--------------------|---------------------|------------------------------------|---------------------------------------|---------------------------------|
| ▲       | M71-16-430      | 500             | 25.40              | 9.53                | Location ID, 1-4 Outlet Faceplates | 24                                    | 3                               |
| ▲       | M71-17-430      | 500             | 25.40              | 12.70               | Location ID, 1-4 Outlet Faceplates | 24                                    | 5                               |
| ■       | BM71-40-412     | 5000            | 49.23              | 9.53                | Desi-Strip Inserts                 | 40                                    | 3                               |
| ■       | M71-40-412      | 750             | 49.23              | 9.53                | Desi-Strip Inserts                 | 40                                    | 3                               |
| ▲       | M71-45-422      | 500             | 38.10              | 9.53                | Location ID                        | 37                                    | 3                               |
| ▲       | M71-45-430      | 500             | 38.10              | 9.53                | Location ID                        | 37                                    | 3                               |
| ▲       | M71-68-430      | 750             | 6.10               | 3.81                | Siemon Faceplates                  | 4                                     | 2                               |
| ▲       | M71-71-430      | 750             | 8.89               | 5.08                | Siemon Faceplates                  | 7                                     | 2                               |

Order references beginning with "B" indicate bulk rolls.

## Patch Panel Identification

- B-412 Polypropylene Tag
- B-422 Permanent Glossy Polyester
- B-423 Permanent Polyester
- B-430 Permanent Clear Polyester





| Diagram | Order Reference | Tags Per Roll | Label Width A (mm) | Label Height B (mm) | Application                                      | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|---------|-----------------|---------------|--------------------|---------------------|--------------------------------------------------|---------------------------------------|---------------------------------|
| ▲       | M71-10-423      | 750           | 19.05              | 6.35                | Patch Panel - ID Port, Voice/Data Identification | 18                                    | 2                               |
| ●       | M71C-230-412    | 1 (cont.)     | 5.84               | 15.24 m             | Broadcast Patch Bay Strips                       | 50                                    | 4                               |
| ●       | M71C-375-412    | 1 (cont.)     | 9.53               | 15.24 m             | Broadcast Patch Bay Strips                       | 50                                    | 3                               |
| ●       | M71C-375-422    | 1 (cont.)     | 9.53               | 15.24 m             | Outlet, Pach panel, Cont. Tape, Cut to size      | 50                                    | 3                               |
| ●       | M71C-375-430    | 1 (cont.)     | 9.53               | 15.24 m             | Outlet, Pach panel, Cont. Tape, Cut to size      | 50                                    | 3                               |
| ●       | M71C-475-412    | 1 (cont.)     | 12.70              | 15.24 m             | Broadcast Patch Bay Strips, Racks& Panels        | 50                                    | 4                               |
| ●       | M71C-500-412    | 1 (cont.)     | 12.70              | 15.24 m             | Broadcast Patch Bay Strips                       | 50                                    | 5                               |
| ●       | M71C-500-422    | 1 (cont.)     | 12.70              | 15.24 m             | Outlet, Pach panel, Cont. Tape, Cut to size      | 50                                    | 5                               |
| ●       | M71C-500-430    | 1 (cont.)     | 12.70              | 15.24 m             | Outlet, Pach panel, Cont. Tape, Cut to size      | 50                                    | 5                               |
| ●       | M71C-785-412    | 1 (cont.)     | 19.94              | 15.24 m             | Broadcast Patch Bay Strips                       | 50                                    | 8                               |



For more information on our materials or to help you choose, visit [www.bradyeurope.com](http://www.bradyeurope.com)

## Racks, Panels and General Identification

- B-412 Polypropylene Tag
- B-422 Permanent Glossy Polyester
- B-423 Permanent Polyester
- B-430 Permanent Clear Polyester



| Diagram | Order Reference | Labels Per Roll | Label Width A (mm) | Label Height B (mm) | Application                                        | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points |
|---------|-----------------|-----------------|--------------------|---------------------|----------------------------------------------------|---------------------------------------|---------------------------------|
| ▲       | BM71-20-422     | 1000            | 50.80              | 25.40               | Racks, Panels & General ID                         | 46                                    | 10                              |
| ▲       | M71-20-483      | 100             | 50.80              | 25.40               | Racks, Panels & General ID                         | 46                                    | 10                              |
| ▲       | M71-23-483      | 100             | 101.60             | 25.40               | Racks, Panels & General ID                         | 50                                    | 9                               |
| ▲       | M71-30-483      | 250             | 38.10              | 19.05               | Racks, Panels & General ID                         | 37                                    | 8                               |
| ▲       | M71-31-483      | 250             | 38.10              | 25.40               | Racks, Panels & General ID                         | 37                                    | 10                              |
| ▲       | M71-37-422      | 100             | 76.20              | 48.26               | Racks, Panels & General ID                         | 50                                    | 20                              |
| ▲       | M71-37-483      | 100             | 76.20              | 48.26               | Racks, Panels & General ID                         | 50                                    | 20                              |
| ▲       | M71-38-483      | 100             | 101.60             | 48.26               | Racks, Panels & General ID                         | 50                                    | 20                              |
| ▲       | M71-61-483      | 100             | 12.70              | 50.80               | Racks, Panels & General ID                         | 50                                    | 5                               |
| ▲       | M71-65-483      | 250             | 34.93              | 25.40               | Racks, Panels & General ID                         | 35                                    | 10                              |
| ●       | M71C-230-412    | 1 (cont.)       | 5.84               | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 2                               |
| ●       | M71C-375-412    | 1 (cont.)       | 9.53               | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 3                               |
| ●       | M71C-375-422    | 1 (cont.)       | 9.53               | 15.24 m             | Closet Hardware Labels, Racks, Panels & General ID | 50                                    | 3                               |
| ●       | M71C-375-430    | 1 (cont.)       | 9.53               | 15.24 m             | Closet Hardware Labels, Racks, Panels & General ID | 50                                    | 3                               |
| ●       | M71C-500-412    | 1 (cont.)       | 12.70              | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 5                               |
| ●       | M71C-500-422    | 1 (cont.)       | 12.70              | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 5                               |
| ●       | M71C-500-430    | 1 (cont.)       | 12.70              | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 5                               |
| ●       | M71C-500-483    | 1 (cont.)       | 12.70              | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 5                               |
| ●       | M71C-785-412    | 1 (cont.)       | 19.94              | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 8                               |
| ●       | M71C-1000-422   | 1 (cont.)       | 25.40              | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 10                              |
| ●       | M71C-1000-430   | 1 (cont.)       | 25.40              | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 5                               |
| ●       | M71C-1000-483   | 1 (cont.)       | 25.40              | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 10                              |
| ●       | M71C-1900-483   | 1 (cont.)       | 48.26              | 15.24 m             | Racks, Panels & General ID                         | 50                                    | 10                              |

Order references beginning with "B" indicate bulk rolls.

## Bulk Packaging



Bulk labels are designed for the BMP™71 Label Printer as a cost-effective solution for high volume labelling needs.

Order references beginning with "B" indicate bulk rolls.



# Circuit Board and Component Identification Labels

## Material to Circuit Board Process Cross Reference Guide






| Brady material number (B-number) |       |        |       | Through Hole Technology |        | Surface Mount Technology (SMT) | After Process |
|----------------------------------|-------|--------|-------|-------------------------|--------|--------------------------------|---------------|
|                                  |       |        |       | Top                     | Bottom | Top or Bottom                  |               |
| B-426                            | B-457 | B-478  | B-479 | ✓ YES                   | ✓ YES  | ✓ YES                          | ✓ YES         |
| B-422                            | B-423 | B-428  | B-437 | ✓ YES*                  | ✗ NO   | ✗ NO                           | ✓ YES         |
| B-459                            | B-473 | B-498* |       |                         |        |                                |               |

\*In extreme high temperatures, testing of these materials is recommended.

### Polyimides

- **B-426 High Temperature Amber Polyimide:**  
Withstands extremely high temperatures
- **B-457 High Temperature White Polyimide:**  
good contrast and smear resistance
- **B-477 Static Dissipative Polyimide:**  
Static dissipative adhesive and liner
- **B-478 Static Dissipative Polyimide:**  
Static dissipative adhesive and liner; low profile






| Order Reference | Labels Per Roll | Width A (mm) | Height B (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points | Max. Bar Code Characters** | Through Hole Technology Top | Through Hole Technology Bottom | SMT Top/Bottom | After Process |
|-----------------|-----------------|--------------|---------------|---------------------------------------|---------------------------------|----------------------------|-----------------------------|--------------------------------|----------------|---------------|
| M71-2-477       | 100             | 6.35         | 50.80         | 41                                    | 2                               | 23*                        | ✓                           | ✓                              | ✓              | ✓             |
| M71-3-457       | 500             | 9.53         | 9.53          | 7                                     | 3                               | 1                          | ✓                           | ✓                              | ✓              | ✓             |
| M71-4-478       | 500             | 10.16        | 10.16         | 8                                     | 4                               | 2                          | ✓                           | ✓                              | ✓              | ✓             |
| M71-9-426       | 750             | 16.51        | 5.08          | 13                                    | 2                               | 5*                         | ✓                           | ✓                              | ✓              | ✓             |
| M71-9-478       | 750             | 16.51        | 5.08          | 13                                    | 2                               | 5*                         | ✓                           | ✓                              | ✓              | ✓             |
| M71-10-457      | 750             | 19.05        | 6.35          | 15                                    | 2                               | 6*                         | ✓                           | ✓                              | ✓              | ✓             |
| M71-13-426      | 750             | 22.86        | 6.35          | 18                                    | 2                               | 8*                         | ✓                           | ✓                              | ✓              | ✓             |
| M71-14-477      | 750             | 25.40        | 4.75          | 20                                    | 1                               | 10                         | ✓                           | ✓                              | ✓              | ✓             |
| M71-16-426      | 500             | 25.40        | 9.53          | 20                                    | 4                               | 10                         | ✓                           | ✓                              | ✓              | ✓             |
| M71-16-457      | 500             | 25.40        | 9.53          | 20                                    | 4                               | 10                         | ✓                           | ✓                              | ✓              | ✓             |
| M71-17-426      | 500             | 25.40        | 12.70         | 20                                    | 5                               | 10                         | ✓                           | ✓                              | ✓              | ✓             |
| M71-25-478      | 750             | 31.75        | 6.35          | 26                                    | 2                               | 13*                        | ✓                           | ✓                              | ✓              | ✓             |
| M71-28-426      | 750             | 38.10        | 6.35          | 31                                    | 2                               | 17*                        | ✓                           | ✓                              | ✓              | ✓             |

\*No human readable characters below / above barcode

\*\*Values for barcode 128, width 2 Dot, ratio 2:1

### Tedlar®

- **B-437 Flame-Retardant White Tedlar®**



| Order Reference | Labels Per Roll | Width A (mm) | Height B (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points | Max. Bar Code Characters** | Through Hole Technology Top | Through Hole Technology Bottom | SMT Top/Bottom | After Process |
|-----------------|-----------------|--------------|---------------|---------------------------------------|---------------------------------|----------------------------|-----------------------------|--------------------------------|----------------|---------------|
| M71-10-437      | 750             | 19.05        | 6.35          | 15                                    | 2                               | 6*                         | ✓                           | ✗                              | ✗              | ✓             |
| M71-15-437      | 750             | 25.40        | 6.99          | 20                                    | 2                               | 10*                        | ✓                           | ✗                              | ✗              | ✓             |
| M71-29-437      | 500             | 38.10        | 12.70         | 31                                    | 5                               | 17                         | ✓                           | ✗                              | ✗              | ✓             |

Tedlar® is a registered trademark of DuPont.

\*No human readable characters below / above barcode

\*\*Values for barcode 128, width 2 Dot, ratio 2:1

✓ Yes, this material will work with this application.




✗ No, this material does not work with this application.

✓ In extreme high temperatures, testing of these materials is recommended.

# Circuit Board and Component Identification Labels

## Vinyl Cloth

- **B-498 White Vinyl Cloth:**  
with repositionable adhesive



| Order Reference | Labels Per Roll | Width A (mm) | Height B (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points | Max. Bar Code Characters** | Through Hole Technology |        | SMT Top/Bottom | After Process |
|-----------------|-----------------|--------------|---------------|---------------------------------------|---------------------------------|----------------------------|-------------------------|--------|----------------|---------------|
|                 |                 |              |               |                                       |                                 |                            | Top                     | Bottom |                |               |
| M71-7-498       | 500             | 12.70        | 12.70         | 10                                    | 5                               | 3                          | ✓                       | ✗      | ✗              | ✓             |
| M71-10-498      | 750             | 19.05        | 6.35          | 15                                    | 2                               | 6*                         | ✓                       | ✗      | ✗              | ✓             |
| M71-16-498      | 500             | 25.40        | 9.53          | 20                                    | 4                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| M71-17-498      | 500             | 25.40        | 12.70         | 20                                    | 5                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| BM71-29-498     | 5000            | 38.10        | 12.70         | 31                                    | 5                               | 17                         | ✓                       | ✗      | ✗              | ✓             |
| M71-29-498      | 500             | 38.10        | 12.70         | 31                                    | 5                               | 17                         | ✓                       | ✗      | ✗              | ✓             |
| M71-32-498      | 250             | 38.10        | 38.10         | 37                                    | 16                              | 17                         | ✓                       | ✗      | ✗              | ✓             |




\*No human readable characters below / above barcode

\*\*Values for barcode 128, width 2 Dot, ratio 2:1

Order references beginning with "B" indicate bulk rolls.

## Polyester

- **B-423, B-459 Permanent White Polyester:**
- **B-428 Permanent Metallised Polyester:**
- **B-473 Static Dissipative Polyester:**  
Static dissipative adhesive and liner



| Order Reference | Labels Per Roll | Width A (mm) | Height B (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points | Max. Bar Code Characters** | Through Hole Technology |        | SMT Top/Bottom | After Process |
|-----------------|-----------------|--------------|---------------|---------------------------------------|---------------------------------|----------------------------|-------------------------|--------|----------------|---------------|
|                 |                 |              |               |                                       |                                 |                            | Top                     | Bottom |                |               |
| M71-1-423       | 750             | 6.35         | 6.35          | 5                                     | 2                               | 0                          | ✓                       | ✗      | ✗              | ✓             |
| M71-2-423       | 100             | 50.80        | 6.35          | 41                                    | 2                               | 23*                        | ✓                       | ✗      | ✗              | ✓             |
| M71-3-423       | 500             | 9.53         | 9.53          | 7                                     | 3                               | 0                          | ✓                       | ✗      | ✗              | ✓             |
| M71-4-423       | 500             | 10.16        | 10.16         | 8                                     | 4                               | 0                          | ✓                       | ✗      | ✗              | ✓             |
| M71-5-423       | 750             | 12.70        | 5.08          | 11                                    | 1                               | 3                          | ✓                       | ✗      | ✗              | ✓             |
| M71-6-423       | 750             | 12.70        | 6.99          | 11                                    | 2                               | 3                          | ✓                       | ✗      | ✗              | ✓             |
| M71-6-473       | 750             | 12.70        | 6.99          | 11                                    | 2                               | 3                          | ✓                       | ✗      | ✗              | ✓             |
| M71-7-423       | 500             | 12.70        | 12.70         | 10                                    | 5                               | 3                          | ✓                       | ✗      | ✗              | ✓             |
| BM71-7-423      | 5000            | 12.70        | 12.70         | 10                                    | 5                               | 3                          | ✓                       | ✗      | ✗              | ✓             |
| M71-9-423       | 750             | 16.51        | 5.08          | 13                                    | 2                               | 5*                         | ✓                       | ✗      | ✗              | ✓             |
| M71-9-473       | 750             | 16.51        | 5.08          | 13                                    | 2                               | 5*                         | ✓                       | ✗      | ✗              | ✓             |
| M71-10-423      | 750             | 19.05        | 6.35          | 15                                    | 2                               | 6*                         | ✓                       | ✗      | ✗              | ✓             |
| M71-10-473      | 750             | 19.05        | 6.35          | 15                                    | 2                               | 6*                         | ✓                       | ✗      | ✗              | ✓             |
| M71-13-423      | 750             | 22.86        | 6.35          | 18                                    | 2                               | 8*                         | ✓                       | ✗      | ✗              | ✓             |
| M71-14-423      | 750             | 25.40        | 4.75          | 20                                    | 1                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| M71-15-423      | 750             | 25.40        | 6.99          | 20                                    | 2                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| M71-15-428      | 750             | 25.40        | 6.99          | 20                                    | 2                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| M71-16-423      | 500             | 25.40        | 9.53          | 20                                    | 4                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| BM71-16-423     | 5000            | 25.40        | 9.53          | 20                                    | 4                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| M71-16-473      | 500             | 25.40        | 9.53          | 20                                    | 4                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| M71-17-423      | 500             | 25.40        | 12.70         | 20                                    | 5                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| BM71-17-423     | 5000            | 25.40        | 12.70         | 20                                    | 5                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| M71-17-428      | 500             | 25.40        | 12.70         | 20                                    | 5                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| M71-17-473      | 500             | 25.40        | 12.70         | 20                                    | 5                               | 10                         | ✓                       | ✗      | ✗              | ✓             |
| M71-19-423      | 250             | 25.40        | 25.40         | 20                                    | 10                              | 10                         | ✓                       | ✗      | ✗              | ✓             |
| BM71-19-423     | 2500            | 25.40        | 25.40         | 20                                    | 10                              | 10                         | ✓                       | ✗      | ✗              | ✓             |
| M71-20-423      | 100             | 50.80        | 25.40         | 41                                    | 10                              | 23                         | ✓                       | ✗      | ✗              | ✓             |
| BM71-20-423     | 1000            | 50.80        | 25.40         | 41                                    | 10                              | 23                         | ✓                       | ✗      | ✗              | ✓             |
| M71-20-459      | 100             | 50.80        | 25.40         | 41                                    | 10                              | 23                         | ✓                       | ✗      | ✗              | ✓             |
| M71-25-423      | 750             | 31.75        | 6.35          | 26                                    | 2                               | 13*                        | ✓                       | ✗      | ✗              | ✓             |
| M71-26-423      | 100             | 69.85        | 31.75         | 57                                    | 12                              | 32                         | ✓                       | ✗      | ✗              | ✓             |
| M71-27-423      | 750             | 38.10        | 3.18          | 31                                    | 1                               | 17                         | ✓                       | ✗      | ✗              | ✓             |
| M71-28-423      | 750             | 38.10        | 6.35          | 31                                    | 2                               | 17                         | ✓                       | ✗      | ✗              | ✓             |
| M71-28-473      | 750             | 38.10        | 6.35          | 31                                    | 2                               | 17                         | ✓                       | ✗      | ✗              | ✓             |
| M71-29-423      | 500             | 38.10        | 12.70         | 31                                    | 5                               | 17                         | ✓                       | ✗      | ✗              | ✓             |
| BM71-29-423     | 5000            | 38.10        | 12.70         | 31                                    | 5                               | 17                         | ✓                       | ✗      | ✗              | ✓             |
| M71-29-459      | 500             | 38.10        | 12.70         | 31                                    | 5                               | 17                         | ✓                       | ✗      | ✗              | ✓             |
| M71-30-459      | 250             | 38.10        | 19.05         | 31                                    | 8                               | 17                         | ✓                       | ✗      | ✗              | ✓             |
| M71-37-423      | 100             | 76.20        | 48.26         | 60                                    | 19                              | 35                         | ✓                       | ✗      | ✗              | ✓             |
| M71-38-423      | 100             | 101.60       | 48.26         | 82                                    | 19                              | 47                         | ✓                       | ✗      | ✗              | ✓             |
| M71C-500-423    | 1 (cont.)       | 12.70        | 15.24 m       | 50                                    | 5                               |                            | ✓                       | ✗      | ✗              | ✓             |

\*No human readable characters below / above barcode

\*\*Values for barcode 128, width 2 Dot, ratio 2:1

Order references beginning with "B" indicate bulk rolls.

✓ Yes, this material will work with this application.



✗ No, this material does not work with this application.

✓ In extreme high temperatures, testing of these materials is recommended.

# Security Identification Labels

## Tamper Indicating Labels

- B-351 Tamper-Resistant White Vinyl
- B-352 Tamper-Resistant Metallised Vinyl
- B-530 Tamper-Resistant White Vinyl



| Diagram | Order Reference | Labels Per Roll | Colour | Width A (mm) | Height B (mm) | Max. Characters per line for 5 Points | Max. Lines of Text for 5 Points | Surface Suitability |
|---------|-----------------|-----------------|--------|--------------|---------------|---------------------------------------|---------------------------------|---------------------|
| ▲       | M71-17-351      | 500             | White  | 25.40        | 12.70         | 20                                    | 5                               | ✓                   |
| ▲       | M71-17-352      | 500             | Silver | 25.40        | 12.70         | 20                                    | 5                               | ✓                   |
| ▲       | M71-20-351      | 100             | White  | 50.80        | 25.40         | 46                                    | 10                              | ✓                   |
| ▲       | M71-20-352      | 100             | Silver | 50.80        | 25.40         | 46                                    | 10                              | ✓                   |
| ▲       | M71-31-351      | 250             | White  | 38.10        | 25.40         | 37                                    | 10                              | ✓                   |
| ▲       | M71-31-352      | 250             | Silver | 38.10        | 25.40         | 37                                    | 10                              | ✓                   |
| ▲       | M71-37-351      | 100             | White  | 76.20        | 48.26         | 50                                    | 20                              | ✓                   |
| ▲       | M71-37-352      | 100             | Silver | 76.20        | 48.26         | 50                                    | 20                              | ✓                   |
| ●       | M71C-500-530    | 1 (cont.)       | White  | 12.70        | 15.24 m       | 50                                    | 2                               | ✓                   |
| ●       | M71C-1000-530   | 1 (cont.)       | White  | 25.40        | 15.24 m       | 50                                    | 5                               | ✓                   |
| ●       | M71C-2000-530   | 1 (cont.)       | White  | 50.80        | 15.24 m       | 50                                    | 10                              | ✓                   |

✓ Material suitable for smooth surfaces.

✓ Material suitable for smooth and textured surfaces.

✓ Material suitable for smooth, textured and highly textured surfaces.


## Laboratory Identification Labels

**F** Freezer  
**N** Liquid nitrogen

**A** Autoclave  
**H** Hot water (100°C) bath

## Self-Laminating Labels

- B-427 Vinyl: excellent abrasion and smudge resistance.
- B-461 Polyester: resistant to extreme temperatures (-196°C to 130°C)




| Diagram | Order Reference | Labels Per Roll | Label Width A (mm) | Label Height B (mm) | Write-On Height C (mm) | Environment    | Application                                        | Vial/Tube size                                          |
|---------|-----------------|-----------------|--------------------|---------------------|------------------------|----------------|----------------------------------------------------|---------------------------------------------------------|
| ✗       | M71-19-427      | 250             | 25.40              | 25.40               | 9.53                   | <b>F N</b>     | Straws                                             | 0.25 mL Straw                                           |
| ✗       | BM71-19-427     | 2500            | 25.40              | 25.40               | 9.53                   | <b>F N</b>     | Straws                                             | 0.2 5mL Straw                                           |
| ✗       | M71-19-427-YL   | 250             | 25.40              | 25.40               | 9.53                   | <b>F N</b>     | Straws                                             | 0.25 mL Straw                                           |
| ✗       | M71-21-427      | 100             | 25.40              | 63.50               | 19.53                  | <b>F N</b>     | Straws                                             | 0.5 ml Straw                                            |
| ✗       | BM71-21-427     | 1000            | 25.40              | 63.50               | 19.53                  | <b>F N</b>     | Straws                                             | 0.5 ml Straw                                            |
| ✗       | M71-21-427-YL   | 100             | 25.40              | 63.50               | 19.53                  | <b>F N</b>     | Straws                                             | 0.5 ml Straw                                            |
| ✗       | M71-30-427-AW   | 250             | 38.10              | 19.05               | —                      | <b>F N</b>     | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0 ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ⊗       | BM71-30-427     | 2500            | 19.05              | 38.10               | 12.70                  | <b>F N</b>     | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0 ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ✗       | BM71-75-461     | 1000            | 66.68              | 25.40               | 25.40                  | <b>F N A H</b> | Cryo Vial                                          | 1.0 - 8.0 ml Vial/Tube                                  |

AW = All White (no transparent area) – YL = Yellow

Order references beginning with "B" indicate bulk rolls.

## Vinyl & Nylon Cloth Labels

- **B-498 Vinyl Cloth:**  
repositionable adhesive
- **B-499 Nylon Cloth:**  
high adhesion




| Diagram | Order Reference | Labels Per Roll | Label Width A (mm) | Label Height B (mm) | Label Diameter C (mm) | Environment | Application                                                   | Vial/Tube size                                                                    |
|---------|-----------------|-----------------|--------------------|---------------------|-----------------------|-------------|---------------------------------------------------------------|-----------------------------------------------------------------------------------|
| ▲       | M71-11-498      | 500             | 12.70              | 19.05               | -                     | F           | Centrifuge, Eppendorf, PCR Tube                               | 0.5 - 0.7ml Tube                                                                  |
| ▲       | BM71-11-498     | 5000            | 12.70              | 19.05               | -                     | F           | Centrifuge, Eppendorf, PCR Tube                               | 0.5 - 0.7ml Tube                                                                  |
| ▲       | M71-11-499      | 500             | 12.70              | 19.05               | -                     | F N A       | Centrifuge, Eppendorf, PCR Tube, Cryo Vial                    | 0.5 - 0.7ml Tube - 0.6ml Vial/Tube                                                |
| ▲       | M71-16-498      | 500             | 9.53               | 25.40               | -                     | F           | Centrifuge, Eppendorf, PCR Tube                               | 0.5 - 0.7ml Tube                                                                  |
| ▲       | M71-16-499      | 500             | 9.53               | 25.40               | -                     | F N A       | Centrifuge, Eppendorf, PCR Tube                               | 0.5 - 0.7ml Tube                                                                  |
| ▲       | M71-17-498      | 500             | 25.40              | 12.70               | -                     | F           | Conical Tube, Bottles, Petri Dish, Deep Well Plate            | 50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate                            |
| ▲       | M71-29-498      | 500             | 38.10              | 12.70               | -                     | F           | Conical Tube, Cryo Vial, Bottles, Petri Dish, Deep Well Plate | 12.0 - 24.0ml Vial/Tube<br>50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ▲       | BM71-29-498     | 5000            | 12.70              | 38.10               | -                     | F           | Cryo Vial, Conical Tube, Bottles, Petri Dish, Deep Well Plate | 12.0 - 24.0ml Vial/Tube<br>50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ▲       | M71-29-499      | 500             | 12.70              | 38.10               | -                     | F N A       | Conical Tube, Cryo Vial, Bottles, Petri Dish, Deep Well Plate | 12.0 - 24.0ml Vial/Tube<br>50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ▲       | M71-30-499      | 250             | 19.05              | 38.10               | -                     | F N A       | Conical Tube, Bottles, Petri Dish, Deep Well Plate            | 50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate                            |
| ▲       | M71-31-498      | 250             | 25.40              | 38.10               | -                     | F           | Conical Tube, Bottles, Petri Dish, Deep Well Plate            | 50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate                            |
| ▲       | M71-31-499      | 250             | 25.40              | 38.10               | -                     | F N A       | Conical Tube, Bottles, Petri Dish, Deep Well Plate            | 50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate                            |
| ▲       | M71-78-499      | 250             | 48.26              | 25.40               | -                     | F N A       | Conical Tube, Bottles, Petri Dish, Deep Well Plate            | 50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate                            |
| ▲       | M71-81-499      | 750             | 48.26              | 6.35                | -                     | F N A       | Well Plate                                                    |                                                                                   |
| ▼       | M71-82-499      | 500             | -                  | -                   | 9.53                  | F N A       | Vial Top                                                      | 0.6 - 1.5ml Vial/Tube                                                             |
| ▼       | M71-83-499      | 500             | -                  | -                   | 9.53                  | F N A       | Vial Top                                                      | 1.0 - 2.0ml Vial/Tube                                                             |
| ▲       | M71-84-499      | 500             | 22.86              | 12.70               | -                     | F N A       | Centrifuge, Cryo Vial, Eppendorf, PCR Tube                    | 0.5 - 0.7ml Tube - 1.5 - 2.0ml Tube<br>0.6 ml Vial/Tube - 1.0 - 8.0ml Vial/Tube   |
| ◆       | M71-98-499      | 500             | 25.40              | 9.53                | 9.53                  | F N A       | Centrifuge, Cryo Vial, Eppendorf, PCR Tube, Vial, Vial Top    | 0.5 - 0.7ml Tube - 1.0 - 8.0ml Vial/Tube<br>0.6 - 1.5ml Vial/Tube                 |

Order references beginning with "B" indicate bulk rolls.

## Polyester Labels

- **B-423 Glossy White Polyester**
- **B-430 Glossy Clear Polyester**
- **B-488 Matt White Polyester**



| Diagram | Order Reference | Labels Per Roll | Label Width A (mm) | Label Height B (mm) | Environment | Application                                        | Vial/Tube size                                          |
|---------|-----------------|-----------------|--------------------|---------------------|-------------|----------------------------------------------------|---------------------------------------------------------|
| ▲       | M71-2-423       | 100             | 50.80              | 6.35                | F A         | Well Plate                                         |                                                         |
| ▲       | M71-7-423       | 500             | 12.70              | 12.70               | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0 ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ▲       | BM71-7-423      | 5000            | 12.70              | 12.70               | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0 ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ▲       | M71-14-423      | 750             | 25.40              | 4.75                | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0 ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ▲       | M71-15-423      | 750             | 25.40              | 6.99                | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0 ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ▲       | M71-17-423      | 500             | 25.40              | 12.70               | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0 ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ▲       | M71-17-430      | 500             | 25.40              | 12.70               | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0 ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ▲       | M71-20-423      | 100             | 50.80              | 25.40               | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate  |
| ▲       | BM71-20-423     | 1000            | 50.80              | 25.40               | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate  |
| ▲       | M71-22-423      | 100             | 76.20              | 25.40               | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0ml Conical Tube/Bottles/Petri Dish/Deep Well Plate  |
| ▲       | M71-31-423      | 250             | 38.10              | 25.40               | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0 ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |
| ▲       | M71-80-488      | 250             | 19.05              | 22.86               | F A         | Slide                                              |                                                         |
| ▲       | M71-81-488      | 750             | 48.26              | 6.35                | F A         | Well Plate                                         |                                                         |
| ▲       | M71-97-488      | 250             | 22.86              | 22.86               | F A         | Slide                                              |                                                         |
| ▲       | M71C-500-430    | 1 (cont.)       | 12.70              | 15.24M              | F A         | Conical Tube, Bottles, Petri Dish, Deep Well Plate | 50.0 ml Conical Tube/Bottles/Petri Dish/Deep Well Plate |

Order references beginning with "B" indicate bulk rolls.

# Brady Corporation

“Our mission is to provide innovative identification solutions which improve safety, security, productivity and performance for customers worldwide.”



## Company Overview

Brady was founded in 1914 in Eau Claire, Wisconsin, as W.H. Brady Co., and renamed Brady Corporation in 1998. The company began selling products internationally in 1947. In 1984, Brady went public, with stock trading on the Nasdaq Stock Market, and in 1999, moved trading of its stock to the New York Stock Exchange, where it trades under the symbol BRC. The company's global headquarters is in Milwaukee, Wisconsin.

## Brady manufactures and markets:

- products for identification and safety applications such as signs and markers, and the printers and software to produce them
- products for wire identification, including labelling materials and tools for wire and cable marking in the electrical and telecommunication markets
- high-performance identification products, including labels and signs that remain legible and highly adhesive even in harsh environments
- precision die-cut parts, including custom die-cut and slit materials for use in cellular phones, pagers, computer disk drives and automotive electronic components

## Operations – Some facts:

- 7000 employees around the world
- Operations in 26 countries
- Distribution in more than 100 countries through more than 4,400 distributor partners



**BRADY Belgium**  
Industriepark C/3  
Lindestraat 20  
9240 Zele  
Tel. +32 (0) 52 45 78 11  
Fax +32 (0) 52 45 78 12

**BRADY Denmark**  
Svendborgvej 39B  
5260 Odense S  
Tel. +45 66 14 44 00  
Fax +45 66 14 44 50

**BRADY France**  
Parc EURO CIT  
45, avenue de l'Europe  
59436 Roncq Cedex  
Tel. +33 (0) 3 20 01 08 70  
Fax +33 (0) 3 20 01 08 76

**BRADY Germany**  
Büchenhöfe 2  
63329 Egelsbach  
Tel. +49 (0) 6103 7598 660  
Fax +49 (0) 6103 7598 670

**BRADY Hungary**  
Puskás Tivadar u. 4.  
2040 Budaörs  
Tel. +36 23 500 275  
Fax +36 23 500 276

**BRADY Italy**  
Via Pitagora 18  
20128 Milano  
Tel. +39 02 26 00 00 22  
Fax +39 02 25 75 351

**BRADY Middle-East**  
PO BOX 18015  
Jebel Ali, Dubai, UAE  
Tel. +971 4881 2524  
Fax +971 4881 3183

**BRADY Norway**  
Breivika Industrivei 9  
6018 Ålesund  
Tel. +47 70 19 10 30  
Fax +47 70 19 05 67

**Brady Slovakia**  
Na Pátoch 18  
831 06 Bratislava  
Tel. +421 2 3300 4800  
Fax +421 2 3300 4801

**BRADY Spain**  
Carretera de Barcelona, 88  
Esc B Entresuelo 9C  
08302 Mataró  
Tel. +34 900 902 993  
Fax +34 900 902 994

**Brady Sweden**  
Vallgatan 5  
170 67 Solna  
Tel. +46 (0) 8 590 057 30  
Fax +46 (0) 8 590 818 68

**BRADY Turkey**  
Selvili Sok. No: 3/4  
4. Levent İstanbul 34330  
Tel. +90 212 264 02 20 / 264 02 21  
Fax +90 212 270 83 19

**BRADY United Kingdom**  
Wildmere Industrial Estate  
Banbury, Oxon – OX16 3JU  
Tel. +44 (0) 1295 228 288  
Fax +44 (0) 1295 228 100

**BRADY WORLDWIDE**

|                        |                 |
|------------------------|-----------------|
| Africa .....           | 971-4881-2524   |
| Australia .....        | 612-8717-6300   |
| Brazil .....           | 55-11-3686-4720 |
| Canada .....           | 1-800-263-6179  |
| China (Beijing) .....  | 86-10-6788-7799 |
| China (Shanghai) ..... | 86-21-6886-3666 |
| China (Wuxi) .....     | 86-510-528-2222 |
| Hong Kong .....        | 852-2359-3149   |
| Japan .....            | 81-45-461-3600  |
| Korea .....            | 82-31-451-6600  |
| Latin America .....    | 1-414-540-5560  |
| Malaysia .....         | 60-4-646-2700   |
| Mexico .....           | 525-399-6963    |
| New-Zealand .....      | 61-2-8717-2200  |
| Philippines .....      | 63-2-658-2077   |
| Singapore .....        | 65-6477-7261    |
| Taiwan .....           | 886-3-327-7788  |
| Thailand .....         | 66-2-793-9200   |
| U.S.A. ....            | 1-800-537-8791  |

Your distributor

