



UNIVERSAL SERIAL BUS: KUSBX-SMT2 Series SMT USB A Type Plug

Product Features

Surface Mount 4 Pin Plug
Available with 1.35mm Plastic Posts
Designed for Use in Dongles and Adapters
CSA/NRTL/US Certified File No. LR78160
UL File No. E134345

Performance Specifications

Materials and Finish

Insulator

PA6T Thermoplastic, UL94V-0 Rated,
Black or White Color

Contacts

Phosphor Bronze

Shell

Steel, Tin Plated

Electrical Characteristics

Rated Voltage

30V AC (RMS)

Rated Current

1A

Contact Resistance

30 milliohms Max.

Insulation Resistance

1000 Megohms Min.

Dielectric Withstanding Voltage

500V AC

Operating Temperature

See Drawing

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-			
Series		Style	Insulator Color	Plating Option

Series

KUSBX - Universal Serial Bus

Style

SMT2-AP5S - SMT Plug with 1.35mm Plastic Posts

Insulator Color Option

B - Black

W - White

Plating Option

Blank - Gold Flash

30 - 30µ" Gold Plating

Contact Kycon for more options

KUSBX-SMT2AP5S Series

Dimensions in mm

