


Specifications:

connector description	dc plug, 5.5x2.5x18.5 mm, molding style, spring contacts, P/N 50-00129
overmold	30P, PVC, black, P/N 24-00006
strain relief	30P, PVC, black, P/N 23-00007
wire description	2C, 18 AWG, UL2468, 300V, 80C, 4.4 mm, VW-1, PVC, 48P, P/N 30-00007
cable outer diameter	Ø4.4 mm
cable color	black
cable length	1830 ± 50 mm
rated current	7 A, 12 Vdc

Notes:

Function test: no open, no reversed polarity, no short circuit, no INT
RoHS compliant

Mechanical drawing:

tolerance X: ± 0.5 mm .X: ± 0.3 mm .XX: ± 0.05 mm
applicable unless otherwise indicated in specification or on drawings

Tensility International Corporation reserves the right to substitute parts which are functionally equivalent to the ones specified.

Initial**Date**

Revision notes:

Rev	Date	Description
A	June 28, 2012	initial release

Specification Approval

Spec sign-off verifies that you have reviewed the entire specification, tested a sample of the product, and confirm that it meets your requirements. This specification reflects the part as it will be ordered. Orders will not be processed until the specification pages have been initialed and the approval page has been signed. This specification is confidential and is not to be transmitted without prior approval from Tensility.

Signature _____

Name _____

Company _____

Title _____

Date _____

Branch _____