






NOTES:

1. MATERIAL: SEE SHEET 3
2. FINISH: NONE
3. PRODUCT SPECIFICATION: NONE
4. PACKAGING PER PK-42400-001
5. HOUSING ACCEPTS 41422 SERIES .250 FEMALE CRIMP TERMINALS AND MATES WITH .250/6.35 WIDE, .31/.79 LONG, .032/0.81 THICK SPADE TERMINALS.
6. SEE SHEET 3 FOR 4-CKT. OPTIONS AND PART NUMBERS.







4-CKT HOUSING

MODIFY 3-CKT VER. EC NO: UCP2009-3090 DRWN:BWIRKUS 2009/06/22 CHKD: 2009/06/22 APPR:BWIRKUS 2009/07/28	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY	DATE	TITLE POWER RECEPTACLE HOUSING 3 & 4 CKT; DUAL FLANGE FOR .250 FEM. FLAT BLADE			
			4 PLACES	± ---	± ---	B. WIRKUS	9-4-2008				
			3 PLACES	± ---	± .005	CHECKED BY	DATE				
			2 PLACES	± 0.13	± .010	B. WIRKUS	9-4-2008				
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE				
			ANGULAR ±1/2°			A. PATEL	9-5-2008	 MOLEX INCORPORATED			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.				DOCUMENT NO.	SHEET NO.
						SEE SHEET 3				SD-42400-001	
B1	REV		SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							




NOTES:

1. MATERIAL: PA6 (NYLON), UL94V-0, BLACK
2. FINISH: NONE
3. PRODUCT SPECIFICATION: NONE
4. PACKAGING PER PK-42400-001
5. HOUSING ACCEPTS 41422 SERIES .250 FEMALE CRIMP TERMINALS AND MATES WITH .250/6.35 WIDE, .31/.79 LONG, .032/0.81 THICK SPADE TERMINALS.
6. SEE SHEET 3 FOR PART NUMBER AND DESCRIPTION.






3-CKT. HOUSING

ADD 2ND FLANGE EC NO: UCP2009-3090 DWN:BWI RKUS CHKD: 2009/06/12 APPR:BWI RKUS 2009/07/28	DESCRIPTION B1	REV	QUALITY SYMBOLS ▽=0 ◇=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
					mm	INCH	DRAWN BY B. WIRKUS	DATE 9-4-2008	TITLE POWER RECEPTACLE HOUSING 3 & 4 CKT; DUAL FLANGE FOR .250 FEM. FLAT BLADE MOLEX MOLEX INCORPORATED	
				4 PLACES	± ---	± ---	CHECKED BY B. WIRKUS	DATE 9-4-2008		
				3 PLACES	± ---	± .005	APPROVED BY A. PATEL	DATE 9-5-2008		
				2 PLACES	± 0.13	± .010	MATERIAL NO. 424003001	DOCUMENT NO. SD-42400-001		
1 PLACE	± 0.25	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	SHEET NO. 2 OF 3				



42400-100* SQUARE PEG OPTION



42400-200* ROUND PEG OPTION

ENG. NUMBER	MATERIAL NO.	NO. OF CKTS.	MATERIAL	COLOR	POLARIZING PEG
42400-0001	006-02-3042	4	PA (NYLON), UL94V-2	NATURAL	NO PEG
42400-0003	424000003	4	PA (NYLON), UL94V-0	WHITE	NO PEG
42400-0004	424000004	4	PA (NYLON), UL94V-0	BLACK	NO PEG
42400-1003	424001003	4	PA (NYLON), UL94V-0	WHITE	SQUARE PEG
42400-1004	424001004	4	PA (NYLON), UL94V-0	BLACK	SQUARE PEG
42400-2001	424002001	4	PA (NYLON), UL94V-2	NATURAL	ROUND PEG
42400-2003	424002003	4	PA (NYLON), UL94V-0	WHITE	ROUND PEG
42400-2004	424002004	4	PA (NYLON), UL94V-0	BLACK	ROUND PEG
42400-3001	424003001	3	PA (NYLON), UL94V-0	BLACK	NO PEG

MODIFY 3-CKT VER EC NO: UCP2009-3090 DRWN:BWIRKUS 2009/06/22 CHKD: 2009/06/22 APPR:BWIRKUS 2009/07/28	QUALITY SYMBOLS =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE IN/MM	SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	TITLE POWER RECEPTACLE HOUSING 3 & 4 CKT, DUAL FLANGE FOR .250 FEM. FLAT BLADE	MOLEX INCORPORATED	DOCUMENT NO. SD-42400-001	SHEET NO. 3 OF 3
B1	REV	DESCRIPTION	MATERIAL NO.	DRAWN BY B. WIRKUS	DATE 9-4-2008	CHECKED BY B. WIRKUS	DATE 9-4-2008	APPROVED BY A. PATEL	DATE 9-5-2008	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[42400-2004](#)