






PCB LAYOUT

NOTES: ALL DIMENSIONS AND NOTES MARKED * ARE CRITICAL AND MUST BE CHECKED IN ACCORDANCE WITH QUALITY DOC. QI-02A

*NOTE: FOR WAYS WITH *PLEASE CHECK WITH TECHNICAL SALES FOR AVAILABILITY

NO. OF WAYS PER ROW	PART NO	DIM (MM)	
		A	B
5	M40-3020546R	4.00	7.30
△* 6	M40-3020646R	5.00	8.30
△* 7	M40-3020746R	6.00	9.30
△* 8	M40-3020846R	7.00	10.30
△* 9	M40-3020946R	8.00	11.30
10	M40-3021046R	9.00	12.30
△ 15	M40-3021546R	14.00	17.30

SPECIFICATIONS:

MATERIAL:-

MOULDING: NYLON 9T, UL94V-0

CONTACT: PHOSPHOR BRONZE, T=0.2MM

FINISH:-

TIN (SEMI GLOSS)

ELECTRICAL:-

CURRENT RATING: 1A AC/DC

WORKING VOLTAGE: 50V AC/DC

WITHSTANDING VOLTAGE: 500V AC/MINUTE

CONTACT RESISTANCE: 20 mΩ MAX.

INSULATION RESISTANCE: 100 MΩ MIN.

ENVIRONMENTAL:-

TEMPERATURE RANGE: -25°C TO +85°C



*NOTE:

REMOVE R FOR LOOSE BAG PACKING

ORDER CODE

M40-302 XX 46R

NO. OF WAYS

WITH R: REEL PACKING

WITHOUT R: LOOSE BAG PACKING

(10pcs Per Strip, 10 Strips per Bag)

Allan	7	28.07.09	A225
Allan	6	06.10.08	A166
Allan	5	25.06.08	A136
Allan	4	25.06.08	A132
Allan	3	19.06.08	A130
Allan	2	29.06.07	A056
Allan	1	01.08.06	-

NAME	ISS.	DATE	C/NOTE
------	------	------	--------

APPROVED:

CHECKED:

DRAWN: Allan

CUSTOMER REF.:

ASSEMBLY DRG:

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.15mm
X.XXX = ±0.08mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE NOTES
FINISH: SEE NOTES
S/AREA: mm²

TITLE:
WAFER 1.00MM DIL
SMT TYPE

DRAWING NUMBER:
M40-302 XX 46R

SHT
1
OF
1