


## Stainless Steel and Brass Marker Plates and Tags

- Provides permanent identification of pipes, conduit, valves, cables and equipment in harsh environments
- Designed for use with Panduit® Pan-Steel® Stainless Steel Cable Ties for fast installation at lowest installed cost
- All marker plates/tags can be embossed or laser etched with Panduit Factory Custom Marking Service


- For on-site custom marking see page E4.6
- Designated plates feature easy feed design with a raised slot to simplify cable tie installation and improve productivity



MMP350-C



MMP350H-C



MMP350DB-C




MMP350W38-C



MMP172-C



MMP172W38-C



MMP350W17-Q

| Part Number            | Material            | Color   | Length/<br>Diameter |      | Width |      | Custom Marking<br>Parameters*                   |                       | Used<br>with<br>Pan-Steel®<br>Cable<br>Ties** | Thickness |      | Std.<br>Pkg.<br>Qty. | Std.<br>Ctn.<br>Qty. |
|------------------------|---------------------|---------|---------------------|------|-------|------|-------------------------------------------------|-----------------------|-----------------------------------------------|-----------|------|----------------------|----------------------|
|                        |                     |         |                     |      |       |      | Max. 3/16"<br>(4.77mm)<br>Character<br>Per Line | Max. Lines<br>of Text |                                               |           |      |                      |                      |
| <b>MMP350-C‡</b>       | 304 Stainless Steel | Natural | 3.50                | 89.0 | 0.75  | 19.0 | 23                                              | 3                     | MLT-S                                         | 0.010     | 0.25 | 100                  | 1000                 |
| <b>MMP350-C316‡</b>    | 316 Stainless Steel | Natural | 3.50                | 89.0 | 0.75  | 19.0 | 23                                              | 3                     | MLT-S                                         | 0.010     | 0.25 | 100                  | 1000                 |
| <b>MMP350H-C‡</b>      | 304 Stainless Steel | Natural | 3.50                | 89.0 | 0.75  | 19.0 | 20                                              | 3                     | MLT-H                                         | 0.010     | 0.25 | 100                  | 1000                 |
| <b>MMP350H-C316‡</b>   | 316 Stainless Steel | Natural | 3.50                | 89.0 | 0.75  | 19.0 | 20                                              | 3                     | MLT-H                                         | 0.010     | 0.25 | 100                  | 1000                 |
| <b>MMP350DB-C‡</b>     | 304 Stainless Steel | Natural | 3.50                | 89.0 | 1.12  | 29.0 | 20                                              | 3                     | MLT-H                                         | 0.015     | 0.38 | 100                  | 1000                 |
| <b>MMP350DB-C316‡</b>  | 316 Stainless Steel | Natural | 3.50                | 89.0 | 1.12  | 29.0 | 20                                              | 3                     | MLT-H                                         | 0.015     | 0.38 | 100                  | 1000                 |
| <b>MMP350W38-C‡</b>    | 304 Stainless Steel | Natural | 3.50                | 89.0 | 0.38  | 10.0 | 23                                              | 1                     | MLT-S                                         | 0.010     | 0.25 | 100                  | 1000                 |
| <b>MMP350W38-C316‡</b> | 316 Stainless Steel | Natural | 3.50                | 89.0 | 0.38  | 10.0 | 23                                              | 1                     | MLT-S                                         | 0.010     | 0.25 | 100                  | 1000                 |
| <b>MMP172-C‡</b>       | 304 Stainless Steel | Natural | 1.72                | 44.0 | 0.75  | 19.0 | 8                                               | 3                     | MLT-S                                         | 0.010     | 0.25 | 100                  | 1000                 |
| <b>MMP172-C316‡</b>    | 316 Stainless Steel | Natural | 1.72                | 44.0 | 0.75  | 19.0 | 8                                               | 3                     | MLT-S                                         | 0.010     | 0.25 | 100                  | 1000                 |
| <b>MMP172W38-C‡</b>    | 304 Stainless Steel | Natural | 1.72                | 44.0 | 0.38  | 10.0 | 8                                               | 1                     | MLT-S                                         | 0.010     | 0.25 | 100                  | 1000                 |
| <b>MMP172W38-C316‡</b> | 316 Stainless Steel | Natural | 1.72                | 44.0 | 0.38  | 10.0 | 8                                               | 1                     | MLT-S                                         | 0.010     | 0.25 | 100                  | 1000                 |
| <b>MMP350W17-Q</b>     | 304 Stainless Steel | Natural | 3.50                | 89.0 | 1.73  | 44.0 | 23                                              | 6                     | MLT-S                                         | 0.015     | 0.38 | 25                   | 250                  |

\*See page E4.2 for Panduit Factory Custom Marking Service information.

\*\*See pages B3.5 – B3.7 for Pan-Steel® Stainless Steel Cable Ties.

‡Easy feed marker plate with raised cable tie slot.

Table continues on page E4.4