







THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

- 1 MATERIAL:
RECEPTACLE HOUSING, UL 94V-0 RATED THERMOPLASTIC, COLOR:SEE TABLE
CONTACT, PHOSPHOR BRONZE
FRONT NUT, UL 94V-0 RATED THERMOPLASTIC, COLOR:SEE TABLE
HEX NUT, BRASS
- 2 FINISH:
CONTACT, 0.75µm MIN. GOLD OVER NICKEL
HEX NUT,NICKEL
- 3 SOLDER TERMINATION CONTACT, 26 AWG WIRE MAX.
- 4 10.0 MAXIMUM PANEL THICKNESS
5. INSTALLS FROM FRONT OR REAR OF PANEL
6. INGRESS PROTECTION: IP50 (MATED)
- 7 PRELIMINARY PART NUMBER.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C3	REVISED PER ECO-11-005027	12MAR2011	RK	HMR



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.L.KOLLER 21JUN2005	 TE Connectivity			
		CHK L.BREKOSKY 28JUN2005				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME RECEPTACLE ASSEMBLY PANEL MOUNT 6 POSITION		RESTRICTED TO -	
		0 PLC ± 1 PLC ±0.2 2 PLC ±0.08 3 PLC ± 4 PLC ± ANGLES ±1° FINISH				
MATERIAL 			SIZE A2		CAGE CODE 00779	
			DRAWING NO C=1877067			
			WEIGHT -			
			CUSTOMER DRAWING		SCALE 5:1	
					SHEET 1 OF 2	
					REV C3	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

AD

00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

40°	BLUE	BLACK	4-1877067-2
	BLUE	GRAY	4-1877067-1
40°	GREEN	BLACK	4-1877067-0
	GREEN	GRAY	3-1877067-9
40°	YELLOW	BLACK	3-1877067-8
	YELLOW	GRAY	3-1877067-7
40°	WHITE	BLACK	3-1877067-6
	WHITE	GRAY	3-1877067-5
40°	RED	BLACK	3-1877067-4
	RED	GRAY	3-1877067-3
40°	BLACK	BLACK	3-1877067-2
	BLACK	GRAY	3-1877067-1
40°	GRAY	BLACK	3-1877067-0
	GRAY	GRAY	2-1877067-9
80°	BLACK	GRAY	2-1877067-8
	GRAY	BLACK	2-1877067-7
0°	BLACK	GRAY	2-1877067-6
	GRAY	BLACK	2-1877067-5
80°	BLUE	BLACK	2-1877067-4
	BLUE	GRAY	2-1877067-3
0°	BLUE	BLACK	2-1877067-2
	BLUE	GRAY	2-1877067-1
80°	GREEN	BLACK	2-1877067-0
	GREEN	GRAY	1-1877067-9
0°	GREEN	BLACK	1-1877067-8
	GREEN	GRAY	1-1877067-7
80°	YELLOW	BLACK	1-1877067-6
	YELLOW	GRAY	1-1877067-5
0°	YELLOW	BLACK	1-1877067-4
	YELLOW	GRAY	1-1877067-3
80°	WHITE	BLACK	1-1877067-2
	WHITE	GRAY	1-1877067-1
0°	WHITE	BLACK	1-1877067-0
	WHITE	GRAY	1877067-9
80°	RED	BLACK	1877067-8
	RED	GRAY	1877067-7
0°	RED	BLACK	1877067-6
	RED	GRAY	1877067-5
80°	BLACK	BLACK	1877067-4
	GRAY	GRAY	1877067-3
0°	BLACK	BLACK	1877067-2
	GRAY	GRAY	1877067-1
KEYING	FRONT NUT COLOR	HOUSING COLOR	PART NUMBER

60°	BLUE	BLACK	5-1877067-6
	BLUE	GRAY	5-1877067-5
60°	GREEN	BLACK	5-1877067-4
	GREEN	GRAY	5-1877067-3
60°	YELLOW	BLACK	5-1877067-2
	YELLOW	GRAY	5-1877067-1
60°	WHITE	BLACK	5-1877067-0
	WHITE	GRAY	4-1877067-9
60°	RED	BLACK	4-1877067-8
	RED	GRAY	4-1877067-7
60°	BLACK	BLACK	4-1877067-6
	BLACK	GRAY	4-1877067-5
60°	GRAY	BLACK	4-1877067-4
	GRAY	GRAY	4-1877067-3

80° KEYING

RECEPTACLE FRONT VIEW

SCALE 4:1

0° KEYING

RECEPTACLE FRONT VIEW

SCALE 4:1

40° KEYING

RECEPTACLE FRONT VIEW

SCALE 4:1

60° KEYING

RECEPTACLE FRONT VIEW

SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R.L.KOLLER
CHK
L.BREKOSKY
APVD
-

21JUN2005
28JUN2005

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.2
2 PLC ±0.08
3 PLC ±
4 PLC ±
ANGLES ±1°
FINISH

PRODUCT SPEC
108-2249
APPLICATION SPEC
114-13184
WEIGHT
-

CUSTOMER DRAWING

NAME
RECEPTACLE ASSEMBLY
PANEL MOUNT
6 POSITION

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-1877067

RESTRICTED TO
-

SCALE
5:1

SHEET
2

OF
2

REV
C3

1471-9 (3/11)