

Strong Tip General Purpose Tweezers

★★★★ High Precision

★★ Fine Precision ★ General Precision

Available in NEVERUST®, S/S Antimagnetic, Carbon Steel.

#10G Design 4 3/8" long
Tapered tips with medium serrated points.

PART #	MATERIAL	STARS
10G-SA	NEVERUST®	★★★★



#8 Design 4 1/4" long
Straight wide body tweezers with flat sharp points.

PART #	MATERIAL	STARS
8-SA-PI	S/S Antimagnetic	★★



#AH Design 5" long
Wide diamond shape tips with sharp serrated points.

PART #	MATERIAL	STARS
AH-SA-SE	S/S Antimagnetic	★



#AA Design 5" long
Straight tips with medium points and vinyl grips.

PART #	MATERIAL	STARS
AA-SA-SE-PH	S/S Antimagnetic	★



#24 Design 6 1/2" long
Angled tips with blunt serrated points and vinyl grips.

PART #	MATERIAL	STARS
24-SA-SE-PH	S/S Antimagnetic	★



★★★★★ Five Star 7000 Series Medium Head Cutters

Made in the U.S.A.

Edge hardened to 63/65 Rockwell "C".

Stainless steel leaf springs – fine cutting of small leads and wires.

WIRE CATCH

add suffix **-W**





7240EW shown

7100 Series Medium Head Cutters with Long Foam Cushion Grips

5 3/4" Medium Round Head Cutters



PART #	CUT TYPE	CUTTING CAPACITY
7140E	Semi-flush	.008" - .042"
7141E	Max flush	.005" - .040"
7142E	Opti-flush	.003" - .032"



7200 Series Medium Head Cutters with ESD Safe Molded Grips



5" Medium Round Head Cutters

PART #	CUT TYPE	CUTTING CAPACITY
7240E	Semi-flush	.008" - .042"
7241E	Max flush	.005" - .040"
7242E	Opti-flush	.003" - .032"




5 3/4" Medium Tapered Head Cutters

PART #	CUT TYPE	CUTTING CAPACITY
7143E	Semi-flush	.008" - .036"
7144E	Max flush	.005" - .036"
7145E	Opti-flush	.002" - .028"





5" Medium Tapered Head Cutters

PART #	CUT TYPE	CUTTING CAPACITY
7243E	Semi-flush	.008" - .036"
7244E	Max flush	.005" - .036"
7245E	Opti-flush	.002" - .028"




5 3/4" Medium Tapered/Relieved Cutters


PART #	CUT TYPE	CUTTING CAPACITY
7146E	Semi-flush	.008" - .036"
7147E	Max flush	.005" - .036"
7148E	Opti-flush	.002" - .028"



5" Medium Tapered/Relieved Cutters

PART #	CUT TYPE	CUTTING CAPACITY
7246E	Semi-flush	.008" - .036"
7247E	Max flush	.005" - .036"
7248E	Opti-flush	.002" - .028"





2629


★★ Stainless Steel Pliers

Small Head Design

Forged stainless steel, Smooth or serrated inside jaws.


4 3/4" Stainless Steel Chain Nose Pliers

PART #	JAW FINISH
2644	Smooth
2644D	Serrated




4 3/4" Stainless Steel Round Nose Pliers

PART #	JAW FINISH
2643	Smooth





4 3/4" Stainless Steel Needle Nose Pliers

PART #	JAW FINISH
2647	Smooth





4 3/4" Stainless Steel Flat Nose Pliers

PART #	JAW FINISH
2642	Smooth




4 3/4" Stainless Steel Needle Nose Pliers

PART #	JAW FINISH
2647D	Serrated



4 1/2" Stainless Steel Bent Nose Pliers

PART #	JAW FINISH
2629	Smooth




★★ Stainless Steel Pliers

Medium Head Design

Forged stainless steel, ESD Safe molded grips, smooth or serrated inside jaws.


5 3/4" Stainless Steel Chain Nose Pliers

PART #	JAW FINISH
2844	Smooth
2844D	Serrated




5 3/4" Stainless Steel Flat Nose Pliers

PART #	JAW FINISH
2842	Smooth
2842D	Serrated




5 1/2" Stainless Steel Needle Nose Pliers

PART #	JAW FINISH
2847	Smooth
2847D	Serrated




5 3/4" Stainless Steel Bent Nose Pliers

PART #	JAW FINISH
2829	Smooth




5 3/4" Stainless Steel Round Nose Pliers

PART #	JAW FINISH
2843	Smooth



5 3/4" Stainless Steel "Duck Bill" Pliers

PART #	JAW FINISH
2818	Smooth



Scissors – Scalpels

★★★★★ **High Quality Scissors - Medical Grade - Made in Switzerland**

★★★★★ **Scalpel Blades and Handles - Made in Germany**

★★★★★ **Safety Scalpels - Made in United Kingdom**

361 ★★★★★

3 ¼" Extra Fine Blade Medical Scissors.

Stainless Steel with ¾" Curved Blade.
Ideal for ultra miniature work and in
confined areas. Made in Switzerland.



362 ★★★★★

3 ¼" Fine Blade Medical Scissors.

Stainless Steel with 7/8" Curved Blade.
Thin blades for close tolerance cutting.
Made in Switzerland.



363 ★★★★★

3 ¾" Round Blade Medical Scissors.


Stainless Steel with 1 ¼" Curved Blade.
A heavy duty miniature scissor for general
use. Made in Switzerland.



364 ★★★★★

3 ¾" Fine Blade Medical Scissors.

Stainless Steel with 1 ¼" Curved Blade.
Ideal for delicate applications where
small strong blades are required. Made in
Switzerland.




Medical Scalpels

Scalpel Handles & Blade Removers


177 ★★★★★

5" Scalpel Handle made of Stainless Steel
with outside finger serrations for positive
gripping and easy use. Cleanroom safe,
fits scalpel blades numbers **177-10**,
177-11, **177-12**, **177-15**.



175-11 ★★★★★

The Safety Scalpel has a smaller handle
to fit between your thumb and index
finger. It's easy to use and comes with a
number 11 style blade and safety cover.



177A ★★★★★

Scalpel Blade Remover is safe and easy
to use.



For use with 177 Scalpel Handle.

Scalpel Blades

177-10 ★★★★★

**Large Round Stainless Steel
Scalpel Blade.**



177-11 ★★★★★

**Angled Stainless Steel
Scalpel Blade.**



177-12 ★★★★★

**Curved Stainless Steel
Scalpel Blade.**



177-15 ★★★★★

**Fine Stainless Steel
Scalpel Blade.**

