




Specifications
 Current Rating: 1.0A AC/DC
 Voltage Rating: 30V AC/DC
 Contact Resistance: 20m ohm. Max.
 Insulation Resistance: 1000M ohm. Min.
 Withstanding Voltage: 750V AC For One Minute
 Operating Temperature Range: -40°C to +105°C
 Material and Finish
 Insulator: Higt Temp. Plastic (PBT UL94V-0)
 Contact: Copper Alloy
 Finish: Selective Plated Gold 1u" Tin 100u"
 Over nickel 50u"
 Shell: Tin Plated 100u"
 How To Order
 5075AR-04-XX-XX-F1

Lead Free
 Standard Selective Plated
 15: Selective Gold Plated 15u"
 30: Selective Gold Plated 30u"
 BK: Black
 WH: White



PCB LAYOUT
 TOLERANCE: ±0.10

SECTION A-A

DRAWN:
 Jeremy Liu

CHECKED:
 Jerry Chen

APPROVAL:
 Mike Wu

GENERAL TOLERANCE:
 .X=±0.20
 .XX=±0.15

UNIT: MM
 SCALE: 1:1

SHEET: 1 / 1
 PROJECTION:



繼德工業股份有限公司
 Netron Industrial Co., Ltd.

DESCRIPTION:

USB A Type PCB Female Right Angle

PART NO:

5075AR-04-XX-XX-F1

SIZE

A4

RoHS Compliant

REV	DATE	FILE	BY
B	14-Sep-2006	ECN-CN060906	Wendy
A	02-Aug-2004	(PC0001)	Jeremy Liu

100-317-158

351-413-001