



721

Combustible Gas Leak Detector with LCD Display

Features

- Combustible Gas Leak Detector capable of displaying real ppm, stepped ppm, and %LEL (Lower Explosive Limit).
- 10ppm sensitivity (methane)
- Detect combustible gases including natural gas, propane, butane, etc.
- Thumbwheel adjustable tic rate to locate leaks quickly and accurately.
- Two line display with bargraph and backlight
- Audio / Visual alarm indication with user adjustable alarm point.
- Earphone jack for use in noisy environments.
- Approximately 20 hours of continuous use (C cell alkaline batteries x2)

Specifications

Leak Detection Sensitivity (methane): 10ppm

Display Type: Dual display with analog bargraph and backlight

Display Modes: Real (ppm), Leak Level (stepped ppm), %LEL

Ranges:

Real ppm: 0 to 9999ppm

Stepped ppm: 0, 500, 1000, 3000, 5000, 9999ppm

%LEL: 0 to 19.9%

Audible Leak Indication: Adjustable tic rate via side thumb wheel

Alarm Indication: Visual and audible (User adjustable alarm level)

Sensor Test and Zero: Automatic at start up

Goose Neck: 16" long with visual alarm indicator in sensor housing



Dimensions

Size: 9.4" x 2.9" x 2.2" (240mm x 74mm x 55mm)

Weight: 1 lb (454g)