


3.5mm 4 Cond Plug

171-7435

KOBI CONN

3.5mm 4 Cond Plug



DIMENSIONS: mm (In.)

SPECIFICATIONS	
Handle:	Polyethylene
Contacts:	Nickel plated brass
Color:	Black
Insulator:	PBT G15%
Recommended Wire:	28 AWG
Insulation resistance:	100 Megaohm min. @ 500VDC
Dielectric Strenght:	500VAC (for one minute)
Mating jacks:	161-6435
	161-5435
	161-7900

Date Last Revised: 3-02-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300338

171-7435

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-7435](#)