



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
▶ 2 mm system
▶ 2 mm safety system
▶ 4 mm system
▶ 4 mm sliding sleeve system
▶ 4 mm safety system
sockets
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ plugs ▶ plugs ▶ SLS 200

SLS 200

datasheet for SLS 200
article number: 932153101



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:		order number: 932 153-101	
description:		Contact protected plug with screw connection for cables up to 2.5 mm², with onward connection capability (4 mm socket).br> Insulated by latching and sprung insulating sleeve, to be released by pressure on the lateral locking spring. plug with contact spring, 4mm diameter.	
typ:		SLS 200 rot/red	
system:		4mm sliding sleeve system	
order number:		932 153-101	
color			
other color versions:			
technical data			
measurement category acc. to IEC 61010:		CAT I	
pin dimensions		4 mm	
type of contact:		pin (spring loaded)	
type of termination:		screw	
rated voltage:		30 VAC / 60 VDC	
rated current:		30 A	
Please consider derating curve!			
contact resistance:		5 mOhm	
material			
contact material:		contact pin: brass contact spring: copper - beryllium	
contact surface material:		nickel	
housing material:		PP	
environmental conditions:			
temperature range:		-25 °C to +80 °C	
drawing			
			