







PCB LAYOUT - COMPONENT VIEW



Pick & Place Pad



MATERIAL:

HOUSING MATERIAL: PA6T
FLAMABILITY RATING: UL94-V0
COLOR: RED
CONTACT MATERIAL: PHOSPHOR BRONZE
CONTACT TYPE: STAMPED
CONTACT PLATING: MATT TIN OVER NICKEL
QUALITY CLASS: 25 MATING CYCLES
PITCH; 2.54 MM PER ROW

ENVIRONNEMENTAL:

OPERATING TEMPERATURE: -40°C UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL:

CURRENT RATING: 1.5A PER PIN (PCB PIN)
WORKING VOLTAGE: 100VAC
INSULATION RESISTANCE: >1000MOHM
DIELECTRIC WITHSTANDING VOLT.: 500VAC/MN
CONTACT RESISTANCE: 10mOHM MAX

STANDARD

RoHS CERTIFIED: E323964 / MOD. NUMBER 69035728xx7x

SOLDERING:

REFLOW PROCESS ONLY

DIMENSION:

DIM.A= 1.27 x No. of Spaces
DIM.B= DIM.A + 3.30
DIM.C= DIM.A + 4.30

AVAILABLE


xx : 4 TO 26 CIRCUITS

PACKAGING:

TAPE & REEL

RoHS Compliant

PROJECTION:



GENERAL TOLERANCE

.X = ± 0.2

.XX = ± 0.15



APPROVAL: RJ

UNIT: MM

SCALE:

SHEET: 1/2


DRAW: EAGER


DESCRIPTION: MM MALE SMT CONNECTOR WITHOUT LATCH AND WITHOUT POLARIZATION

WERI PART NO: 690 357 28 xx 76

SIZE

A4



RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15	 WÜRTH ELEKTRONIK		
G								
F								
E								
D								
C				APPROVAL: RJ	UNIT: MM	DESCRIPTION: MM MALE SMT CONNECTOR WITHOUT LATCH AND POLARIZATION	SIZE	
B					SCALE:			
A					SHEET: 2/2			WERI PART NO: 690 357 28 xx 76
REV	DATE	FILE	BY		DRAW: EAGER			