

Vises, Work Holding Tools

PanaPress. Mini Arbor Press

Mobile Electronics Mounts

InDash Custom Dash Mounts

iPod-iPhone Holders-Mounts

Smartphone Accessories

Smartphone Screen Protectors

CCTV, Security Camera Mounts

Audio/Video Mounts

Model: 883-03 Dual Option Mount, 3" (Black)

AVOID SURPRISES...WITH TWO MOUNTING OPTIONS, WE'VE GOT YOU COVERED!

You'll never be without the right mount when you take along Dual Option Mounts from PanaVise.

- 3" (76.2mm) overall mount length
- Includes two mounting bases that screw easily into the machined aluminum alloy shaft [0.875" (22.2mm) in diameter]
- Use the Tri-Foot Base [4" (101.6mm) outside diameter with three 0.265" (6.7mm) holes on a 3.25" (82.5mm) bolt circle] for solid surfaces, or the T-Bar Clip for drop ceiling rails
- Full range of motion at the camera: 210° Tilt, 360° Turn & 360° Rotation
- Knob and tamper-resistant set-screw adjusting options included
- 1/4-20 mounting stud with lockring



Quantity



Click on any of the above images to find out more about the products pictured.