

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190670084](#)
Status: **Active**
Description: NylaKrimp™ Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud #8

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Ring and Spade Terminals
Series [19067](#)
Mil-Spec N/A
Product Name NylaKrimp™
Type Ring

Physical
Barrel Type Closed - Brazed
Flammability 94V-0
Insulation Nylon (PA)
Material - Plating Mating Tin
Packaging Type Bag
Plating min: Mating (µin) 100
Plating min: Mating (µm) 2.5
Plating min: Termination (µin) 100
Plating min: Termination (µm) 2.5
Stud Size 5/16" (M8)
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 12.95mm (.510") max.
Wire Size AWG 4

Electrical
CSA LR18689
UL E32244

Material Info
Old Part Number F-967-56

Reference - Drawing Numbers
Sales Drawing SD-19067-018




image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19067Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Putt Pump Dieless Head System	0192860065
Die Set (large) for the HHLS Hydraulic Crimper	0192890007
Hand Crimp Tool	0640013900
Manual Putt Pump Hydraulic System, Die set required	0192860117

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION