


Ferrite Chip Beads provide an effective means of EMI/RFI attenuation for electronic equipment. These items are specially designed for flow, reflow, and wave soldering applications.



Dimensions (In.)

Specifications:

- Impedance tolerance (Ω): $120 \pm 25\%$ @ 100MHz
- DC resistance: $.60\Omega$ max.
- Rated current: 200mA (max.)
- Operating temperature: $-25^\circ\text{C} \sim 85^\circ\text{C}$
- Storage temperature: $-40^\circ\text{C} \sim 85^\circ\text{C}$

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[436-1121](#)