

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0529210804](#)
Status: **Obsolete**
Description: 0.635mm (.025") Pitch SlimStack™ Receptacle, Surface Mount, Dual Row, Vertical Stacking, 3.00mm (.118") Stacking Height, Tube or Embossed Tape or Embossed Tape with Cover Packaging, 80 Circuits
Replacement Part Number: [529210874](#)

Documents:
[Drawing \(PDF\)](#)

General

Product Family	PCB Receptacles
Series	52921
Application	Board-to-Board, Signal
Comments	Stacking-Type Solder Tab Plating: Tin-Lead
Product Name	SlimStack™
Replacement Part Number	529210874

Physical

Circuits (Loaded)	80
Durability (mating cycles max)	50
Glow-Wire Compliant	No
Mated Height	3.00mm (.118")
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.64mm (.025")
Polarized to PCB	Yes
Robotic Placement	Vacuum Pick-Up Tape
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Surface Mount


Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	100V

Material Info

Reference - Drawing Numbers

Product Specification	PS-52921-001
Sales Drawing	SD-52921-***2, SD-52921-***4



EU RoHS

Not RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[52921Series](#)

Mates With

[53671](#)