


Bits and Sleeves



Standard Wrap



Modified Wrap

All bits and sleeves listed below fit the universal collet as fitted to the tools opposite.

| Wire Size<br>AWG   | Terminal<br>Min. | Diagonal<br>Max. | Terminal<br>Hole<br>Depth | BIT                |            | SLEEVE             |            |
|--------------------|------------------|------------------|---------------------------|--------------------|------------|--------------------|------------|
|                    |                  |                  |                           | Mftrs.<br>List No. | Order Code | Mftrs.<br>List No. | Order Code |
| Standard Wrap      |                  |                  |                           |                    |            |                    |            |
| 22                 | 1.55             | 2.18             | 25.4                      | 18632              | 147-841    | 18840              | 147-842    |
| 24                 | 1.4              | 1.88             | 25.4                      | 512058             | 147-845    | 512056             | 147-846    |
| 26                 | 1.47             | 1.88             | 25.4                      | 504910             | 147-847    | 512056             | 147-846    |
| Modified wrap      |                  |                  |                           |                    |            |                    |            |
| 24                 | 1.33             | 1.88             | 28.8                      | 26263              | 147-848    | 18840              | 147-842    |
| 26                 | 0.58             | 0.99             | 19.1                      | 506445             | 147-849    | 507100             | 147-850    |
| 26                 | 1.35             | 1.75             | 25.4                      | 502118             | 147-851    | 512056             | 147-846    |
| 30                 | 0.79             | 0.86             | 19.1                      | 507063             | 147-853    | 507100             | 147-850    |
| 30                 | 0.84             | 0.91             | 19.1                      | 507573             | 147-854    | 507100             | 147-850    |
| Cut Strip and Wrap |                  |                  |                           |                    |            |                    |            |
| 30                 | 0.76             | 0.86             | 25.4                      | 990764             | 109-261    | 990765             | 109-365    |

222653,401577

222653,401577

| BITS               |            | SLEEVES    |            |
|--------------------|------------|------------|------------|
| Standard Wrap      | Order Code | Order Code | Price Each |
| 22AWG              | 147-841    | 147-842    |            |
| 24AWG              | 147-845    | 147-846    |            |
| 26AWG              | 147-847    | 147-846    |            |
| Modified Wrap      |            |            |            |
| 24AWG              | 147-848    | 147-842    |            |
| 26AWG              | 147-849    | 147-850    |            |
| 26AWG              | 147-851    | 147-846    |            |
| 30AWG              | 147-853    | 147-850    |            |
| 30AWG              | 147-854    | 147-850    |            |
| Cut Strip and Wrap |            |            |            |
| 30AWG              | 109-261    | 109-365    |            |