




G3G225 Series Centrifugal Blower

Ø 225mm EC-Systems™


- AC input, single inlet, forward-curved centrifugal blower with integrated electronics.
- Cable exit: variable
- Scroll housing and impeller made of galvanized sheet steel.
- Variable mounting position.
- Direction of rotation is CW as seen from intake side.
- Maintenance-free ball bearings.
- Technical features: integrated electronics, PWM/Linear input, alarm relay.
- UL and CSA approvals on request.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Wgt. (lbs)
G3G225-AD29-71	1	988.8	200-277	50/60	570	75	60	Ball	Leads	16.54



		n [RPM]	P ₁ [W]	I [A]	η _{IL} [%]	Lp _A [dBA]			n [RPM]	P ₁ [W]	I [A]	η _{IL} [%]	Lp _A [dBA]
1	①	—	—	—	—	—	1	⑨	1300	290	1.70	—	71
1	②	1750	560	3.30	51	75	1	⑩	1300	225	1.40	51	66
1	③	1830	475	2.80	60	73	1	⑪	1300	170	1.10	60	63
1	④	1970	335	2.10	59	72	1	⑫	1300	108	0.70	59	61
1	⑤	1610	570	3.40	—	76	1	⑬	1000	140	0.90	—	64
1	⑥	1610	430	2.50	51	72	1	⑭	1000	105	0.70	51	60
1	⑦	1610	325	1.90	60	69	1	⑮	1000	84	0.60	60	56
1	⑧	1610	195	1.20	59	66	1	⑯	1000	55	0.40	59	54

Curve



ebmpapst

e-mail: sales@us.ebmpapst.com · TEL: 860-674-1515 · FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2006 © ebm-papst Inc. reserves the right to change any specifications or data without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[G3G225-AD29-71](#)