


- About Leviton
- A Century of Success
- Press
- Join Our eMailing List
- Trade Shows
- RoHS
- Career Opportunities
- Contact Us
- All Leviton Products
- Electrical
- Network Solutions
- Lighting Controls
- Entertainment
- Home Automation
- Connected Home
- Energy Management
- Power Quality
- Library Home
- Application Notes
- Brochures / Catalogs
- Case Studies
- DDLs
- Downloads
- Drawings
- Line Cards
- Manuals / Instructions
- Product Specifications / Datasheets
- Software
- Specs (AIA / CSI)
- Take One
- Tech Notes
- Technical Articles
- Videos
- ez-Biz
- ez-Find
- ez-Learn
- ez-Configurator
- Distribution Home
- Contractor Connection
- ez-Learn
- ez-Find
- Sign In - B2B
- OEM Home
- How to Buy
- Whats New
- Press/News
- Retail Home
- Product Information
- How To
- Merchandising
- Energy Smart Living
- International Home
- China (English)
- China (Chinese)
- Mexico (English)
- Mexico (Spanish)
- Middle East (English)
- International Contact
- Press
- Products
- Trade Shows
- Made to Order
- EZE-Rough
- Acenti Devices
- AC Switches
- Appliance Switches
- Architectural Controls
- Camera Systems
- Combination Devices
- Connectors & Cables
- Cord Sets
- Corrosion Resistant Devices
- Daylighting Controls
- Decora Devices
- Dimmers
- Cam-Type Devices
- Electrical Accessories
- Entertainment Accessories
- Entertainment Fixtures
- Entertainment Lighting Controls
- Entertainment Lighting Kits



- Electrical
- Network Solutions
- Lighting Controls
- Entertainment
- Home Automation
- Connected Home
- Energy Management
- Power Quality



ZOOM

Quantity: 1

1221-2KL

Description

20 Amp, 120/277 Volt, Key Locking Single-Pole AC Quiet Switch, Industrial Grade, Self Grounding, Back & Side Wired, - Chrome

Additional Product Information

- [Dimensional Drawing](#)
- [Wiring Diagram](#)

Product Features

Grounding: Self Grounding

Amperage: 20 Amp

Voltage: 120/277 Volt

HP Rating: 1HP-120V 2HP-240V-277V

Max. Amperage: 16 Amp

Termination: Back & Side

Actuator Material: Steel

Body Material: Thermoplastic

Strap Material: Steel

Color: Chrome

Standards and Certifications: UL/CSA

Warranty: 10 Year Limited

Features and Benefits

- Key-operating locking mechanism for maximum tamper-proof operation in schools, institutions, public housing, trailer parks, loading docks, freight yards and other areas
- Chrome lock dome with 2 keys provided per switch
- Back and side wire terminals accept up to #14 - #10 AWG copper or copper clad wire
- Large, slotted terminal screws with external wire clamps
- Triple-combination mounting screws for fast, easy installation
- Heavy-gauge rust-resistant mounting strap with steel grounding screw and self-grounding clip (self grounding when used in a properly grounded metal wallbox)
- Key removable in ON or OFF positions
- Backed by a Limited Ten-Year Warranty