

USB to DC Power Cable – M/M, USB-A to 3.5 x 1.35 mm DC Barrel Plug, 3 ft.

MODEL NUMBER: **U152-003-3P5**



USB to 5V DC power cable powers a 5V DC device using your computer's USB port instead of the device's power supply.

Features

USB to DC Adapter Charges 5V DC Peripherals via USB Port

Now you can power up your external 5V DC devices without having to carry around a bulky DC transformer or find room for it in your surge protector or power strip. This USB to 5V DC power cable connects to your computer or laptop's USB-A port to provide power to operate your device. You can also connect your device to a USB wall charger or car charger. It's recommended for powering devices with a 3.5 x 1.35 millimeter 5V DC barrel jack, such as external hard drives, wireless routers, Bluetooth speakers and credit card readers.

Lifetime Warranty

The U152-003-3P5 is backed by a lifetime warranty, ensuring reliability and performance.

Highlights

- USB to DC adapter powers 5V DC devices through your PC or laptop's USB-A port
- Avoid carrying bulky transformers in your laptop bag or blocking power strip outlets
- Polarity: positive tip, negative sleeve
- Recommended for devices with 3.5 x 1.35 mm barrel connector with positive center pin

Applications

- Power an external hard drive via USB port or hub to avoid blocking outlets on your surge protector with a bulky transformer
- Connect a credit card reader to your laptop to ring up sales
- Charge your wireless speaker through your computer's USB port instead of plugging it into a wall socket

Package Includes

- U152-003-3P5 USB to DC Power Cable – M/M, USB-A to 3.5 x 1.35 mm DC Barrel Plug, 3 ft.

Specifications

OVERVIEW

UPC Code	037332212986
----------	--------------

INPUT

Cable Length (ft.)	3
Cable Length (m)	1
PHYSICAL	
Wire Gauge (AWG)	20
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Weight (lbs.)	0.11
Shipping Weight (kg)	0.05
Unit Packaging Type	Polybag
Material of Construction	PVC
Color	Black
Cable Outer Diameter (OD)	5.0+-0.15mm
Cable Jacket Rating	CMR
ENVIRONMENTAL	
Operating Temperature Range	5 ~ 50C (41 ~ 122F)
Storage Temperature Range	-25 ~ 70C (-13 ~ 158F)
Operating Humidity Range	20% ~ 85% RH
Storage Humidity Range	0% ~ 90% RH
CONNECTIONS	
Side A - Connector 1	(1) USB A (MALE)
Side B - Connector 1	(1) 3.5mm x 1.35mm (5V DC Barrel)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Technology	USB
CERTIFICATIONS	
Certifications	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>