

Datasheet

Item No. 92.042.3353.1

Male connector GST18i4S S1 SW

Device connectors, built-in components, GST18i4, 4 pole, female, screw connection, 250/400V, 16A, color of coding: black



| | |
|------------|---------------|
| Item No. | 92.042.3353.1 |
| EAN | 4015573545946 |
| order unit | 100 Piece(s) |

Approvals



Technical data

General

| | |
|-----------------------------------|---------------------|
| ArticlePrice | udp_no_price |
| Rated current | 20 A |
| Rated voltage | 400 V |
| Pollution degree | 2 |
| Mechanical coding | Yes |
| Rated impulse voltage | 4 kV |
| Interlockable | Yes |
| Color of coding/ contact carrier | Black |
| Connection cross section solid | 2.5 mm ² |
| Cross section solid 2 | 0.5 mm ² |
| Connection cross section stranded | 2.5 mm ² |
| Cross section stranded 2 | 0.5 mm ² |
| Terminations per pole | 1 |

Model

| | |
|---------------------------|------------------------------|
| Model | Plug |
| Number of poles | 4 |
| Connection type | Screw connection |
| Connecting thread metric | M3 |
| Angle of plug | Straight |
| Degree of protection (IP) | IP20 |
| Built-in component | Built-in component/connector |

Material

| | |
|--|------------|
| Housing material | Polyamide |
| Halogen free | Yes |
| Contact material | CuZn |
| Insulation components continuous temperature | 100 °C |
| Surface finish | Tin-plated |

Dimensions

| | |
|--------|---------|
| Length | 31.5 mm |
| Width | 38 mm |
| Height | 19.5 mm |

Drawings