




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/17/08	D.GRIFFIN




2X MOLDED BOOT, BLUE

2X MOLDED BOOT, YELLOW

WIRING MAP			
CABLE	"P1"	COLOR	"P2"
PAIR 1	1	BROWN	1
	3	WHITE	3
	2	DRAIN	2
PAIR 2	4	GREEN	4
	6	WHITE	6
	5	DRAIN	5
PAIR 3	7	RED	7
	9	WHITE	9
	8	DRAIN	8
PAIR 4	10	BLUE	10
	12	WHITE	12
	11	DRAIN	11
	13	BLACK	13
	14	RED	14
PAIR 5	15	ORANGE	15
	16	YELLOW	16
	17	PURPLE	17
	18	GRAY	18
	19	WHITE	19
	SHELL	BRAID	SHELL

PART NUMBER	LENGTH	
	METERS	FEET
PHDMICAMM-1M	1.0	3.28
PHDMICAMM-2M	2.0	6.56
PHDMICAMM-3M	3.0	9.84
PHDMICAMM-4M	4.0	13.12
PHDMICAMM-5M	5.0	16.40

NOTES:
CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED IN A POLYBAG.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.CASTRO	6/17/08		
	CHECKED BY M.SEDLESKI	6/17/08	CATEGORY VIDEO	
	APPROVED BY G.PEPIN	6/17/08	PRODUCT DESCRIPTION HDMI ASSEMBLY M/M	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
COLOR VARIATIONS MAY OCCUR		DWG. NO. PHDMICAMM	REV. A	SCALE: NONE
		CAD FILE: PHDMICAMM.SLDDRW	SHEET 1 OF 1	