

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [15015-0825](#)
Status: **Active**
Overview: [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Description: 0.30mm Pitch Premo-Flex™ Etched Polyimide Jumper, Same Side Contacts (Type A), 0.203m Cable Length, 0.12mm Cable Thickness, 25 Circuits

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-15015-001 \(PDF\)](#)

General

Product Family	Cable
Series	15015
Crimp Quality Equipment	Yes
Overview	Premo-Flex™ FFC and Etched Polyimide Jumpers
Product Name	Premo-Flex™ Jumper
UPC	884982822696

Physical

Cable Length	0.203m
Circuits (Loaded)	25
Circuits (maximum)	25
Net Weight	1.000/g
Packaging Type	Bag
Pitch - Termination Interface	0.30mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.2A
Voltage - Maximum	50V AC/DC

Material Info

Reference - Drawing Numbers

Product Specification	PS-15015-001
Sales Drawing	SD-15015-001



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[15015Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION