SKINTOP® GMP-GL

Hexagonal Locknuts for NPT, PG & Metric Connectors

RoHS

These lock nuts are designed to be used with SKINTOP® cable connectors with NPT, PG and Metric Threads



SKINTOP® GMP-GL: NPT SKINTOP® Nylon Locknuts

Part Number	Thread Type & Size	SW Wrenching Flats inches	B Nut Thickness inches	Standard Pack Size	Weight 100 pcs. lbs.
911370	NPT- 3/8”	.866	.198”	100	0.05
911371	NPT- 1/2”	1.063	.236”	100	0.05
911372	NPT- 3/4”	1.417	.276”	50	1.00
911373	NPT- 1”	1.654	.276”	50	1.50

* NPT Locknuts- Black only

SKINTOP® GMP-GL: PG SKINTOP® Nylon Locknuts

Black Part Number	Gray Part Number	Thread Type & Size	SW Wrenching Flats inches	B Nut Thickness	Standard Pack Size	Weight 100 pcs. lbs.
53019200	53019000	PG-7	.748	.197	100	.25
53019210	53019010	PG-9	.866	.197	100	.50
53019220	53019020	PG-11	.945	.197	100	.50
53019230	53019030	PG-13	1.063	.236	100	.50
53019240	53019040	PG-16	1.181	.236	100	.75
53019250	53019050	PG-21	1.417	.276	50	1.00
53019260	53019060	PG-29	1.811	.276	50	1.50
53019270	53019070	PG-36	2.362	.315	25	3.25
53019280	53019080	PG-42	2.559	.315	25	3.25
53019290	53019090	PG-48	2.756	.315	25	3.50

SKINTOP® GMP-GL: Metric SKINTOP® Nylon Locknuts

Black Part Number	Gray Part Number	Thread Type & Size	SW Wrenching Flats inches	SW Wrenching Flats mm²	B Nut Thickness inches	B Nut Thickness mm²	Standard Pack Size	Weight 100 pcs. lbs.
53119100	53119000	M-12X1.5	.669	17	.197	5	100	.25
53119110	53119010	M-16X1.5	.866	22	.197	5	100	.50
53119120	53119020	M-20X1.5	1.063	27	.236	6	100	.50
53119130	53119030	M-25X1.5	1.339	34	.236	6	100	.75
53119140	53119040	M-32X1.5	1.614	41	.276	7	100	1.25
53119150	53119050	M-40X1.5	1.969	50	.276	7	25	1.75
53119160	53119060	M-50X1.5	2.362	60	.315	8	25	2.00
53119170	53119070	M-63X1.5	2.953	75	.315	8	25	3.00