

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	OWN	APVD
			A	REVISED PER 0720-0230-93	2/28/94	DKS	DAP

AMP WIRE RANGE	 Listed FILE E13288
12-10 AWG STRANDED	12-10 AWG STRANDED

D

C

B



A

D

C

B

A



- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B545

52269-1

PART NO.

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 2-8-93	 Tyco Electronics Corporation Harrisburg, PA 17105-3608				
	DIMENSIONS:		CHK DA PATTERSON 2-8-93	NAME TERMINAL, RING TONGUE, BUDGET -				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JL MECKLEY 2-8-93					
VOLTAGE RATING: N/A	MM[INCHES]		PRODUCT SPEC -					
CIRCULAR MIL AREA: 2.62-6.64mm²[5,180-13,100] STRANDED		0 PLC ± -	APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
		1 PLC ± -		A2	00779	C=52269	-	
		2 PLC ± -						
		3 PLC ± -						
		4 PLC ± -						
		ANGLES ± -	WEIGHT					
	MATERIAL	FINISH	-					
	COPPER 	TIN PLATE 	CUSTOMER DRAWING	SCALE 4:1		SHEET 1 of 1		REV A