

Slotted Wall Wiring Duct, 3" X 2", Non-Adhesive, PVC, White, 30ft/Box

Article Number: 181-32008

Part Number: 181-32008

Type: SL3X2

- ▶ Cable Ties
- ▶ Cable Ties with Fasteners
- ▶ Cable Tie Tools
- ▶ Clamps and Clips
- ▶ Heatshrink Moulded Shapes
- ▶ Mounts
- ▶ Heavy Duty Mounts
- ▶ Wire Connectors
- ▶ Wiring Duct
- ▶ Wiring Protection
- ▶ Labels, Printers and Software
- ▶ Pre-Terminated Networking
- ▶ Copper Network Solutions
- ▶ Fiber Network Solutions
- ▶ Jacks and Wall Plates
- ▶ Racks - Cable Management
- ▶ Surface Raceway Systems

- Find a Distributor
- Order Samples
- Get Technical Drawings



→ **Base Data**

Part No.	181-32008
Type	SL3X2
Color	White (WH)
Features	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening design in the finger of the duct helps keep wires in place. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection

→ Product Dimensions

Length (L)	6.0ft / 1.83m
Width (W) (imperial)	3.03"
Width (W)	76.96mm
Width (W2)	3.0" / 76.2mm
Width (W3)	0.4" / 10.16mm
Width (W4)	1.0" / 25.4mm
Width (W5)	1.62" / 41.1mm
Width (W6)	1.0" / 25.4mm
Height (H)	2.0" / 50.8mm
Mounting Hole Centers	4.00" / 101.6mm

➔ Material and Specifications

Material	Polyvinylchloride (PVC)
CSA Certified	Yes
Flammability	self-extinguishing
Material Specification	RoHS
Operating Temperature	+122 °F (+50 °C)
Specification	CSA / UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes / Yes

➡ Logistic and Packaging

Packaging Type	box
Pkg. Qty.	30ft / 9.14m
Carton Qty.	120
UPC	089306313007

Find a Distributor

Get Product Samples

Get Technical Drawings