




⊕ ⊕ ⊕ ⊕ ⊕ ⊕ ⊕ ⊕

⊕ ⊕ ⊕ ⊕ ⊕ ⊕ ⊕ ⊕

.300

.100 TYP

⊕ ⊕ ⊕ ⊕ ⊕ ⊕ ⊕ ⊕

⊕ ⊕ ⊕ ⊕ ⊕ ⊕ ⊕ ⊕

∅.036±.003 TYP

∅.009

RECOMMENDED MOUNTING HOLE PATTERN

SCALE 4:1

OBSOLETE	TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641612-5
	4	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641612-4
OBSOLETE	TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641612-3
	4	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641612-2
	TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641612-1
CONTACT FINISH		CONTACT MAT'L	HOUSING MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± 0°-30°

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH
SEE TABLE

DWN
R BROWN

OK
H WYNKOOP

APVD
H WYNKOOP

NAME
SOCKET ASSY, DIP, LADDER, RET LEG, 20 POS, DIPLOMATE™ DL

SIZE
A1

CAGE CODE
00779

DRAWING NO
641612

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV V

AMP 4805 REV 31MAR2000

09JAN01 12:03pm AMP01193