

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		- .N/A .	
© COPYRIGHT		N/A		BY TYCO ELECTRONICS CORPORATION.	
ALL RIGHTS RESERVED.					
PART NO.	'A' 	LEAD COLOR	REMARKS		
862547-1	6.00 [152.4]	WHITE			
862547-2	8.00 [203.2]				
862547-3	10.00 [254.0]				
862547-4	12.00 [304.8]				
862547-5	15.00 [381.0]				
862547-6	18.00 [457.2]				
862547-7	21.00 [533.4]			OBSOLETE	
862547-8	24.00 [609.6]				
862547-9	36.00 [914.4]				
1-862547-0	19.00 [482.6]			OBSOLETE	
1-862547-1	20.00 [508.0]			OBSOLETE	
1-862547-2	9.00 [228.6]				
1-862547-3	40.00 [1016.0]			OBSOLETE	
1-862547-4	600.00 [15240.0]			OBSOLETE	
1-862547-5	11.25 [285.8]			OBSOLETE	
1-862547-6	30.00 [762.0]			OBSOLETE	
1-862547-7	60.00 [1524.0]			OBSOLETE	
1-862547-8	14.50 [368.3]			OBSOLETE	
1-862547-9	48.00 [1219.2]				
2-862547-0	72.00 [1828.8]				
2-862547-1	180.00 [4572.0]			OBSOLETE	
2-862547-2	22.00 [558.8]			OBSOLETE	
2-862547-3	23.00 [584.2]			OBSOLETE	
2-862547-4	26.00 [660.4]			OBSOLETE	
2-862547-5	240.00 [6096.0]				
2-862547-6	16.50 [419.1]			OBSOLETE	
2-862547-7	33.00 [838.2]				
2-862547-8	96.00 [2438.4]				
2-862547-9	144.00 [3657.6]	WHITE			
3-862547-0	40.00 [1016.0]	BLUE			
5-862547-2	8.00 [203.2]	WHITE			
5-862547-4	12.00 [304.8]				
5-862547-6	18.00 [457.2]				
6-862547-2	9.00 [228.6]				
6-862547-9	48.00 [1219.2]				
7-862547-7	33.00 [838.2]	WHITE			

LOC		DIST		REVISIONS					
DF		S0		P	LTR	DESCRIPTION	DATE	DWN	APVD
			Z	REV PER ECO-05-002582			06-05	AA	DE

-  TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = 1%
2. MARKED PER MIL-STD-130.
3. TO MATE WITH AMP LGH-1/2L
RECEPTACLE WITH .89 [22.6] BARREL DEPTH.
-  PIGTAIL IS SOLDER DIPPED.
5. OPERATING VOLTAGE: 15 KVDC AT 0 TO 70,000
FEET, -55°C TO 125°C.
-  INSULATION CUT TO LENGTH, BUT NOT REMOVED.

