



NOTES:


1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. CONTACT RATING (NON-SWITCHING) 5A
6. OPERATING FORCE: 425 $\pm$ 100 CM/STANDARD
7. OPERATING TEMP: -30 $^{\circ}$ to 85 $^{\circ}$ C
8. CIRCUIT DP: 6 POSITIONS, 30 $^{\circ}$ INDEX.
9. DIELECTRIC STRENGTH 1000V RMS min. @ SEA LEVEL
10. DESIGNATE MAJOR DIMENSIONS
11. HARDWARE SUPPLIED ON SWITCH - SEE BELOW
STOPRING, LOCKWASHER, & HEXNUT



CONTACT CONFIGURATION
(*MBB*)



RECOMMENDED P.C.B. LAYOUT



B	12821	REVISED NOTE 11	3/05/03	RJC	
A	11252	RELEASED FOR PRODUCTION	3/5/01	RJC	
REV.	ECN No.	DESCRIPTION	DATE	CHKD	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					
E-SWITCH®					
TITLE KC-26-A-(30.0mm) 01-S-P-S					
SCALE 1.5:1		DATE 3/5/01	DR CJB	DWG G510550	REV B