


TRANSIENT VOLTAGE SUPPRESSORS

1500 W	REVERSE STAND-OFF VOLTAGE V_R (Volts)	MAXIMUM REVERSE LEAKAGE at V_R I_R (ua)	MINIMUM BREAKDOWN VOLTAGE at 1.0 mA V_B (Volts)	MAXIMUM CLAMPING VOLTAGE at $I_{PP}=1.0A$ V_C (Volts)	MAXIMUM CLAMPING VOLTAGE at $I_{PP}=1.0A$ V_C (Volts)	MAXIMUM PEAK PULSE CURRENT I_{PP} (Amps)	PACKAGE QUANT. Bulk/Reel	OUTLINE Inches/Millimeters
1N6373	5.0	300	6.0	7.1	7.5	100	500/ 1400	 DO-201
1N6374	8.0	25	9.4	11.3	11.5	100		
1N6375	10.0	2.0	11.7	13.7	14.1	90		
1N6376	12.0	2.0	14.1	16.1	16.5	70		
1N6377	15.0	2.0	17.6	20.1	20.6	60		
1N6378	18.0	2.0	21.2	24.2	25.2	50		
1N6379	22.0	2.0	25.9	29.8	32.0	40		
1N6380	36.0	2.0	42.4	50.6	54.3	23		
1N6381	45.0	2.0	52.9	63.3	70.0	19		
1N6382	8.0	25	9.4	11.4	11.6	100		
1N6383	10.0	2.0	11.7	14.1	14.5	90		
1N6384	12.0	2.0	14.1	16.7	17.1	70		
1N6385	15.0	2.0	17.6	20.8	21.4	60		
1N6386	18.0	2.0	21.2	24.8	25.5	50		
1N6387	22.0	2.0	25.9	30.8	32.0	40		
1N6388	36.0	2.0	42.4	50.6	54.3	23		
1N6389	45.0	2.0	52.9	63.3	70.0	19		
ICTE-5	5.0	300	6.0	7.1	7.5	100		
ICTE-8	8.0	25	9.4	11.3	11.5	100		
ICTE-10	10.0	2.0	11.7	13.7	14.1	90		
ICTE-12	12.0	2.0	14.1	16.1	16.5	70		
ICTE-15	15.0	2.0	17.6	20.1	20.6	60		
ICTE-18	18.0	2.0	21.2	24.2	25.2	50		
ICTE-22	22.0	2.0	25.9	29.8	32.0	40		
ICTE-36	36.0	2.0	42.4	50.6	54.3	23		
ICTE-45	45.0	2.0	52.9	63.3	70.0	19		
ICTE-8C	8.0	25	9.4	11.4	11.6	100		
ICTE-10C	10.0	2.0	11.8	14.1	14.5	90		
ICTE-12C	12.0	2.0	14.1	16.7	17.1	70		
ICTE-15C	15.0	2.0	17.6	20.8	21.4	60		
ICTE-18C	18.0	2.0	21.2	24.8	25.5	50		
ICTE-22C	22.0	2.0	25.9	30.8	32.0	40		
ICTE-36C	36.0	2.0	42.4	50.6	54.3	23		
ICTE-45C	45.0	2.0	52.9	63.3	70.0	19		
1N5908	5.0	300	6.0	7.6	8.0	120		